



产品描述

MASTERColour CDM-TC

系列单端紧凑型高光效放电灯在整个寿命期间具有稳定的光色和明亮通透的闪光

优点

- 陶瓷金卤灯技术
- 优异的色彩表现力,让颜色更加活泼跳跃,提升商业吸引力
- 卓越的色彩稳定性,在寿命周期内无色差,最大程度保证环境的舒适性
- 节能省电,高光效,长寿命,热辐射少,节约运行成本
- 营造更自由的商业氛围
- 结合-Tm,可设计相同款式不同尺寸的灯具营造灵活的照明空间
- 任意点灯位置
- 防紫外线玻壳,减少商品褪色的危险

特点

- 暖色和白色两种,具有良好的显色性
- 紧凑的光源尺寸可使灯具设计最优化,从而达到最大光强
- 任意燃点位置

应用

- 用于商店、商店橱窗、室内办公场所的照明
- 室外装饰：泛光照明和步行区的照明(需使用具备一定防护等级的灯具)
- 适用于封闭式(硬质玻璃前罩)的灯具
- 最好与电子镇流器配套使用,延长光源寿命,增强系统效率和防止频闪
- 必须使用强电流保护装置(IEC 61167)
- 部分此系列产品只能使用电子镇流器以达到最佳设计性能和安全性能
- 如果电压经常超过额定电压的 3%,必须采用其他等级的镇流器

安全提示


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR CDM-TC 0001

二维绘图



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC 35W/830	15 mm	0.5 in	5 mm	51 mm	53 mm	52 mm	85 mm
G8.5 1CT/12							

