



Product Description

MASTERColour CDM-T

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Benefits

- Stable color impression over lifetime
- Stable colour impression over lifetime
- High lamp efficacy results in low operating costs and low heat generation
- High lamp efficacy results in low operating costs and low heat generation
- Long lamp life compared with incandescent and halogen lamps
- Long lamp life compared with incandescent and halogen lamps
- Relatively low heat output enhances comfort for shoppers and staff
- Relatively low heat output enhances comfort for shoppers and staff
- All types are UV-Block for reduced fading risks
- All types are UV-Block for reduced fading risks

Features

- Crisp white light
- Warm or cool white colour impression
- Superior color quality
- Colour rendering good to excellent
- Allows small-size luminaires designs that give high beam intensities
- Allows small-size luminaires designs that give high beam intensities

Application

- Shops and shop windows, offices and public buildings
- Shops and shop windows, offices and public buildings
- Decorative outdoor: floodlighting and pedestrian areas
- Decorative outdoor: floodlighting and pedestrian areas

MASTERCoulour CDM-T

Warnings and Safety


- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR CDM-T 0005

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 150W/830 G12 1CT	20 mm	0.75 inch	9 mm	55 mm	57 mm	56 mm	110 mm
MASTERC CDM-T 150W/942 G12 1CT	20 mm	0.75 inch	8 mm	55 mm	57 mm	56 mm	110 mm

MASTERCoulour CDM-T

General Information	
Cap-Base	G12
Operating Position	UNIVERSAL
Operating and Electrical	
Power Consumption	150.1 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T19
Approval and Application	
Energy Consumption kWh/1000 h	151 kWh

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Correlated Color		Color rendering	Luminous Efficacy	Luminous Flux
		Coordinate X (Nom)	Coordinate Y (Nom)	Color Designation	Temperature (Nom)	index (CRI)	(rated) (Nom)	
928083705125	MASTERC CDM-T 150W/830 G12 1CT	0.434	0.398	Warm White (WW)	3000 K	88	88 lm/W	13,000 lm
928084605131	MASTERC CDM-T 150W/942 G12 1CT	0.371	0.366	Cool White (CW)	4200 K	96	82 lm/W	12,100 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Order Code	Full Product Name	Voltage (Nom)
928083705125	MASTERC CDM-T 150W/830 G12 1CT	96 V	928084605131	MASTERC CDM-T 150W/942 G12 1CT	90 V

Approval and Application

Order Code	Full Product Name	Mercury (Hg)	Mercury (Hg)
		Content (Max)	Content (Nom)
928083705125	MASTERC CDM-T 150W/830 G12 1CT	14.3 mg	14.3 mg
928084605131	MASTERC CDM-T 150W/942 G12 1CT	10.4 mg	10.4 mg

