



# Product Description

## MASTER HPI-T Plus

Quartz metal halide lamps with clear outer bulb

### Benefits

- High safety and comfort level, maintained over life
- Minimal maintenance cost
- Initial investment saving options with "Plus"-concept

### Features

- Clear tubular outer bulb
- Unique 3-band technology resulting in high luminous efficacy, both initially and over long lifetime
- Renders a natural white colour appearance and good colour stability

### Application

- Sports lighting, floodlighting of buildings and monuments, area lighting e.g. harbours and building sites, canopy lighting e.g. petrol stations, horticultural lighting

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MASTER HPI-T Plus

## Versions



LPPR HPI-T

## Dimensional drawing



| Product                               | D (max) | O     | L      | C (max) |
|---------------------------------------|---------|-------|--------|---------|
| MASTER HPI-T Plus 250W/645 E40 1SL/12 | 47 mm   | 29 mm | 155 mm | 255 mm  |

