



產品說明

MASTER MHN-LA 複金屬燈

雙封式袖珍型石英複金屬燈

优点

- 適合小巧、高效率的袖珍型光學燈具系統，提供良好光束控制與極低的散溢光
- 良好的演色性，打造令人愉悅的氛圍，提升選手與觀眾的視覺舒適感
- 連續光譜分佈，適合半專業體育館與常有電視轉播的專業體育館照明應用

特点

- 光源精巧 (長弧燈)，高流明效率
- 雙封裝概念，延長使用壽命
- 自然白光、高演色性、穩定光色
- 自然光色溫，減緩從自然光轉為人工光源的不適感

应用


- 專業和半專業運動照明和泛光照明

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MASTER MHN-LA 複金屬燈

二维绘图



Product	D (max)	O	X	A
MASTER MHN-LA 1000W/842 230V XWH	40 mm	40.5 mm	35 mm	286 mm
MASTER MHN-LA 1000W/956 230V XWH	40 mm	40.5 mm	35 mm	286 mm
MASTER MHN-LA 2000W/842 400V XWH	40 mm	108 mm	58 mm	353 mm
MASTER MHN-LA 2000W/956 400V XWH	40 mm	108 mm	58 mm	353 mm

一般資訊	
燈座基底	X528
操作位置	P5
控制與調光	
可調光	否
機械與外罩	
燈泡表層	透明
燈泡形狀	TD40

照明技術

Order Code	Full Product Name	色度坐標 X (標稱)	色度坐標 Y (Nom)	色彩名稱	相關色溫 (標稱)	演色性指數 (CRI)	光效 (額定) (標準)
928071305130	MASTER MHN-LA 2000W/842 400V XWH	370	370	冷白光 (CW)	4200 K	72	104 lm/W
928072505130	MASTER MHN-LA 2000W/956 400V XWH	330	339	日光	5600 K	82	93 lm/W
928072205130	MASTER MHN-LA 1000W/956 230V XWH	337	331	日光	5600 K	80	86.0 lm/W
928073005130	MASTER MHN-LA 1000W/842 230V XWH	366	370	冷白光 (CW)	4200 K	70	92.00 lm/W

運轉與電力

Order Code	Full Product Name	電壓 (標稱)	耗電量
928071305130	MASTER MHN-LA 2000W/842 400V XWH	235 V	2,050 W
928072505130	MASTER MHN-LA 2000W/956 400V XWH	225 V	2,050 W

Order Code	Full Product Name	電壓 (標稱)	耗電量
928072205130	MASTER MHN-LA 1000W/956 230V XWH	125 V	1,040.0 W
928073005130	MASTER MHN-LA 1000W/842 230V XWH	125 V	1,040.0 W

認證與應用

Order Code	Full Product Name	能源消耗 kWh/ 1000 h	汞 (Hg) 含量 (標稱)
928071305130	MASTER MHN-LA 2000W/842 400V XWH	2,244 kWh	194 mg
928072505130	MASTER MHN-LA 2000W/956 400V XWH	2,244 kWh	140 mg

Order Code	Full Product Name	能源消耗 kWh/ 1000 h	汞 (Hg) 含量 (標稱)
928072205130	MASTER MHN-LA 1000W/956 230V XWH	1,144 kWh	95 mg
928073005130	MASTER MHN-LA 1000W/842 230V XWH	1,144 kWh	112 mg

MASTER MHN-LA 複金屬燈

