



# Product Description

## MASTER MHN-SA

Compact quartz metal halide lamps with double-pinch

### Benefits

- Allows compact and very efficient luminaire systems with high precision optics for good beam control and minimal spill light
- Very good color rendering creates a pleasant ambience with high visual comfort for players and spectators
- Continuous spectral distribution offers a superior solution for (semi-) professional stadiums with regular TV coverage

### Features

- Very compact source (Short Arc) with high luminous efficacy and superior color rendering
- Double-pinch concept results in long lifetime
- Natural white color appearance, high color rendering and good color stability
- Daylight color temperature eases transition from daylight to artificial lighting

### Application

- Professional sports lighting and floodlighting

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MASTER MHN-SA

## Versions



LPPR MHN-SA X830R

## Dimensional drawing



| Product                                     | D (max) | O     | X     | A      | C (max) |
|---|---------|-------|-------|--------|---------|
| MASTER MHN-SA 2000W/956 400V XW<br>HO UNP/1 | 41 mm   | 25 mm | 34 mm | 226 mm | 369 mm  |

