



Product description

MH-NaSc

Sodium Scandium Metal Halide Lamps consisting of a gasfilled glass bulb, which alternatively are clear or internal coated, and a quartz discharge tube (DT).

Benefits

- Energy saving solution with better color appearance and rendering property for conventional version.



Features

- Quartz discharge tube containing high-pressure mercury and a mixture of Sodium and Scandium halides, which contribute to multi-lines spectra; with Ar to aid ignition.
- Better colour rendering index around 60
- Luminous efficacy up to 90 lm/W
- Low wattage lamps with extra quartz tube around DT to prevent the risk of outer bulb shattering when abnormal operated or to the end of life.
- Universal operation position permitted

Application

- Stadium and sports facilities lighting
- Industrial and commercial lighting—factory
- supermarket and exhibition hall etc.
- Public lighting—square, station, port, airport etc.
- Decorative flood lighting—monument, buildings e.g.
- hotel

Dimensional drawing



Product	D (max)	L (min)	C (max)
MH - 250W/640 E40 CL U 1SL/12	91 mm	149 mm	226 mm

Product	D (max)	L (min)	C (max)
MH 100W/640 E27 CL 1SL/24	56 mm	83 mm	141 mm
MH 400W/640 E40 CL U 1SL/6	121 mm	184 mm	290 mm
MH 70W/640 E27 CL 1SL/24	56 mm	83 mm	141 mm

General Information	
Operating Position	H
Light Technical	
Color Designation	Cool White (CW)
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

General Information

Order Code	Full Product Name	Cap-Base	Order Code	Full Product Name	Cap-Base
928484400092	MH 70W/640 E27 CL 1SL/24	E27	928480300097	MH - 250W/640 E40 CL U 1SL/12	E40
928484500092	MH 100W/640 E27 CL 1SL/24	E27	928480400097	MH 400W/640 E40 CL U 1SL/6	E40

Light Technical

Order Code	Full Product Name	Chromaticity Coordinate X (Nom)	Chromaticity Coordinate Y (Nom)	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
928484400092	MH 70W/640 E27 CL 1SL/24	390	380	4000 K	60	74 lm/W
928484500092	MH 100W/640 E27 CL 1SL/24	375	385	4200 K	65	92 lm/W
928480300097	MH - 250W/640 E40 CL U 1SL/12	390	390	4000 K	60	82 lm/W
928480400097	MH 400W/640 E40 CL U 1SL/6	390	400	3900 K	60	97.5 lm/W

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928484400092	MH 70W/640 E27 CL 1SL/24	85 V	76 W
928484500092	MH 100W/640 E27 CL 1SL/24	100 V	105 W
928480300097	MH - 250W/640 E40 CL U 1SL/12	133 V	250.0 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
928480400097	MH 400W/640 E40 CL U 1SL/6	135 V	400.0 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
928484400092	MH 70W/640 E27 CL 1SL/24	ED55
928484500092	MH 100W/640 E27 CL 1SL/24	ED55

Order Code	Full Product Name	Bulb Shape
928480300097	MH - 250W/640 E40 CL U 1SL/12	ED90
928480400097	MH 400W/640 E40 CL U 1SL/6	ED120

Approval and Application

Order Code	Full Product Name	Energy Consumption	Mercury (Hg)
		kWh/1000 h	Content (Nom)
928484400092	MH 70W/640 E27 CL 1SL/24	-	12 mg
928484500092	MH 100W/640 E27 CL 1SL/24	110 kWh	10.2 mg
928480300097	MH - 250W/640 E40 CL U 1SL/12	275 kWh	33 mg

Order Code	Full Product Name	Energy Consumption	Mercury (Hg)
		kWh/1000 h	Content (Nom)
928480400097	MH 400W/640 E40 CL U 1SL/6	440 kWh	38 mg

