



Product Description

ML

Mixed Light lamps

Benefits

- Direct retrofit for incandescent lamps
- Higher efficacy and lifetime than incandescent

Features

- High-pressure mercury tube in series with a tungsten filament
- Runs on mains voltage without additional gear
- Combines a continuous spectrum from the incandescent source and a line spectrum from the high-pressure mercury source

Application

- Public outdoor lighting, car parks, workshops, garages and shops

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR ML E27

Dimensional drawing



Product	D (max)	C (max)
ML 160W E27 220-230V SG 1CT/24	76 mm	172 mm

