



For every project where light really matters. A slim fit

CoreLine SlimDownlight

CoreLine slimdownlight delivers on the CoreLine promise of innovative, easy to use and high-quality indoor LED downlights. CoreLine slimdownlight is an innovative range of recessed and surface-mounted luminaires. It is designed to provide uniform lighting across multiple application areas. With instant energy savings and a longer lifetime, this is an environmentally friendly and cost saving solution. Its MultiColorTemp feature offers a choice of two color temperatures in a single luminaire. This makes it easy to select the right product, gives you the flexibility respond to customer preferences on site, and means fewer product codes on stock. Simple and easy installation means our slim downlight fits the same size cut-out, while the minimal built-in depth of 34mm makes this product an ideal space saving solution, especially for projects with limited fitting space. InterAct Ready option with integrated wireless communications in this family is available, to be used with InterAct gateways, sensors and software.

Benefits

- MultiColorTemp option to change color temperature on site and simplify product selection
- Energy saving and longer lifetime to reduce overall operating costs
- Covers recessed and surface-mounted installations
- Fits suspended ceilings with low space (Product height < 50mm)
- Surface of light effect creates a comfortable, uniform look

CoreLine SlimDownlight

Features

- MultiColorTemp feature: two color temperature options in a single luminaire (3000K-4000K)
- Recessed (DN145B) and surface-mounted versions (DN145C)
- Energy-efficient with a long lifespan: up to 100lm/W and 50,000 hours @L70
- Push-in connector with through-wiring option
- Multiple light output options: 650/1100/2100 lumen
- Color temperature: 3000K and 4000K
- Choice of drivers; DALI and wireless with Interact ready
- Total height (including driver): 34mm recessed; 50mm surface mounted

Application

- Corridors
- Retail stores
- Reception areas
- Restrooms
- Technical rooms

Versions

CoreLine SlimDownlight DN145B
Micro All-in



CoreLine SlimDownlight DN145B
Compact All-in



Coreline SlimDownlight-DN145B
10S



Coreline SlimDownlight-DN145B
6S








CoreLine SlimDownlight DN145B
Mini All-in



CoreLine SlimDownlight

Dimensional drawing



Product details

CoreLine SlimDownlight 2100lm
side view

CoreLine SlimDownlight Surface-
mounted 2100lm



CoreLine SlimDownlight


Product details



Philips CoreLine SlimDownlight
Recessed DT01



CoreLine SlimDownlight 2100lm
with PSU driver and easy
connector



CoreLine SlimDownlight 2100lm



Philips CoreLine SlimDownlight
Surface DT02



Philips CoreLine SlimDownlight
Surface DT01

General Information	
Driver included	Yes
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20/44
Approval and Application	
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

General Information

Order Code	Full Product Name	Lamp family code	Light source replaceable
911401806380	DN145C LED10S/830 PSU II WH	LED10S	No
911401806480	DN145C LED10S/840 PSU II WH	LED10S	No
911401806580	DN145C LED20S/830 PSU II WH	LED20S	No
911401806680	DN145C LED20S/840 PSU II WH	LED20S	No
911401816085	DN145B LED6S/830_840 PSU WH	-	-
910500465903	DN145B LED20S/830 PSD-E II WH	LED20S	No
910500465904	DN145B LED20S/840 PSD-E II WH	LED20S	No
910505101197	DN145B LED20S/830 WIA-E WH	-	No
910505101198	DN145B LED20S/840 WIA-E WH	-	No
911401806180	DN145B LED20S/830 PSU II WH	LED20S	No
911401806280	DN145B LED20S/840 PSU II WH	LED20S	No
911401816285	DN145B LED20S/830_840 PSU WH	-	-
910500465901	DN145B LED10S/830 PSD-E II WH	LED10S	No
910500465902	DN145B LED10S/840 PSD-E II WH	LED10S	No
910505101195	DN145B LED10S/830 WIA-E WH	-	No
910505101196	DN145B LED10S/840 WIA-E WH	-	No
911401805980	DN145B LED10S/830 PSU II WH	LED10S	No
911401806080	DN145B LED10S/840 PSU II WH	LED10S	No
911401805780	DN145B LED6S/830 PSU II WH	LED6S	No
911401805880	DN145B LED6S/840 PSU II WH	LED6S	No
911401816185	DN145B LED10S/830_840 PSU WH	-	-

CoreLine SlimDownlight

Light Technical (1/2)

			Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
Order Code	Full Product Name	All-in Type			
911401806380	DN145C LED10S/830 PSU II WH	-	120 degree(s)	3000 K	100 lm/W
911401806480	DN145C LED10S/840 PSU II WH	-	120 degree(s)	4000 K	100 lm/W
911401806580	DN145C LED20S/830 PSU II WH	-	120 degree(s)	3000 K	100 lm/W
911401806680	DN145C LED20S/840 PSU II WH	-	120 degree(s)	4000 K	100 lm/W
911401816085	DN145B LED6S/ 830_840 PSU WH	All-in, Multi Color Temperature	-	3000 K	100 lm/W
910500465903	DN145B LED20S/830 PSD-E II WH	-	120 degree(s)	3000 K	93 lm/W
910500465904	DN145B LED20S/840 PSD-E II WH	-	120 degree(s)	4000 K	93 lm/W
910505101197	DN145B LED20S/830 WIA-E WH	-	120 degree(s)	3000 K	93 lm/W
910505101198	DN145B LED20S/840 WIA-E WH	-	120 degree(s)	4000 K	93 lm/W
911401806180	DN145B LED20S/830 PSU II WH	-	120 degree(s)	3000 K	100 lm/W
911401806280	DN145B LED20S/840 PSU II WH	-	120 degree(s)	4000 K	100 lm/W

			Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
Order Code	Full Product Name	All-in Type			
911401816285	DN145B LED20S/ 830_840 PSU WH	All-in, Multi Color Temperature	-	3000 K	100 lm/W
910500465901	DN145B LED10S/830 PSD-E II WH	-	120 degree(s)	3000 K	85 lm/W
910500465902	DN145B LED10S/840 PSD-E II WH	-	120 degree(s)	4000 K	85 lm/W
910505101195	DN145B LED10S/830 WIA-E WH	-	120 degree(s)	3000 K	93 lm/W
910505101196	DN145B LED10S/840 WIA-E WH	-	120 degree(s)	4000 K	93 lm/W
911401805980	DN145B LED10S/830 PSU II WH	-	120 degree(s)	3000 K	100 lm/W
911401806080	DN145B LED10S/840 PSU II WH	-	120 degree(s)	4000 K	100 lm/W
911401805780	DN145B LED6S/830 PSU II WH	-	120 degree(s)	3000 K	100 lm/W
911401805880	DN145B LED6S/840 PSU II WH	-	120 degree(s)	4000 K	100 lm/W
911401816185	DN145B LED10S/ 830_840 PSU WH	All-in, Multi Color Temperature	-	3000 K	100 lm/W

Light Technical (2/2)

		Number of light sources		Optic type
Order Code	Full Product Name	Luminous Flux		
911401806380	DN145C LED10S/830 PSU II WH	1,100 lm	1	Beam angle 90°
911401806480	DN145C LED10S/840 PSU II WH	1,100 lm	1	Beam angle 90°
911401806580	DN145C LED20S/830 PSU II WH	2,100 lm	1	Beam angle 90°

		Number of light sources		Optic type
Order Code	Full Product Name	Luminous Flux		
911401806680	DN145C LED20S/840 PSU II WH	2,100 lm	1	Beam angle 90°
911401816085	DN145B LED6S/830_840 PSU WH	650 lm	-	Wide beam
910500465903	DN145B LED20S/830 PSD-E II WH	2,100 lm	1	Beam angle 90°

CoreLine SlimDownlight

Order Code	Full Product Name	Luminous Flux	Number of light	
			sources	Optic type
910500465904	DN145B LED20S/840 PSD-E II WH	2,100 lm	1	Beam angle 90°
910505101197	DN145B LED20S/830 WIA-E WH	2,100 lm	-	Beam angle 90°
910505101198	DN145B LED20S/840 WIA-E WH	2,100 lm	-	Beam angle 90°
911401806180	DN145B LED20S/830 PSU II WH	2,100 lm	1	Beam angle 90°
911401806280	DN145B LED20S/840 PSU II WH	2,100 lm	1	Beam angle 90°
911401816285	DN145B LED20S/830_840 PSU WH	2,100 lm	-	Wide beam
910500465901	DN145B LED10S/830 PSD-E II WH	1,100 lm	1	Beam angle 90°
910500465902	DN145B LED10S/840 PSD-E II WH	1,100 lm	1	Beam angle 90°

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Suitable for random	
			switching	
911401806380	DN145C LED10S/830 PSU II WH	11 W	Yes	
911401806480	DN145C LED10S/840 PSU II WH	11 W	Yes	
911401806580	DN145C LED20S/830 PSU II WH	21 W	Yes	
911401806680	DN145C LED20S/840 PSU II WH	21 W	Yes	
911401816085	DN145B LED6S/830_840 PSU WH	6.5 W	Not applicable	
910500465903	DN145B LED20S/830 PSD-E II WH	22.5 W	Yes	
910500465904	DN145B LED20S/840 PSD-E II WH	22.5 W	Yes	
910505101197	DN145B LED20S/830 WIA-E WH	22.5 W	Yes	
910505101198	DN145B LED20S/840 WIA-E WH	22.5 W	Yes	
911401806180	DN145B LED20S/830 PSU II WH	21 W	Yes	

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401806380	DN145C LED10S/830 PSU II WH	No	Not applicable
911401806480	DN145C LED10S/840 PSU II WH	No	Not applicable
911401806580	DN145C LED20S/830 PSU II WH	No	Not applicable
911401806680	DN145C LED20S/840 PSU II WH	No	Not applicable
911401816085	DN145B LED6S/830_840 PSU WH	No	-
910500465903	DN145B LED20S/830 PSD-E II WH	Yes	Not applicable
910500465904	DN145B LED20S/840 PSD-E II WH	Yes	Not applicable
910505101197	DN145B LED20S/830 WIA-E WH	Yes	Not applicable

Order Code	Full Product Name	Luminous Flux	Number of light	
			sources	Optic type
910505101195	DN145B LED10S/830 WIA-E WH	1,100 lm	-	Beam angle 90°
910505101196	DN145B LED10S/840 WIA-E WH	1,100 lm	-	Beam angle 90°
911401805980	DN145B LED10S/830 PSU II WH	1,100 lm	1	Beam angle 90°
911401806080	DN145B LED10S/840 PSU II WH	1,100 lm	1	Beam angle 90°
911401805780	DN145B LED6S/830 PSU II WH	650 lm	1	Beam angle 90°
911401805880	DN145B LED6S/840 PSU II WH	650 lm	1	Beam angle 90°
911401816185	DN145B LED10S/830_840 PSU WH	1,100 lm	-	Wide beam

Order Code	Full Product Name	Power Consumption	Suitable for random	
			switching	
911401806280	DN145B LED20S/840 PSU II WH	21 W	Yes	
911401816285	DN145B LED20S/830_840 PSU WH	21 W	Not applicable	
910500465901	DN145B LED10S/830 PSD-E II WH	13 W	Yes	
910500465902	DN145B LED10S/840 PSD-E II WH	13 W	Yes	
910505101195	DN145B LED10S/830 WIA-E WH	13 W	Yes	
910505101196	DN145B LED10S/840 WIA-E WH	13 W	Yes	
911401805980	DN145B LED10S/830 PSU II WH	11 W	Yes	
911401806080	DN145B LED10S/840 PSU II WH	11 W	Yes	
911401805780	DN145B LED6S/830 PSU II WH	6.5 W	Yes	
911401805880	DN145B LED6S/840 PSU II WH	6.5 W	Yes	
911401816185	DN145B LED10S/830_840 PSU WH	11 W	Not applicable	

Order Code	Full Product Name	Dimmable	Maximum dim level
910505101198	DN145B LED20S/840 WIA-E WH	Yes	Not applicable
911401806180	DN145B LED20S/830 PSU II WH	No	Not applicable
911401806280	DN145B LED20S/840 PSU II WH	No	Not applicable
911401816285	DN145B LED20S/830_840 PSU WH	No	-
910500465901	DN145B LED10S/830 PSD-E II WH	Yes	Not applicable
910500465902	DN145B LED10S/840 PSD-E II WH	Yes	Not applicable
910505101195	DN145B LED10S/830 WIA-E WH	Yes	Not applicable
910505101196	DN145B LED10S/840 WIA-E WH	Yes	Not applicable

CoreLine SlimDownlight

Order Code	Full Product Name	Dimmable	Maximum dim level
911401805980	DN145B LED10S/830 PSU II WH	No	Not applicable
911401806080	DN145B LED10S/840 PSU II WH	No	Not applicable
911401805780	DN145B LED6S/830 PSU II WH	No	Not applicable

Mechanical and Housing

Order Code	Full Product Name	Optical cover type
911401806380	DN145C LED10S/830 PSU II WH	Opal
911401806480	DN145C LED10S/840 PSU II WH	Opal
911401806580	DN145C LED20S/830 PSU II WH	Opal
911401806680	DN145C LED20S/840 PSU II WH	Opal
911401816085	DN145B LED6S/830_840 PSU WH	-
910500465903	DN145B LED20S/830 PSD-E II WH	Opal
910500465904	DN145B LED20S/840 PSD-E II WH	Opal
910505101197	DN145B LED20S/830 WIA-E WH	-
910505101198	DN145B LED20S/840 WIA-E WH	-
911401806180	DN145B LED20S/830 PSU II WH	Opal
911401806280	DN145B LED20S/840 PSU II WH	Opal

Emergency Operation

Order Code	Full Product Name	Central Emergency
911401806380	DN145C LED10S/830 PSU II WH	-
911401806480	DN145C LED10S/840 PSU II WH	-
911401806580	DN145C LED20S/830 PSU II WH	-
911401806680	DN145C LED20S/840 PSU II WH	-
911401816085	DN145B LED6S/830_840 PSU WH	No
910500465903	DN145B LED20S/830 PSD-E II WH	-
910500465904	DN145B LED20S/840 PSD-E II WH	-
910505101197	DN145B LED20S/830 WIA-E WH	-
910505101198	DN145B LED20S/840 WIA-E WH	-
911401806180	DN145B LED20S/830 PSU II WH	-
911401806280	DN145B LED20S/840 PSU II WH	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
911401806380	DN145C LED10S/830 PSU II WH	0 to +35 °C	1	1.6
911401806480	DN145C LED10S/840 PSU II WH	0 to +35 °C	1	1.6

Order Code	Full Product Name	Dimmable	Maximum dim level
911401805880	DN145B LED6S/840 PSU II WH	No	Not applicable
911401816185	DN145B LED10S/830_840 PSU WH	No	-

Order Code	Full Product Name	Optical cover type
911401816285	DN145B LED20S/830_840 PSU WH	-
910500465901	DN145B LED10S/830 PSD-E II WH	Opal
910500465902	DN145B LED10S/840 PSD-E II WH	Opal
910505101195	DN145B LED10S/830 WIA-E WH	-
910505101196	DN145B LED10S/840 WIA-E WH	-
911401805980	DN145B LED10S/830 PSU II WH	Opal
911401806080	DN145B LED10S/840 PSU II WH	Opal
911401805780	DN145B LED6S/830 PSU II WH	Opal
911401805880	DN145B LED6S/840 PSU II WH	Opal
911401816185	DN145B LED10S/830_840 PSU WH	-

Order Code	Full Product Name	Central Emergency
911401816285	DN145B LED20S/830_840 PSU WH	No
910500465901	DN145B LED10S/830 PSD-E II WH	-
910500465902	DN145B LED10S/840 PSD-E II WH	-
910505101195	DN145B LED10S/830 WIA-E WH	-
910505101196	DN145B LED10S/840 WIA-E WH	-
911401805980	DN145B LED10S/830 PSU II WH	-
911401806080	DN145B LED10S/840 PSU II WH	-
911401805780	DN145B LED6S/830 PSU II WH	-
911401805880	DN145B LED6S/840 PSU II WH	-
911401816185	DN145B LED10S/830_840 PSU WH	No

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
911401806580	DN145C LED20S/830 PSU II WH	0 to +35 °C	1	1.6
911401806680	DN145C LED20S/840 PSU II WH	0 to +35 °C	1	1.6
911401816085	DN145B LED6S/830_840 PSU WH	-20 to +40 °C	-	-

CoreLine SlimDownlight

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910500465903	DN145B LED20S/830 PSD-E II WH	0 to +35 °C	1	0.4
910500465904	DN145B LED20S/840 PSD-E II WH	0 to +35 °C	1	0.4
910505101197	DN145B LED20S/830 WIA-E WH	0 to +35 °C	1	0.4
910505101198	DN145B LED20S/840 WIA-E WH	0 to +35 °C	1	0.4
911401806180	DN145B LED20S/830 PSU II WH	0 to +35 °C	1	1.6
911401806280	DN145B LED20S/840 PSU II WH	0 to +35 °C	1	1.6
911401816285	DN145B LED20S/830_840 PSU WH	-20 to +40 °C	-	-
910500465901	DN145B LED10S/830 PSD-E II WH	0 to +35 °C	1	0.4

Order Code	Full Product Name	Ambient temperature range	Flickering value (PstLM) - Flickering value as per EN 61000-3-3	Stroboscopic effect visibility measure (SVM)
910500465902	DN145B LED10S/840 PSD-E II WH	0 to +35 °C	1	0.4
910505101195	DN145B LED10S/830 WIA-E WH	0 to +35 °C	1	0.4
910505101196	DN145B LED10S/840 WIA-E WH	0 to +35 °C	1	0.4
911401805980	DN145B LED10S/830 PSU II WH	0 to +35 °C	1	1.6
911401806080	DN145B LED10S/840 PSU II WH	0 to +35 °C	1	1.6
911401805780	DN145B LED6S/830 PSU II WH	0 to +35 °C	1	1.6
911401805880	DN145B LED6S/840 PSU II WH	0 to +35 °C	1	1.6
911401816185	DN145B LED10S/830_840 PSU WH	-20 to +40 °C	-	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401806380	DN145C LED10S/830 PSU II WH	(0.43657,0.40454) SDCM<3	+/-10%
911401806480	DN145C LED10S/840 PSU II WH	(0.38212,0.38031) SDCM<3	+/-10%
911401806580	DN145C LED20S/830 PSU II WH	(0.43657,0.40454) SDCM<3	+/-10%
911401806680	DN145C LED20S/840 PSU II WH	(0.38212,0.38031) SDCM<3	+/-10%
911401816085	DN145B LED6S/830_840 PSU WH	(0.44, 0.41) SDCM <3; (0.38, 0.38) SDCM <3	-10% / +10%
910500465903	DN145B LED20S/830 PSD-E II WH	(0.43657,0.40454) SDCM<3	+/-10%
910500465904	DN145B LED20S/840 PSD-E II WH	(0.38212,0.38031) SDCM<3	+/-10%
910505101197	DN145B LED20S/830 WIA-E WH	(0.43657,0.40454) SDCM<3	+/-10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
910505101198	DN145B LED20S/840 WIA-E WH	(0.38212,0.38031) SDCM<3	+/-10%
911401806180	DN145B LED20S/830 PSU II WH	(0.43657,0.40454) SDCM<3	+/-10%
911401806280	DN145B LED20S/840 PSU II WH	(0.38212,0.38031) SDCM<3	+/-10%
911401816285	DN145B LED20S/830_840 PSU WH	(0.44, 0.41) SDCM <3; (0.38, 0.38) SDCM <3	-10% / +10%
910500465901	DN145B LED10S/830 PSD-E II WH	(0.43657,0.40454) SDCM<3	+/-10%
910500465902	DN145B LED10S/840 PSD-E II WH	(0.38212,0.38031) SDCM<3	+/-10%
910505101195	DN145B LED10S/830 WIA-E WH	(0.43657,0.40454) SDCM<3	+/-10%
910505101196	DN145B LED10S/840 WIA-E WH	(0.38212,0.38031) SDCM<3	+/-10%

CoreLine SlimDownlight

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401805980	DN145B LED10S/830 PSU II WH	(0.43657,0.40454) SDCM<3	+/-10%
911401806080	DN145B LED10S/840 PSU II WH	(0.38212,0.38031) SDCM<3	+/-10%
911401805780	DN145B LED6S/830 PSU II WH	(0.43657,0.40454) SDCM<3	+/-10%

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
911401806380	DN145C LED10S/830 PSU II WH	0.0015 %
911401806480	DN145C LED10S/840 PSU II WH	0.0015 %
911401806580	DN145C LED20S/830 PSU II WH	0.0015 %
911401806680	DN145C LED20S/840 PSU II WH	0.0015 %
911401816085	DN145B LED6S/830_840 PSU WH	-
910500465903	DN145B LED20S/830 PSD-E II WH	0.0015 %
910500465904	DN145B LED20S/840 PSD-E II WH	0.0015 %
910505101197	DN145B LED20S/830 WIA-E WH	-
910505101198	DN145B LED20S/840 WIA-E WH	-
911401806180	DN145B LED20S/830 PSU II WH	0.0015 %
911401806280	DN145B LED20S/840 PSU II WH	0.0015 %

Product Data


Order Code	Full Product Name	Product family code
911401806380	DN145C LED10S/830 PSU II WH	-
911401806480	DN145C LED10S/840 PSU II WH	-
911401806580	DN145C LED20S/830 PSU II WH	-
911401806680	DN145C LED20S/840 PSU II WH	-
911401816085	DN145B LED6S/830_840 PSU WH	-
910500465903	DN145B LED20S/830 PSD-E II WH	DN145B
910500465904	DN145B LED20S/840 PSD-E II WH	DN145B
910505101197	DN145B LED20S/830 WIA-E WH	DN145B
910505101198	DN145B LED20S/840 WIA-E WH	DN145B
911401806180	DN145B LED20S/830 PSU II WH	-
911401806280	DN145B LED20S/840 PSU II WH	-

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
911401805880	DN145B LED6S/840 PSU II WH	(0.38212,0.38031) SDCM<3	+/-10%
911401816185	DN145B LED10S/830_840 PSU WH	(0.44, 0.40) SDCM <3; (0.38, 0.38) SDCM <3	-10% / +10%


Order Code	Full Product Name	Driver failure rate at 5000 h
911401816285	DN145B LED20S/830_840 PSU WH	-
910500465901	DN145B LED10S/830 PSD-E II WH	0.0015 %
910500465902	DN145B LED10S/840 PSD-E II WH	0.0015 %
910505101195	DN145B LED10S/830 WIA-E WH	-
910505101196	DN145B LED10S/840 WIA-E WH	-
911401805980	DN145B LED10S/830 PSU II WH	0.0015 %
911401806080	DN145B LED10S/840 PSU II WH	0.0015 %
911401805780	DN145B LED6S/830 PSU II WH	-
911401805880	DN145B LED6S/840 PSU II WH	-
911401816185	DN145B LED10S/830_840 PSU WH	-

Order Code	Full Product Name	Product family code
911401816285	DN145B LED20S/830_840 PSU WH	-
910500465901	DN145B LED10S/830 PSD-E II WH	DN145B
910500465902	DN145B LED10S/840 PSD-E II WH	DN145B
910505101195	DN145B LED10S/830 WIA-E WH	DN145B
910505101196	DN145B LED10S/840 WIA-E WH	DN145B
911401805980	DN145B LED10S/830 PSU II WH	-
911401806080	DN145B LED10S/840 PSU II WH	-
911401805780	DN145B LED6S/830 PSU II WH	-
911401805880	DN145B LED6S/840 PSU II WH	-
911401816185	DN145B LED10S/830_840 PSU WH	-


Polar Wide Diagrams




Polar Normal (separate) - DN145BI - 910500465901




Polar Normal (separate) - DN145BI - 910500465903




Polar Normal (separate) - DN145BI - 910500465904




Polar Normal (separate) - DN145BI - 910500465902




Polar Normal (separate) - DN145BI - 910505101196




Polar Normal (separate) - DN145BI - 910505101198




Polar Normal (separate) - DN145BI - 910505101195




Polar Normal (separate) - DN145BI - 910505101197




Polar Normal (separate) - null - 911401816185




Polar Normal (separate) - null - 911401816285




Polar Normal (separate) - null - 911401805880



Polar Normal (separate) - null - 911401806180



Polar Normal (separate) - null - 911401806580



Polar Normal (separate) - null - 911401806480

CoreLine SlimDownlight

