



# Suitable for high ceiling delivering comfortable light

## GreenSpace Surface mounted

GreenSpace DN397C is brand new offering to accommodate extremely high ceiling with leading efficacy, design compactness and good reliability

### Benefits

- Energy saving
- Superior optics with flexibility
- Good light quality for visual comfort
- Easy installation

### Features

- High efficacy
- Two beam options
- SDCM 3, CRI >80
- Surface mounted & suspended

### Application

- Airport
- Exhibition center
- Semi-outdoor


# GreenSpace Surface mounted

## Versions



GreenSpace Surface mounted PSU

## Dimensional drawing



## GreenSpace Surface mounted

### General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

### Light Technical

Beam angle of light source	120 degree(s)
Color rendering index (CRI)	≥80
Luminous Flux	12,000 lm

### Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	102 W
Suitable for random switching	No

### Controls and Dimming

Dimmable	No
Maximum dim level	Not applicable

### Mechanical and Housing

Optical cover type	Lens
Housing Color	White
Mech. impact protection code	IK06
Ingress protection code	IP65

### Approval and Application

Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on easy flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s

### Initial Performance (IEC Compliant)

Initial chromaticity	-
Luminous flux tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.0013 %
Median useful life L80B50	34,000 hour(s)
Median useful life L90B50	15,000 hour(s)

### Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Optic type
911401557351	DN397C LED12/830 PSU WH WB GM	3000 K	115 lm/W	Beam angle 55°
911401557451	DN397C LED12/840 PSU WH WB GM	4000 K	120 lm/W	Beam angle 55°
911401557751	DN397C LED12/840 PSU WH MB GM	4000 K	120 lm/W	Beam angle 30°

## GreenSpace Surface mounted

