



GreenSpace – high-efficiency sustainable LED solution

GreenSpace

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable color performance and high color rendering. The product's long lifetime makes it a true 'fit and forget' solution.

Benefits

- High system efficacy: > 80 lm/W (mini, DN460B/DN461B); > 100 lm/W (compact, DN470B/DN471B)
- Up to 70% energy saving: total cost of ownership recovered in less than 2 years
- Office lighting norm-compliant, with stable color performance and high color rendering

Features

- Energy-efficient, durable LED technology
- High system efficacy: > 80 lm/W (mini, DN460B/DN461B); > 100 lm/W (compact, DN470B/DN471B)
- Stable color performance and high color rendering
- Available with IP44 or emergency lighting
- Available in UGR22 and UGR19 versions

Application


- Offices
- Retail
- Hotels and hospitals

Versions



Greenspace EU gen 2-DN463B

Dimensional drawing



Product details

Greenspace_EU_gen_2-DN473B-DPP.TIF




Greenspace_EU_gen_2-DN472B-DPP.TIF



Greenspace_EU_gen_2-DN462_463_472_473B-1DPP.TIF



Greenspace_EU_gen_2-DN462_463_472_473B-3DPP.TIF



Product details

Greenspace_EU_gen_2-DN462B-DPP.TIF



Greenspace_EU_gen_2-DN462_463_472_473B-2DPP.TIF



General Information	
Driver included	Yes
Gear	-
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Optic type	-
Operating and Electrical	
Protection class IEC	Safety class II
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Mechanical and Housing	
Optical cover type	-
Housing Color	White
Mech. impact protection code	IK02
Approval and Application	
CE mark	Yes
Flammability mark	-
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Lamp family code
79324100	DN461B LED11S/840 PSU-E C WH P	LED11S
98307900	DN471B LED20S/830 WIA-E C WH P	20S
98309300	DN471B LED20S/840 WIA-E C WH P	20S
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	20S
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	20S
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	20S
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	20S
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	30S
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	30S
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	30S
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	30S
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	20S
98338300	DN473B LED20S/840 DIA-VLC-E C WH PCC P	20S
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	30S
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	30S
01309400	DN471B LED20S/830 PSD-E C WH P	20S
01310000	DN471B LED20S/840 PSD-E C WH P	20S
38474600	DN473B LED20S/830 PSU-E C WH PCC P	LED20S
38475300	DN473B LED20S/840 PSU-E C WH PCC P	LED20S
79331900	DN471B LED20S/830 PSU-E C WH P	LED20S
79332600	DN471B LED20S/840 PSU-E C WH P	LED20S
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	LED20S
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	LED20S
94583100	DN471B LED30S/830 PSU-E C WH P	-
94584800	DN471B LED30S/840 PSU-E C WH P	-
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	-
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	-
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	11S
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	20S
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	20S
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	20S
98305500	DN470B LED20S/840 WIA-E C WH P	20S
98311600	DN472B LED20S/830 WIA-E C WH PCC P	20S
98313000	DN472B LED20S/840 WIA-E C WH PCC P	20S
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	30S
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	30S
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	30S

Order Code	Full Product Name	Lamp family code
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	30S
98330700	DN472B LED20S/830 DIA-VLC-E C WH PCC P	20S
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	20S
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	30S
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	30S
98366600	DN470B LED20S/830 WIA-E C WH P	20S
01290500	DN470B LED20S/830 PSD-E C WH P	20S
01291200	DN470B LED30S/830 PSD-E C WH P	30S
01307000	DN470B LED20S/840 PSD-E C WH P	20S
01308700	DN470B LED30S/840 PSD-E C WH P	30S
38470800	DN472B LED20S/830 PSU-E C WH PCC P	LED20S
38471500	DN472B LED20S/840 PSU-E C WH PCC P	LED20S
79327200	DN470B LED20S/830 PSU-E C WH P	LED20S
79328900	DN470B LED20S/840 PSU-E C WH P	LED20S
79351700	DN470B LED20S/830 PSU-E C ELP3 WH P	LED20S
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	LED20S
94575600	DN470B LED30S/830 PSU-E C WH P	-
94576300	DN470B LED30S/840 PSU-E C WH P	-
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	-
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	-
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	11S
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	11S
38462300	DN462B LED11S/830 PSU-E C WH PCC P	LED11S
79319700	DN460B LED11S/830 PSU-E C WH P	LED11S
79320300	DN460B LED11S/840 PSU-E C WH P	LED11S
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	LED11S
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	11S
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	11S
79335700	DN462B LED11S/830 PSU-E C WH PCO P	LED11S
79336400	DN462B LED11S/840 PSU-E C WH PCO P	LED11S
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	20S
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	20S
01311700	DN472B LED11S/830 PSD-E C WH PCO P	11S
01312400	DN472B LED11S/840 PSD-E C WH PCO P	11S
79347000	DN472B LED20S/830 PSU-E C WH PCO P	LED20S
79348700	DN472B LED20S/840 PSU-E C WH PCO P	LED20S

Light Technical (1/2)

Full Product		Beam angle of light	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
Order Code	Name	source	(Nom)	(Nom)	Flux
79324100	DN461B LED11S/840 PSU-E C WH P	- degree(s)	4000 K	134 lm/W	1,100 lm
98307900	DN471B LED20S/830 WIA-E C WH P	- degree(s)	3000 K	137 lm/W	1,800 lm
98309300	DN471B LED20S/840 WIA-E C WH P	- degree(s)	4000 K	141 lm/W	1,850 lm

Full Product		Beam angle of light	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
Order Code	Name	source	(Nom)	(Nom)	Flux
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	- degree(s)	3000 K	133 lm/W	1,800 lm
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	- degree(s)	3000 K	133 lm/W	1,800 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	- degree(s)	4000 K	136 lm/W	1,850 lm
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	136 lm/W	1,850 lm
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	- degree(s)	3000 K	130 lm/W	2,700 lm
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	- degree(s)	3000 K	130 lm/W	2,700 lm
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	- degree(s)	4000 K	134 lm/W	2,800 lm
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	134 lm/W	2,800 lm
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	- degree(s)	3000 K	126 lm/W	1,750 lm
98338300	DN473B LED20S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	130 lm/W	1,800 lm
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	- degree(s)	3000 K	124 lm/W	2,600 lm
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	128 lm/W	2,700 lm
01309400	DN471B LED20S/830 PSD-E C WH P	-	3000 K	135 lm/W	1,800 lm
01310000	DN471B LED20S/840 PSD-E C WH P	-	4000 K	139 lm/W	1,850 lm
38474600	DN473B LED20S/830	- degree(s)	3000 K	130 lm/W	1,750 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSU-E C WH PCC P				
38475300	DN473B LED20S/840 PSU-E C WH PCC P	- degree(s)	4000 K	134 lm/W	1,800 lm
79331900	DN471B LED20S/830 PSU-E C WH P	- degree(s)	3000 K	137 lm/W	1,800 lm
79332600	DN471B LED20S/840 PSU-E C WH P	- degree(s)	4000 K	141 lm/W	1,850 lm
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	- degree(s)	3000 K	137 lm/W	1,800 lm
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	141 lm/W	1,850 lm
94583100	DN471B LED30S/830 PSU-E C WH P	- degree(s)	3000 K	131 lm/W	2,700 lm
94584800	DN471B LED30S/840 PSU-E C WH P	- degree(s)	4000 K	135 lm/W	2,800 lm
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	- degree(s)	3000 K	131 lm/W	2,700 lm
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	135 lm/W	2,800 lm
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	138 lm/W	1,200 lm
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	- degree(s)	3000 K	139 lm/W	1,900 lm
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	- degree(s)	3000 K	139 lm/W	1,900 lm
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	- degree(s)	4000 K	143 lm/W	1,950 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
98305500	DN470B LED20S/840 WIA-E C WH P	- degree(s)	4000 K	148 lm/W	1,950 lm
98311600	DN472B LED20S/830 WIA-E C WH PCC P	- degree(s)	3000 K	137 lm/W	1,800 lm
98313000	DN472B LED20S/840 WIA-E C WH PCC P	- degree(s)	4000 K	141 lm/W	1,850 lm
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	- degree(s)	3000 K	137 lm/W	2,900 lm
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	- degree(s)	3000 K	137 lm/W	2,900 lm
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	- degree(s)	4000 K	141 lm/W	2,900 lm
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	141 lm/W	2,900 lm
98330700	DN472B LED20S/830 DIA-VLC-E C WH PCC P	- degree(s)	3000 K	133 lm/W	1,800 lm
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	136 lm/W	1,850 lm
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	- degree(s)	3000 K	130 lm/W	2,700 lm
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	134 lm/W	2,800 lm
98366600	DN470B LED20S/830 WIA-E C WH P	- degree(s)	3000 K	144 lm/W	1,900 lm
01290500	DN470B LED20S/830 PSD-E C WH P	-	3000 K	142 lm/W	1,900 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01291200	DN470B LED30S/830 PSD-E C WH P	-	3000 K	136 lm/W	2,900 lm
01307000	DN470B LED20S/840 PSD-E C WH P	-	4000 K	146 lm/W	1,950 lm
01308700	DN470B LED30S/840 PSD-E C WH P	-	4000 K	139 lm/W	2,900 lm
38470800	DN472B LED20S/830 PSU-E C WH PCC P	- degree(s)	3000 K	137 lm/W	1,800 lm
38471500	DN472B LED20S/840 PSU-E C WH PCC P	- degree(s)	4000 K	141 lm/W	1,850 lm
79327200	DN470B LED20S/830 PSU-E C WH P	- degree(s)	3000 K	143 lm/W	1,900 lm
79328900	DN470B LED20S/840 PSU-E C WH P	- degree(s)	4000 K	147 lm/W	1,950 lm
79351700	DN470B LED20S/830 PSU-E C ELP3 WH P	- degree(s)	3000 K	143 lm/W	1,900 lm
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	147 lm/W	1,950 lm
94575600	DN470B LED30S/830 PSU-E C WH P	- degree(s)	3000 K	137 lm/W	2,900 lm
94576300	DN470B LED30S/840 PSU-E C WH P	- degree(s)	4000 K	141 lm/W	2,900 lm
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	- degree(s)	3000 K	137 lm/W	2,900 lm
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	141 lm/W	2,900 lm
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	132 lm/W	1,150 lm

Order Code	Full Product	Beam	Correlated	Luminous	Luminous
	Name	angle of light source	Color Temperature (Nom)	Efficacy (rated) (Nom)	
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	126 lm/W	1,100 lm
38462300	DN462B LED11S/830 PSU-E C WH PCC P	- degree(s)	3000 K	127 lm/W	1,050 lm
79319700	DN460B LED11S/830 PSU-E C WH P	- degree(s)	3000 K	133 lm/W	1,100 lm
79320300	DN460B LED11S/840 PSU-E C WH P	- degree(s)	4000 K	137 lm/W	1,150 lm
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	137 lm/W	1,150 lm
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	- degree(s)	3000 K	114 lm/W	980 lm
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	- degree(s)	4000 K	118 lm/W	1,000 lm
79335700	DN462B LED11S/830 PSU-E C WH PCO P	- degree(s)	3000 K	119 lm/W	980 lm

Order Code	Full Product	Beam	Correlated	Luminous	Luminous
	Name	angle of light source	Color Temperature (Nom)	Efficacy (rated) (Nom)	
79336400	DN462B LED11S/840 PSU-E C WH PCO P	- degree(s)	4000 K	122 lm/W	1,000 lm
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	- degree(s)	3000 K	118 lm/W	1,600 lm
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	- degree(s)	4000 K	121 lm/W	1,650 lm
01311700	DN472B LED11S/830 PSD-E C WH PCO P	-	3000 K	115 lm/W	940 lm
01312400	DN472B LED11S/840 PSD-E C WH PCO P	-	4000 K	118 lm/W	960 lm
79347000	DN472B LED20S/830 PSU-E C WH PCO P	- degree(s)	3000 K	121 lm/W	1,600 lm
79348700	DN472B LED20S/840 PSU-E C WH PCO P	- degree(s)	4000 K	125 lm/W	1,650 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Upward light output ratio
79324100	DN461B LED11S/840 PSU-E C WH P	1	-
98307900	DN471B LED20S/830 WIA-E C WH P	-	0
98309300	DN471B LED20S/840 WIA-E C WH P	-	0
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	-	0
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	-	0
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	-	0
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	-	0
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	-	0
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	-	0
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	-	0
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	-	0
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	-	0
98338300	DN473B LED20S/840 DIA-VLC-E C WH PCC P	-	0
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	-	0
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	-	0
01309400	DN471B LED20S/830 PSD-E C WH P	-	0

Order Code	Full Product Name	Number of light sources	Upward light output ratio
01310000	DN471B LED20S/840 PSD-E C WH P	-	0
38474600	DN473B LED20S/830 PSU-E C WH PCC P	1	-
38475300	DN473B LED20S/840 PSU-E C WH PCC P	1	-
79331900	DN471B LED20S/830 PSU-E C WH P	1	-
79332600	DN471B LED20S/840 PSU-E C WH P	1	-
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	1	-
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	1	-
94583100	DN471B LED30S/830 PSU-E C WH P	-	-
94584800	DN471B LED30S/840 PSU-E C WH P	-	-
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	-	-
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	-	-
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	-	0
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	-	0
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	-	0

Order Code	Full Product Name	Number of light sources	Upward light output ratio
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	-	0
98305500	DN470B LED20S/840 WIA-E C WH P	-	0
98311600	DN472B LED20S/830 WIA-E C WH PCC P	-	0
98313000	DN472B LED20S/840 WIA-E C WH PCC P	-	0
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	-	0
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	-	0
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	-	0
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	-	0
98330700	DN472B LED20S/830 DIA-VLC-E C WH PCC P	-	0
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-	0
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-	0
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-	0
98366600	DN470B LED20S/830 WIA-E C WH P	-	0
01290500	DN470B LED20S/830 PSD-E C WH P	-	0
01291200	DN470B LED30S/830 PSD-E C WH P	-	0
01307000	DN470B LED20S/840 PSD-E C WH P	-	0
01308700	DN470B LED30S/840 PSD-E C WH P	-	0
38470800	DN472B LED20S/830 PSU-E C WH PCC P	1	-
38471500	DN472B LED20S/840 PSU-E C WH PCC P	1	-
79327200	DN470B LED20S/830 PSU-E C WH P	1	-

Order Code	Full Product Name	Number of light sources	Upward light output ratio
79328900	DN470B LED20S/840 PSU-E C WH P	1	-
79351700	DN470B LED20S/830 PSU-E C ELP3 WH P	1	-
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	1	-
94575600	DN470B LED30S/830 PSU-E C WH P	-	-
94576300	DN470B LED30S/840 PSU-E C WH P	-	-
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	-	-
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	-	-
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	-	0
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	-	0
38462300	DN462B LED11S/830 PSU-E C WH PCC P	1	-
79319700	DN460B LED11S/830 PSU-E C WH P	1	-
79320300	DN460B LED11S/840 PSU-E C WH P	1	-
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	1	-
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	-	0
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	-	0
79335700	DN462B LED11S/830 PSU-E C WH PCO P	1	-
79336400	DN462B LED11S/840 PSU-E C WH PCO P	1	-
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	-	0
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	-	0
01311700	DN472B LED11S/830 PSD-E C WH PCO P	-	0
01312400	DN472B LED11S/840 PSD-E C WH PCO P	-	0
79347000	DN472B LED20S/830 PSU-E C WH PCO P	1	-
79348700	DN472B LED20S/840 PSU-E C WH PCO P	1	-

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption
79324100	DN461B LED11S/840 PSU-E C WH P	220-240 V	8.2 W
98307900	DN471B LED20S/830 WIA-E C WH P	220-240 V	13.2 W
98309300	DN471B LED20S/840 WIA-E C WH P	220-240 V	13.2 W
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	220-240 V	13.7 W
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	220-240 V	13.7 W
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	220-240 V	13.7 W
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	220-240 V	13.7 W
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	220-240 V	20.9 W
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	220-240 V	20.9 W
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	220-240 V	20.9 W
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	220-240 V	20.9 W
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	220-240 V	13.7 W

Order Code	Full Product Name	Input Voltage	Power Consumption
98338300	DN473B LED20S/840 DIA-VLC-E C WH PCC P	220-240 V	13.7 W
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	220-240 V	20.9 W
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	220-240 V	20.9 W
01309400	DN471B LED20S/830 PSD-E C WH P	220-240 V	13.5 W
01310000	DN471B LED20S/840 PSD-E C WH P	220-240 V	13.5 W
38474600	DN473B LED20S/830 PSU-E C WH PCC P	220 to 240 V	13.3 W
38475300	DN473B LED20S/840 PSU-E C WH PCC P	220 to 240 V	13.3 W
79331900	DN471B LED20S/830 PSU-E C WH P	220-240 V	13.3 W
79332600	DN471B LED20S/840 PSU-E C WH P	220-240 V	13.3 W
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	220-240 V	13.3 W
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	220-240 V	13.3 W
94583100	DN471B LED30S/830 PSU-E C WH P	220-240 V	20.9 W
94584800	DN471B LED30S/840 PSU-E C WH P	220-240 V	20.9 W
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	220-240 V	20.9 W

Order Code	Full Product Name	Input Voltage	Power
			Consumption
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	220-240 V	20.9 W
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	220-240 V	8.6 W
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	220-240 V	13.7 W
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	220-240 V	13.7 W
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	220-240 V	13.7 W
98305500	DN470B LED20S/840 WIA-E C WH P	220-240 V	13.2 W
98311600	DN472B LED20S/830 WIA-E C WH PCC P	220-240 V	13.2 W
98313000	DN472B LED20S/840 WIA-E C WH PCC P	220-240 V	13.2 W
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	220-240 V	20.9 W
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	220-240 V	20.9 W
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	220-240 V	20.9 W
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	220-240 V	20.9 W
98330700	DN472B LED20S/830 DIA-VLC-E C WH PCC P	220-240 V	13.7 W
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	220-240 V	13.7 W
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	220-240 V	20.9 W
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	220-240 V	20.9 W
98366600	DN470B LED20S/830 WIA-E C WH P	220-240 V	13.2 W
01290500	DN470B LED20S/830 PSD-E C WH P	220-240 V	13.5 W
01291200	DN470B LED30S/830 PSD-E C WH P	220-240 V	21.2 W
01307000	DN470B LED20S/840 PSD-E C WH P	220-240 V	13.5 W
01308700	DN470B LED30S/840 PSD-E C WH P	220-240 V	21.2 W
38470800	DN472B LED20S/830 PSU-E C WH PCC P	220 to 240 V	13.3 W
38471500	DN472B LED20S/840 PSU-E C WH PCC P	220 to 240 V	13.3 W
79327200	DN470B LED20S/830 PSU-E C WH P	220-240 V	13.3 W

Controls and Dimming

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
79324100	DN461B LED11S/840 PSU-E C WH P	No	Not applicable
98307900	DN471B LED20S/830 WIA-E C WH P	Yes	1%
98309300	DN471B LED20S/840 WIA-E C WH P	Yes	1%
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	Yes	1%

Order Code	Full Product Name	Input Voltage	Power
			Consumption
79328900	DN470B LED20S/840 PSU-E C WH P	220-240 V	13.3 W
79351700	DN470B LED20S/830 PSU-E C ELP3 WH P	220-240 V	13.3 W
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	220-240 V	13.3 W
94575600	DN470B LED30S/830 PSU-E C WH P	220-240 V	20.9 W
94576300	DN470B LED30S/840 PSU-E C WH P	220-240 V	20.9 W
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	220-240 V	20.9 W
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	220-240 V	20.9 W
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	220-240 V	8.6 W
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	220-240 V	8.6 W
38462300	DN462B LED11S/830 PSU-E C WH PCC P	220 to 240 V	8.2 W
79319700	DN460B LED11S/830 PSU-E C WH P	220-240 V	8.2 W
79320300	DN460B LED11S/840 PSU-E C WH P	220-240 V	8.2 W
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	220-240 V	8.2 W
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	220-240 V	8.6 W
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	220-240 V	8.6 W
79335700	DN462B LED11S/830 PSU-E C WH PCO P	220-240 V	8.2 W
79336400	DN462B LED11S/840 PSU-E C WH PCO P	220-240 V	8.2 W
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	220-240 V	13.7 W
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	220-240 V	13.7 W
01311700	DN472B LED11S/830 PSD-E C WH PCO P	220-240 V	8.2 W
01312400	DN472B LED11S/840 PSD-E C WH PCO P	220-240 V	8.2 W
79347000	DN472B LED20S/830 PSU-E C WH PCO P	220-240 V	13.3 W
79348700	DN472B LED20S/840 PSU-E C WH PCO P	220-240 V	13.3 W

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	Yes	1%
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	Yes	1%
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	Yes	1%

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	Yes	1%
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	Yes	1%
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	Yes	1%
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	Yes	1%
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	Yes	1%
98338300	DN473B LED20S/840 DIA-VLC-E C WH PCC P	Yes	1%
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	Yes	1%
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	Yes	1%
01309400	DN471B LED20S/830 PSD-E C WH P	Yes	1%
01310000	DN471B LED20S/840 PSD-E C WH P	Yes	1%
38474600	DN473B LED20S/830 PSU-E C WH PCC P	No	Not applicable
38475300	DN473B LED20S/840 PSU-E C WH PCC P	No	Not applicable
79331900	DN471B LED20S/830 PSU-E C WH P	No	Not applicable
79332600	DN471B LED20S/840 PSU-E C WH P	No	Not applicable
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	No	Not applicable
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	No	Not applicable
94583100	DN471B LED30S/830 PSU-E C WH P	No	Not applicable
94584800	DN471B LED30S/840 PSU-E C WH P	No	Not applicable
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	No	Not applicable
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	No	Not applicable
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	Yes	1%
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	Yes	1%
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	Yes	1%
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	Yes	1%
98305500	DN470B LED20S/840 WIA-E C WH P	Yes	1%
98311600	DN472B LED20S/830 WIA-E C WH PCC P	Yes	1%
98313000	DN472B LED20S/840 WIA-E C WH PCC P	Yes	1%
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	Yes	1%
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	Yes	1%
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	Yes	1%
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	Yes	1%
98330700	DN472B LED20S/830 DIA-VLC-E C WH PCC P	Yes	1%

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
79324100	DN461B LED11S/840 PSU-E C WH P	IP20
98307900	DN471B LED20S/830 WIA-E C WH P	IP20
98309300	DN471B LED20S/840 WIA-E C WH P	IP20
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	IP20

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	Yes	1%
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	Yes	1%
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	Yes	1%
98366600	DN470B LED20S/830 WIA-E C WH P	Yes	1%
01290500	DN470B LED20S/830 PSD-E C WH P	Yes	1%
01291200	DN470B LED30S/830 PSD-E C WH P	Yes	1%
01307000	DN470B LED20S/840 PSD-E C WH P	Yes	1%
01308700	DN470B LED30S/840 PSD-E C WH P	Yes	1%
38470800	DN472B LED20S/830 PSU-E C WH PCC P	No	Not applicable
38471500	DN472B LED20S/840 PSU-E C WH PCC P	No	Not applicable
79327200	DN470B LED20S/830 PSU-E C WH P	No	Not applicable
79328900	DN470B LED20S/840 PSU-E C WH P	No	Not applicable
79351700	DN470B LED20S/830 PSU-E C ELP3 WH P	No	Not applicable
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	No	Not applicable
94575600	DN470B LED30S/830 PSU-E C WH P	No	Not applicable
94576300	DN470B LED30S/840 PSU-E C WH P	No	Not applicable
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	No	Not applicable
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	No	Not applicable
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	Yes	1%
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	Yes	1%
38462300	DN462B LED11S/830 PSU-E C WH PCC P	No	Not applicable
79319700	DN460B LED11S/830 PSU-E C WH P	No	Not applicable
79320300	DN460B LED11S/840 PSU-E C WH P	No	Not applicable
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	No	Not applicable
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	Yes	1%
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	Yes	1%
79335700	DN462B LED11S/830 PSU-E C WH PCO P	No	Not applicable
79336400	DN462B LED11S/840 PSU-E C WH PCO P	No	Not applicable
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	Yes	1%
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	Yes	1%
01311700	DN472B LED11S/830 PSD-E C WH PCO P	Yes	1%
01312400	DN472B LED11S/840 PSD-E C WH PCO P	Yes	1%
79347000	DN472B LED20S/830 PSU-E C WH PCO P	No	Not applicable
79348700	DN472B LED20S/840 PSU-E C WH PCO P	No	Not applicable

Order Code	Full Product Name	Ingress protection code
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	IP20
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	IP20
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	IP20
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	IP20

Order Code	Full Product Name	Ingress protection code
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	IP20
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	IP20
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	IP20
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	IP20/54
98338300	DN473B LED20S/840 DIA-VLC-E C WH PCC P	IP20/54
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	IP20/54
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	IP20/54
01309400	DN471B LED20S/830 PSD-E C WH P	IP20
01310000	DN471B LED20S/840 PSD-E C WH P	IP20
38474600	DN473B LED20S/830 PSU-E C WH PCC P	IP20/54
38475300	DN473B LED20S/840 PSU-E C WH PCC P	IP20/54
79331900	DN471B LED20S/830 PSU-E C WH P	IP20
79332600	DN471B LED20S/840 PSU-E C WH P	IP20
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	IP20
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	IP20
94583100	DN471B LED30S/830 PSU-E C WH P	IP20
94584800	DN471B LED30S/840 PSU-E C WH P	IP20
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	IP20
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	IP20
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	IP20
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	IP20
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	IP20
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	IP20
98305500	DN470B LED20S/840 WIA-E C WH P	IP20
98311600	DN472B LED20S/830 WIA-E C WH PCC P	IP20/54
98313000	DN472B LED20S/840 WIA-E C WH PCC P	IP20/54
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	IP20
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	IP20
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	IP20
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	IP20
98330700	DN472B LED20S/830 DIA-VLC-E C WH PCC P	IP20/54
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	IP20/54
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	IP20/54

Order Code	Full Product Name	Ingress protection code
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	IP20/54
98366600	DN470B LED20S/830 WIA-E C WH P	IP20
01290500	DN470B LED20S/830 PSD-E C WH P	IP20
01291200	DN470B LED30S/830 PSD-E C WH P	IP20
01307000	DN470B LED20S/840 PSD-E C WH P	IP20
01308700	DN470B LED30S/840 PSD-E C WH P	IP20
38470800	DN472B LED20S/830 PSU-E C WH PCC P	IP20/54
38471500	DN472B LED20S/840 PSU-E C WH PCC P	IP20/54
79327200	DN470B LED20S/830 PSU-E C WH P	IP20
79328900	DN470B LED20S/840 PSU-E C WH P	IP20
79351700	DN470B LED20S/830 PSU-E C ELP3 WH P	IP20
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	IP20
94575600	DN470B LED30S/830 PSU-E C WH P	IP20
94576300	DN470B LED30S/840 PSU-E C WH P	IP20
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	IP20
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	IP20
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	IP20
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	IP20/54
38462300	DN462B LED11S/830 PSU-E C WH PCC P	IP20/54
79319700	DN460B LED11S/830 PSU-E C WH P	IP20
79320300	DN460B LED11S/840 PSU-E C WH P	IP20
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	IP20
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	IP20/54
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	IP20/54
79335700	DN462B LED11S/830 PSU-E C WH PCO P	IP20/54
79336400	DN462B LED11S/840 PSU-E C WH PCO P	IP20/54
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	IP20/54
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	IP20/54
01311700	DN472B LED11S/830 PSD-E C WH PCO P	IP20/54
01312400	DN472B LED11S/840 PSD-E C WH PCO P	IP20/54
79347000	DN472B LED20S/830 PSU-E C WH PCO P	IP20/54
79348700	DN472B LED20S/840 PSU-E C WH PCO P	IP20/54

Emergency Operation

					Rated duration of the emergency lighting (when fully charged)
Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	
79324100	DN461B LED11S/840 PSU-E C WH P	No	-	-	-
98307900	DN471B LED20S/830 WIA-E C WH P	No	-	-	-
98309300	DN471B LED20S/840 WIA-E C WH P	No	-	-	-

					Rated duration of the emergency lighting (when fully charged)
Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	380 lm	3 hour(s)
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	380 lm	3 hour(s)
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	No	-	-	-
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	380 lm	3 hour(s)
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	No	-	-	-
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	380 lm	3 hour(s)
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	No	-	-	-
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	No	-	-	-
98338300	DN473B LED20S/840 DIA-VLC-E C WH PCC P	No	-	-	-
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	No	-	-	-
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	No	-	-	-
01309400	DN471B LED20S/830 PSD-E C WH P	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
01310000	DN471B LED20S/840 PSD-E C WH P	No	-	-	-
38474600	DN473B LED20S/830 PSU-E C WH PCC P	No	-	-	-
38475300	DN473B LED20S/840 PSU-E C WH PCC P	No	-	-	-
79331900	DN471B LED20S/830 PSU-E C WH P	No	-	-	-
79332600	DN471B LED20S/840 PSU-E C WH P	No	-	-	-
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	-	3 hour(s)
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	-	3 hour(s)
94583100	DN471B LED30S/830 PSU-E C WH P	No	-	-	-
94584800	DN471B LED30S/840 PSU-E C WH P	No	-	-	-
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	-	3 hour(s)
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	-	3 hour(s)
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	398 lm	3 hour(s)
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	No	-	-	-
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	398 lm	3 hour(s)
98305500	DN470B LED20S/840 WIA-E C WH P	No	-	-	-
98311600	DN472B LED20S/830 WIA-E C WH PCC P	No	-	-	-
98313000	DN472B LED20S/840 WIA-E C WH PCC P	No	-	-	-
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	398 lm	3 hour(s)
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	No	-	-	-
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	398 lm	3 hour(s)
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	No	-	-	-
98330700	DN472B LED20S/830	No	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
	DIA-VLC-E C WH PCC P				
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	No	-	-	-
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	No	-	-	-
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	No	-	-	-
98366600	DN470B LED20S/830 WIA-E C WH P	No	-	-	-
01290500	DN470B LED20S/830 PSD-E C WH P	No	-	-	-
01291200	DN470B LED30S/830 PSD-E C WH P	No	-	-	-
01307000	DN470B LED20S/840 PSD-E C WH P	No	-	-	-
01308700	DN470B LED30S/840 PSD-E C WH P	No	-	-	-
38470800	DN472B LED20S/830 PSU-E C WH PCC P	No	-	-	-
38471500	DN472B LED20S/840 PSU-E C WH PCC P	No	-	-	-
79327200	DN470B LED20S/830 PSU-E C WH P	No	-	-	-
79328900	DN470B LED20S/840 PSU-E C WH P	No	-	-	-
79351700	DN470B LED20S/830	No	Emergency lighting 3 hours	-	3 hour(s)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
	PSU-E C ELP3 WH P		duration Pro version		
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	No	Emergency lighting 3 hours	-	3 hour(s)
94575600	DN470B LED30S/830 PSU-E C WH P	No	-	-	-
94576300	DN470B LED30S/840 PSU-E C WH P	No	-	-	-
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	No	Emergency lighting 3 hours	-	3 hour(s)
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	No	Emergency lighting 3 hours	-	3 hour(s)
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	No	-	-	-
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	No	-	-	-
38462300	DN462B LED11S/830 PSU-E C WH PCC P	No	-	-	-
79319700	DN460B LED11S/830 PSU-E C WH P	No	-	-	-
79320300	DN460B LED11S/840 PSU-E C WH P	No	-	-	-
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	-	Emergency lighting 3 hours	-	3 hour(s)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Emergency flux	Rated duration of the emergency lighting (when fully charged)
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	No	-	-	-
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	No	-	-	-
79335700	DN462B LED11S/830 PSU-E C WH PCO P	No	-	-	-
79336400	DN462B LED11S/840 PSU-E C WH PCO P	No	-	-	-
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	No	-	-	-
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	No	-	-	-
01311700	DN472B LED11S/830 PSD-E C WH PCO P	No	-	-	-
01312400	DN472B LED11S/840 PSD-E C WH PCO P	No	-	-	-
79347000	DN472B LED20S/830 PSU-E C WH PCO P	No	-	-	-
79348700	DN472B LED20S/840 PSU-E C WH PCO P	No	-	-	-

Approval and Application

					Stroboscopic effect visibility measure (SVM)
Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	
79324100	DN461B LED11S/840 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98307900	DN471B LED20S/830 WIA-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98309300	DN471B LED20S/840 WIA-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98338300	DN473B LED20S/840	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-

					Stroboscopic effect visibility measure (SVM)
Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	
	DIA-VLC-E C WH PCC P				
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
01309400	DN471B LED20S/830 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	0.4
01310000	DN471B LED20S/840 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	0.4
38474600	DN473B LED20S/830 PSU-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
38475300	DN473B LED20S/840 PSU-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79331900	DN471B LED20S/830 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79332600	DN471B LED20S/840 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
94583100	DN471B LED30S/830 PSU-E C WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
94584800	DN471B LED30S/840 PSU-E C WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	Stroboscopic effect visibility measure (SVM)
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	0.4
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98305500	DN470B LED20S/840 WIA-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98311600	DN472B LED20S/830 WIA-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98313000	DN472B LED20S/840 WIA-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	Stroboscopic effect visibility measure (SVM)
98330700	DN472B LED20S/830 DIA-VLC-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98366600	DN470B LED20S/830 WIA-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
01290500	DN470B LED20S/830 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	0.4
01291200	DN470B LED30S/830 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	0.4
01307000	DN470B LED20S/840 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	0.4
01308700	DN470B LED30S/840 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	0.4
38470800	DN472B LED20S/830 PSU-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
38471500	DN472B LED20S/840 PSU-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79327200	DN470B LED20S/830 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79328900	DN470B LED20S/840 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79351700	DN470B LED20S/830	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-

					Stroboscopic effect visibility measure (SVM)
Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	
	PSU-E C ELP3 WH P				
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
94575600	DN470B LED30S/830 PSU-E C WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
94576300	DN470B LED30S/840 PSU-E C WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
38462300	DN462B LED11S/830 PSU-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79319700	DN460B LED11S/830 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	0.4
79320300	DN460B LED11S/840 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79340100	DN460B LED11S/840	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
79324100	DN461B LED11S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
98307900	DN471B LED20S/830 WIA-E C WH P	(0.43, 0.40) SDCM<3

					Stroboscopic effect visibility measure (SVM)
Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	
	PSU-E C ELP3 WH P				
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79335700	DN462B LED11S/830 PSU-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79336400	DN462B LED11S/840 PSU-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
01311700	DN472B LED11S/830 PSD-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	0.4
01312400	DN472B LED11S/840 PSD-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	0.4
79347000	DN472B LED20S/830 PSU-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79348700	DN472B LED20S/840 PSU-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-

Order Code	Full Product Name	Initial chromaticity
98309300	DN471B LED20S/840 WIA-E C WH P	(0.38, 0.38) SDCM<3
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	(0.43, 0.40) SDCM<3

Order Code	Full Product Name	Initial chromaticity
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	(0.38, 0.38) SDCM<3
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	(0.43, 0.40) SDCM<3
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	(0.38, 0.38) SDCM<3
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
98338300	DN473B LED20S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
01309400	DN471B LED20S/830 PSD-E C WH P	(0.43, 0.40) SDCM<3
01310000	DN471B LED20S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3
38474600	DN473B LED20S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3
38475300	DN473B LED20S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3
79331900	DN471B LED20S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
79332600	DN471B LED20S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	(0.43, 0.40) SDCM<3
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
94583100	DN471B LED30S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
94584800	DN471B LED30S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	(0.43, 0.40) SDCM<3
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	(0.43, 0.40) SDCM<3
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	(0.38, 0.38) SDCM<3
98305500	DN470B LED20S/840 WIA-E C WH P	(0.38, 0.38) SDCM<3
98311600	DN472B LED20S/830 WIA-E C WH PCC P	(0.43, 0.40) SDCM<3
98313000	DN472B LED20S/840 WIA-E C WH PCC P	(0.38, 0.38) SDCM<3
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	(0.43, 0.40) SDCM<3
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	(0.38, 0.38) SDCM<3
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
98330700	DN472B LED20S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3

Order Code	Full Product Name	Initial chromaticity
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
98366600	DN470B LED20S/830 WIA-E C WH P	(0.43, 0.40) SDCM<3
01290500	DN470B LED20S/830 PSD-E C WH P	(0.43, 0.40) SDCM<3
01291200	DN470B LED30S/830 PSD-E C WH P	(0.43, 0.40) SDCM<3
01307000	DN470B LED20S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3
01308700	DN470B LED30S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3
38470800	DN472B LED20S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3
38471500	DN472B LED20S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3
79327200	DN470B LED20S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
79328900	DN470B LED20S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
79351700	DN470B LED20S/830 PSU-E C ELP3 WH P	(0.43, 0.40) SDCM<3
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
94575600	DN470B LED30S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
94576300	DN470B LED30S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	(0.43, 0.40) SDCM<3
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3
38462300	DN462B LED11S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3
79319700	DN460B LED11S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3
79320300	DN460B LED11S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	(0.43, 0.40) SDCM<3
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	(0.38, 0.38) SDCM<3
79335700	DN462B LED11S/830 PSU-E C WH PCO P	(0.43, 0.40) SDCM<3
79336400	DN462B LED11S/840 PSU-E C WH PCO P	(0.38, 0.38) SDCM<3
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	(0.43, 0.40) SDCM<3
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	(0.38, 0.38) SDCM<3
01311700	DN472B LED11S/830 PSD-E C WH PCO P	(0.43, 0.40) SDCM<3
01312400	DN472B LED11S/840 PSD-E C WH PCO P	(0.38, 0.38) SDCM<3
79347000	DN472B LED20S/830 PSU-E C WH PCO P	(0.43, 0.40) SDCM<3
79348700	DN472B LED20S/840 PSU-E C WH PCO P	(0.38, 0.38) SDCM<3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
79324100	DN461B LED11S/840 PSU-E C WH P	1 %
98307900	DN471B LED20S/830 WIA-E C WH P	-
98309300	DN471B LED20S/840 WIA-E C WH P	-
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	-
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	-
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	-
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	-
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	-
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	-
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	-
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	-
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	-

Order Code	Full Product Name	Driver failure rate at 5000 h
98338300	DN473B LED20S/840 DIA-VLC-E C WH PCC P	-
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	-
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	-
01309400	DN471B LED20S/830 PSD-E C WH P	-
01310000	DN471B LED20S/840 PSD-E C WH P	-
38474600	DN473B LED20S/830 PSU-E C WH PCC P	1 %
38475300	DN473B LED20S/840 PSU-E C WH PCC P	1 %
79331900	DN471B LED20S/830 PSU-E C WH P	1 %
79332600	DN471B LED20S/840 PSU-E C WH P	1 %
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	1 %
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	1 %
94583100	DN471B LED30S/830 PSU-E C WH P	1 %

Order Code	Full Product Name	Driver failure rate at 5000 h
94584800	DN471B LED30S/840 PSU-E C WH P	1 %
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	1 %
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	1 %
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	-
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	-
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	-
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	-
98305500	DN470B LED20S/840 WIA-E C WH P	-
98311600	DN472B LED20S/830 WIA-E C WH PCC P	-
98313000	DN472B LED20S/840 WIA-E C WH PCC P	-
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	-
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	-
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	-
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	-
98330700	DN472B LED20S/830 DIA-VLC-E C WH PCC P	-
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-
98366600	DN470B LED20S/830 WIA-E C WH P	-
01290500	DN470B LED20S/830 PSD-E C WH P	-
01291200	DN470B LED30S/830 PSD-E C WH P	-
01307000	DN470B LED20S/840 PSD-E C WH P	-
01308700	DN470B LED30S/840 PSD-E C WH P	-
38470800	DN472B LED20S/830 PSU-E C WH PCC P	1 %
38471500	DN472B LED20S/840 PSU-E C WH PCC P	1 %

Order Code	Full Product Name	Driver failure rate at 5000 h
79327200	DN470B LED20S/830 PSU-E C WH P	1 %
79328900	DN470B LED20S/840 PSU-E C WH P	1 %
79351700	DN470B LED20S/830 PSU-E C ELP3 WH P	1 %
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	1 %
94575600	DN470B LED30S/830 PSU-E C WH P	1 %
94576300	DN470B LED30S/840 PSU-E C WH P	1 %
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	1 %
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	1 %
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	-
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	-
38462300	DN462B LED11S/830 PSU-E C WH PCC P	1 %
79319700	DN460B LED11S/830 PSU-E C WH P	1 %
79320300	DN460B LED11S/840 PSU-E C WH P	1 %
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	1 %
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	-
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	-
79335700	DN462B LED11S/830 PSU-E C WH PCO P	1 %
79336400	DN462B LED11S/840 PSU-E C WH PCO P	1 %
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	-
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	-
01311700	DN472B LED11S/830 PSD-E C WH PCO P	-
01312400	DN472B LED11S/840 PSD-E C WH PCO P	-
79347000	DN472B LED20S/830 PSU-E C WH PCO P	1 %
79348700	DN472B LED20S/840 PSU-E C WH PCO P	1 %

Product Data




Order Code	Full Product Name	Product family code
79324100	DN461B LED11S/840 PSU-E C WH P	DN461B
98307900	DN471B LED20S/830 WIA-E C WH P	DN471B
98309300	DN471B LED20S/840 WIA-E C WH P	DN471B
98322200	DN471B LED20S/830 DIA-VLC-E C ELP3 WH P	DN471B
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	DN471B
98324600	DN471B LED20S/840 DIA-VLC-E C ELP3 WH P	DN471B
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	DN471B
98326000	DN471B LED30S/830 DIA-VLC-E C ELP3 WH P	DN471B
98327700	DN471B LED30S/830 DIA-VLC-E C WH P	DN471B
98328400	DN471B LED30S/840 DIA-VLC-E C ELP3 WH P	DN471B
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	DN471B
98337600	DN473B LED20S/830 DIA-VLC-E C WH PCC P	DN473B
98338300	DN473B LED20S/840 DIA-VLC-E C WH PCC P	DN473B
98339000	DN473B LED30S/830 DIA-VLC-E C WH PCC P	DN473B
98340600	DN473B LED30S/840 DIA-VLC-E C WH PCC P	DN473B
01309400	DN471B LED20S/830 PSD-E C WH P	DN471B
01310000	DN471B LED20S/840 PSD-E C WH P	DN471B
38474600	DN473B LED20S/830 PSU-E C WH PCC P	DN473B
38475300	DN473B LED20S/840 PSU-E C WH PCC P	DN473B
79331900	DN471B LED20S/830 PSU-E C WH P	DN471B
79332600	DN471B LED20S/840 PSU-E C WH P	DN471B
79355500	DN471B LED20S/830 PSU-E C ELP3 WH P	DN471B

Order Code	Full Product Name	Product family code
79356200	DN471B LED20S/840 PSU-E C ELP3 WH P	DN471B
94583100	DN471B LED30S/830 PSU-E C WH P	DN471B
94584800	DN471B LED30S/840 PSU-E C WH P	DN471B
94595400	DN471B LED30S/830 PSU-E C ELP3 WH P	DN471B
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	DN471B
98299700	DN470B LED11S/840 DIA-VLC-E C WH P	DN470B
98300000	DN470B LED20S/830 DIA-VLC-E C ELP3 WH P	DN470B
98301700	DN470B LED20S/830 DIA-VLC-E C WH P	DN470B
98302400	DN470B LED20S/840 DIA-VLC-E C ELP3 WH P	DN470B
98305500	DN470B LED20S/840 WIA-E C WH P	DN470B
98311600	DN472B LED20S/830 WIA-E C WH PCC P	DN472B
98313000	DN472B LED20S/840 WIA-E C WH PCC P	DN472B
98318500	DN470B LED30S/830 DIA-VLC-E C ELP3 WH P	DN470B
98319200	DN470B LED30S/830 DIA-VLC-E C WH P	DN470B
98320800	DN470B LED30S/840 DIA-VLC-E C ELP3 WH P	DN470B
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	DN470B
98330700	DN472B LED20S/830 DIA-VLC-E C WH PCC P	DN472B
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	DN472B
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	DN472B
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	DN472B
98366600	DN470B LED20S/830 WIA-E C WH P	DN470B
01290500	DN470B LED20S/830 PSD-E C WH P	DN470B

Order Code	Full Product Name	Product family code
01291200	DN470B LED30S/830 PSD-E C WH P	DN470B
01307000	DN470B LED20S/840 PSD-E C WH P	DN470B
01308700	DN470B LED30S/840 PSD-E C WH P	DN470B
38470800	DN472B LED20S/830 PSU-E C WH PCC P	DN472B
38471500	DN472B LED20S/840 PSU-E C WH PCC P	DN472B
79327200	DN470B LED20S/830 PSU-E C WH P	DN470B
79328900	DN470B LED20S/840 PSU-E C WH P	DN470B
79351700	DN470B LED20S/830 PSU-E C ELP3 WH P	DN470B
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	DN470B
94575600	DN470B LED30S/830 PSU-E C WH P	DN470B
94576300	DN470B LED30S/840 PSU-E C WH P	DN470B
94591600	DN470B LED30S/830 PSU-E C ELP3 WH P	DN470B
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	DN470B
98254600	DN460B LED11S/840 DIA-VLC-E C WH P	DN460B
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	DN462B

Order Code	Full Product Name	Product family code
38462300	DN462B LED11S/830 PSU-E C WH PCC P	DN462B
79319700	DN460B LED11S/830 PSU-E C WH P	DN460B
79320300	DN460B LED11S/840 PSU-E C WH P	DN460B
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	DN460B
98293500	DN462B LED11S/830 DIA-VLC-E C WH PCO P	DN462B
98295900	DN462B LED11S/840 DIA-VLC-E C WH PCO P	DN462B
79335700	DN462B LED11S/830 PSU-E C WH PCO P	DN462B
79336400	DN462B LED11S/840 PSU-E C WH PCO P	DN462B
98331400	DN472B LED20S/830 DIA-VLC-E C WH PCO P	DN472B
98333800	DN472B LED20S/840 DIA-VLC-E C WH PCO P	DN472B
01311700	DN472B LED11S/830 PSD-E C WH PCO P	DN472B
01312400	DN472B LED11S/840 PSD-E C WH PCO P	DN472B
79347000	DN472B LED20S/830 PSU-E C WH PCO P	DN472B
79348700	DN472B LED20S/840 PSU-E C WH PCO P	DN472B




Polar Wide Diagrams



Polar Normal (separate) - DN460BN - 910505102113

Polar Normal (separate) - DN460BN - 910505102118

Polar Normal (separate) - DN460BN - 910505102035




Polar Normal (separate) - DN460BN - 910505102082


Polar Normal (separate) - DN460BN - 910505102119

Polar Normal (separate) - DN460BN - 910505102087


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 910505102091




Polar Normal (separate) - DN460BN - 910505102110




Polar Normal (separate) - DN460BN - 910505102293




Polar Normal (separate) - DN460BN - 910505102291




Polar Normal (separate) - DN460BN - 910505102102




Polar Normal (separate) - DN460BN - 910505102120



Polar Normal (separate) - DN460BN - 910505102107




Polar Normal (separate) - DN460BN - 910505102081




Polar Normal (separate) - DN460BN - 910505102103


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 910505102111




Polar Normal (separate) - DN460BN - 910505102108




Polar Normal (separate) - DN460BN - 910505102271




Polar Normal (separate) - DN460BN - 910505102093




Polar Normal (separate) - DN460BN - 910505102106




Polar Normal (separate) - DN460BN - 910505102272



Polar Normal (separate) - DN460BN - 910505102109




Polar Normal (separate) - DN460BN - 910505102098




Polar Normal (separate) - DN460BN - 910505102292


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 910505102104




Polar Normal (separate) - DN460BN - 910505102089




Polar Normal (separate) - DN460BN - 910505102115




Polar Normal (separate) - DN460BN - 910505102116




Polar Normal (separate) - DN460BN - 910505102075




Polar Normal (separate) - DN460BN - 910505102290



Polar Normal (separate) - DN460BN - 910505102079




Polar Normal (separate) - DN460BN - 910505102073




Polar Normal (separate) - DN460BN - 910505102099


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 910505102105




Polar Normal (separate) - DN460BN - 910505102121




Polar Normal (separate) - DN460BN - 910505102074




Polar Normal (separate) - DN460BN - 910505102085




Polar Normal (separate) - DN460BN - 910505102288




Polar Normal (separate) - DN460BN - 912500100062



Polar Normal (separate) - DN460BN - 912500100070




Polar Normal (separate) - DN460BN - 912500100071




Polar Normal (separate) - DN460BN - 912500100075


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 912500100074




Polar Normal (separate) - DN460BN - 912500100515




Polar Normal (separate) - DN460BN - 912500100519




Polar Normal (separate) - DN460BN - 912500100522




Polar Normal (separate) - DN460BN - 912500100523




Polar Normal (separate) - DN460BN - 912500100514



Polar Normal (separate) - DN460BN - 912500100527




Polar Normal (separate) - DN460BN - 912500100531




Polar Normal (separate) - DN460BN - 912500100526


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 912500100535




Polar Normal (separate) - DN460BN - 912500100543




Polar Normal (separate) - DN460BN - 912500100542




Polar Normal (separate) - DN460BN - 912500100530




Polar Normal (separate) - DN460BN - 912500100550




Polar Normal (separate) - DN460BN - 912500100551



Polar Normal (separate) - DN460BN - 912500100547




Polar Normal (separate) - DN460BN - 912500101315




Polar Normal (separate) - DN460BN - 912500100546


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 912500101314




Polar Normal (separate) - DN460BN - 912500101322




Polar Normal (separate) - DN460BN - 912500101307




Polar Normal (separate) - DN460BN - 912500101323




Polar Normal (separate) - DN460BN - 912500101326




Polar Normal (separate) - DN460BN - 912500101305



Polar Normal (separate) - DN460BN - 912500101327




Polar Normal (separate) - DN460BN - 910505102080




Polar Normal (separate) - DN460BN - 910505102101


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 910505102114



Polar Normal (separate) - DN460BN - 910505102112



Polar Normal (separate) - DN460BN - 910505102147



Polar Normal (separate) - DN460BN - 910505102289

