



GreenSpace – high-efficiency sustainable LED solution

GreenSpace

Customers want to strike the ideal balance between their initial investment and the cost of the installation during its lifetime. GreenSpace is a cost-efficient and sustainable downlight that can be used to replace conventional CFL downlights in general lighting applications. It features the latest LED technology, which enables extremely low power consumption, while delivering consistent light output, stable color performance and high color rendering. The product's long lifetime makes it a true 'fit and forget' solution.

Benefits

- High system efficacy: > 80 lm/W (mini, DN460B/DN461B); > 100 lm/W (compact, DN470B/DN471B)
- Up to 70% energy saving: total cost of ownership recovered in less than 2 years
- Office lighting norm-compliant, with stable color performance and high color rendering

Features

- Energy-efficient, durable LED technology
- High system efficacy: > 80 lm/W (mini, DN460B/DN461B); > 100 lm/W (compact, DN470B/DN471B)
- Stable color performance and high color rendering
- Available with IP44 or emergency lighting
- Available in UGR22 and UGR19 versions

Application

- Offices
- Retail
- Hotels and hospitals

Versions



Greenspace Mini DN462B with
Poycarbonate Cover Opal



Greenspace Compact DN472B with
Poycarbonate Cover Opal











GreenSpace perfect fit 230mm
cut-out



GreenSpace perfect fit family

Dimensional drawing



Product details

Greenspace_EU_gen_2-DN473B-DPP.TIF




Greenspace_EU_gen_2-DN472B-DPP.TIF



Greenspace_EU_gen_2-DN462_463_472_473B-1DPP.TIF



Greenspace_EU_gen_2-DN462_463_472_473B-3DPP.TIF



Greenspace_EU_gen_2-DN462B-DPP.TIF



Greenspace_EU_gen_2-DN462_463_472_473B-2DPP.TIF



Greenspace_EU_gen_2-DN463B-DPP.TIF



General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class II
Line Frequency	50 to 60 Hz
Controls and Dimming	
Embedded control	-
Mechanical and Housing	
Optical cover type	-
Housing Color	White
Approval and Application	
CE mark	Yes
Flammability mark	-

General Information

Order Code	Full Product Name	Lamp family code	Light source replaceable
01306300	DN461B LED11S/840 PSD-E C WH P	11S	No
38467800	DN463B LED11S/840 PSU-E C WH PCC P	LED11S	No
79324100	DN461B LED11S/840 PSU-E C WH P	LED11S	No
98309300	DN471B LED20S/840 WIA-E C WH P	20S	No
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	20S	No
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	20S	No
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	30S	No
01309400	DN471B LED20S/830 PSD-E C WH P	20S	No
01310000	DN471B LED20S/840 PSD-E C WH P	20S	No
38475300	DN473B LED20S/840 PSU-E C WH PCC P	LED20S	No
79331900	DN471B LED20S/830 PSU-E C WH P	LED20S	No
79332600	DN471B LED20S/840 PSU-E C WH P	LED20S	No
94584800	DN471B LED30S/840 PSU-E C WH P	-	No
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	-	No
98305500	DN470B LED20S/840 WIA-E C WH P	20S	No
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	30S	No
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	20S	No
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	30S	No
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	30S	No
01307000	DN470B LED20S/840 PSD-E C WH P	20S	No
38470800	DN472B LED20S/830 PSU-E C WH PCC P	LED20S	No
38471500	DN472B LED20S/840 PSU-E C WH PCC P	LED20S	No
79327200	DN470B LED20S/830 PSU-E C WH P	LED20S	No
79328900	DN470B LED20S/840 PSU-E C WH P	LED20S	No
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	LED20S	No
94575600	DN470B LED30S/830 PSU-E C WH P	-	No
94576300	DN470B LED30S/840 PSU-E C WH P	-	No
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	-	No
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	11S	No
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	11S	No
01304900	DN460B LED11S/840 PSD-E C WH P	11S	No
38462300	DN462B LED11S/830 PSU-E C WH PCC P	LED11S	No
38463000	DN462B LED11S/840 PSU-E C PCC WH P	LED11S	No
79319700	DN460B LED11S/830 PSU-E C WH P	LED11S	No
79320300	DN460B LED11S/840 PSU-E C WH P	LED11S	No
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	LED11S	No
79336400	DN462B LED11S/840 PSU-E C WH PCO P	LED11S	No
79347000	DN472B LED20S/830 PSU-E C WH PCO P	LED20S	No
79348700	DN472B LED20S/840 PSU-E C WH PCO P	LED20S	No
56409100	TCTT225 20S/840 PSU-E WH	-	-
56410700	TCTT230 20S/840 PSU-E WH	-	-

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01306300	DN461B LED11S/840 PSD-E C WH P	-	4000 K	135 lm/W	1,100 lm
38467800	DN463B LED11S/840 PSU-E C WH PCC P	- degree(s)	4000 K	124 lm/W	1,000 lm
79324100	DN461B LED11S/840 PSU-E C WH P	- degree(s)	4000 K	134 lm/W	1,100 lm
98309300	DN471B LED20S/840 WIA-E C WH P	- degree(s)	4000 K	141 lm/W	1,850 lm
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	- degree(s)	3000 K	133 lm/W	1,800 lm
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	136 lm/W	1,850 lm
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	134 lm/W	2,800 lm
01309400	DN471B LED20S/830 PSD-E C WH P	-	3000 K	135 lm/W	1,800 lm
01310000	DN471B LED20S/840 PSD-E C WH P	-	4000 K	139 lm/W	1,850 lm
38475300	DN473B LED20S/840 PSU-E C WH PCC P	- degree(s)	4000 K	134 lm/W	1,800 lm
79331900	DN471B LED20S/830 PSU-E C WH P	- degree(s)	3000 K	137 lm/W	1,800 lm
79332600	DN471B LED20S/840 PSU-E C WH P	- degree(s)	4000 K	141 lm/W	1,850 lm
94584800	DN471B LED30S/840 PSU-E C WH P	- degree(s)	4000 K	135 lm/W	2,800 lm
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	135 lm/W	2,800 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
98305500	DN470B LED20S/840 WIA-E C WH P	- degree(s)	4000 K	148 lm/W	1,950 lm
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	- degree(s)	4000 K	141 lm/W	2,900 lm
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	136 lm/W	1,850 lm
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	- degree(s)	3000 K	130 lm/W	2,700 lm
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	134 lm/W	2,800 lm
01307000	DN470B LED20S/840 PSD-E C WH P	-	4000 K	146 lm/W	1,950 lm
38470800	DN472B LED20S/830 PSU-E C WH PCC P	- degree(s)	3000 K	137 lm/W	1,800 lm
38471500	DN472B LED20S/840 PSU-E C WH PCC P	- degree(s)	4000 K	141 lm/W	1,850 lm
79327200	DN470B LED20S/830 PSU-E C WH P	- degree(s)	3000 K	143 lm/W	1,900 lm
79328900	DN470B LED20S/840 PSU-E C WH P	- degree(s)	4000 K	147 lm/W	1,950 lm
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	147 lm/W	1,950 lm
94575600	DN470B LED30S/830 PSU-E C WH P	- degree(s)	3000 K	143 lm/W	2,900 lm
94576300	DN470B LED30S/840 PSU-E C WH P	- degree(s)	4000 K	147 lm/W	2,900 lm
94592300	DN470B LED30S/840	- degree(s)	4000 K	147 lm/W	2,900 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSU-E C ELP3 WH P				
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	- degree(s)	3000 K	122 lm/W	1,050 lm
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	- degree(s)	4000 K	126 lm/W	1,100 lm
01304900	DN460B LED11S/840 PSD-E C WH P	-	4000 K	138 lm/W	1,150 lm
38462300	DN462B LED11S/830 PSU-E C WH PCC P	- degree(s)	3000 K	127 lm/W	1,050 lm
38463000	DN462B LED11S/840 PSU-E C PCC WH P	- degree(s)	4000 K	130 lm/W	1,100 lm
79319700	DN460B LED11S/830 PSU-E C WH P	- degree(s)	3000 K	133 lm/W	1,100 lm
79320300	DN460B LED11S/840 PSU-E C WH P	- degree(s)	4000 K	137 lm/W	1,150 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	- degree(s)	4000 K	137 lm/W	1,150 lm
79336400	DN462B LED11S/840 PSU-E C WH PCO P	- degree(s)	4000 K	122 lm/W	1,000 lm
79347000	DN472B LED20S/830 PSU-E C WH PCO P	- degree(s)	3000 K	121 lm/W	1,600 lm
79348700	DN472B LED20S/840 PSU-E C WH PCO P	- degree(s)	4000 K	125 lm/W	1,650 lm
56409100	TCCT225 20S/840 PSU-E WH	90 degree(s)	4000 K	148 lm/W	1,964 lm
56410700	TCCT230 20S/840 PSU-E WH	90 degree(s)	4000 K	148 lm/W	1,964 lm

Light Technical (2/2)

Order Code	Full Product Name	Number of light sources	Optic type	Upward light output ratio
01306300	DN461B LED11S/840 PSD-E C WH P	-	-	0
38467800	DN463B LED11S/840 PSU-E C WH PCC P	1	-	-
79324100	DN461B LED11S/840 PSU-E C WH P	1	-	-
98309300	DN471B LED20S/840 WIA-E C WH P	-	-	0
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	-	-	0
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	-	-	0
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	-	-	0
01309400	DN471B LED20S/830 PSD-E C WH P	-	-	0
01310000	DN471B LED20S/840 PSD-E C WH P	-	-	0
38475300	DN473B LED20S/840 PSU-E C WH PCC P	1	-	-
79331900	DN471B LED20S/830 PSU-E C WH P	1	-	-

Order Code	Full Product Name	Number of light sources	Optic type	Upward light output ratio
79332600	DN471B LED20S/840 PSU-E C WH P	1	-	-
94584800	DN471B LED30S/840 PSU-E C WH P	-	-	-
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	-	-	-
98305500	DN470B LED20S/840 WIA-E C WH P	-	-	0
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	-	-	0
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-	-	0
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-	-	0
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-	-	0
01307000	DN470B LED20S/840 PSD-E C WH P	-	-	0
38470800	DN472B LED20S/830 PSU-E C WH PCC P	1	-	-

Order Code	Full Product Name	Number of light sources	Optic type	Upward light output ratio
38471500	DN472B LED20S/840 PSU-E C WH PCC P	1	-	-
79327200	DN470B LED20S/830 PSU-E C WH P	1	-	-
79328900	DN470B LED20S/840 PSU-E C WH P	1	-	-
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	1	-	-
94575600	DN470B LED30S/830 PSU-E C WH P	-	-	-
94576300	DN470B LED30S/840 PSU-E C WH P	-	-	-
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	-	-	-
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	-	-	0
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	-	-	0
01304900	DN460B LED11S/840 PSD-E C WH P	-	-	0
38462300	DN462B LED11S/830 PSU-E C WH PCC P	1	-	-

Order Code	Full Product Name	Number of light sources	Optic type	Upward light output ratio
38463000	DN462B LED11S/840 PSU-E C PCC WH P	1	-	-
79319700	DN460B LED11S/830 PSU-E C WH P	1	-	-
79320300	DN460B LED11S/840 PSU-E C WH P	1	-	-
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	1	-	-
79336400	DN462B LED11S/840 PSU-E C WH PCO P	1	-	-
79347000	DN472B LED20S/830 PSU-E C WH PCO P	1	-	-
79348700	DN472B LED20S/840 PSU-E C WH PCO P	1	-	-
56409100	TCTT225 20S/840 PSU-E WH	-	Beam angle 90°	-
56410700	TCTT230 20S/840 PSU-E WH	-	Beam angle 90°	-

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
01306300	DN461B LED11S/840 PSD-E C WH P	220-240 V	8.2 W	Yes
38467800	DN463B LED11S/840 PSU-E C WH PCC P	220 to 240 V	8.2 W	Yes
79324100	DN461B LED11S/840 PSU-E C WH P	220-240 V	8.2 W	Yes
98309300	DN471B LED20S/840 WIA-E C WH P	220-240 V	13.2 W	Yes
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	220-240 V	13.7 W	Yes
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	220-240 V	13.7 W	Yes
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	220-240 V	20.9 W	Yes
01309400	DN471B LED20S/830 PSD-E C WH P	220-240 V	13.5 W	Yes
01310000	DN471B LED20S/840 PSD-E C WH P	220-240 V	13.5 W	Yes
38475300	DN473B LED20S/840 PSU-E C WH PCC P	220 to 240 V	13.3 W	Yes
79331900	DN471B LED20S/830 PSU-E C WH P	220-240 V	13.3 W	Yes
79332600	DN471B LED20S/840 PSU-E C WH P	220-240 V	13.3 W	Yes
94584800	DN471B LED30S/840 PSU-E C WH P	220-240 V	20.9 W	Yes

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	220-240 V	20.9 W	Yes
98305500	DN470B LED20S/840 WIA-E C WH P	220-240 V	13.2 W	Yes
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	220-240 V	20.9 W	Yes
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	220-240 V	13.7 W	Yes
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	220-240 V	20.9 W	Yes
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	220-240 V	20.9 W	Yes
01307000	DN470B LED20S/840 PSD-E C WH P	220-240 V	13.5 W	Yes
38470800	DN472B LED20S/830 PSU-E C WH PCC P	220 to 240 V	13.3 W	Yes
38471500	DN472B LED20S/840 PSU-E C WH PCC P	220 to 240 V	13.3 W	Yes
79327200	DN470B LED20S/830 PSU-E C WH P	220-240 V	13.3 W	Yes
79328900	DN470B LED20S/840 PSU-E C WH P	220-240 V	13.3 W	Yes
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	220-240 V	13.3 W	Yes
94575600	DN470B LED30S/830 PSU-E C WH P	220-240 V	20.9 W	Yes

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
94576300	DN470B LED30S/840 PSU-E C WH P	220-240 V	20.9 W	Yes
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	220-240 V	20.9 W	Yes
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	220-240 V	8.6 W	Yes
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	220-240 V	8.6 W	Yes
01304900	DN460B LED11S/840 PSD-E C WH P	220-240 V	8.2 W	Yes
38462300	DN462B LED11S/830 PSU-E C WH PCC P	220 to 240 V	8.2 W	Yes
38463000	DN462B LED11S/840 PSU-E C PCC WH P	220 to 240 V	8.2 W	Yes
79319700	DN460B LED11S/830 PSU-E C WH P	220-240 V	8.2 W	Yes

Order Code	Full Product Name	Input Voltage	Power Consumption	Suitable for random switching
79320300	DN460B LED11S/840 PSU-E C WH P	220-240 V	8.2 W	Yes
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	220-240 V	8.2 W	Yes
79336400	DN462B LED11S/840 PSU-E C WH PCO P	220-240 V	8.2 W	Yes
79347000	DN472B LED20S/830 PSU-E C WH PCO P	220-240 V	13.3 W	Yes
79348700	DN472B LED20S/840 PSU-E C WH PCO P	220-240 V	13.3 W	Yes
56409100	TCTT225 20S/840 PSU-E WH	220/240 V	13.3 W	No
56410700	TCTT230 20S/840 PSU-E WH	220/240 V	13.3 W	No

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
01306300	DN461B LED11S/840 PSD-E C WH P	Yes	1%
38467800	DN463B LED11S/840 PSU-E C WH PCC P	No	Not applicable
79324100	DN461B LED11S/840 PSU-E C WH P	No	Not applicable
98309300	DN471B LED20S/840 WIA-E C WH P	Yes	1%
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	Yes	1%
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	Yes	1%
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	Yes	1%
01309400	DN471B LED20S/830 PSD-E C WH P	Yes	1%
01310000	DN471B LED20S/840 PSD-E C WH P	Yes	1%
38475300	DN473B LED20S/840 PSU-E C WH PCC P	No	Not applicable
79331900	DN471B LED20S/830 PSU-E C WH P	No	Not applicable
79332600	DN471B LED20S/840 PSU-E C WH P	No	Not applicable
94584800	DN471B LED30S/840 PSU-E C WH P	No	Not applicable
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	No	Not applicable
98305500	DN470B LED20S/840 WIA-E C WH P	Yes	1%
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	Yes	1%
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	Yes	1%
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	Yes	1%
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	Yes	1%
01307000	DN470B LED20S/840 PSD-E C WH P	Yes	1%

Order Code	Full Product Name	Dimmable	Maximum dim level
38470800	DN472B LED20S/830 PSU-E C WH PCC P	No	Not applicable
38471500	DN472B LED20S/840 PSU-E C WH PCC P	No	Not applicable
79327200	DN470B LED20S/830 PSU-E C WH P	No	Not applicable
79328900	DN470B LED20S/840 PSU-E C WH P	No	Not applicable
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	No	Not applicable
94575600	DN470B LED30S/830 PSU-E C WH P	No	Not applicable
94576300	DN470B LED30S/840 PSU-E C WH P	No	Not applicable
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	No	Not applicable
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	Yes	1%
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	Yes	1%
01304900	DN460B LED11S/840 PSD-E C WH P	Yes	1%
38462300	DN462B LED11S/830 PSU-E C WH PCC P	No	Not applicable
38463000	DN462B LED11S/840 PSU-E C PCC WH P	No	Not applicable
79319700	DN460B LED11S/830 PSU-E C WH P	No	Not applicable
79320300	DN460B LED11S/840 PSU-E C WH P	No	Not applicable
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	No	Not applicable
79336400	DN462B LED11S/840 PSU-E C WH PCO P	No	Not applicable
79347000	DN472B LED20S/830 PSU-E C WH PCO P	No	Not applicable
79348700	DN472B LED20S/840 PSU-E C WH PCO P	No	Not applicable
56409100	TCTT225 20S/840 PSU-E WH	No	-
56410700	TCTT230 20S/840 PSU-E WH	No	-

Mechanical and Housing

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
01306300	DN461B LED11S/840 PSD-E C WH P	IK02	IP20
38467800	DN463B LED11S/840 PSU-E C WH PCC P	IK06	IP20/54
79324100	DN461B LED11S/840 PSU-E C WH P	IK02	IP20
98309300	DN471B LED20S/840 WIA-E C WH P	IK02	IP20
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	IK02	IP20
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	IK02	IP20
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	IK02	IP20
01309400	DN471B LED20S/830 PSD-E C WH P	IK02	IP20
01310000	DN471B LED20S/840 PSD-E C WH P	IK02	IP20
38475300	DN473B LED20S/840 PSU-E C WH PCC P	IK06	IP20/54
79331900	DN471B LED20S/830 PSU-E C WH P	IK02	IP20
79332600	DN471B LED20S/840 PSU-E C WH P	IK02	IP20
94584800	DN471B LED30S/840 PSU-E C WH P	IK02	IP20
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	IK02	IP20
98305500	DN470B LED20S/840 WIA-E C WH P	IK02	IP20
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	IK02	IP20
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	IK02	IP20
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	IK02	IP20
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	IK02	IP20/54
01307000	DN470B LED20S/840 PSD-E C WH P	IK02	IP20
38470800	DN472B LED20S/830 PSU-E C WH PCC P	IK06	IP20/54

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
38471500	DN472B LED20S/840 PSU-E C WH PCC P	IK06	IP20/54
79327200	DN470B LED20S/830 PSU-E C WH P	IK02	IP20
79328900	DN470B LED20S/840 PSU-E C WH P	IK02	IP20
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	IK02	IP20
94575600	DN470B LED30S/830 PSU-E C WH P	IK02	IP20
94576300	DN470B LED30S/840 PSU-E C WH P	IK02	IP20
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	IK02	IP20
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	IK02	IP20
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	IK02	IP20
01304900	DN460B LED11S/840 PSD-E C WH P	IK02	IP20
38462300	DN462B LED11S/830 PSU-E C WH PCC P	IK06	IP20/54
38463000	DN462B LED11S/840 PSU-E C PCC WH P	IK06	IP20/54
79319700	DN460B LED11S/830 PSU-E C WH P	IK02	IP20
79320300	DN460B LED11S/840 PSU-E C WH P	IK02	IP20
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	IK02	IP20
79336400	DN462B LED11S/840 PSU-E C WH PCO P	IK06	IP20/54
79347000	DN472B LED20S/830 PSU-E C WH PCO P	IK06	IP20/54
79348700	DN472B LED20S/840 PSU-E C WH PCO P	IK06	IP20/54
56409100	TCCT225 20S/840 PSU-E WH	IK02	IP20
56410700	TCCT230 20S/840 PSU-E WH	IK02	IP20

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
01306300	DN461B LED11S/840 PSD-E C WH P	No	-	-
38467800	DN463B LED11S/840 PSU-E C WH PCC P	No	-	-
79324100	DN461B LED11S/840 PSU-E C WH P	No	-	-
98309300	DN471B LED20S/840 WIA-E C WH P	No	-	-
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	No	-	-
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	No	-	-
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	No	-	-
01309400	DN471B LED20S/830 PSD-E C WH P	No	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
01310000	DN471B LED20S/840 PSD-E C WH P	No	-	-
38475300	DN473B LED20S/840 PSU-E C WH PCC P	No	-	-
79331900	DN471B LED20S/830 PSU-E C WH P	No	-	-
79332600	DN471B LED20S/840 PSU-E C WH P	No	-	-
94584800	DN471B LED30S/840 PSU-E C WH P	No	-	-
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
98305500	DN470B LED20S/840 WIA-E C WH P	No	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
98321500	DN470B LED30S/840 DIA- VLC-E C WH P	No	-	-
98332100	DN472B LED20S/840 DIA- VLC-E C WH PCC P	No	-	-
98334500	DN472B LED30S/830 DIA- VLC-E C WH PCC P	No	-	-
98335200	DN472B LED30S/840 DIA- VLC-E C WH PCC P	No	-	-
01307000	DN470B LED20S/840 PSD- E C WH P	No	-	-
38470800	DN472B LED20S/830 PSU- E C WH PCC P	No	-	-
38471500	DN472B LED20S/840 PSU- E C WH PCC P	No	-	-
79327200	DN470B LED20S/830 PSU- E C WH P	No	-	-
79328900	DN470B LED20S/840 PSU- E C WH P	No	-	-
79352400	DN470B LED20S/840 PSU- E C ELP3 WH P	No	Emergency lighting 3 hours duration Pro version	3 hour(s)
94575600	DN470B LED30S/830 PSU- E C WH P	No	-	-
94576300	DN470B LED30S/840 PSU- E C WH P	No	-	-
94592300	DN470B LED30S/840 PSU- E C ELP3 WH P	No	Emergency lighting 3	3 hour(s)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Rated duration of the emergency lighting (when fully charged)
			hours duration Pro version	
98292800	DN462B LED11S/830 DIA- VLC-E C WH PCC P	No	-	-
98294200	DN462B LED11S/840 DIA- VLC-E C WH PCC P	No	-	-
01304900	DN460B LED11S/840 PSD- E C WH P	No	-	-
38462300	DN462B LED11S/830 PSU-E C WH PCC P	No	-	-
38463000	DN462B LED11S/840 PSU-E C PCC WH P	No	-	-
79319700	DN460B LED11S/830 PSU- E C WH P	No	-	-
79320300	DN460B LED11S/840 PSU- E C WH P	No	-	-
79340100	DN460B LED11S/840 PSU- E C ELP3 WH P	-	Emergency lighting 3 hours duration Pro version	3 hour(s)
79336400	DN462B LED11S/840 PSU-E C WH PCO P	No	-	-
79347000	DN472B LED20S/830 PSU- E C WH PCO P	No	-	-
79348700	DN472B LED20S/840 PSU- E C WH PCO P	No	-	-
56409100	TCTT225 20S/840 PSU-E WH	No	-	-
56410700	TCTT230 20S/840 PSU-E WH	No	-	-

Approval and Application (1/2)

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
01306300	DN461B LED11S/840 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	-
38467800	DN463B LED11S/840	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
	PSU-E C WH PCC P				
79324100	DN461B LED11S/840 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
98309300	DN471B LED20S/840 WIA-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
01309400	DN471B LED20S/830 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	-
01310000	DN471B LED20S/840 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	-
38475300	DN473B LED20S/840 PSU-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79331900	DN471B LED20S/830 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79332600	DN471B LED20S/840 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
94584800	DN471B LED30S/840 PSU-E C WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
98305500	DN470B LED20S/840 WIA-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
01307000	DN470B LED20S/840 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	-
38470800	DN472B LED20S/830 PSU-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
38471500	DN472B LED20S/840 PSU-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79327200	DN470B LED20S/830 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79328900	DN470B LED20S/840 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
94575600	DN470B LED30S/830 PSU-E C WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
94576300	DN470B LED30S/840 PSU-E C WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	+10 to +40 °C	-	Temperature 750 °C, duration 30 s	-
98292800	DN462B LED11S/830	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
	DIA-VLC-E C WH PCC P				
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
01304900	DN460B LED11S/840 PSD-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	-
38462300	DN462B LED11S/830 PSU-E C WH PCC P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
38463000	DN462B LED11S/840 PSU-E C PCC WH P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79319700	DN460B LED11S/830 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 650 °C, duration 30 s	-
79320300	DN460B LED11S/840 PSU-E C WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-

Order Code	Full Product Name	Ambient temperature range	ENEC mark	Glow-wire test	Flickering value (PstLM) - Flickering value as per EN 61000-3-3
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79336400	DN462B LED11S/840 PSU-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79347000	DN472B LED20S/830 PSU-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
79348700	DN472B LED20S/840 PSU-E C WH PCO P	-15 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	-
56409100	TCTT225 20S/840 PSU-E WH	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	1
56410700	TCTT230 20S/840 PSU-E WH	+10 to +40 °C	ENEC mark	Temperature 750 °C, duration 30 s	1

Approval and Application (2/2)

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
01306300	DN461B LED11S/840 PSD-E C WH P	0.4
38467800	DN463B LED11S/840 PSU-E C WH PCC P	-
79324100	DN461B LED11S/840 PSU-E C WH P	-
98309300	DN471B LED20S/840 WIA-E C WH P	-
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	-
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	-
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	-
01309400	DN471B LED20S/830 PSD-E C WH P	0.4
01310000	DN471B LED20S/840 PSD-E C WH P	0.4
38475300	DN473B LED20S/840 PSU-E C WH PCC P	-
79331900	DN471B LED20S/830 PSU-E C WH P	-
79332600	DN471B LED20S/840 PSU-E C WH P	-
94584800	DN471B LED30S/840 PSU-E C WH P	-
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	-
98305500	DN470B LED20S/840 WIA-E C WH P	-
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	-
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-
01307000	DN470B LED20S/840 PSD-E C WH P	0.4
38470800	DN472B LED20S/830 PSU-E C WH PCC P	-
38471500	DN472B LED20S/840 PSU-E C WH PCC P	-
79327200	DN470B LED20S/830 PSU-E C WH P	-
79328900	DN470B LED20S/840 PSU-E C WH P	-
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	-
94575600	DN470B LED30S/830 PSU-E C WH P	-
94576300	DN470B LED30S/840 PSU-E C WH P	-
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	-
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	-
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	-
01304900	DN460B LED11S/840 PSD-E C WH P	0.4
38462300	DN462B LED11S/830 PSU-E C WH PCC P	-
38463000	DN462B LED11S/840 PSU-E C PCC WH P	-
79319700	DN460B LED11S/830 PSU-E C WH P	0.4
79320300	DN460B LED11S/840 PSU-E C WH P	-
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	-

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
79336400	DN462B LED11S/840 PSU-E C WH PCO P	-
79347000	DN472B LED20S/830 PSU-E C WH PCO P	-
79348700	DN472B LED20S/840 PSU-E C WH PCO P	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
01306300	DN461B LED11S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
38467800	DN463B LED11S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3	+/-10%
79324100	DN461B LED11S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
98309300	DN471B LED20S/840 WIA-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	(0.43, 0.40) SDCM<3	+/-10%
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
01309400	DN471B LED20S/830 PSD-E C WH P	(0.43, 0.40) SDCM<3	+/-10%
01310000	DN471B LED20S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
38475300	DN473B LED20S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3	+/-10%
79331900	DN471B LED20S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3	+/-10%
79332600	DN471B LED20S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
94584800	DN471B LED30S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3	+/-10%
98305500	DN470B LED20S/840 WIA-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3	+/-10%
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3	+/-10%
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3	+/-10%
01307000	DN470B LED20S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
38470800	DN472B LED20S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3	+/-10%
38471500	DN472B LED20S/840 PSU-E C WH PCC P	(0.38, 0.38) SDCM<3	+/-10%

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
01306300	DN461B LED11S/840 PSD-E C WH P	-

Order Code	Full Product Name	Stroboscopic effect visibility measure (SVM)
56409100	TCTT225 20S/840 PSU-E WH	0.4
56410700	TCTT230 20S/840 PSU-E WH	0.4

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
79327200	DN470B LED20S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3	+/-10%
79328900	DN470B LED20S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3	+/-10%
94575600	DN470B LED30S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3	+/-10%
94576300	DN470B LED30S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3	+/-10%
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	(0.43, 0.40) SDCM<3	+/-10%
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	(0.38, 0.38) SDCM<3	+/-10%
01304900	DN460B LED11S/840 PSD-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
38462300	DN462B LED11S/830 PSU-E C WH PCC P	(0.44, 0.40) SDCM<3	+/-10%
38463000	DN462B LED11S/840 PSU-E C PCC WH P	(0.38, 0.38) SDCM<3	+/-10%
79319700	DN460B LED11S/830 PSU-E C WH P	(0.43, 0.40) SDCM<3	+/-10%
79320300	DN460B LED11S/840 PSU-E C WH P	(0.38, 0.38) SDCM<3	+/-10%
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	(0.38, 0.38) SDCM<3	+/-10%
79336400	DN462B LED11S/840 PSU-E C WH PCO P	(0.38, 0.38) SDCM<3	+/-10%
79347000	DN472B LED20S/830 PSU-E C WH PCO P	(0.43, 0.40) SDCM<3	+/-10%
79348700	DN472B LED20S/840 PSU-E C WH PCO P	(0.38, 0.38) SDCM<3	+/-10%
56409100	TCTT225 20S/840 PSU-E WH	(0.38, 0.38) SDCM < 3	-10% / +10%
56410700	TCTT230 20S/840 PSU-E WH	(0.38, 0.38) SDCM < 3	-10% / +10%

Order Code	Full Product Name	Driver failure rate at 5000	
		h	
79324100	DN461B LED11S/840 PSU-E C WH P	1 %	
98309300	DN471B LED20S/840 WIA-E C WH P	-	
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	-	
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	-	
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	-	
01309400	DN471B LED20S/830 PSD-E C WH P	-	
01310000	DN471B LED20S/840 PSD-E C WH P	-	
38475300	DN473B LED20S/840 PSU-E C WH PCC P	1 %	
79331900	DN471B LED20S/830 PSU-E C WH P	1 %	
79332600	DN471B LED20S/840 PSU-E C WH P	1 %	
94584800	DN471B LED30S/840 PSU-E C WH P	1 %	
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	1 %	
98305500	DN470B LED20S/840 WIA-E C WH P	-	
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	-	
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	-	
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	-	
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	-	
01307000	DN470B LED20S/840 PSD-E C WH P	-	
38470800	DN472B LED20S/830 PSU-E C WH PCC P	1 %	
38471500	DN472B LED20S/840 PSU-E C WH PCC P	1 %	


Order Code	Full Product Name	Driver failure rate at 5000	
		h	
79327200	DN470B LED20S/830 PSU-E C WH P	1 %	
79328900	DN470B LED20S/840 PSU-E C WH P	1 %	
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	1 %	
94575600	DN470B LED30S/830 PSU-E C WH P	1 %	
94576300	DN470B LED30S/840 PSU-E C WH P	1 %	
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	1 %	
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	-	
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	-	
01304900	DN460B LED11S/840 PSD-E C WH P	-	
38462300	DN462B LED11S/830 PSU-E C WH PCC P	1 %	
38463000	DN462B LED11S/840 PSU-E C PCC WH P	1 %	
79319700	DN460B LED11S/830 PSU-E C WH P	1 %	
79320300	DN460B LED11S/840 PSU-E C WH P	1 %	
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	1 %	
79336400	DN462B LED11S/840 PSU-E C WH PCO P	1 %	
79347000	DN472B LED20S/830 PSU-E C WH PCO P	1 %	
79348700	DN472B LED20S/840 PSU-E C WH PCO P	1 %	
56409100	TCTT225 20S/840 PSU-E WH	-	
56410700	TCTT230 20S/840 PSU-E WH	-	

Product Data


Order Code	Full Product Name	Product family code
01306300	DN461B LED11S/840 PSD-E C WH P	DN461B
38467800	DN463B LED11S/840 PSU-E C WH PCC P	DN463B
79324100	DN461B LED11S/840 PSU-E C WH P	DN461B
98309300	DN471B LED20S/840 WIA-E C WH P	DN471B
98323900	DN471B LED20S/830 DIA-VLC-E C WH P	DN471B
98325300	DN471B LED20S/840 DIA-VLC-E C WH P	DN471B
98329100	DN471B LED30S/840 DIA-VLC-E C WH P	DN471B
01309400	DN471B LED20S/830 PSD-E C WH P	DN471B
01310000	DN471B LED20S/840 PSD-E C WH P	DN471B
38475300	DN473B LED20S/840 PSU-E C WH PCC P	DN473B
79331900	DN471B LED20S/830 PSU-E C WH P	DN471B
79332600	DN471B LED20S/840 PSU-E C WH P	DN471B
94584800	DN471B LED30S/840 PSU-E C WH P	DN471B
94596100	DN471B LED30S/840 PSU-E C ELP3 WH P	DN471B
98305500	DN470B LED20S/840 WIA-E C WH P	DN470B
98321500	DN470B LED30S/840 DIA-VLC-E C WH P	DN470B
98332100	DN472B LED20S/840 DIA-VLC-E C WH PCC P	DN472B
98334500	DN472B LED30S/830 DIA-VLC-E C WH PCC P	DN472B
98335200	DN472B LED30S/840 DIA-VLC-E C WH PCC P	DN472B
01307000	DN470B LED20S/840 PSD-E C WH P	DN470B
38470800	DN472B LED20S/830 PSU-E C WH PCC P	DN472B

Order Code	Full Product Name	Product family code
38471500	DN472B LED20S/840 PSU-E C WH PCC P	DN472B
79327200	DN470B LED20S/830 PSU-E C WH P	DN470B
79328900	DN470B LED20S/840 PSU-E C WH P	DN470B
79352400	DN470B LED20S/840 PSU-E C ELP3 WH P	DN470B
94575600	DN470B LED30S/830 PSU-E C WH P	DN470B
94576300	DN470B LED30S/840 PSU-E C WH P	DN470B
94592300	DN470B LED30S/840 PSU-E C ELP3 WH P	DN470B
98292800	DN462B LED11S/830 DIA-VLC-E C WH PCC P	DN462B
98294200	DN462B LED11S/840 DIA-VLC-E C WH PCC P	DN462B
01304900	DN460B LED11S/840 PSD-E C WH P	DN460B
38462300	DN462B LED11S/830 PSU-E C WH PCC P	DN462B
38463000	DN462B LED11S/840 PSU-E C PCC WH P	DN462B
79319700	DN460B LED11S/830 PSU-E C WH P	DN460B
79320300	DN460B LED11S/840 PSU-E C WH P	DN460B
79340100	DN460B LED11S/840 PSU-E C ELP3 WH P	DN460B
79336400	DN462B LED11S/840 PSU-E C WH PCO P	DN462B
79347000	DN472B LED20S/830 PSU-E C WH PCO P	DN472B
79348700	DN472B LED20S/840 PSU-E C WH PCO P	DN472B
56409100	TCTT225 20S/840 PSU-E WH	-
56410700	TCTT230 20S/840 PSU-E WH	-


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 910505102113




Polar Normal (separate) - DN460BN - 910505102285




Polar Normal (separate) - DN460BN - 910505102110




Polar Normal (separate) - DN460BN - 910505102291




Polar Normal (separate) - DN460BN - 910505102102




Polar Normal (separate) - DN460BN - 910505102106



Polar Normal (separate) - DN460BN - 910505102104




Polar Normal (separate) - DN460BN - 910505102089




Polar Normal (separate) - DN460BN - 910505102287


Polar Wide Diagrams




**Polar Normal (separate) - DN460BN -
910505102115**




**Polar Normal (separate) - DN460BN -
910505102116**




**Polar Normal (separate) - DN460BN -
910505102290**




Polar Normal (separate) - DN460BN - 910505102074




**Polar Normal (separate) - DN460BN -
910505102085**




**Polar Normal (separate) - DN460BN -
910505102288**



Polar Normal (separate) - DN460BN - 912500100062




Polar Normal (separate) - DN460BN - 912500100070




**Polar Normal (separate) - DN460BN -
912500100071**


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 912500100063




Polar Normal (separate) - DN460BN - 912500100075




Polar Normal (separate) - DN460BN - 912500100067




Polar Normal (separate) - DN460BN - 912500100515




Polar Normal (separate) - DN460BN - 912500100519




Polar Normal (separate) - DN460BN - 912500100522



Polar Normal (separate) - DN460BN - 912500100523




Polar Normal (separate) - DN460BN - 912500100514




Polar Normal (separate) - DN460BN - 912500100527


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 912500100531




Polar Normal (separate) - DN460BN - 912500100526




Polar Normal (separate) - DN460BN - 912500100535




Polar Normal (separate) - DN460BN - 912500100543




Polar Normal (separate) - DN460BN - 912500100542




Polar Normal (separate) - DN460BN - 912500100547



Polar Normal (separate) - DN460BN - 912500101315




Polar Normal (separate) - DN460BN - 912500101307




Polar Normal (separate) - DN460BN - 912500101323


Polar Wide Diagrams




Polar Normal (separate) - DN460BN - 912500101305




Polar Normal (separate) - DN460BN - 912500101327



Polar Normal (separate) - DN460BN - 910505102072



Polar Normal (separate) - TCTTPFI - 912500102954



Polar Normal (separate) - TCTTPFI - 912500102953

