



# Philips LuxSpace Mini, recessed – high efficiency, visual comfort and a stylish design

## LuxSpace Mini, recessed

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also user costs where they see much bigger impact on return. Therefore, LuxSpace is designed to provide the perfect combination of efficiency, visual comfort and design, without compromising on lighting performance (color rendering and light distribution). It offers a wide choice of options for creating the desired ambience to support user comfort, no matter the application is.

### Benefits

- Best-in-class efficacy with up to 150lm/W
- Creates a gentle, natural light, ensuring visual comfort
- Perfect ceiling integration with narrow rim or rimless version for plaster ceilings
- Improved glare control with office compliancy
- Provides uniform lighting thanks to wide light distribution

## LuxSpace Mini, recessed

### Features

- Mini version for recessed with 150mm cut-out diameter (DN560B/DN561B)
- Choice of four optics: high-gloss, faceted, matt and white
- UGR19 and UGR22 versions with different product heights
- Selection of colors: High-gloss metalized, white (RAL9003), grey (RAL9006), black (RAL9004) as standard (any other RAL color possible upon request)
- Compliant for central emergency lighting with DC (upon request)
- Multiple additional options: Emergency lighting (single battery 3 hours), through-wiring, Eca and B2ca cable & connector options
- Extended useful lifetime 50,000 hours at L90

### Application


- Offices
- Retail
- Hospitals and Care Centers
- Hospitality

### Versions




IPPR\_DN560Bi\_0009-Product photo

### Dimensional drawing



# LuxSpace Mini, recessed

## Polar Wide Diagrams



Polar Normal (separate) - DN560BI -  
910505100917

