



LuxSpace surface-mounted – high efficiency, visual comfort and a stylish design

LuxSpace, surface mounted

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

Benefits

- Product which delivers visual comfort and stylish design
- Creates a gentle, natural light, ensuring visual comfort

Features

- Choice of four optics: high-gloss, faceted, matt and white
- Heights: deep (up to UGR 19), low (up to UGR 22)
- Light color: 830, 840, 927, 930 and 940 (CRI90 versions upon request)
- Colors: high-gloss metalized, white (RAL9003), grey (RAL9006), black (RAL9004) as standard (any other RAL color possible upon request)
- Compliant for central emergency lighting with DC (upon request)
- 3C track and pendant version (upon request)

LuxSpace, surface mounted

Application


- Offices
- Retail
- Hospitals
- Hotels
- Airports

Versions



LuxSpace surface mounted-DN570C D250

Dimensional drawing



LuxSpace, surface mounted

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Optic type	-
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +25 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
910505100959	DN570C LED20S/830 PSU-E C WH	3000 K	134 lm/W	2,200 lm
910505100960	DN570C LED20S/840 PSU-E C WH	4000 K	149 lm/W	2,200 lm
910505100961	DN571C LED20S/830 PSU-E C WH	3000 K	134 lm/W	2,200 lm
910505100962	DN571C LED20S/840 PSU-E C WH	4000 K	149 lm/W	2,200 lm
910505100963	DN570C LED20S/830 DIA-VLC-E C WH	3000 K	134 lm/W	2,200 lm
910505100964	DN570C LED20S/840 DIA-VLC-E C WH	4000 K	149 lm/W	2,200 lm
910505100965	DN571C LED20S/830 DIA-VLC-E C WH	3000 K	134 lm/W	2,200 lm
910505100966	DN571C LED20S/840 DIA-VLC-E C WH	4000 K	149 lm/W	2,200 lm
910505100967	DN570C LED24S/830 PSU-E C WH	3000 K	130 lm/W	2,600 lm
910505100968	DN570C LED24S/840 PSU-E C WH	4000 K	141 lm/W	2,600 lm
910505100969	DN570C LED24S/830 DIA-VLC-E C WH	3000 K	130 lm/W	2,600 lm
910505100970	DN570C LED24S/840 DIA-VLC-E C WH	4000 K	141 lm/W	2,600 lm
910505100971	DN571C LED24S/830 DIA-VLC-E C WH	3000 K	130 lm/W	2,600 lm
910505100972	DN571C LED24S/840 DIA-VLC-E C WH	4000 K	141 lm/W	2,600 lm
910505100973	DN570C LED40S/830 PSU-E C WH	3000 K	133 lm/W	4,400 lm
910505100974	DN570C LED40S/840 PSU-E C WH	4000 K	147 lm/W	4,400 lm
910505100975	DN570C LED40S/830 DIA-VLC-E C WH	3000 K	133 lm/W	4,400 lm
910505100976	DN570C LED40S/840 DIA-VLC-E C WH	4000 K	147 lm/W	4,400 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
910505100959	DN570C LED20S/830 PSU-E C WH	16.4 W	910505100968	DN570C LED24S/840 PSU-E C WH	18.4 W
910505100960	DN570C LED20S/840 PSU-E C WH	14.8 W	910505100969	DN570C LED24S/830 DIA-VLC-E C WH	20 W
910505100961	DN571C LED20S/830 PSU-E C WH	16.4 W	910505100970	DN570C LED24S/840 DIA-VLC-E C WH	18.4 W
910505100962	DN571C LED20S/840 PSU-E C WH	14.8 W	910505100971	DN571C LED24S/830 DIA-VLC-E C WH	20 W
910505100963	DN570C LED20S/830 DIA-VLC-E C WH	16.4 W	910505100972	DN571C LED24S/840 DIA-VLC-E C WH	18.4 W
910505100964	DN570C LED20S/840 DIA-VLC-E C WH	14.8 W	910505100973	DN570C LED40S/830 PSU-E C WH	33 W
910505100965	DN571C LED20S/830 DIA-VLC-E C WH	16.4 W	910505100974	DN570C LED40S/840 PSU-E C WH	30 W
910505100966	DN571C LED20S/840 DIA-VLC-E C WH	14.8 W	910505100975	DN570C LED40S/830 DIA-VLC-E C WH	33 W
910505100967	DN570C LED24S/830 PSU-E C WH	20 W	910505100976	DN570C LED40S/840 DIA-VLC-E C WH	30 W

Controls and Dimming

LuxSpace, surface mounted

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910505100959	DN570C LED20S/830 PSU-E C WH	No	-
910505100960	DN570C LED20S/840 PSU-E C WH	No	-
910505100961	DN571C LED20S/830 PSU-E C WH	No	-
910505100962	DN571C LED20S/840 PSU-E C WH	No	-
910505100963	DN570C LED20S/830 DIA-VLC-E C WH	Yes	1%
910505100964	DN570C LED20S/840 DIA-VLC-E C WH	Yes	1%
910505100965	DN571C LED20S/830 DIA-VLC-E C WH	Yes	1%
910505100966	DN571C LED20S/840 DIA-VLC-E C WH	Yes	1%
910505100967	DN570C LED24S/830 PSU-E C WH	No	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505100959	DN570C LED20S/830 PSU-E C WH	(0.43, 0.40) SDCM <2
910505100960	DN570C LED20S/840 PSU-E C WH	(0.38, 0.38) SDCM <2
910505100961	DN571C LED20S/830 PSU-E C WH	(0.43, 0.40) SDCM <2
910505100962	DN571C LED20S/840 PSU-E C WH	(0.38, 0.38) SDCM <2
910505100963	DN570C LED20S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM <2
910505100964	DN570C LED20S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM <2
910505100965	DN571C LED20S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM <2
910505100966	DN571C LED20S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM <2
910505100967	DN570C LED24S/830 PSU-E C WH	(0.43, 0.40) SDCM <2

Product Data




Order Code	Full Product Name	Product family code
910505100959	DN570C LED20S/830 PSU-E C WH	DN570C
910505100960	DN570C LED20S/840 PSU-E C WH	DN570C
910505100961	DN571C LED20S/830 PSU-E C WH	DN571C
910505100962	DN571C LED20S/840 PSU-E C WH	DN571C
910505100963	DN570C LED20S/830 DIA-VLC-E C WH	DN570C
910505100964	DN570C LED20S/840 DIA-VLC-E C WH	DN570C
910505100965	DN571C LED20S/830 DIA-VLC-E C WH	DN571C
910505100966	DN571C LED20S/840 DIA-VLC-E C WH	DN571C
910505100967	DN570C LED24S/830 PSU-E C WH	DN570C

Order Code	Full Product Name	Maximum dim	
		Dimmable	level
910505100968	DN570C LED24S/840 PSU-E C WH	No	-
910505100969	DN570C LED24S/830 DIA-VLC-E C WH	Yes	1%
910505100970	DN570C LED24S/840 DIA-VLC-E C WH	Yes	1%
910505100971	DN571C LED24S/830 DIA-VLC-E C WH	Yes	1%
910505100972	DN571C LED24S/840 DIA-VLC-E C WH	Yes	1%
910505100973	DN570C LED40S/830 PSU-E C WH	No	-
910505100974	DN570C LED40S/840 PSU-E C WH	No	-
910505100975	DN570C LED40S/830 DIA-VLC-E C WH	Yes	1%
910505100976	DN570C LED40S/840 DIA-VLC-E C WH	Yes	1%

Order Code	Full Product Name	Initial chromaticity
910505100968	DN570C LED24S/840 PSU-E C WH	(0.38, 0.38) SDCM <2
910505100969	DN570C LED24S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM <2
910505100970	DN570C LED24S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM <2
910505100971	DN571C LED24S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM <2
910505100972	DN571C LED24S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM <2
910505100973	DN570C LED40S/830 PSU-E C WH	(0.43, 0.40) SDCM <2
910505100974	DN570C LED40S/840 PSU-E C WH	(0.38, 0.38) SDCM <2
910505100975	DN570C LED40S/830 DIA-VLC-E C WH	(0.43, 0.40) SDCM <2
910505100976	DN570C LED40S/840 DIA-VLC-E C WH	(0.38, 0.38) SDCM <2

Order Code	Full Product Name	Product family code
910505100968	DN570C LED24S/840 PSU-E C WH	DN570C
910505100969	DN570C LED24S/830 DIA-VLC-E C WH	DN570C
910505100970	DN570C LED24S/840 DIA-VLC-E C WH	DN570C
910505100971	DN571C LED24S/830 DIA-VLC-E C WH	DN571C
910505100972	DN571C LED24S/840 DIA-VLC-E C WH	DN571C
910505100973	DN570C LED40S/830 PSU-E C WH	DN570C
910505100974	DN570C LED40S/840 PSU-E C WH	DN570C
910505100975	DN570C LED40S/830 DIA-VLC-E C WH	DN570C
910505100976	DN570C LED40S/840 DIA-VLC-E C WH	DN570C




Polar Wide Diagrams



Polar Normal (separate) - DN570BI - 910505100959

Polar Normal (separate) - DN570BI - 910505100965




Polar Normal (separate) - DN570BI - 910505100968



Polar Normal (separate) - DN570BI - 910505100967

Polar Normal (separate) - DN570BI - 910505100969

Polar Normal (separate) - DN570BI - 910505100970




Polar Normal (separate) - DN570BI - 910505100962


Polar Normal (separate) - DN570BI - 910505100960

Polar Normal (separate) - DN570BI - 910505100973


Polar Wide Diagrams




Polar Normal (separate) - DN570BI - 910505100974




Polar Normal (separate) - DN570BI - 910505100966




Polar Normal (separate) - DN570BI - 910505100975




Polar Normal (separate) - DN570BI - 910505100972




Polar Normal (separate) - DN570BI - 910505100976




Polar Normal (separate) - DN570BI - 910505100971



Polar Normal (separate) - DN570BI - 910505100961



Polar Normal (separate) - DN570BI - 910505100964



Polar Normal (separate) - DN570BI - 910505100963

LuxSpace, surface mounted

