



LuxSpace square, recessed – high efficiency, visual comfort and a stylish design

LuxSpace square, recessed

Customers are looking to optimize all their resources, and that means not just their running costs (energy, etc.) but also their human resources. Energy savings are therefore a priority, but they must not have an adverse effect on the well-being of employees, who need a pleasant environment in order to be more productive, or on customers, who want to enjoy their shopping experience. LuxSpace provides the perfect combination of efficiency, light comfort and design, without compromising on lighting performance (color rendering and color uniformity). It offers a wide choice of options for creating the desired ambience, no matter the application.

Benefits

- Best-in-class efficacy
- Creates a gentle, natural light, ensuring visual comfort
- Perfect integration with the ceiling thanks to the thin, narrow rim; rimless version ideal for integration into plaster ceilings

LuxSpace square, recessed


Features

- Choice of four optics: high-gloss, faceted, matt and white
- Rim colors: high-gloss metalized, white (RAL9010), grey, black (RAL9004) as standard (any other RAL color possible upon request)
- Rimless version available
- Compliant for central emergency lighting with DC
- Multiple additional options: emergency lighting (single battery 3 hours), through-wiring

Application

- Offices
- Retail
- Hospitals
- Hotels
- Airports

Dimensional drawing



LuxSpace square, recessed

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>80
Optic type	-
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Yes
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +25 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Product Data	
Product family code	DN572B

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	
		Temperature (Nom)	(rated) (Nom)	Luminous Flux
910505100948	DN572B LED20S/840 PSU-E C WH	4000 K	149 lm/W	2,200 lm
910505100951	DN572B LED24S/830 PSU-E C WH	3000 K	130 lm/W	2,600 lm
910505100952	DN572B LED24S/840 PSU-E C WH	4000 K	141 lm/W	2,600 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505100948	DN572B LED20S/840 PSU-E C WH	14.8 W
910505100951	DN572B LED24S/830 PSU-E C WH	20 W


Order Code	Full Product Name	Power Consumption
910505100952	DN572B LED24S/840 PSU-E C WH	18.4 W

Initial Performance (IEC Compliant)


Order Code	Full Product Name	Initial chromaticity
910505100948	DN572B LED20S/840 PSU-E C WH	(0.38, 0.38) SDCM <2
910505100951	DN572B LED24S/830 PSU-E C WH	(0.43, 0.40) SDCM <2

Order Code	Full Product Name	Initial chromaticity
910505100952	DN572B LED24S/840 PSU-E C WH	(0.38, 0.38) SDCM <2


Polar Wide Diagrams



Polar Normal (separate) - DN572BI - 910505100951



Polar Normal (separate) - DN572BI - 910505100948



Polar Normal (separate) - DN572BI - 910505100952

