



Unrivalled performance, familiar shape

MasterColor CDM ED17 Protected Elite 4200K

MasterColor Elite Protected Ceramic Metal Halide ED-17 4200K Lamps provide excellent lumen maintenance and outstanding performance over time in a protected lamp.

Benefits

- Excellent color – Up to 93 CRI (color rendering index)
- Color stability over life within +/- 200 K
- Lamp to lamp color consistency over life
- High lamp efficacy
- Elite 50W lamp provides 29% more initial lumens as compared to a standard MasterColor Protected CMH ED-17 50W lamp*
- Elite 50W lamp provided 52% more mean lumens as compared to a standard MasterColor Protected CMH ED-17 50W lamp+
- * Philips MasterColor Elite Protected CMH ED-17 4200K 50W Lamps provide 4645 initial lumens compared to MasterColor Protected ED-17 50W lamp at 3600 initial lumens.
- + Philips MasterColor Elite Protected CMH ED-17 4200K 50W Lamps provide 3716 mean lumens compared to MasterColor Protected ED-17 50W lamp at 2450 mean lumens.

Features

- Application versatility
- Universal operating position
- Suitable for use in open fixtures
- Dimension, base and light center length are same as standard MasterColor ED-17 lamps
- Available in 50W, 70 W and 100W Elite lamps

MasterColor CDM ED17 Protected Elite 4200K


Application

- Ideal for general lighting,downlighting,and flood lighting.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- WARNING: The arc-tube of metal halide lamps are designed to operate under high pressure and at temperatures up to 1000°C and can unexpectedly rupture due to internal or external factors such as a ballast failure or misapplication. If the arc-tube ruptures for any reason, the outer bulb may break and pieces of extremely hot glass might be discharged into the surrounding environment. If such a rupture were to happen, THERE IS A RISK OF PERSONAL INJURY, PROPERTY DAMAGE, BURNS AND FIRE. These lamps are designed to retain all the glass particles, should an arc tube rupture occur. The following operating instructions are recommended to minimize the occurrences.
- The arc-tube of metal halide lamps are designed to operate under high pressure and at temperatures up to 1000°C and can unexpectedly rupture due to internal or external factors such as a ballast failure or misapplication. If the arc-tube ruptures for any reason, the outer bulb may break and pieces of extremely hot glass might be discharged into the surrounding environment. If such a rupture were to happen, THERE IS A RISK OF PERSONAL INJURY, PROPERTY DAMAGE, BURNS AND FIRE. These lamps are designed to retain all the glass particles, should an arc tube rupture occur. The following operating instructions are recommended to minimize the occurrences.
- RELAMP FIXTURES AT OR BEFORE THE END OF RATED LIFE. Allowing lamps to operate until they fail is not advised and may increase the possibility of inner arc tube rupture.

Dimensional drawing



Product	D	C (max)
MHC100/U/MP/4K ELITE	2.125 inch	5.438 inch
MHC50/U/MP/4K ELITE	2.125 inch	5.438 inch
MHC70/U/MP/4K ELITE	2.125 inch	5.438 inch

General Information	
Cap-Base	E26
Operating Position	UNIVERSAL
Light Technical	
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	90
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED17P

Light Technical

Order Code	Full Product Name	Chromaticity	Chromaticity	Luminous	Luminous
		Coordinate X (Nom)	Coordinate Y (Nom)	Efficacy (Rated) (Min)	Efficacy (rated) (Nom)
928601177801	MHC50/U/MP/4K ELITE	0.377	0.367	86 lm/W	92 lm/W
928601177901	MHC70/U/MP/4K ELITE	0.441	0.392	85 lm/W	92 lm/W
928601178101	MHC100/U/MP/4K ELITE	0.382	0.371	91 lm/W	94 lm/W

MasterColor CDM ED17 Protected Elite 4200K

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power Consumption
928601177801	MHC50/U/MP/4K ELITE	0.67 A	88 V	-
928601177901	MHC70/U/MP/4K ELITE	0.9 A	100 V	70.4 W

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power Consumption
928601178101	MHC100/U/MP/4K ELITE	1.1 A	103 V	-

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Max)
928601177801	MHC50/U/MP/4K ELITE	5.4 mg
928601177901	MHC70/U/MP/4K ELITE	7.1 mg

Order Code	Full Product Name	Mercury (Hg) Content (Max)
928601178101	MHC100/U/MP/4K ELITE	10.3 mg

