



Product Description

PAR38

Pressed-glass 121 mm diameter reflector lamps of high luminous intensity

Benefits

- Produces the same useful light as conventional PAR lamps at 20% lower energy

Features

- Spot versions have a stippled front reflector producing a narrow, homogeneous beam
- Flood versions have a front refractor composed of prismatic elements

Application

- Can be used indoors and outdoors, or wherever blown-bulb reflector lamps would be too vulnerable
- Indoors: shops, window displays, homes, hotels, restaurants, theatres, museums, exhibitions and buildings
- Outdoors: floodlighting, advertising signs, buildings, statues, podiums, sports grounds, parks and gardens
- Can be installed outdoors without any protection, provided they are used in a watertight lampholder
- For outdoor use, a heat-resistant rubber ring must be fitted between the lamp and the lampholder


PAR38

Versions



LPPR IPAR38-E E27 E2751 FL

Dimensional drawing



Product	D (max)		C (max)	
PAR38 120W E27/51 220-240V PAR38 30D 1CT	121 mm	137 mm	123 mm	
PAR38 80W E27 230V PAR38 FL 30D 1CT/12	123 mm	137 mm		

General Information	
Rated Lifetime (Hours)	2,000 hour(s)
Nominal lifetime	2,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Beam Angle (Nom)	30 degree(s)
Color rendering index (CRI)	100
Operating and Electrical	
Starting Time (Nom)	0.0 s
Mechanical and Housing	
Bulb Shape	PAR38

General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle
923810544296	PAR38 80W E27 230V PAR38 FL 30D	E27	8,000
	1CT/12		

Order Code	Full Product Name	Cap-Base	Switching Cycle
923815643301	PAR38 120W E27/51 220-240V PAR38 30D	E27/51	-
	1CT		

Light Technical

PAR38

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux
923810544296	PAR38 80W E27 230V PAR38 FL 30D 1CT/12	2700 K	-

Order Code	Full Product Name	Correlated Color	
		Temperature (Nom)	Luminous Flux
923815643301	PAR38 120W E27/51 220-240V PAR38 30D 1CT	-	1,150 lm

Operating and Electrical

Order Code	Full Product Name	Warm-up	Voltage (Nom)	Power Consumption
		time to 60% light		
923810544296	PAR38 80W E27 230V PAR38 FL 30D 1CT/12	instant full light s	230 V	80.0 W
923815643301	PAR38 120W E27/51 220-240V PAR38 30D 1CT	-	220-240 V	120 W



Controls and Dimming

Order Code	Full Product Name	Dimmable
923810544296	PAR38 80W E27 230V PAR38 FL 30D 1CT/12	Yes

Order Code	Full Product Name	Dimmable
923815643301	PAR38 120W E27/51 220-240V PAR38 30D 1CT	-


Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
923810544296	PAR38 80W E27 230V PAR38 FL 30D 1CT/12	80 kWh
923815643301	PAR38 120W E27/51 220-240V PAR38 30D 1CT	-




PAR38

Accent Diagrams




Accent Diagram - PAR38 120W E27/51
220-240V PAR38 30D 1CT




Accent Diagram - PAR38 80W E27 230V PAR38
FL 30D 1CT/12

Beam Diagrams



Beam diagram - PAR38 120W E27/51 220-240V
PAR38 30D 1CT



Beam diagram - PAR38 80W E27 230V PAR38
FL 30D 1CT/12

