



MASTER LEDspot LV – The ideal solution for spot lighting

MASTER VALUE LEDspot LV

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot and general lighting applications in the hospitality industry. It is particularly suited to public areas such as receptions, lobbies, corridors, stairwells and washrooms, where the light is on all the time. The robustly designed MASTER LEDspot offers a choice of beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

Benefits

- Up to 80% energy saving compared with halogen lamp
- Broad compatibility with transformers
- Suitable to retrofit with low-voltage halogen lamps covering GU5.3 and GU4 base types

Features

- Dimmable (6.5–35W versions)
- Innovative AirFlux technology for passive cooling, depending upon model
- Warm and cool white light
- Lifetime:
 - 40,000 hours MASTER LED
 - 25,000 hours MASTER LED VALUE
- TransforMax technology to ensure compatibility with existing transformers (depending upon model)

MASTER VALUE LEDspot LV

Application

- Ideal for accent lighting in hotels, hospitals, shops and museums (e.g. floors, elevators, displays)

Warnings and Safety



- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Versions



LEDspots MAS SLR 2 MR11 GU4

Dimensional drawing



Product	D	C
MASTER LED 5.5-50W 2700K MR16 24D	50.2 mm	49 mm
MASTER LED 5.5-50W 2700K MR16 36D	50.2 mm	49 mm
MASTER LED 5.5-50W 3000K MR16 24D	50.2 mm	49 mm
MASTER LED 5.5-50W 3000K MR16 36D	50.2 mm	49 mm
MASTER LED 5.5-50W 4000K MR16 36D	50.2 mm	49 mm

Product	D	C
MAS LEDspotLV 3.5-20W 827 MR11 24D	35.1 mm	39.5 mm

MASTER VALUE LEDspot LV

General Information	
Switching Cycle	50,000
Light Technical	
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	- Hz
Line Frequency	- Hz
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime	Order Code	Full Product Name	Cap-Base	Nominal lifetime
929001145908	MASTER LED 5.5-50W 2700K MR16 24D	GU5.3	25,000 hour(s)	929001146708	MASTER LED 5.5-50W 3000K MR16 24D	GU5.3	25,000 hour(s)
929001146108	MASTER LED 5.5-50W 2700K MR16 36D	GU5.3	25,000 hour(s)	929001146908	MASTER LED 5.5-50W 4000K MR16 36D	GU5.3	25,000 hour(s)
929001146608	MASTER LED 5.5-50W 3000K MR16 36D	GU5.3	25,000 hour(s)	929003087002	MAS LEDspotLV 3.5-20W 827 MR11 24D	GU4	40,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color Code	Luminous Flux	Luminous Intensity (Nom)
929001145908	MASTER LED 5.5-50W 2700K MR16 24D	24 degree(s)	2700 K	827	415 lm	1,800 cd
929001146108	MASTER LED 5.5-50W 2700K MR16 36D	36 degree(s)	2700 K	827	415 lm	1,000 cd
929001146608	MASTER LED 5.5-50W 3000K MR16 36D	36 degree(s)	3000 K	830	425 lm	1,000 cd
929001146708	MASTER LED 5.5-50W 3000K MR16 24D	24 degree(s)	3000 K	830	425 lm	1,800 cd
929001146908	MASTER LED 5.5-50W 4000K MR16 36D	36 degree(s)	4000 K	840	450 lm	1,000 cd
929003087002	MAS LEDspotLV 3.5-20W 827 MR11 24D	24 degree(s)	2700 K	827	200 lm	1,000 cd

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Power Consumption	Wattage Equivalent
929001145908	MASTER LED 5.5-50W 2700K MR16 24D	5.5 W	50 W	929001146708	MASTER LED 5.5-50W 3000K MR16 24D	5.5 W	50 W
929001146108	MASTER LED 5.5-50W 2700K MR16 36D	5.5 W	50 W	929001146908	MASTER LED 5.5-50W 4000K MR16 36D	5.5 W	50 W
929001146608	MASTER LED 5.5-50W 3000K MR16 36D	5.5 W	50 W	929003087002	MAS LEDspotLV 3.5-20W 827 MR11 24D	3.5 W	20 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)	Order Code	Full Product Name	T-Case Maximum (Nom)
929001145908	MASTER LED 5.5-50W 2700K MR16 24D	95 °C	929001146708	MASTER LED 5.5-50W 3000K MR16 24D	95 °C
929001146108	MASTER LED 5.5-50W 2700K MR16 36D	95 °C	929001146908	MASTER LED 5.5-50W 4000K MR16 36D	95 °C
929001146608	MASTER LED 5.5-50W 3000K MR16 36D	95 °C	929003087002	MAS LEDspotLV 3.5-20W 827 MR11 24D	85 °C

Mechanical and Housing







MASTER VALUE LEDspot LV

Order Code	Full Product Name	Bulb Shape
929001145908	MASTER LED 5.5-50W 2700K MR16 24D	MR16
929001146108	MASTER LED 5.5-50W 2700K MR16 36D	MR16
929001146608	MASTER LED 5.5-50W 3000K MR16 36D	MR16


Order Code	Full Product Name	Bulb Shape
929001146708	MASTER LED 5.5-50W 3000K MR16 24D	MR16
929001146908	MASTER LED 5.5-50W 4000K MR16 36D	MR16
929003087002	MAS LEDspotLV 3.5-20W 827 MR11 24D	MR11

Approval and Application


Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
929001145908	MASTER LED 5.5-50W 2700K MR16 24D	-
929001146108	MASTER LED 5.5-50W 2700K MR16 36D	-
929001146608	MASTER LED 5.5-50W 3000K MR16 36D	-
929001146708	MASTER LED 5.5-50W 3000K MR16 24D	-
929001146908	MASTER LED 5.5-50W 4000K MR16 36D	-
929003087002	MAS LEDspotLV 3.5-20W 827 MR11 24D	4 kWh




Accent Diagrams




Accent Diagram - MASTER LED 5.5-50W 2700K
MR16 24D




Accent Diagram - MASTER LED 5.5-50W 2700K
MR16 36D




Accent Diagram - MASTER LED 5.5-50W 3000K
MR16 36D



Accent Diagram - MASTER LED 5.5-50W 3000K
MR16 24D




Accent Diagram - MASTER LED 5.5-50W 4000K
MR16 36D




Accent Diagram - MAS LEDspotLV 3.5-20W 827
MR11 24D


Beam Diagrams



Beam diagram - MASTER LED 5.5-50W 2700K
MR16 24D




Beam diagram - MASTER LED 5.5-50W 2700K
MR16 36D




Beam diagram - MASTER LED 5.5-50W 3000K
MR16 36D

MASTER VALUE LEDspot LV


Beam Diagrams



Beam diagram - MASTER LED 5.5-50W 3000K MR16 24D



Beam diagram - MASTER LED 5.5-50W 4000K MR16 36D



Beam diagram - MAS LEDspotLV 3.5-20W 827 MR11 24D

