



MASTER Value LED-spot 230V er perfekt til spotbelysning og er en optimal kombination af værdi og ydelse

MASTER LED-spot 230V GU10

MASTER VALUE leverer en varm, halogenlignende stråleeffekt og er perfekt til spotbelysning. Takket være dens høje CRI gengiver den mere naturlige farver, skaber hyggelige og komfortable atmosfærer i beboelsesområder, hoteller og restauranter og fremhæver varers skønhed i butikker. Disse MV GU10 LED-spots har det velkendte look, og samme følelse som spotlyskilder, mens de bevarer den klassiske skønhed ved glasspots og samtidigt tilføjer LED-teknologiens stærke ydeevne. Lysdæmpningsfunktionen giver dig mulighed for at skabe den atmosfære, du ønsker, og den fungerer med et bredt udvalg af lysdæmpere. MASTER VALUE er desuden mere energibesparende end normale LED-spots.

Fordele

- Op til 80 % energibesparelse med MASTER VALUE spotlights sammenlignet med halogenpærer
- Bedste gengivelse af atmosfæren fra en halogenspot
- Perfekt til erstatning af traditionelle GU10-lyskilder

MASTER LED-spot 230V GU10

Funktioner

- Dæmpbar: Jo mere du dæmper, desto varmere lys får du
- Kompatibel med en bred vifte af lysdæmpere
- Levetid: 25.000 timer
- Tydeligt defineret strålespredning
- Intet ultraviolet lys og med kold stråle (intet infrarødt lys), hvilket gør den egnet til belysning af varmefølsomme genstande (mad, organisk materiale, malerier osv.)
- Patenteret intelligent driver

Anvendelsesområder

- Hotel og restauration
- Detailhandel
- Boligområder

Advarsler og sikkerhed

- Driftstemperaturområde er mellem -20 ° C og 45 ° C omgivelsestemperatur
- Kun til anvendelse i tørre eller fugtige steder og de fleste af åbne armaturer med fatninger, der tilbyder tilstrækkeligt plads (10 mm frit luftrum)
- Ikke beregnet til brug med nødlysarmaturer eller udgangsllys

Versions




LEDspots 50W GU10 PAR16



LEDspots VLE D 650lm GU10 930 120D


Målskitse



Product	D	C
MAS LED spot VLE D 3.7-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 mm	54 mm

MASTER LED-spot 230V GU10

Målskitse



Product	D	C
MAS LED spot VLE D 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 965 36D	50 mm	54 mm
MAS LED spot VLE D 650lm GU10 930 120D	50 mm	55,5 mm
MAS LED spot VLE D 680lm GU10 940 120D	50 mm	55,5 mm
MAS LED spot VLE D 680lm GU10 965 120D	50 mm	55,5 mm
MAS LED spot VLE DT 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	50 mm	54 mm
MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	50 mm	54 mm

Generelle oplysninger	
Fod	GU10
Normeret levetid	25.000 t
Lys teknisk	
Farvegengivelsesindeks (CRI)	90
LLMF ved den nominelle levetids udløb (nom.)	70 %
Drift og el	
Indgangsfrekvens	50 til 60 Hz
Opstartstid (nom.)	0,5 s
Lysstyringssystemer og dæmpning	
Dæmpbar	Kun med visse lysdæmpere
Mekanik og armaturhus	
Lyskildeform	PAR16

Order Code	Full Product Name	Skiftecyklus
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	50.000
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	50.000
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	50.000
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	50.000
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	50.000
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	50.000
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	50.000
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	50.000
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	50.000
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	50.000
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	50.000
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	50.000
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	50.000
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	50.000
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	50.000
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	50.000
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	50.000
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	50.000
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	50.000
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	50.000
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	50.000

MASTER LED-spot 230V GU10

Order Code	Full Product Name	Skiftecyklus
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	25.000
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	25.000
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	25.000
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	50.000
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	50.000
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	50.000
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	50.000
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	50.000

Lysteknisk (1/2)

Order Code	Full Product Name	Spredningsvinkel (nom.)	Korreleret farvetemperatur (nom.)		
			Farvekode	Lysstrøm	
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	36 °	2200 K	922-927	575 lm
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	36 °	2700 K	927	575 lm
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	36 °	3000 K	930	575 lm
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	36 °	4000 K	940	575 lm
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	36 °	6500 K	965	575 lm
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	36 °	3000 K	930	270 lm
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	36 °	3000 K	930	365 lm
929001349102	MAS LED spot VLE D	60 °	2700 K	927	355 lm

Order Code	Full Product Name	Spredningsvinkel (nom.)	Korreleret farvetemperatur (nom.)		
			Farvekode	Lysstrøm	
929001349202	MAS LED spot VLE D 4.9-50W GU10 927 60D	60 °	3000 K	930	365 lm
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	36 °	2200 K	922-927	355 lm
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	36 °	2700 K	927	270 lm
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	36 °	2200 K	922-927	270 lm
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	36 °	2200 K	922-927	280 lm
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	36 °	2200 K	922-927	355 lm
929004247302	MAS LED spot VLE D 2.8-35W	36 °	2700 K	927	270 lm

MASTER LED-spot 230V GU10

Order Code	Full Product Name	Spredningsvinkel (nom.)	Korreleret farvetemperatur		
			(nom.)	Farvekode	Lysstrøm
	GU10 927 36D				
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	36 °	3000 K	930	270 lm
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	36 °	4000 K	940	285 lm
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	60 °	2700 K	927	270 lm
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	36 °	2700 K	927	355 lm
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	36 °	3000 K	930	365 lm
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	36 °	4000 K	940	380 lm
929004248202	MAS LED spot VLE D 3.7-50W	60 °	2700 K	927	355 lm

Lysteknisk (2/2)

Order Code	Full Product Name	Lysstyrke (nom.)
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	950 cd
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	950 cd
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	1.000 cd
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	1.000 cd
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	1.000 cd
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	500 cd
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	650 cd

Order Code	Full Product Name	Spredningsvinkel (nom.)	Korreleret farvetemperatur		
			(nom.)	Farvekode	Lysstrøm
	GU10 927 60D				
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	60 °	3000 K	930	365 lm
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	60 °	4000 K	940	370 lm
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	36 °	2700 K	927	355 lm
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	36 °	3000 K	930	365 lm
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	120 °	3000 K	930	650 lm
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	120 °	4000 K	940	680 lm
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	120 °	6500 K	965	680 lm

MASTER LED-spot 230V GU10

Order Code	Full Product Name	Lysstyrke (nom.)
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	600 cd
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	600 cd
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	600 cd
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	300 cd
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	750 cd
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	750 cd
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	800 cd
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	400 cd

Order Code	Full Product Name	Lysstyrke (nom.)
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	400 cd
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	420 cd
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	750 cd
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	750 cd
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	220 cd
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	220 cd
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	220 cd

Drift og el

Order Code		Full Product		
		Name	Linjefrekvens	Strømforbrug Wattforbrugsækvivalent
929004255702		MAS LED spot VLE DT 5.5-80W GU10 927 36D	-	5,5 W 80 W
929004255802		MAS LED spot VLE D 5.5-80W GU10 927 36D	-	5,5 W 80 W
929004255902		MAS LED spot VLE D 5.5-80W GU10 930 36D	-	5,5 W 80 W
929004256002		MAS LED spot VLE D 5.5-80W GU10 940 36D	-	5,5 W 80 W
929004256102		MAS LED spot VLE D 5.5-80W GU10 965 36D	-	5,5 W 80 W
929001348302		MAS LED spot VLE D 3.7-35W GU10 930 36D	50 to 60 Hz	3,7 W 35 W
929001348902		MAS LED spot VLE D 4.9-50W GU10 930 36D	50 to 60 Hz	4,9 W 50 W
929001349102		MAS LED spot VLE D 4.9-50W GU10 927 60D	50 to 60 Hz	4,9 W 50 W
929001349202		MAS LED spot VLE D 4.9-50W GU10 930 60D	50 to 60 Hz	4,9 W 50 W

Order Code		Full Product		
		Name	Linjefrekvens	Strømforbrug Wattforbrugsækvivalent
929001350302		MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 to 60 Hz	4,9 W 50 W
929002979402		MAS LED spot VLE D 3.7-35W GU10 927 36D	50 to 60 Hz	3,7 W 35 W
929002979702		MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 to 60 Hz	3,7 W 35 W
929004247102		MAS LED spot VLE DT 2.8-35W GU10 927 36D	-	2,8 W 35 W
929004247202		MAS LED spot VLE DT 3.7-50W GU10 927 36D	-	3,7 W 50 W
929004247302		MAS LED spot VLE D 2.8-35W GU10 927 36D	-	2,8 W 35 W
929004247402		MAS LED spot VLE D 2.8-35W GU10 930 36D	-	2,8 W 35 W
929004247502		MAS LED spot VLE D 2.8-35W GU10 940 36D	-	2,8 W 35 W
929004247602		MAS LED spot VLE D 2.8-35W GU10 927 60D	-	2,8 W 35 W
929004247902		MAS LED spot VLE D	-	3,7 W 50 W

MASTER LED-spot 230V GU10

Full Product				
Order Code	Name	Linjefrekvens	Strømforbrug	Wattforbrugsækvivalent
	3.7-50W GU10			
	927 36D			
929004248002	MAS LED spot -		3,7 W	50 W
	VLE D			
	3.7-50W GU10			
	930 36D			
929004248102	MAS LED spot -		3,7 W	50 W
	VLE D			
	3.7-50W GU10			
	940 36D			
929004248202	MAS LED spot -		3,7 W	50 W
	VLE D			
	3.7-50W GU10			
	927 60D			
929004248302	MAS LED spot -		3,7 W	50 W
	VLE D			
	3.7-50W GU10			
	930 60D			
929004248402	MAS LED spot -		3,7 W	50 W
	VLE D			

Full Product				
Order Code	Name	Linjefrekvens	Strømforbrug	Wattforbrugsækvivalent
	3.7-50W GU10			
	940 60D			
929004247952	MAS LEDspot -		3,7 W	50 W
	VLE D			
	3.7-50W GU10			
	92736D5CT			
929004248052	MAS LEDspot -		3,7 W	50 W
	VLE D			
	3.7-50W GU10			
	93036D5CT			
929004256202	MAS LED spot -		5,5 W	-
	VLE D 650lm			
	GU10 930			
	120D			
929004256302	MAS LED spot -		5,5 W	-
	VLE D 680lm			
	GU10 940			
	120D			
929004256402	MAS LED spot -		5,5 W	-
	VLE D 680lm			
	GU10 965			
	120D			

Temperatur

Order Code	Full Product Name	T-kappe, maks. (nom.)
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	66 °C
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	66 °C
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	66 °C
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	66 °C
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	66 °C
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	80 °C
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	80 °C
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	80 °C
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	80 °C
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	80 °C
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	70 °C
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	70 °C
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	52 °C
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	60 °C
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	50 °C

Order Code	Full Product Name	T-kappe, maks. (nom.)
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	50 °C
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	50 °C
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	50 °C
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	66 °C
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	66 °C
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	66 °C
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	62 °C
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	62 °C
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	62 °C
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	66 °C
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	66 °C
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	66 °C
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	66 °C
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	66 °C

Mekanik og armaturhus

Order Code	Full Product Name	Pære finish
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	Klar
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	Klar
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	Klar
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	Klar

Order Code	Full Product Name	Pære finish
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	Klar
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	-
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	-
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	-

MASTER LED-spot 230V GU10

Order Code	Full Product Name	Pære finish
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	-
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	-
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	-
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	-
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	Klar
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	Klar
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	Klar
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	Klar
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	Klar
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	Klar
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	Klar

Order Code	Full Product Name	Pære finish
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	Klar
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	Klar
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	Klar
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	Klar
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	Klar
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	Klar
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	Klar
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	Matteret
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	Matteret
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	Matteret





Godkendelse og anvendelsesområde



Order Code	Full Product Name	Omgivelsestemperaturområde	Energiforbrug kWh/1000 t.
929004255702	MAS LED spot VLE DT 5.5-80W GU10 927 36D	-20 til +45 °C	6 kWh
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	-20 til +45 °C	6 kWh
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	-20 til +45 °C	6 kWh
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	-20 til +45 °C	6 kWh
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	-20 til +45 °C	6 kWh
929001348302	MAS LED spot VLE D 3.7-35W GU10 930 36D	-	4 kWh
929001348902	MAS LED spot VLE D 4.9-50W GU10 930 36D	-	5 kWh
929001349102	MAS LED spot VLE D 4.9-50W GU10 927 60D	-	5 kWh
929001349202	MAS LED spot VLE D 4.9-50W GU10 930 60D	-	5 kWh
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	-	5 kWh
929002979402	MAS LED spot VLE D 3.7-35W GU10 927 36D	-	4 kWh
929002979702	MAS LED spot VLE DT 3.7-35W GU10 927 36D	-	4 kWh

Order Code	Full Product Name	Omgivelsestemperaturområde	Energiforbrug kWh/1000 t.
929004247102	MAS LED spot VLE DT 2.8-35W GU10 927 36D	-20 til +45 °C	3 kWh
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	-20 til +45 °C	4 kWh
929004247302	MAS LED spot VLE D 2.8-35W GU10 927 36D	-20 til +45 °C	3 kWh
929004247402	MAS LED spot VLE D 2.8-35W GU10 930 36D	-20 til +45 °C	3 kWh
929004247502	MAS LED spot VLE D 2.8-35W GU10 940 36D	-20 til +45 °C	3 kWh
929004247602	MAS LED spot VLE D 2.8-35W GU10 927 60D	-20 til +45 °C	3 kWh
929004247902	MAS LED spot VLE D 3.7-50W GU10 927 36D	-20 til +45 °C	4 kWh
929004248002	MAS LED spot VLE D 3.7-50W GU10 930 36D	-20 til +45 °C	4 kWh
929004248102	MAS LED spot VLE D 3.7-50W GU10 940 36D	-20 til +45 °C	4 kWh
929004248202	MAS LED spot VLE D 3.7-50W GU10 927 60D	-20 til +45 °C	4 kWh
929004248302	MAS LED spot VLE D 3.7-50W GU10 930 60D	-20 til +45 °C	4 kWh
929004248402	MAS LED spot VLE D 3.7-50W GU10 940 60D	-20 til +45 °C	4 kWh











MASTER LED-spot 230V GU10

Order Code	Full Product Name	Omgivelsestemperaturområde	Energiforbrug kWh/1000 t.
929004247952	MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	-20 til +45 °C	4 kWh
929004248052	MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	-20 til +45 °C	4 kWh
929004256202	MAS LED spot VLE D 650lm GU10 930 120D	-20 til +45 °C	6 kWh
929004256302	MAS LED spot VLE D 680lm GU10 940 120D	-20 til +45 °C	6 kWh
929004256402	MAS LED spot VLE D 680lm GU10 965 120D	-20 til +45 °C	6 kWh








MASTER LED-spot 230V GU10




MASTER LED-spot 230V GU10




Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W GU10 930 36D




Accent Diagram - MAS LED spot VLE DT 4.9-50W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W GU10 930 36D



Accent Diagram - MAS LED spot VLE D 4.9-50W GU10 930 36D




Accent Diagram - MAS LED spot VLE D 4.9-50W GU10 930 60D




Accent Diagram - MAS LED spot VLE DT 3.7-35W GU10 927 36D


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D




Accent Diagram - MAS LED spot VLE DT
5.5-80W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 965 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 940 36D



Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 930 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 927 36D




Accent Diagram - MAS LEDspot VLE D 3.7-50W
GU10 92736D5CT

MASTER LED-spot 230V GU10


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W GU10 940 60D




Accent Diagram - MAS LED spot VLE D 2.8-35W GU10 927 60D



Accent Diagram - MAS LED spot VLE D 3.7-50W GU10 930 60D




Accent Diagram - MAS LED spot VLE DT 2.8-35W GU10 927 36D




Accent Diagram - MAS LED spot VLE DT 3.7-50W GU10 927 36D


Beam Diagrams



Beam diagram - MAS LED spot VLE DT 5.5-80W GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-35W GU10 927 36D




Beam diagram - MAS LED spot VLE DT 4.9-50W GU10 927 36D


Beam Diagrams




Beam diagram - MAS LED spot VLE D 3.7-35W GU10 930 36D




Beam diagram - MAS LED spot VLE D 4.9-50W GU10 930 36D




Beam diagram - MAS LED spot VLE D 4.9-50W GU10 930 60D




Beam diagram - MAS LED spot VLE D 2.8-35W GU10 940 36D




Beam diagram - MAS LED spot VLE D 3.7-50W GU10 940 36D




Beam diagram - MAS LED spot VLE D 2.8-35W GU10 927 60D



Beam diagram - MAS LED spot VLE DT 2.8-35W GU10 927 36D




Beam diagram - MAS LED spot VLE D 2.8-35W GU10 930 36D




Beam diagram - MAS LED spot VLE D 5.5-80W GU10 965 36D


Beam Diagrams




Beam diagram - MAS LED spot VLE DT 3.7-35W
GU10 927 36D




Beam diagram - MAS LEDspot VLE D 3.7-50W
GU10 92736D5CT




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Beam diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D




Beam diagram - MAS LED spot VLE DT 3.7-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 930 60D



Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 60D



Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 927 36D



Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 930 36D

MASTER LED-spot 230V GU10

