



Die dimmbaren Rennertypen

MASTER LEDspot & Value GU10 Hochvolt- Reflektorlampen

MASTER LEDspot GU10 Lampen sind mit ihren kompakten Abmessung der ideale Ersatz für handelsübliche Hochvolt-Halogen-Reflektorlampen. Sie bieten lange Lebensdauer und hohe Energieeffizienz für eine dimmbare Allgemein- und Akzentbeleuchtung.

Vorteile

- Hohe Farbwiedergabe
- Klassische Optik im Retro-Design wie ein Halogenreflektor
- Über 80% Energieeinsparung im Vergleich zu HV-Halogen-Reflektorlampen bei vergleichbarer Lichtleistung und Zeitspanne
- DimTone (DT) Versionen: das Licht wird beim Dimmen wärmer

Merkmale

- Lange Nutzlebensdauer
- Gute Farbwiedergabe
- Zwei Ausstrahlungswinkel (36° und 60°)
- Frei von Quecksilber und gefährlichen Substanzen
- Dimmbar an von Philips empfohlenen Dimmern (www.philips.de/master-led-lampen)

Anwendung

- Für Akzent- und Allgemeinbeleuchtung in Hotels, Restaurants, Shops, Museen und Krankenhäusern
- Nur in offenen/belüfteten Leuchten verwenden
- Einzusetzen im Innenbereich bei Temperaturen von -20 bis +45°C

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen

Hinweise

- Nicht für Gleichspannung geeignet
- Nicht für elektronische Schalter geeignet
- Max. 80% Luftfeuchtigkeit
- Min. 10 mm Luftraum beim Deckeneinbau zur Gewährleistung der konstanten Wärmeableitung
- Eine Liste empfohlener und getesteter Dimmer finden Sie unter www.philips.de/master-led-lampen



Versions



LEDspots 50W GU10 PAR16

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen

Abmessungsskizzen



Product	D	C
MAS LED spot VLE D 3.7-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 6.2-80W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 mm	54 mm

Product	D	C
MAS LED spot VLE D 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE DT 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LEDspot VLE D 3.7-50W GU10 92736D5CT	50 mm	54 mm
MAS LEDspot VLE D 3.7-50W GU10 93036D5CT	50 mm	54 mm
MAS LEDspot VLE D 4.7-50W GU10 82736D5CT	50 mm	54 mm

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen

Allgemeine Informationen	
Sockel	GU10
Nennlebensdauer	25.000 Stunde(n)
Lichttechnische Daten	
Restlichtstrom am Ende der Nennlebensdauer (Nom.)	70 %
Betrieb und Elektrik	
Eingangsfrequenz	50 bis 60 Hz
Startzeit (Nom)	0,5 s
Lichtregelung und Dimmen	
Dimmbar	Nur mit Spezial-Dimmern
Mechanik und Gehäuse	
Kolbenform	PAR16

Allgemeine Informationen

Order Code	Full Product Name	Schaltzyklus	Order Code	Full Product Name	Schaltzyklus
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	50.000	39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	50.000
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	50.000	39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	50.000
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	50.000	39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	50.000
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	50.000	39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	50.000
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	50.000	39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	50.000
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	50.000	39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	50.000
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	50.000	39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	50.000
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	50.000	39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	50.000
70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	50.000	39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	25.000
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	50.000	39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	25.000
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	50.000	39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	25.000
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	50.000	31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	50.000
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	50.000	05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	50.000
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	50.000	05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	50.000

Lichttechnische Daten

Order Code	Full Product Name	Ausstrahlungswinkel (Nom)	Ähnlichste	Farbwiedergabeindex		Farbcode	Lichtstrom	Lichtstärke (Nom)
			Farbtemperatur	(CRI)				
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	36 Grad	4000 K	90		940	575 lm	850 cd
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	36 Grad	2200 K	90		922-927	575 lm	950 cd
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	36 Grad	2700 K	90		927	575 lm	950 cd
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	36 Grad	3000 K	90		930	575 lm	1.000 cd
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	36 Grad	4000 K	90		940	575 lm	1.000 cd

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen

Order Code	Full Product Name	Ausstrahlungswinkel (Nom)	Ähnlichste	Farbwiedergabeindex		Lichtstrom	Lichtstärke (Nom)
			Farbtemperatur	(CRI)	Farbcode		
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	36 Grad	3000 K	90	930	270 lm	500 cd
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	36 Grad	4000 K	90	940	285 lm	500 cd
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	60 Grad	4000 K	90	940	285 lm	350 cd
70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	36 Grad	3000 K	90	930	365 lm	650 cd
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	60 Grad	2700 K	90	927	355 lm	400 cd
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	60 Grad	3000 K	90	930	365 lm	400 cd
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	36 Grad	2200 K	90	922-927	355 lm	650 cd
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	36 Grad	2700 K	90	927	270 lm	500 cd
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	36 Grad	2200 K	90	922-927	270 lm	500 cd
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	36 Grad	2200 K	90	922-927	280 lm	550 cd
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	36 Grad	2200 K	90	922-927	355 lm	700 cd
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	36 Grad	2700 K	90	927	270 lm	600 cd
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	36 Grad	3000 K	90	930	270 lm	600 cd
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	36 Grad	4000 K	90	940	285 lm	600 cd
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	36 Grad	2700 K	90	927	355 lm	750 cd
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	36 Grad	3000 K	90	930	365 lm	750 cd
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	36 Grad	4000 K	90	940	380 lm	800 cd
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	60 Grad	2700 K	90	927	355 lm	400 cd
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	60 Grad	3000 K	90	930	365 lm	400 cd
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	60 Grad	4000 K	90	940	370 lm	420 cd
31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	36 Grad	2700 K	80	827	345 lm	650 cd
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	36 Grad	2700 K	90	927	355 lm	750 cd
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	36 Grad	3000 K	90	930	365 lm	750 cd

Betrieb und Elektrik

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen

Order Code	Full Product Name	Netzfrequenz	Äquivalente	
			Systemleistung	Leistung
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	50 to 60 Hz	6,2 W	80 W
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	-	5,5 W	80 W
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	-	5,5 W	80 W
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	-	5,5 W	80 W
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	-	5,5 W	80 W
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	50 to 60 Hz	3,7 W	35 W
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	50 to 60 Hz	3,7 W	35 W
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	50 to 60 Hz	3,7 W	35 W
70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	50 to 60 Hz	4,9 W	50 W
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	50 to 60 Hz	4,9 W	50 W
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	50 to 60 Hz	4,9 W	50 W
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	50 to 60 Hz	4,9 W	50 W
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	50 to 60 Hz	3,7 W	35 W
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	50 to 60 Hz	3,7 W	35 W
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	-	2,8 W	35 W

Order Code	Full Product Name	Netzfrequenz	Äquivalente	
			Systemleistung	Leistung
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	-	3,7 W	50 W
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	-	2,8 W	35 W
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	-	2,8 W	35 W
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	-	2,8 W	35 W
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	-	3,7 W	50 W
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	-	3,7 W	50 W
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	-	3,7 W	50 W
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	-	3,7 W	50 W
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	-	3,7 W	50 W
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	-	3,7 W	50 W
31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	50 to 60 Hz	4,7 W	50 W
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	-	3,7 W	50 W
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	-	3,7 W	50 W

Temperatur

Order Code	Full Product Name	Gehäusetemperatur (Nom)
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	80 °C
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	66 °C
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	66 °C
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	66 °C
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	66 °C
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	80 °C

Order Code	Full Product Name	Gehäusetemperatur (Nom)
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	80 °C
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	80 °C
70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	80 °C
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	80 °C
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	80 °C
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	80 °C

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen

Order Code	Full Product Name	Gehäusetemperatur (Nom)
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	70 °C
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	70 °C
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	52 °C
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	60 °C
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	50 °C
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	50 °C
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	50 °C
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	66 °C

Order Code	Full Product Name	Gehäusetemperatur (Nom)
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	66 °C
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	66 °C
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	62 °C
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	62 °C
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	62 °C
31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	80 °C
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	66 °C
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	66 °C

Mechanik und Gehäuse

Order Code	Full Product Name	Kolbenausführung
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	-
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	Klar
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	Klar
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	Klar
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	Klar
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	-
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	-
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	-
70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	-
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	-
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	-
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	-
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	-
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	-

Order Code	Full Product Name	Kolbenausführung
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	Klar
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	Klar
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	Klar
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	Klar
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	Klar
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	Klar
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	Klar
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	Klar
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	Klar
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	Klar
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	Klar
31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	-
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	Klar
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	Klar

Genehmigung und Anwendung


Order Code	Full Product Name	Umgebungstemperaturbereich	Energieverbrauch kWh/1.000 Std.
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	-	7 kWh
03821000	MASTER LED spot VLE DT 5.5-80W GU10 927 36D	-20 bis +45 °C	6 kWh
03835700	MASTER LED spot VLE D 5.5-80W GU10 927 36D	-20 bis +45 °C	6 kWh
03827200	MASTER LED spot VLE D 5.5-80W GU10 930 36D	-20 bis +45 °C	6 kWh



Order Code	Full Product Name	Umgebungstemperaturbereich	Energieverbrauch kWh/1.000 Std.
03823400	MASTER LED spot VLE D 5.5-80W GU10 940 36D	-20 bis +45 °C	6 kWh
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	-	4 kWh
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	-	4 kWh
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	-	4 kWh

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen













Order Code	Full Product Name	Umgebungstemperaturbereich	Energieverbrauch kWh/1.000 Std.
70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	-	5 kWh
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	-	5 kWh
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	-	5 kWh
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	-	5 kWh
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	-	4 kWh
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	-	4 kWh
39914300	MASTER LED spot VLE DT 2.8-35W GU10 927 36D	-20 bis +45 °C	3 kWh
39948800	MASTER LED spot VLE DT 3.7-50W GU10 927 36D	-20 bis +45 °C	4 kWh
39912900	MASTER LED spot VLE D 2.8-35W GU10 927 36D	-20 bis +45 °C	3 kWh
39928000	MASTER LED spot VLE D 2.8-35W GU10 930 36D	-20 bis +45 °C	3 kWh
39930300	MASTER LED spot VLE D 2.8-35W GU10 940 36D	-20 bis +45 °C	3 kWh
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	-20 bis +45 °C	4 kWh
39944000	MASTER LED spot VLE D 3.7-50W GU10 930 36D	-20 bis +45 °C	4 kWh
39946400	MASTER LED spot VLE D 3.7-50W GU10 940 36D	-20 bis +45 °C	4 kWh
39934100	MASTER LED spot VLE D 3.7-50W GU10 927 60D	-20 bis +45 °C	4 kWh
39936500	MASTER LED spot VLE D 3.7-50W GU10 930 60D	-20 bis +45 °C	4 kWh
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	-20 bis +45 °C	4 kWh

Order Code	Full Product Name	Umgebungstemperaturbereich	Energieverbrauch kWh/1.000 Std.
31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	-	5 kWh
05236000	MASTER LEDspot VLE D 3.7-50W GU10 92736D5CT	-20 bis +45 °C	4 kWh
05238400	MASTER LEDspot VLE D 3.7-50W GU10 93036D5CT	-20 bis +45 °C	4 kWh













MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen




MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen




MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 930 36D




Accent Diagram - MAS LED spot VLE DT
4.9-50W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 930 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 940 60D




Accent Diagram - MAS LED spot VLE D
4.9-50W GU10 930 36D




Accent Diagram - MAS LED spot VLE D
4.9-50W GU10 927 60D



Accent Diagram - MAS LED spot VLE DT
3.7-35W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 6.2-80W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen


Accent Diagrams




Accent Diagram - MAS LED spot VLE DT
5.5-80W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 940 36D




Accent Diagram - MAS LEDspot VLE D 3.7-50W
GU10 93036D5CT



Accent Diagram - MAS LEDspot VLE D 4.7-50W
GU10 82736D5CT




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 36D

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W GU10 940 60D



Accent Diagram - MAS LED spot VLE D 3.7-50W GU10 930 60D




Accent Diagram - MAS LED spot VLE DT 2.8-35W GU10 927 36D




Accent Diagram - MAS LED spot VLE DT 3.7-50W GU10 927 36D


Beam Diagrams



Beam diagram - MAS LED spot VLE DT 5.5-80W GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-35W GU10 927 36D




Beam diagram - MAS LED spot VLE DT 4.9-50W GU10 927 36D

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen


Beam Diagrams




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 930 36D




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 940 60D




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 930 36D




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 927 60D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 940 36D




Beam diagram - MAS LEDspot VLE D 4.7-50W
GU10 82736D5CT



Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 36D




Beam diagram - MAS LED spot VLE DT 2.8-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 930 36D

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen


Beam Diagrams




Beam diagram - MAS LED spot VLE D 5.5-80W
GU10 940 36D




Beam diagram - MAS LED spot VLE DT 3.7-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Beam diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D




Beam diagram - MAS LED spot VLE DT 3.7-50W
GU10 927 36D



Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 930 60D




Beam diagram - MAS LED spot VLE D 6.2-80W
GU10 940 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 60D

MASTER LEDspot & Value GU10 Hochvolt-Reflektorlampen

Beam Diagrams



Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 927 36D



Beam diagram - MAS LEDspot VLE D 3.7-50W
GU10 93036D5CT

