



The perfect replacement for mains voltage halogen spots

MASTER VALUE LEDspot MV

Delivering a warm, halogen-like accent beam, the MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it achieves more natural colours, creating cosy and comfortable ambience for residential and hospitality projects, and emphasising the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. The MASTER VALUE also offers more energy savings than normal LED spots.

Benefits

- With MASTER VALUE spotlight, up to 80% energy saving compared with halogen lamps
- Best mimic of a halogen spot for atmosphere creation
- Perfect replacement for traditional GU10 lamps

Features

- Dimmable range
- Compatible with an extensive range of dimmers
- Patented intelligent driver
- Lifetime of 25,000 hours
- No UV and Cool Beam (no IR), making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings etc.)

Application



- Hospitality
- Retail
- Residential

MASTER VALUE LEDspot MV

Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

Dimensional drawing



Product	D	C
MAS LED spot VLE D 3.7-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 650lm GU10 930 120D	50 mm	54 mm
MAS LED spot VLE D 680lm GU10 940 120D	50 mm	54 mm
MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLEDT4.9-50W GU10 927 36DUK	50 mm	54 mm
MAS LEDspotVLE D 4.9-50W GU10 930 36D UK	50 mm	54 mm
MASLEDspot VLE D 6.2-80W GU10 930 36D UK	50 mm	54 mm
MASLEDspot VLE D 6.2-80W GU10 940 36D UK	50 mm	54 mm

Product	D	C
MAS LED spot VLE D 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 650lm GU10 930 120D	50 mm	55.5 mm
MAS LED spot VLE D 680lm GU10 965 120D	50 mm	55.5 mm
MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLEDT3.7-50W GU10 927 36DUK	50 mm	54 mm
MAS LEDspotVLE D 3.7-50W GU10 940 36D UK	50 mm	54 mm
MASLEDspot VLE D 5.5-80W GU10 927 36D UK	50 mm	54 mm

General Information

Cap base	GU10
Nominal lifetime	25,000 h

Light Technical

Colour rendering index (CRI)	90
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical

Input frequency	50 to 60 Hz
Starting time (nom.)	0.5 s

Mechanical and Housing

Bulb shape	PAR16
------------	-------

General Information

MASTER VALUE LEDspot MV

Order Code	Full Product Name	Switching Cycle
70523701	MASTERLEDspot VLE D 6.2-80W GU10 940 36D UK	50,000
70525101	MASTERLEDspot VLE D 6.2-80W GU10 930 36D UK	50,000
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	50,000
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	50,000
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	50,000
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	50,000
70787601	MASTER LEDspotVLE D 4.9-50W GU10 930 36D UK	50,000
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	50,000
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	50,000
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	50,000
70811801	MASTER LED spot VLEDT4.9-50W GU10 927 36DUK	50,000

Order Code	Full Product Name	Switching Cycle
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	50,000
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	50,000
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	50,000
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	50,000
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	50,000
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	50,000
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	25,000
70609800	MASTER LED spot VLE D 650lm GU10 930 120D	50,000
70611100	MASTER LED spot VLE D 680lm GU10 940 120D	50,000
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	50,000
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	50,000

Light Technical

Correlated Colour Temperature								
Order Code	Full Product Name	Beam angle (nom.)	(Nom)	Colour Code	Luminous Flux	Luminous intensity (nom.)		
70523701	MASTERLEDspot VLE D 6.2-80W GU10 940 36D UK	36 degree(s)	4000 K	940	575 lm	850 cd		
70525101	MASTERLEDspot VLE D 6.2-80W GU10 930 36D UK	36 degree(s)	3000 K	930	575 lm	850 cd		
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	36 degree(s)	2700 K	927	575 lm	950 cd		
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	36 degree(s)	3000 K	930	270 lm	500 cd		
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	36 degree(s)	4000 K	940	285 lm	500 cd		
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	60 degree(s)	4000 K	940	285 lm	350 cd		
70787601	MASTER LEDspotVLE D 4.9-50W GU10 930 36D UK	36 degree(s)	3000 K	930	365 lm	650 cd		
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	60 degree(s)	2700 K	927	355 lm	400 cd		
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	60 degree(s)	3000 K	930	365 lm	400 cd		
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	36 degree(s)	2200 K	922-927	355 lm	650 cd		
70811801	MASTER LED spot VLEDT4.9-50W GU10 927 36DUK	36 degree(s)	2200 K	922-927	355 lm	650 cd		
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	36 degree(s)	2700 K	927	270 lm	500 cd		
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	36 degree(s)	2200 K	922-927	270 lm	500 cd		
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	60 degree(s)	2700 K	927	270 lm	300 cd		
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	36 degree(s)	2200 K	922-927	355 lm	700 cd		
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	36 degree(s)	2700 K	927	355 lm	750 cd		
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	36 degree(s)	4000 K	940	380 lm	800 cd		
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	60 degree(s)	4000 K	940	370 lm	420 cd		
70609800	MASTER LED spot VLE D 650lm GU10 930 120D	120 degree(s)	3000 K	930	650 lm	200 cd		
70611100	MASTER LED spot VLE D 680lm GU10 940 120D	120 degree(s)	4000 K	940	680 lm	200 cd		
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	120 degree(s)	3000 K	930	650 lm	220 cd		
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	120 degree(s)	6500 K	965	680 lm	220 cd		

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage equivalent
70523701	MASTERLEDspot VLE D 6.2-80W GU10 940 36D UK	50 to 60 Hz	6.2 W	80 W
70525101	MASTERLEDspot VLE D 6.2-80W GU10 930 36D UK	50 to 60 Hz	6.2 W	80 W
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	-	5.5 W	80 W

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage equivalent
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	50 to 60 Hz	3.7 W	35 W
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	50 to 60 Hz	3.7 W	35 W
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	50 to 60 Hz	3.7 W	35 W

MASTER VALUE LEDspot MV

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage equivalent
70787601	MASTER LEDspotVLE D 4.9-50W GU10 930 36D UK	50 to 60 Hz	4.9 W	50 W
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	50 to 60 Hz	4.9 W	50 W
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	50 to 60 Hz	4.9 W	50 W
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	50 to 60 Hz	4.9 W	50 W
70811801	MASTER LED spot VLEDT4.9-50W GU10 927 36DUK	50 to 60 Hz	4.9 W	50 W
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	50 to 60 Hz	3.7 W	35 W
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	50 to 60 Hz	3.7 W	35 W
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	50 to 60 Hz	3.7 W	35 W

Temperature

Order Code	Full Product Name	T-Case maximum (nom.)
70523701	MASTERLEDspot VLE D 6.2-80W GU10 940 36D UK	80 °C
70525101	MASTERLEDspot VLE D 6.2-80W GU10 930 36D UK	80 °C
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	66 °C
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	80 °C
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	80 °C
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	80 °C
70787601	MASTER LEDspotVLE D 4.9-50W GU10 930 36D UK	65 °C
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	80 °C
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	80 °C
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	80 °C
70811801	MASTER LED spot VLEDT4.9-50W GU10 927 36DUK	65 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
70523701	MASTERLEDspot VLE D 6.2-80W GU10 940 36D UK	Yes
70525101	MASTERLEDspot VLE D 6.2-80W GU10 930 36D UK	Yes
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	Only with specific dimmers
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	Only with specific dimmers
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	Only with specific dimmers
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	Only with specific dimmers

Order Code	Full Product Name	Line Frequency	Power Consumption	Wattage equivalent
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	-	3.7 W	50 W
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	-	3.7 W	50 W
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	-	3.7 W	50 W
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	-	3.7 W	50 W
70609800	MASTER LED spot VLE D 650lm GU10 930 120D	50 to 60 Hz	6.2 W	-
70611100	MASTER LED spot VLE D 680lm GU10 940 120D	50 to 60 Hz	6.2 W	-
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	-	5.5 W	-
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	-	5.5 W	-

Order Code	Full Product Name	T-Case maximum (nom.)
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	70 °C
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	70 °C
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	70 °C
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	60 °C
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	66 °C
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	66 °C
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	62 °C
70609800	MASTER LED spot VLE D 650lm GU10 930 120D	80 °C
70611100	MASTER LED spot VLE D 680lm GU10 940 120D	80 °C
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	66 °C
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	66 °C

Order Code	Full Product Name	Dimmable
70787601	MASTER LEDspotVLE D 4.9-50W GU10 930 36D UK	Yes
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	Only with specific dimmers
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	Only with specific dimmers
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	Only with specific dimmers
70811801	MASTER LED spot VLEDT4.9-50W GU10 927 36DUK	Yes
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	Only with specific dimmers

MASTER VALUE LEDspot MV

Order Code	Full Product Name	Dimmable
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	Only with specific dimmers
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	Only with specific dimmers
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	Only with specific dimmers
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	Only with specific dimmers
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	Only with specific dimmers

Order Code	Full Product Name	Dimmable
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	Only with specific dimmers
70609800	MASTER LED spot VLE D 650lm GU10 930 120D	Only with specific dimmers
70611100	MASTER LED spot VLE D 680lm GU10 940 120D	Only with specific dimmers
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	Only with specific dimmers
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	Only with specific dimmers

Mechanical and Housing

Order Code	Full Product Name	Lamp Finish
70523701	MASTERLEDspot VLE D 6.2-80W GU10 940 36D UK	-
70525101	MASTERLEDspot VLE D 6.2-80W GU10 930 36D UK	-
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	Clear
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	-
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	-
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	-
70787601	MASTER LEDspotVLE D 4.9-50W GU10 930 36D UK	-
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	-
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	-
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	-
70811801	MASTER LED spot VLEDT4.9-50W GU10 927 36DUK	-

Order Code	Full Product Name	Lamp Finish
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	-
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	-
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	-
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	Clear
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	Clear
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	Clear
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	Clear
70609800	MASTER LED spot VLE D 650lm GU10 930 120D	-
70611100	MASTER LED spot VLE D 680lm GU10 940 120D	-
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	Frosted
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	Frosted


Approval and Application

Order Code	Full Product Name	Ambient temperature range	Energy consumption kWh/1,000 hours
70523701	MASTERLEDspot VLE D 6.2-80W GU10 940 36D UK	-	7 kWh
70525101	MASTERLEDspot VLE D 6.2-80W GU10 930 36D UK	-	7 kWh
03841800	MASTERLEDspot VLE D 5.5-80W GU10 927 36D UK	-20 to +45 °C	6 kWh
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	-	4 kWh
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	-	4 kWh
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	-	4 kWh
70787601	MASTER LEDspotVLE D 4.9-50W GU10 930 36D UK	-	5 kWh
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	-	5 kWh
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	-	5 kWh
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	-	5 kWh











Order Code	Full Product Name	Ambient temperature range	Energy consumption kWh/1,000 hours
70811801	MASTER LED spot VLEDT4.9-50W GU10 927 36DUK	-	5 kWh
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	-	4 kWh
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	-	4 kWh
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	-	4 kWh
39926600	MASTER LED spot VLEDT3.7-50W GU10 927 36DUK	-20 to +45 °C	4 kWh
39920400	MASTER LED spot VLE D 3.7-50W GU10 927 36D	-20 to +45 °C	4 kWh
39924200	MASTER LEDspotVLE D 3.7-50W GU10 940 36D UK	-20 to +45 °C	4 kWh
39938900	MASTER LED spot VLE D 3.7-50W GU10 940 60D	-20 to +45 °C	4 kWh
70609800	MASTER LED spot VLE D 650lm GU10 930 120D	-	7 kWh
70611100	MASTER LED spot VLE D 680lm GU10 940 120D	-	7 kWh

MASTER VALUE LEDspot MV



		Ambient temperature range	Energy consumption kWh/1,000 hours
03829600	MASTER LED spot VLE D 650lm GU10 930 120D	-20 to +45 °C	6 kWh
03833300	MASTER LED spot VLE D 680lm GU10 965 120D	-20 to +45 °C	6 kWh




MASTER VALUE LEDspot MV




MASTER VALUE LEDspot MV




Accent Diagrams




Accent Diagram - MAS LED spot VLE DT
4.9-50W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 940 60D



Accent Diagram - MAS LEDspotVLE D 4.9-50W
GU10 930 36D UK




Accent Diagram - MAS LED spot VLE D
4.9-50W GU10 927 60D




Accent Diagram - MAS LED spot VLE DT
3.7-35W GU10 927 36D


Accent Diagrams




Accent Diagram - MASLEDspot VLE D 6.2-80W
GU10 940 36D UK




Accent Diagram - MASLEDspot VLE D 5.5-80W
GU10 927 36D UK




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 927 60D




Accent Diagram - MAS LEDspotVLE D 3.7-50W
GU10 940 36D UK




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 36D



Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 940 60D




Accent Diagram - MASLEDspot VLE D 6.2-80W
GU10 930 36D UK




Accent Diagram - MAS LED spot VLEDT3.7-50W
GU10 927 36DUK


Beam Diagrams




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE DT 4.9-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 940 36D




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 940 60D




Beam diagram - MAS LEDspotVLE D 4.9-50W
GU10 930 36D UK




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 927 60D



Beam diagram - MASLEDspot VLE D 6.2-80W
GU10 930 36D UK




Beam diagram - MAS LEDspotVLE D 3.7-50W
GU10 940 36D UK




Beam diagram - MAS LED spot VLE DT 3.7-35W
GU10 927 36D

MASTER VALUE LEDspot MV


Beam Diagrams




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 927 60D




Beam diagram - MASLEDspot VLE D 5.5-80W
GU10 927 36D UK



Beam diagram - MAS LED spot VLEDT3.7-50W
GU10 927 36DUK



Beam diagram - MASLEDspot VLE D 6.2-80W
GU10 940 36D UK



Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 60D

