



La solution LED professionnelle gradable de référence

Lampes MASTER LEDspot Value GU10 DIM

Grâce à la gamme MASTER LEDspot GU10, il est à présent possible de réduire la consommation énergétique et les coûts de maintenance, sans transiger sur la qualité de lumière

Avantages

- - Retour sur investissement en 1 an sur la base d'un éclairage 24h/24
- - Faible dégagement de chaleur
- - Ne contient pas de mercure et répond à toutes les réglementations européennes en vigueur

Fonctions

- Compatible avec de nombreux variateurs
- Durée de vie de 25 000 à 45 000 heures
- Diffusion du faisceau clairement définie
- Lumière sans UV ni infrarouge pour réduire la chaleur et mieux protéger les objets sensibles à la chaleur

Application

- - Eclairage général et d'accentuation dans les hôtels, restaurants, commerces, bureaux

Mises en garde et sécurité

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights



Lampes MASTER LEDspot Value GU10 DIM

Versions



PAR16 GU10

Schéma dimensionnel



Product	D	C
MAS LED spot VLE D 3.7-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 mm	54 mm

Product	D	C
MAS LED spot VLE D 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 2.8-35W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-50W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 4.8-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE DT 2.8-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 5.5-80W GU10 927 36D	50 mm	54 mm

Lampes MASTER LEDspot Value GU10 DIM

Informations générales	
Culot	GU10
Durée de vie nominale	25.000 h
Données techniques de l'éclairage	
Indice de rendu de couleur (IRC)	90
LLMF à la fin de la durée de vie nominale (nom.)	70 %
Fonctionnement et électricité	
Fréquence d'entrée	50 à 60 Hz
Heure de démarrage (nom.)	0,5 s
Commandes et gradation	
Variation de l'intensité lumineuse	Uniquement avec certains variateurs
Mécanique et boîtier	
Forme de la lampe	PAR16

Informations générales

Order Code	Full Product Name	Nombre de cycles d'allumage
8721103038210	MAS LED spot VLE DT 5.5-80W GU10 927 36D	50.000
8721103038357	MAS LED spot VLE D 5.5-80W GU10 927 36D	50.000
8721103038272	MAS LED spot VLE D 5.5-80W GU10 930 36D	50.000
8721103038234	MAS LED spot VLE D 5.5-80W GU10 940 36D	50.000
8718696707753	MAS LED spot VLE D 3.7-35W GU10 930 36D	50.000
8718696707838	MAS LED spot VLE D 3.7-35W GU10 940 60D	50.000
8718696707876	MAS LED spot VLE D 4.9-50W GU10 930 36D	50.000
8718696707890	MAS LED spot VLE D 4.9-50W GU10 940 36D	50.000
8718696707913	MAS LED spot VLE D 4.9-50W GU10 927 60D	50.000
8718696707937	MAS LED spot VLE D 4.9-50W GU10 930 60D	50.000
8718696707951	MAS LED spot VLE D 4.9-50W GU10 940 60D	50.000
8718696708118	MAS LED spot VLE DT 4.9-50W GU10 927 36D	50.000
8719514312289	MAS LED spot VLE DT 3.7-35W GU10 927 36D	50.000
8719514312265	MAS LED spot VLE D 3.7-35W GU10 927 60D	50.000
8719514308138	MAS LED spot VLE D 4.8-50W GU10 927 36D	50.000
8720169399143	MAS LED spot VLE DT 2.8-35W GU10 927 36D	50.000
8720169399488	MAS LED spot VLE DT 3.7-50W GU10 927 36D	50.000
8720169399129	MAS LED spot VLE D 2.8-35W GU10 927 36D	50.000
8720169399280	MAS LED spot VLE D 2.8-35W GU10 930 36D	50.000
8720169399303	MAS LED spot VLE D 2.8-35W GU10 940 36D	50.000
8720169399167	MAS LED spot VLE D 2.8-35W GU10 927 60D	50.000
8720169399204	MAS LED spot VLE D 3.7-50W GU10 927 36D	50.000
8720169399440	MAS LED spot VLE D 3.7-50W GU10 930 36D	50.000
8720169399464	MAS LED spot VLE D 3.7-50W GU10 940 36D	50.000
8720169399341	MAS LED spot VLE D 3.7-50W GU10 927 60D	25.000
8720169399365	MAS LED spot VLE D 3.7-50W GU10 930 60D	25.000
8720169399389	MAS LED spot VLE D 3.7-50W GU10 940 60D	25.000

Données techniques de l'éclairage (1/2)

Order Code	Full Product Name	Angle du faisceau (nom.)	Température de couleur		Code couleur	Flux lumineux
			corrélée (nom.)			
8721103038210	MAS LED spot VLE DT 5.5-80W GU10 927 36D	36 degré(s)	2200 K		922-927	575 lm
8721103038357	MAS LED spot VLE D 5.5-80W GU10 927 36D	36 degré(s)	2700 K		927	575 lm
8721103038272	MAS LED spot VLE D 5.5-80W GU10 930 36D	36 degré(s)	3000 K		930	575 lm
8721103038234	MAS LED spot VLE D 5.5-80W GU10 940 36D	36 degré(s)	4000 K		940	575 lm
8718696707753	MAS LED spot VLE D 3.7-35W GU10 930 36D	36 degré(s)	3000 K		930	270 lm

Order Code	Full Product Name	Angle du faisceau (nom.)	Température de couleur		Code couleur	Flux lumineux
			corrélée (nom.)			
8718696707838	MAS LED spot VLE D 3.7-35W GU10 940 60D	60 degré(s)	4000 K		940	285 lm
8718696707876	MAS LED spot VLE D 4.9-50W GU10 930 36D	36 degré(s)	3000 K		930	365 lm
8718696707890	MAS LED spot VLE D 4.9-50W GU10 940 36D	36 degré(s)	4000 K		940	380 lm
8718696707913	MAS LED spot VLE D 4.9-50W GU10 927 60D	60 degré(s)	2700 K		927	355 lm
8718696707937	MAS LED spot VLE D 4.9-50W GU10 930 60D	60 degré(s)	3000 K		930	365 lm

Lampes MASTER LEDspot Value GU10 DIM

Order Code	Full Product Name	Angle du faisceau (nom.)	Température de couleur		Flux lumineux
			corrélée (nom.)	Code couleur	
8718696707951	MAS LED spot VLE D 4.9-50W GU10 940 60D	60 degré(s)	4000 K	940	380 lm
8718696708118	MAS LED spot VLE DT 4.9-50W GU10 927 36D	36 degré(s)	2200 K	922-927	355 lm
8719514312289	MAS LED spot VLE DT 3.7-35W GU10 927 36D	36 degré(s)	2200 K	922-927	270 lm
8719514312265	MAS LED spot VLE D 3.7-35W GU10 927 60D	60 degré(s)	2700 K	927	270 lm
8719514308138	MAS LED spot VLE D 4.8-50W GU10 927 36D	36 degré(s)	2700 K	927	355 lm
8720169399143	MAS LED spot VLE DT 2.8-35W GU10 927 36D	36 degré(s)	2200 K	922-927	280 lm
8720169399488	MAS LED spot VLE DT 3.7-50W GU10 927 36D	36 degré(s)	2200 K	922-927	355 lm
8720169399129	MAS LED spot VLE D 2.8-35W GU10 927 36D	36 degré(s)	2700 K	927	270 lm
8720169399280	MAS LED spot VLE D 2.8-35W GU10 930 36D	36 degré(s)	3000 K	930	270 lm

Données techniques de l'éclairage (2/2)

Order Code	Full Product Name	Intensité lumineuse (nom.)
8721103038210	MAS LED spot VLE DT 5.5-80W GU10 927 36D	950 cd
8721103038357	MAS LED spot VLE D 5.5-80W GU10 927 36D	950 cd
8721103038272	MAS LED spot VLE D 5.5-80W GU10 930 36D	1.000 cd
8721103038234	MAS LED spot VLE D 5.5-80W GU10 940 36D	1.000 cd
8718696707753	MAS LED spot VLE D 3.7-35W GU10 930 36D	500 cd
8718696707838	MAS LED spot VLE D 3.7-35W GU10 940 60D	350 cd
8718696707876	MAS LED spot VLE D 4.9-50W GU10 930 36D	650 cd
8718696707890	MAS LED spot VLE D 4.9-50W GU10 940 36D	700 cd
8718696707913	MAS LED spot VLE D 4.9-50W GU10 927 60D	400 cd
8718696707937	MAS LED spot VLE D 4.9-50W GU10 930 60D	400 cd
8718696707951	MAS LED spot VLE D 4.9-50W GU10 940 60D	400 cd
8718696708118	MAS LED spot VLE DT 4.9-50W GU10 927 36D	650 cd
8719514312289	MAS LED spot VLE DT 3.7-35W GU10 927 36D	500 cd
8719514312265	MAS LED spot VLE D 3.7-35W GU10 927 60D	300 cd

Order Code	Full Product Name	Angle du faisceau (nom.)	Température de couleur		Flux lumineux
			corrélée (nom.)	Code couleur	
8720169399303	MAS LED spot VLE D 2.8-35W GU10 940 36D	36 degré(s)	4000 K	940	285 lm
8720169399167	MAS LED spot VLE D 2.8-35W GU10 927 60D	60 degré(s)	2700 K	927	270 lm
8720169399204	MAS LED spot VLE D 3.7-50W GU10 927 36D	36 degré(s)	2700 K	927	355 lm
8720169399440	MAS LED spot VLE D 3.7-50W GU10 930 36D	36 degré(s)	3000 K	930	365 lm
8720169399464	MAS LED spot VLE D 3.7-50W GU10 940 36D	36 degré(s)	4000 K	940	380 lm
8720169399341	MAS LED spot VLE D 3.7-50W GU10 927 60D	60 degré(s)	2700 K	927	355 lm
8720169399365	MAS LED spot VLE D 3.7-50W GU10 930 60D	60 degré(s)	3000 K	930	365 lm
8720169399389	MAS LED spot VLE D 3.7-50W GU10 940 60D	60 degré(s)	4000 K	940	370 lm

Fonctionnement et électricité

Lampes MASTER LEDspot Value GU10 DIM

Order Code	Full Product Name	Fréquence linéaire	Consommation électrique	Puissance équivalente
8721103038210	MAS LED spot VLE DT 5.5-80W GU10 927 36D	-	5,5 W	80 W
8721103038357	MAS LED spot VLE D 5.5-80W GU10 927 36D	-	5,5 W	80 W
8721103038272	MAS LED spot VLE D 5.5-80W GU10 930 36D	-	5,5 W	80 W
8721103038234	MAS LED spot VLE D 5.5-80W GU10 940 36D	-	5,5 W	80 W
8718696707753	MAS LED spot VLE D 3.7-35W GU10 930 36D	50 to 60 Hz	3,7 W	35 W
8718696707838	MAS LED spot VLE D 3.7-35W GU10 940 60D	50 to 60 Hz	3,7 W	35 W
8718696707876	MAS LED spot VLE D 4.9-50W GU10 930 36D	50 to 60 Hz	4,9 W	50 W
8718696707890	MAS LED spot VLE D 4.9-50W GU10 940 36D	50 to 60 Hz	4,9 W	50 W
8718696707913	MAS LED spot VLE D 4.9-50W GU10 927 60D	50 to 60 Hz	4,9 W	50 W
8718696707937	MAS LED spot VLE D 4.9-50W GU10 930 60D	50 to 60 Hz	4,9 W	50 W
8718696707951	MAS LED spot VLE D 4.9-50W GU10 940 60D	50 to 60 Hz	4,9 W	50 W
8718696708118	MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 to 60 Hz	4,9 W	50 W
8719514312289	MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 to 60 Hz	3,7 W	35 W
8719514312265	MAS LED spot VLE D 3.7-35W GU10 927 60D	50 to 60 Hz	3,7 W	35 W

Température

Order Code	Full Product Name	Température maximale du produit (nom.)
8721103038210	MAS LED spot VLE DT 5.5-80W GU10 927 36D	66 °C
8721103038357	MAS LED spot VLE D 5.5-80W GU10 927 36D	66 °C
8721103038272	MAS LED spot VLE D 5.5-80W GU10 930 36D	66 °C

Order Code	Full Product Name	Fréquence linéaire	Consommation électrique	Puissance équivalente
8719514308138	MAS LED spot VLE D 4.8-50W GU10 927 36D	50 to 60 Hz	4,8 W	50 W
8720169399143	MAS LED spot VLE DT 2.8-35W GU10 927 36D	-	2,8 W	35 W
8720169399488	MAS LED spot VLE DT 3.7-50W GU10 927 36D	-	3,7 W	50 W
8720169399129	MAS LED spot VLE D 2.8-35W GU10 927 36D	-	2,8 W	35 W
8720169399280	MAS LED spot VLE D 2.8-35W GU10 930 36D	-	2,8 W	35 W
8720169399303	MAS LED spot VLE D 2.8-35W GU10 940 36D	-	2,8 W	35 W
8720169399167	MAS LED spot VLE D 2.8-35W GU10 927 60D	-	2,8 W	35 W
8720169399204	MAS LED spot VLE D 3.7-50W GU10 927 36D	-	3,7 W	50 W
8720169399440	MAS LED spot VLE D 3.7-50W GU10 930 36D	-	3,7 W	50 W
8720169399464	MAS LED spot VLE D 3.7-50W GU10 940 36D	-	3,7 W	50 W
8720169399341	MAS LED spot VLE D 3.7-50W GU10 927 60D	-	3,7 W	50 W
8720169399365	MAS LED spot VLE D 3.7-50W GU10 930 60D	-	3,7 W	50 W
8720169399389	MAS LED spot VLE D 3.7-50W GU10 940 60D	-	3,7 W	50 W

Order Code	Full Product Name	Température maximale du produit (nom.)
8721103038234	MAS LED spot VLE D 5.5-80W GU10 940 36D	66 °C
8718696707753	MAS LED spot VLE D 3.7-35W GU10 930 36D	80 °C
8718696707838	MAS LED spot VLE D 3.7-35W GU10 940 60D	80 °C

Lampes MASTER LEDspot Value GU10 DIM

Order Code	Full Product Name	Température maximale du produit (nom.)
8718696707876	MAS LED spot VLE D 4.9-50W GU10 930 36D	80 °C
8718696707890	MAS LED spot VLE D 4.9-50W GU10 940 36D	80 °C
8718696707913	MAS LED spot VLE D 4.9-50W GU10 927 60D	80 °C
8718696707937	MAS LED spot VLE D 4.9-50W GU10 930 60D	80 °C
8718696707951	MAS LED spot VLE D 4.9-50W GU10 940 60D	80 °C
8718696708118	MAS LED spot VLE DT 4.9-50W GU10 927 36D	80 °C
8719514312289	MAS LED spot VLE DT 3.7-35W GU10 927 36D	70 °C
8719514312265	MAS LED spot VLE D 3.7-35W GU10 927 60D	70 °C
8719514308138	MAS LED spot VLE D 4.8-50W GU10 927 36D	80 °C
8720169399143	MAS LED spot VLE DT 2.8-35W GU10 927 36D	52 °C
8720169399488	MAS LED spot VLE DT 3.7-50W GU10 927 36D	60 °C

Mécanique et boîtier

Order Code	Full Product Name	Finition ampoule
8721103038210	MAS LED spot VLE DT 5.5-80W GU10 927 36D	Transparent
8721103038357	MAS LED spot VLE D 5.5-80W GU10 927 36D	Transparent
8721103038272	MAS LED spot VLE D 5.5-80W GU10 930 36D	Transparent
8721103038234	MAS LED spot VLE D 5.5-80W GU10 940 36D	Transparent
8718696707753	MAS LED spot VLE D 3.7-35W GU10 930 36D	-
8718696707838	MAS LED spot VLE D 3.7-35W GU10 940 60D	-
8718696707876	MAS LED spot VLE D 4.9-50W GU10 930 36D	-
8718696707890	MAS LED spot VLE D 4.9-50W GU10 940 36D	-
8718696707913	MAS LED spot VLE D 4.9-50W GU10 927 60D	-
8718696707937	MAS LED spot VLE D 4.9-50W GU10 930 60D	-
8718696707951	MAS LED spot VLE D 4.9-50W GU10 940 60D	-
8718696708118	MAS LED spot VLE DT 4.9-50W GU10 927 36D	-
8719514312289	MAS LED spot VLE DT 3.7-35W GU10 927 36D	-
8719514312265	MAS LED spot VLE D 3.7-35W GU10 927 60D	-

Approbation et application

Order Code	Full Product Name	Gamme de températures ambiantes	Consommation d'énergie kWh/ 1 000 h
8721103038210	MAS LED spot VLE DT 5.5-80W GU10 927 36D	-20 à +45 °C	6 kWh
8721103038357	MAS LED spot VLE D 5.5-80W GU10 927 36D	-20 à +45 °C	6 kWh
8721103038272	MAS LED spot VLE D 5.5-80W GU10 930 36D	-20 à +45 °C	6 kWh
8721103038234	MAS LED spot VLE D 5.5-80W GU10 940 36D	-20 à +45 °C	6 kWh
8718696707753	MAS LED spot VLE D 3.7-35W GU10 930 36D	-	4 kWh
8718696707838	MAS LED spot VLE D 3.7-35W GU10 940 60D	-	4 kWh
8718696707876	MAS LED spot VLE D 4.9-50W GU10 930 36D	-	5 kWh



Order Code	Full Product Name	Température maximale du produit (nom.)
8720169399129	MAS LED spot VLE D 2.8-35W GU10 927 36D	50 °C
8720169399280	MAS LED spot VLE D 2.8-35W GU10 930 36D	50 °C
8720169399303	MAS LED spot VLE D 2.8-35W GU10 940 36D	50 °C
8720169399167	MAS LED spot VLE D 2.8-35W GU10 927 60D	50 °C
8720169399204	MAS LED spot VLE D 3.7-50W GU10 927 36D	66 °C
8720169399440	MAS LED spot VLE D 3.7-50W GU10 930 36D	66 °C
8720169399464	MAS LED spot VLE D 3.7-50W GU10 940 36D	66 °C
8720169399341	MAS LED spot VLE D 3.7-50W GU10 927 60D	62 °C
8720169399365	MAS LED spot VLE D 3.7-50W GU10 930 60D	62 °C
8720169399389	MAS LED spot VLE D 3.7-50W GU10 940 60D	62 °C


Order Code	Full Product Name	Finition ampoule
8719514308138	MAS LED spot VLE D 4.8-50W GU10 927 36D	-
8720169399143	MAS LED spot VLE DT 2.8-35W GU10 927 36D	Transparent
8720169399488	MAS LED spot VLE DT 3.7-50W GU10 927 36D	Transparent
8720169399129	MAS LED spot VLE D 2.8-35W GU10 927 36D	Transparent
8720169399280	MAS LED spot VLE D 2.8-35W GU10 930 36D	Transparent
8720169399303	MAS LED spot VLE D 2.8-35W GU10 940 36D	Transparent
8720169399167	MAS LED spot VLE D 2.8-35W GU10 927 60D	Transparent
8720169399204	MAS LED spot VLE D 3.7-50W GU10 927 36D	Transparent
8720169399440	MAS LED spot VLE D 3.7-50W GU10 930 36D	Transparent
8720169399464	MAS LED spot VLE D 3.7-50W GU10 940 36D	Transparent
8720169399341	MAS LED spot VLE D 3.7-50W GU10 927 60D	Transparent
8720169399365	MAS LED spot VLE D 3.7-50W GU10 930 60D	Transparent
8720169399389	MAS LED spot VLE D 3.7-50W GU10 940 60D	Transparent

Order Code	Full Product Name	Gamme de températures ambiantes	Consommation d'énergie kWh/ 1 000 h
8718696707890	MAS LED spot VLE D 4.9-50W GU10 940 36D	-	5 kWh
8718696707913	MAS LED spot VLE D 4.9-50W GU10 927 60D	-	5 kWh
8718696707937	MAS LED spot VLE D 4.9-50W GU10 930 60D	-	5 kWh
8718696707951	MAS LED spot VLE D 4.9-50W GU10 940 60D	-	5 kWh
8718696708118	MAS LED spot VLE DT 4.9-50W GU10 927 36D	-	5 kWh
8719514312289	MAS LED spot VLE DT 3.7-35W GU10 927 36D	-	4 kWh
8719514312265	MAS LED spot VLE D 3.7-35W GU10 927 60D	-	4 kWh











Lampes MASTER LEDspot Value GU10 DIM

Order Code	Full Product Name	Gamme de températures ambiantes	Consommation d'énergie kWh/ 1 000 h
8719514308138	MAS LED spot VLE D 4.8-50W GU10 927 36D	-	5 kWh
8720169399143	MAS LED spot VLE DT 2.8-35W GU10 927 36D	-20 à +45 °C	3 kWh
8720169399488	MAS LED spot VLE DT 3.7-50W GU10 927 36D	-20 à +45 °C	4 kWh
8720169399129	MAS LED spot VLE D 2.8-35W GU10 927 36D	-20 à +45 °C	3 kWh
8720169399280	MAS LED spot VLE D 2.8-35W GU10 930 36D	-20 à +45 °C	3 kWh
8720169399303	MAS LED spot VLE D 2.8-35W GU10 940 36D	-20 à +45 °C	3 kWh
8720169399167	MAS LED spot VLE D 2.8-35W GU10 927 60D	-20 à +45 °C	3 kWh
8720169399204	MAS LED spot VLE D 3.7-50W GU10 927 36D	-20 à +45 °C	4 kWh
8720169399440	MAS LED spot VLE D 3.7-50W GU10 930 36D	-20 à +45 °C	4 kWh
8720169399464	MAS LED spot VLE D 3.7-50W GU10 940 36D	-20 à +45 °C	4 kWh
8720169399341	MAS LED spot VLE D 3.7-50W GU10 927 60D	-20 à +45 °C	4 kWh
8720169399365	MAS LED spot VLE D 3.7-50W GU10 930 60D	-20 à +45 °C	4 kWh
8720169399389	MAS LED spot VLE D 3.7-50W GU10 940 60D	-20 à +45 °C	4 kWh








Lampes MASTER LEDspot Value GU10 DIM




Lampes MASTER LEDspot Value GU10 DIM




Accent Diagrams




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 930 36D




Accent Diagram - MAS LED spot VLE DT
4.9-50W GU10 927 36D




**Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 930 36D**




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 940 60D




Accent Diagram - MAS LED spot VLE D
4.9-50W GU10 940 36D




Accent Diagram - MAS LED spot VLE D
4.9-50W GU10 927 60D



Accent Diagram - MAS LED spot VLE DT
3.7-35W GU10 927 36D




**Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D**




Accent Diagram - MAS LED spot VLE DT
5.5-80W GU10 927 36D

Lampes MASTER LEDspot Value GU10 DIM


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 927 60D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 930 36D



Accent Diagram - MAS LED spot VLE D 3.7-50W
GU10 927 36D




Accent Diagram - MAS LED spot VLE D 2.8-35W
GU10 927 36D




Accent Diagram - MAS LED spot VLE D 4.8-50W
GU10 927 36D

Lampes MASTER LEDspot Value GU10 DIM


Accent Diagrams




Accent Diagram - MAS LED spot VLE D 3.7-50W GU10 940 60D




Accent Diagram - MAS LED spot VLE D 2.8-35W GU10 927 60D



Accent Diagram - MAS LED spot VLE D 3.7-50W GU10 930 60D




Accent Diagram - MAS LED spot VLE DT 2.8-35W GU10 927 36D




Accent Diagram - MAS LED spot VLE DT 3.7-50W GU10 927 36D


Beam Diagrams



Beam diagram - MAS LED spot VLE DT 5.5-80W GU10 927 36D




Beam diagram - MAS LED spot VLE DT 4.9-50W GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-35W GU10 930 36D

Lampes MASTER LEDspot Value GU10 DIM


Beam Diagrams




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 940 60D




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 940 36D




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 927 60D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 940 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 36D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 927 60D



Beam diagram - MAS LED spot VLE DT 2.8-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 4.8-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 930 36D

Lampes MASTER LEDspot Value GU10 DIM


Beam Diagrams




Beam diagram - MAS LED spot VLE D 5.5-80W
GU10 940 36D




Beam diagram - MAS LED spot VLE DT 3.7-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 927 60D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 927 60D




Beam diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D



Beam diagram - MAS LED spot VLE DT 3.7-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 930 60D




Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 940 60D

Lampes MASTER LEDspot Value GU10 DIM

Beam Diagrams



Beam diagram - MAS LED spot VLE D 2.8-35W
GU10 927 36D



Beam diagram - MAS LED spot VLE D 3.7-50W
GU10 930 36D

