



MASTER Value LEDspot MV 性价比出色，非常适合聚光照明

MASTER VALUE LEDspot MV

MASTER VALUE 可提供如同卤素灯般的重点照明暖光束，是聚光照明的理想之选。本产品具有高 CRI，光色更为自然，可为住宅和酒店项目营造温馨舒适的氛围，突显零售商品的独特美感。此 LED MV GU10 射灯采用与普通射灯类似的外观和质感，既保留了玻璃射灯的经典美感，又增添了强大的 LED 技术性能。调光功能可以营造理想的舒心氛围，并可兼容多种调光器。MASTER VALUE 的节能效果比普通 LED 射灯更为出众。

优点

- 与卤素灯相比，MASTER VALUE 射灯的节能效果高达 80%
- 可以很好地模拟卤素射灯营造氛围
- 传统 GU10 灯具的理想替代品

特点

- 可调光范围
- 兼容种类繁多的调光器
- 获得专利的智能驱动器
- 25,000 小时的使用寿命
- 无紫外线和冷光束（无红外线），因此适合热敏感物体（食品、有机材料、绘画等）的照明

应用

- 酒店照明
- 商场照明
- 住宅



MASTER VALUE LEDspot MV

Versions



LEDspot Corepro GU10 PAR16

二维绘图



Product	D	C
MAS LED spot VLE D 6.2-80W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 6.2-80W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 6.2-80W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 6.2-80W GU10 965 36D	50 mm	54 mm
MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 mm	54 mm
Master LED 4.9-50W GU10 927 36D Dim	50 mm	54 mm
Master LED 4.9-50W GU10 930 36D Dim	50 mm	54 mm
Master LED 4.9-50W GU10 940 36D Dim	50 mm	54 mm

Product	D	C
MAS LED spot VLE D 5.5-80W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 5.5-80W GU10 965 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-50W GU10 927 36D	50 mm	54 mm

MASTER VALUE LEDspot MV

一般信息	
底盖	GU10
切换循环	50,000
标称使用寿命	25,000 小时
灯技术	
光束角度 (标称)	36 °
显色指数 (CRI)	90
标称使用寿命结束时灯的光通维持率 (标称)	70 %
操作和电气	
输入频率	50 至 60 Hz
启动时间 (标称)	0.5 s
机械和外壳	
灯泡外形	PAR16

灯技术

Order Code	Full Product Name	相关色温(标称)	颜色代码	光通量	发光强度(标称)
929002059502	MAS LED spot VLE D 6.2-80W GU10 927 36D	2700 K	927	575 lm	850 cd
929002066002	MAS LED spot VLE D 6.2-80W GU10 940 36D	4000 K	940	575 lm	850 cd
929002068402	MAS LED spot VLE D 6.2-80W GU10 930 36D	3000 K	930	575 lm	850 cd
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	6500 K	6500	575 lm	850 cd
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	2700 K	927	575 lm	950 cd
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	3000 K	930	575 lm	1,000 cd
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	4000 K	940	575 lm	1,000 cd
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	6500 K	965	575 lm	1,000 cd
929001348808	Master LED 4.9-50W GU10 927 36D Dim	2700 K	927	395 lm	650 cd
929001348908	Master LED 4.9-50W GU10 930 36D Dim	3000 K	930	405 lm	650 cd
929001349008	Master LED 4.9-50W GU10 940 36D Dim	4000 K	940	420 lm	700 cd
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	2200 K	922-927	355 lm	650 cd
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	2200 K	922-927	355 lm	700 cd

操作和电气

Order Code	Full Product Name	线频率	功耗	瓦数相当
929002059502	MAS LED spot VLE D 6.2-80W GU10 927 36D	50 to 60 Hz	6.2 W	80 W
929002066002	MAS LED spot VLE D 6.2-80W GU10 940 36D	50 to 60 Hz	6.2 W	80 W
929002068402	MAS LED spot VLE D 6.2-80W GU10 930 36D	50 to 60 Hz	6.2 W	80 W
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	50 to 60 Hz	6.2 W	80 W
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	-	5.5 W	80 W
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	-	5.5 W	80 W
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	-	5.5 W	80 W

Order Code	Full Product Name	线频率	功耗	瓦数相当
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	-	5.5 W	80 W
929001348808	Master LED 4.9-50W GU10 927 36D Dim	50 to 60 Hz	5 W	50 W
929001348908	Master LED 4.9-50W GU10 930 36D Dim	50 to 60 Hz	5 W	50 W
929001349008	Master LED 4.9-50W GU10 940 36D Dim	50 to 60 Hz	5 W	50 W
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 to 60 Hz	4.9 W	50 W
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	-	3.7 W	50 W

温度

Order Code	Full Product Name	最大外壳温度 (标称)
929002059502	MAS LED spot VLE D 6.2-80W GU10 927 36D	80 °C
929002066002	MAS LED spot VLE D 6.2-80W GU10 940 36D	80 °C
929002068402	MAS LED spot VLE D 6.2-80W GU10 930 36D	80 °C
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	80 °C
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	66 °C

Order Code	Full Product Name	最大外壳温度 (标称)
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	66 °C
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	66 °C
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	66 °C
929001348808	Master LED 4.9-50W GU10 927 36D Dim	80 °C
929001348908	Master LED 4.9-50W GU10 930 36D Dim	80 °C

MASTER VALUE LEDspot MV

Order Code	Full Product Name	最大外亮温度 (标称)
929001349008	Master LED 4.9-50W GU10 940 36D Dim	80 °C
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	80 °C

控制和调光

Order Code	Full Product Name	可调光
929002059502	MAS LED spot VLE D 6.2-80W GU10 927 36D	仅限于使用特定调光器
929002066002	MAS LED spot VLE D 6.2-80W GU10 940 36D	仅限于使用特定调光器
929002068402	MAS LED spot VLE D 6.2-80W GU10 930 36D	仅限于使用特定调光器
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	仅限于使用特定调光器
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	仅限于使用特定调光器
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	仅限于使用特定调光器
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	仅限于使用特定调光器

机械和外壳

Order Code	Full Product Name	灯泡外观
929002059502	MAS LED spot VLE D 6.2-80W GU10 927 36D	-
929002066002	MAS LED spot VLE D 6.2-80W GU10 940 36D	-
929002068402	MAS LED spot VLE D 6.2-80W GU10 930 36D	-
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	-
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	透明
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	透明
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	透明

审批和申请


Order Code	Full Product Name	环境温度范围	能耗 kWh/ 1000 h
929002059502	MAS LED spot VLE D 6.2-80W GU10 927 36D	-	7 kWh
929002066002	MAS LED spot VLE D 6.2-80W GU10 940 36D	-	7 kWh
929002068402	MAS LED spot VLE D 6.2-80W GU10 930 36D	-	7 kWh
929002209902	MAS LED spot VLE D 6.2-80W GU10 965 36D	-	7 kWh
929004255802	MAS LED spot VLE D 5.5-80W GU10 927 36D	-20 至 +45°C	6 kWh
929004255902	MAS LED spot VLE D 5.5-80W GU10 930 36D	-20 至 +45°C	6 kWh
929004256002	MAS LED spot VLE D 5.5-80W GU10 940 36D	-20 至 +45°C	6 kWh
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	-20 至 +45°C	6 kWh
929001348808	Master LED 4.9-50W GU10 927 36D Dim	-	5 kWh
929001348908	Master LED 4.9-50W GU10 930 36D Dim	-	5 kWh
929001349008	Master LED 4.9-50W GU10 940 36D Dim	-	5 kWh
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	-	5 kWh



Order Code	Full Product Name	最大外亮温度 (标称)
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	60 °C

Order Code	Full Product Name	可调光
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	仅限于使用特定调光器
929001348808	Master LED 4.9-50W GU10 927 36D Dim	是
929001348908	Master LED 4.9-50W GU10 930 36D Dim	是
929001349008	Master LED 4.9-50W GU10 940 36D Dim	是
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	仅限于使用特定调光器
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	仅限于使用特定调光器


Order Code	Full Product Name	灯泡外观
929004256102	MAS LED spot VLE D 5.5-80W GU10 965 36D	透明
929001348808	Master LED 4.9-50W GU10 927 36D Dim	-
929001348908	Master LED 4.9-50W GU10 930 36D Dim	-
929001349008	Master LED 4.9-50W GU10 940 36D Dim	-
929001350302	MAS LED spot VLE DT 4.9-50W GU10 927 36D	-
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	透明

Order Code	Full Product Name	环境温度范围	能耗 kWh/ 1000 h
929004247202	MAS LED spot VLE DT 3.7-50W GU10 927 36D	-20 至 +45°C	4 kWh







Accent Diagrams




Accent Diagram - MAS LED spot VLE DT
4.9-50W GU10 927 36D




Accent Diagram - Master LED 4.9-50W GU10
927 36D Dim




Accent Diagram - MAS LED spot VLE D 6.2-80W
GU10 965 36D




Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 927 36D



Accent Diagram - MAS LED spot VLE D 5.5-80W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 6.2-80W
GU10 930 36D




Accent Diagram - MAS LED spot VLE DT
3.7-50W GU10 927 36D


Beam Diagrams




Beam diagram - MAS LED spot VLE DT 4.9-50W GU10 927 36D




Beam diagram - Master LED 4.9-50W GU10 927 36D Dim




Beam diagram - MAS LED spot VLE D 6.2-80W GU10 930 36D




Beam diagram - MAS LED spot VLE D 5.5-80W GU10 940 36D



Beam diagram - MAS LED spot VLE D 5.5-80W GU10 927 36D



Beam diagram - MAS LED spot VLE DT 3.7-50W GU10 927 36D



Beam diagram - MAS LED spot VLE D 6.2-80W GU10 965 36D

