



# MASTER LEDspot PAR – The energy-saving alternative for lighting in public areas

## MASTER LEDspot PAR

With its robust design and warm-white beam of light, these new-generation PAR lamps are ideal for general lighting and spot lighting in the hospitality industry. There is a choice of dimmable and non-dimmable versions. They are especially suitable for public areas such as lobbies, corridors, stairwells, where the light is always on. Compatible with existing fixtures with an E27 holder and designed for retrofit replacement of halogen/incandescent lamps, MASTER LEDspot PAR deliver huge energy savings and minimize maintenance cost without any reduction in brightness. The IP44-rated outdoor version of the PAR 38 lamp is one of the few energy-saving alternatives to incandescent PAR38 outdoor lamps available today. The dimmable PAR 20 is a perfect replacement for an incandescent spot.

### Benefits

- Up to 80% energy saving compared to halogen lamps
- Retrofittable and compatible with existing fixtures with E27 holder
- Lower maintenance costs

### Features

- Lifetime of 45,000 hours
- Dimmable
- UV- and IR-free light for less heat and protection for heat-sensitive objects
- Free of mercury and hazardous materials

# MASTER LEDspot PAR

## Application


- Especially suitable for public areas like lobbies, corridors, stairwells and restaurants/bars

## Versions




MASTER LEDspot PAR 100W E27 827 25D

## Dimensional drawing




Product	D	C
LEDClassic 10-80WPAR38 827 25D 1CT/3 SRT	122 mm	134 mm




MASTER LEDspot PAR

Accent Diagrams



Accent Diagram - LEDClassic 10-80WPAR38  
827 25D 1CT/3 SRT

Beam Diagrams



Beam diagram - LEDClassic 10-80WPAR38 827  
25D 1CT/3 SRT

