



# SmartBright Panel. Trusted performance. Everyday.

## SmartBright Pro Panel

The Philips SmartBright range is comprised of a selection of essential LED luminaires that come with Philips high levels of quality at a competitive price. Reliable, energy efficient and affordable lighting solutions that you can count on to deliver what they promise. Philips SmartBright Panels are our most affordable LED solution. The complete product family is available in multiple mounting types, product dimensions and lumen options to suit the widest range of applications. And thanks to the Direct-lit structure, SmartBright panels deliver both higher system efficacy and excellent lighting uniformity. The essential range of LED panels for everyday installations.

### Benefits

- Philips quality and reliability
- Energy saving
- Comfortable lighting experience
- Suitable for office working place

### Features


- Modern, unobtrusive design
- System efficacy 105lm/W
- Flicker Free, CRI 80, RG0
- Multiple mounting options: recessed, suspended, plaster ceiling (PCV)

### Application

- Offices
- Hospitals and Care Centers
- Retail

# SmartBright Pro Panel

## Dimensional drawing



## Product details



SmartBright Pro Panel



SmartBright Pro Panel

# SmartBright Pro Panel

Light Technical	
Color rendering index (CRI)	≥80
Luminous Efficacy (rated) (Nom)	105 lm/W
Luminous Flux	4,000 lm
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	38 W
Controls and Dimming	
Dimmable	-
Mechanical and Housing	
Optical cover type	PMMA
Housing Color	White RAL 9003
Mech. impact protection code	IK02
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-10 to +40 °C
CE mark	No
Flammability mark	For mounting on normally flammable surfaces
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical		
Order Code	Full Product Name	Correlated Color Temperature (Nom)
911401816088	RC055B LED40S/865 PSU W60L60 GM G2	6500 K
911401816188	RC055B LED40S/840 PSU W60L60 GM G2	4000 K

