



Trusted performance. Every day.

Ledinaire panel gen5

The Philips Ledinaire panel Gen5 (RC065B/RC066B) range features a selection of popular off-the-shelf LED luminaires that offer Philips high quality at a competitive price. Reliable, energy-efficient and affordable, this latest generation of 600 x 600 mm, 620 x 620 mm, 300 x 1200 mm, and 600 x 1200 Ledinaire LED panel lights are designed for diffuse, comfortable lighting in a wide range of general lighting applications. Our range of Ledinaire panels lighting is also available with accessories for easy installation on different types of ceilings—just what you need.

Benefits

- No risks, trusted performance
- Good quality, easy to use
- No confusion, easy product selection
- Innovative All-in multicolor and basic lighting control versions
- Broad range

Features

- 3400 lm/ 3600 lm / 4100 lm: L80 at 50K hrs, L70 75K hrs and 3-year warranty
- IP20/IP40
- Connectors: white quick connectors and flywire
- Sizes: 60 x 60 mm / 62 x 62 mm / 30 x 120 mm / 60 x 120 mm
- Color rendering: CRI 80 at SDCM <5
- 3000K / 3500K / 4000K / 6500K
- PSU / PSD
- Efficacy: 120lm/W
- All-in: 3000K, 3500K, and 4000K in one luminaire
- Emergency lighting via standalone emergency lighting kit

Ledinaire panel gen5

Application

- Offices
- Healthcare
- Education
- Municipal buildings
- Retail

Versions

Ledinaire Panel PSD All-in
830_835_840 W60L60 OC



Ledinaire Panel



Ledinaire panel G5 60x120



Ledinaire panel G5 62x62



Ledinaire Panel PSU All-in
830_835_840 W60L60 OC



Ledinaire Panel All-in PSU 60x60



Ledinaire Panel G5 All in W30L120
RTP









Ledinaire panel gen5

Versions




Dimensional drawing



Ledinaire panel gen5

Dimensional drawing



Ledinaire panel gen5


Product details



Ledinaire Panel G5 RC066B-
frontside-straight



Ledinaire Panel G5 All in CCT
Switch 3000K



White Quick connector-closed



Panel flywires CFW + backside
panel



Ledinaire Panel G5 All in CCT
Switch PSU ON OFF Driver Open
connector



Ledinaire Panel G5 PSD DALI
Driver Open connector



Ledinaire Panel G5 All in CCT
Switch PSD ON OFF Driver Closed
connector



Ledinaire Panel G5 PSD DALI
Driver Closed connector




RC066B Ledinaire panel G4 -
frontside- angle

Ledinaire panel gen5

Product details




Ledinaire panel G5 frame and optical area 60x120




White Quick connector+wire-closed



Ledinaire Panel Gen 5-RC065B W60L120-backside




RC066B Ledinaire panel G4 - frontside- straight



White Quick connector +wire-open




Ledinaire panel gen 4 PSU driver and open connector



White Quick connector-open



Ledinaire Panel G5 All in CCT Switch PSD ON OFF Driver Open connector



Ledinaire Panel RC065B G5 30x120 Packaging

Ledinaire panel gen5

Product details



RC066B Ledinaire panel G4 -
backside



Panel flywires CFW



Ledinaire Panel RC065B Square
backside



Ledinaire panel G4_BN frame and
optical area 62x62



Ledinaire Panel Gen 5-
RC065B_RC066B Square-
backside-PSU driver and
connector



Ledinaire Panel Gen 5-
RC065B_RC066B Square-
backside



Ledinaire Panel RC065B G5 PSU
30x120 Backside



Ledinaire Panel G5 All in CCT
Switch PSU ON OFF Driver Closed
connector



Ledinaire Panel G5 All in CCT
Switch 3500K

Ledinaire panel gen5

Product details



Ledinaire Panel G5 All in CCT
Switch 4000K



UGR19 optical exit window



Ledinaire Panel Gen 5-RC065B
W60L120-backside-PSU driver
and Flywire



Ledinaire panel gen 4 PSU driver
and closed connector



Ledinaire Panel Gen 5-
RC065B_RC066B Square-
backside-PSU driver and
connector



Ledinaire panel G5 frame and
optical area 62x62

Ledinaire panel gen5

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>80
Operating and Electrical	
Protection class IEC	Safety class II
Line Frequency	50 or 60 Hz
Mechanical and Housing	
Housing Color	White
Mech. impact protection code	IK02
Approval and Application	
CE mark	Yes
ENEC mark	-
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1

General Information

Order Code	Full Product Name	Light source replaceable	Service tag
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	-	-
50129499	RC066B LED34S/840 PSD W62L62 OC BN	No	-
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	-	-
51666399	RC066B 34S/840 PSU W62L62 OC	-	-
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	-	-
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	-	-
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	-	-
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	-	-
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	-	-
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	-	-
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	-	-
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	-	-
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	-	-
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	-	-
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	-	-
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	-	-
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	-	-
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	-	-
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	-	-
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	-	-
36558999	RC066B LED34S/840 PSU W62L62 OC	No	No

Light Technical (1/2)

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	All-in, Multi Color Temperature	90 degree(s)	3000 K	120 lm/W
50129499	RC066B LED34S/840 PSD W62L62 OC BN	-	-	4000 K	100 lm/W
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	-	120 degree(s)	4000 K	120 lm/W
51666399	RC066B 34S/840 PSU W62L62 OC	-	90 degree(s)	4000 K	120 lm/W
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	All-in, Multi Color Temperature	90 degree(s)	3000 K	120 lm/W
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	All-in, Multi Color Temperature	120 degree(s)	3000 K	120 lm/W
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	-	90 degree(s)	4000 K	120 lm/W
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	-	90 degree(s)	4000 K	120 lm/W
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	-	90 degree(s)	6500 K	120 lm/W
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	-	120 degree(s)	4000 K	120 lm/W

Ledinaire panel gen5

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	-	120 degree(s)	6500 K	120 lm/W
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	-	90 degree(s)	4000 K	120 lm/W
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	-	90 degree(s)	4000 K	120 lm/W
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	-	120 degree(s)	4000 K	120 lm/W
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	-	90 degree(s)	4000 K	120 lm/W
51661899	RC065B G5 41S/840 PSU	-	120 degree(s)	4000 K	120 lm/W

Order Code	Full Product Name	All-in Type	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)
	W60L60 NOC CFW CL				
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	-	90 degree(s)	4000 K	120 lm/W
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	-	120 degree(s)	4000 K	120 lm/W
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	-	90 degree(s)	4000 K	120 lm/W
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	All-in, Multi Color Temperature	90 degree(s)	3000 K	120 lm/W
36558999	RC066B LED34S/840 PSU W62L62 OC	-	-	4000 K	100 lm/W

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	3,400 lm	Beam angle 90°
50129499	RC066B LED34S/840 PSD W62L62 OC BN	3,400 lm	Beam angle 90°
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	6,000 lm	Beam angle 120°
51666399	RC066B 34S/840 PSU W62L62 OC	3,400 lm	Beam angle 90°
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	3,400 lm	Beam angle 90°
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	3,400 lm	Beam angle 120°
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	3,400 lm	Beam angle 90°
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	3,400 lm	Beam angle 90°
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	3,400 lm	Beam angle 90°
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	3,400 lm	Beam angle 120°
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	3,400 lm	Beam angle 120°

Order Code	Full Product Name	Luminous Flux	Optic type
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	3,400 lm	Beam angle 90°
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	3,400 lm	Beam angle 90°
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	4,100 lm	Beam angle 120°
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	4,100 lm	Beam angle 90°
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	4,100 lm	Beam angle 120°
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	4,100 lm	Beam angle 90°
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	3,400 lm	Beam angle 120°
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	3,400 lm	Beam angle 90°
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	3,400 lm	Beam angle 90°
36558999	RC066B LED34S/840 PSU W62L62 OC	3,400 lm	Beam angle 90°

Operating and Electrical

Ledinaire panel gen5

Order Code	Full Product Name	Input Voltage	Power	Suitable for random switching
			Consumption	
51697799	RC065B G5 34_36S/ 830_40 PSD W60L60 OC SC	220 to 240 V	28 W	Not applicable
50129499	RC066B LED34S/840 PSD W62L62 OC BN	220-240 V	34 W	Yes
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	220 to 240 V	50 W	Not applicable
51666399	RC066B 34S/840 PSU W62L62 OC	220 to 240 V	28 W	Not applicable
51672499	RC065B G5 34_36S/ 830_40 PSU W60L60 OC SC	220 to 240 V	28 W	Not applicable
51673199	RC065B G5 34_36S/ 830_40 PSU 60x60 NOC SC	220 to 240 V	28 W	Not applicable
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	220 to 240 V	28 W	Not applicable
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	220 to 240 V	28 W	Not applicable
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	220 to 240 V	28 W	Not applicable
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	220 to 240 V	28 W	Not applicable
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	220 to 240 V	28 W	Not applicable

Order Code	Full Product Name	Input Voltage	Power	Suitable for random switching
			Consumption	
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	220 to 240 V	28 W	Not applicable
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	220 to 240 V	28 W	Not applicable
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	220 to 240 V	34 W	Not applicable
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	220 to 240 V	34 W	Not applicable
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	220 to 240 V	34 W	Not applicable
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	220 to 240 V	34 W	Not applicable
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	220 to 240 V	28 W	Not applicable
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	220 to 240 V	28 W	Not applicable
51698499	RC065B G5 34_36S/ 830_40 PSU 30x120 OC SC	220 to 240 V	28 W	Not applicable
36558999	RC066B LED34S/840 PSU W62L62 OC	220-240 V	34 W	Yes

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim
			level
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	Yes	1%
50129499	RC066B LED34S/840 PSD W62L62 OC BN	Yes	3%
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	No	Not applicable
51666399	RC066B 34S/840 PSU W62L62 OC	No	Not applicable
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	No	Not applicable
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	No	Not applicable
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	No	Not applicable
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	No	Not applicable
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	No	Not applicable
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	No	Not applicable
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	No	Not applicable

Order Code	Full Product Name	Dimmable	Maximum dim
			level
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	Yes	1%
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	Yes	1%
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	No	Not applicable
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	No	Not applicable
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	No	Not applicable
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	No	Not applicable
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	No	Not applicable
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	No	Not applicable
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	No	Not applicable
36558999	RC066B LED34S/840 PSU W62L62 OC	No	-

Ledinaire panel gen5

Mechanical and Housing

Order Code	Full Product Name	Ingress protection code
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	IP20/40
50129499	RC066B LED34S/840 PSD W62L62 OC BN	IP20
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	IP20/40
51666399	RC066B 34S/840 PSU W62L62 OC	IP20/40
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	IP20/40
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	IP20/40
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	IP20/40
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	IP20/40
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	IP20/40
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	IP20/40
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	IP20/40

Order Code	Full Product Name	Ingress protection code
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	IP20/40
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	IP20/40
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	IP20/40
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	IP20/40
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	IP20/40
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	IP20/40
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	IP20/40
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	IP20/40
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	IP20/40
36558999	RC066B LED34S/840 PSU W62L62 OC	IP20

Emergency Operation

Order Code	Full Product Name	Central Emergency
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	No
50129499	RC066B LED34S/840 PSD W62L62 OC BN	-
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	No
51666399	RC066B 34S/840 PSU W62L62 OC	No
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	No
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	No
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	No
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	No
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	No
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	No
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	No

Order Code	Full Product Name	Central Emergency
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	No
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	No
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	No
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	No
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	No
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	No
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	No
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	No
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	No
36558999	RC066B LED34S/840 PSU W62L62 OC	-

Approval and Application

Order Code	Full Product Name	Ambient temperature range	Stroboscopic effect visibility measure (SVM)
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	-10 to +35 °C	-
50129499	RC066B LED34S/840 PSD W62L62 OC BN	-10 to +35 °C	0.4
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	-10 to +35 °C	-
51666399	RC066B 34S/840 PSU W62L62 OC	-10 to +35 °C	-
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	-10 to +35 °C	-
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	-10 to +35 °C	-
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	-10 to +35 °C	-
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	-10 to +35 °C	-
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	-10 to +35 °C	-

Order Code	Full Product Name	Ambient temperature range	Stroboscopic effect visibility measure (SVM)
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	-10 to +35 °C	-
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	-10 to +35 °C	-
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	-10 to +35 °C	-
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	-10 to +35 °C	-
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	-10 to +35 °C	-
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	-10 to +35 °C	-
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	-10 to +35 °C	-
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	-10 to +35 °C	-
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	-10 to +35 °C	-

Ledinaire panel gen5

Order Code	Full Product Name	Ambient temperature range	Stroboscopic effect visibility measure (SVM)
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	-10 to +35 °C	-
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	-10 to +35 °C	-

Order Code	Full Product Name	Ambient temperature range	Stroboscopic effect visibility measure (SVM)
36558999	RC066B LED34S/840 PSU W62L62 OC	-10 to +25 °C	0.4

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
51697799	RC065B G5 34_36S/830_40 PSD W60L60 OC SC	(0.43, 0.40) SDCM ≤5(0.38, 0.38) SDCM ≤5	-10% / +10%
50129499	RC066B LED34S/840 PSD W62L62 OC BN	(0.38, 0.38) SDCM ≤5	+/-10%
51669499	RC065B G5 60S/840 PSU 60x120 NOC TPb CFW	(0.38, 0.38) SDCM ≤5	-10% / +10%
51666399	RC066B 34S/840 PSU W62L62 OC	(0.38, 0.38) SDCM ≤5	-10% / +10%
51672499	RC065B G5 34_36S/830_40 PSU W60L60 OC SC	(0.43, 0.40) SDCM ≤5(0.38, 0.38) SDCM ≤5	-10% / +10%
51673199	RC065B G5 34_36S/830_40 PSU 60x60 NOC SC	(0.43, 0.40) SDCM ≤5(0.38, 0.38) SDCM ≤5	-10% / +10%
51651999	RC065B G5 34S/840 PSU W60L60 OC CFW	(0.38, 0.38) SDCM ≤5	-10% / +10%
51652699	RC065B G5 34S/840 PSU W60L60 OC SC	(0.38, 0.38) SDCM ≤5	-10% / +10%
51653399	RC065B G5 34S/865 PSU W60L60 OC CFW	(0.31, 0.33) SDCM ≤5	-10% / +10%
51655799	RC065B G5 34S/840 PSU W60L60 NOC SC	(0.38, 0.38) SDCM ≤5	-10% / +10%
51656499	RC065B G5 34S/865 PSU W60L60 NOC CFW	(0.31, 0.33) SDCM ≤5	-10% / +10%

Order Code	Full Product Name	Initial chromaticity	Luminous flux tolerance
51657199	RC065B G5 34S/840 PSD W60L60 OC CFW	(0.38, 0.38) SDCM ≤5	-10% / +10%
51658899	RC065B G5 34S/840 PSD W60L60 OC SC	(0.38, 0.38) SDCM ≤5	-10% / +10%
51659599	RC065B G5 41S/840 PSU W60L60 NOC CFW	(0.38, 0.38) SDCM ≤5	-10% / +10%
51660199	RC065B G5 41S/840 PSU W60L60 OC CFW	(0.38, 0.38) SDCM ≤5	-10% / +10%
51661899	RC065B G5 41S/840 PSU W60L60 NOC CFW CL	(0.38, 0.38) SDCM ≤5	-10% / +10%
51662599	RC065B G5 41S/840 PSU W60L60 OC CFW CL	(0.38, 0.38) SDCM ≤5	-10% / +10%
51663299	RC065B G5 34S/840 PSU W60L60 NOC CFW CL	(0.38, 0.38) SDCM ≤5	-10% / +10%
51664999	RC065B G5 34S/840 PSU W60L60 OC CFW CL	(0.38, 0.38) SDCM ≤5	-10% / +10%
51698499	RC065B G5 34_36S/830_40 PSU 30x120 OC SC	(0.43, 0.40) SDCM ≤5(0.38, 0.38) SDCM ≤5	-10% / +10%
36558999	RC066B LED34S/840 PSU W62L62 OC	(0.38, 0.38) SDCM ≤5	+/-10%

