



Slim and reliable

RC160V

GreenPerform Panel RC160V is an edge lit slim panel with high efficacy in the market. It offers 3 typical dimensions: 600x600; 300x1200 and 600x1200mm to fit most of indoor applications. Its lower UGR offers better visual comfort as well. In addition, RC160V offers easy connection to control system to bring better energy saving.

Benefits

- High lm/w provides better energy saving
- Dali and Interact interfaces available for easy internet connection
- Lower UGR offer for WELL building certificate
- Multiple mountings to cater for various applications

Features

- System efficiency: max 130lm/W
- CRI 80 and 90 available with SDCM 4
- UGR19 / 16 available for certain types
- IP54 front/IP20 back available for certain types

Application

- Open plan office
- Public indoor area
- Meeting/training room

Specifications

Ingress protection	IP20IP54 front/IP20 back	Installation	Recessed
--------------------	--------------------------	--------------	----------







RC160V

Versions





GreenPerform panel

Dimensional drawing



RC160V

Dimensional drawing



General Information	
Driver included	Yes
Gear	-
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	80
Optic type	Beam angle 100°
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable
Mechanical and Housing	
Optical cover type	PS
Housing Color	White RAL 9003
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +40 °C
CE mark	Yes
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

		Luminous Efficacy	Luminous Flux	Number of light sources
Order Code	Full Product Name	(rated) (Nom)		
911401527932	RC160X LED39/840 W30L120 WIA CAU	130 lm/W	3,900 lm	288
911401528532	RC160X LED39/840 W30L120 SIA CAU	130 lm/W	3,900 lm	288
911401529432	RC160V LED39/840 W30L120 PSU OC CAU	130 lm/W	3,900 lm	288
911401530332	RC160V LED39/840 W30L120 PSD OC CAU	130 lm/W	3,900 lm	288
911401528832	RC160X LED60/840 W60L120 SIA CAU	131 lm/W	6,000 lm	384
911401529732	RC160V LED60/840 W60L120 PSU OC CAU	131 lm/W	6,000 lm	384
911401530632	RC160V LED60/840 W60L120 PSD OC CAU	131 lm/W	6,000 lm	384
911401527632	RC160X LED39/840 W60L60 WIA CAU	130 lm/W	3,900 lm	240
911401528232	RC160X LED39/840 W60L60 SIA CAU	130 lm/W	3,900 lm	240
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	130 lm/W	3,900 lm	240
911401530032	RC160V LED39/840 W60L60 PSD OC CAU	130 lm/W	3,900 lm	240
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	130 lm/W	3,900 lm	240

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401527932	RC160X LED39/840 W30L120 WIA CAU	30 W	911401528532	RC160X LED39/840 W30L120 SIA CAU	30 W

RC160V

Order Code	Full Product Name	Power Consumption
911401529432	RC160V LED39/840 W30L120 PSU OC CAU	30 W
911401530332	RC160V LED39/840 W30L120 PSD OC CAU	30 W
911401528832	RC160X LED60/840 W60L120 SIA CAU	46 W
911401529732	RC160V LED60/840 W60L120 PSU OC CAU	46 W
911401530632	RC160V LED60/840 W60L120 PSD OC CAU	46 W

Order Code	Full Product Name	Power Consumption
911401527632	RC160X LED39/840 W60L60 WIA CAU	30 W
911401528232	RC160X LED39/840 W60L60 SIA CAU	30 W
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	30 W
911401530032	RC160V LED39/840 W60L60 PSD OC CAU	30 W
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	30 W

Controls and Dimming

Order Code	Full Product Name	Dimmable	Maximum dim level
911401527932	RC160X LED39/840 W30L120 WIA CAU	Wireless Dim	Programmable
911401528532	RC160X LED39/840 W30L120 SIA CAU	Auto-Dim	0% (digital)
911401529432	RC160V LED39/840 W30L120 PSU OC CAU	Fixed	0% (digital)
911401530332	RC160V LED39/840 W30L120 PSD OC CAU	DALI	Programmable
911401528832	RC160X LED60/840 W60L120 SIA CAU	Auto-Dim	0% (digital)
911401529732	RC160V LED60/840 W60L120 PSU OC CAU	Fixed	0% (digital)

Order Code	Full Product Name	Dimmable	Maximum dim level
911401530632	RC160V LED60/840 W60L120 PSD OC CAU	DALI	Programmable
911401527632	RC160X LED39/840 W60L60 WIA CAU	Wireless Dim	Programmable
911401528232	RC160X LED39/840 W60L60 SIA CAU	Auto-Dim	0% (digital)
911401529132	RC160V LED39/840 W60L60 PSU OC CAU	Fixed	0% (digital)
911401530032	RC160V LED39/840 W60L60 PSD OC CAU	DALI	Programmable
911401530932	RC160X LED39/840 W60L60 WIA OC CAU	Wireless Dim	Programmable

