



Philips TrueLine recessed: True line of light

TrueLine, recessed

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine recessed is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in suspended and surface-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

TrueLine, recessed

Features

- Highly-uniform lighting with excellent glare control ($UGR < 19$, $L65 < 3000 \text{cd/m}^2$)
- Best-in-class efficacy up to 140 lm/W
- 3000K, 4000K, and Tunable White versions, all CRI > 90
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options


Application

- Offices
- Education
- Retail

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions



TrueLine recessed-RC530B L1130



TrueLineRecessed PCV ASYMMETRIC RTP




TrueLine Recessed-U3





TrueLineRecessed VPC NOC IP RTP

Dimensional drawing





Recessed VPC_W8L150_no sensor



Dimensional drawing



Recessed VPC_W8L120_sensor/IP



Recessed VPC_W8L120_no sensor



Product details



TrueLineRecessed NOC OPTICS
DP



TrueLine_Recessed U4 DP

Product details



TrueLine_recessed-RC530B_PCV_L1130-DP.tif




TrueLine-RC530_RC531_RC534B_VPC-DPP.tif




TrueLine-RC530_RC531_RC532_RC533B_PCV-1DPP.tif



TrueLine-RC530_RC531_RC532_RC533B_PCV-2DPP.tif



TrueLine-RC530_RC531_RC534B_VPC_PI5-DPP.tif



TrueLine-RC534B_SM534C_SP534P-DPP.tif



TrueLineRecessed OC OPTICS DP



TrueLineRecessed PCV line CONNECTED DP1



TrueLineRecessed VPC line CONNECTED DP2

Product details



TrueLineRecessed VPC line
CONNECTED DP1



TrueLine_Recessed-U3



TrueLineRecessed PCV line
CONNECTED DP2



TrueLine_Recessed-U0



TrueLineRecessed VPC LINE RTP



TrueLine_Recessed IP DP



TrueLineRecessed ASYMMETRIC
OPTICS DP

General Information	
Driver included	Yes
Number of gear units	1 unit
Light Technical	
Color rendering index (CRI)	>90
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Operating and Electrical	
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	+10 to +40 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing Color	White
Approval and Application	
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Application Conditions	
Maximum dim level	1%

General Information

Order Code	Full Product Name	Embedded control	Light source replaceable	Product family code	Service tag
910505103104	RC530B 15S/940 PSD W8L115 PCV	-	No	RC530B	Yes
910505103107	RC530B 31S/940 PSD W8L141 PCV	-	No	RC530B	Yes
910505103110	RC530B 43S/940 PSD W8L141 PCV	-	No	RC530B	Yes
910505103114	RC530B 19S/940 PSD W8L141 PCV	-	No	RC530B	Yes
910505103115	RC530B 34S/940 PSD W8L115 PCV	-	No	RC530B	Yes
910505103116	RC531B 15S/930 PSD W8L115 PCV	-	No	RC531B	Yes
910505103117	RC531B 15S/940 PSD W8L115 PCV	-	No	RC531B	Yes
910505103121	RC531B 31S/940 PSD W8L141 PCV	-	No	RC531B	Yes
910505103127	RC530B 50S/940 PSD W8L141 PCV	-	No	RC530B	Yes
910505103129	RC531B 19S/940 PSD W8L141 PCV	-	No	RC531B	Yes
910505103147	RC530B 40S/940 POE W8L120 VPC U0	Upgradable sensor slot empty with cover	No	RC530B	Yes
910505103284	RC530B 34S/TW9 DIA W8L115 PCV	-	No	RC530B	Yes
910505103286	RC530B 40S/TW9 DIA W8L115 PCV	-	No	RC530B	Yes
910505103287	RC530B 50S/TW9 DIA W8L145 PCV	-	No	RC530B	Yes
910505103292	RC530B 34S/940 PSD W8L115 PCV SC	-	No	RC530B	Yes
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	-	No	RC532B	-
910505103138	RC531B 31S/940 W8L150 VPC ELP3	-	No	RC531B	Yes
910505103140	RC531B 19S/940 W8L150 VPC ELP3	-	No	RC531B	Yes
910505103141	RC530B 50S/940 W8L150 VPC ELP3	-	No	RC530B	Yes
910505103144	RC530B 43S/940 W8L150 VPC ELP3	-	No	RC530B	Yes
910505103154	RC530B 43S/940 PSD W8L150 VPC ELD3	-	No	RC530B	Yes
910505103135	RC530B 43S/940 W8L145 PCV ELP3	-	No	RC530B	Yes
910505103136	RC530B 50S/940 W8L145 PCV ELP3	-	No	RC530B	Yes
910505103139	RC531B 19S/940 W8L145 PCV ELP3	-	No	RC531B	Yes

Order Code	Full Product Name	Embedded control	Light source replaceable	Product family code	Service tag
910505103145	RC531B 31S/940 W8L145 PCV ELP3	-	No	RC531B	Yes
910505103153	RC531B 19S/940 PSD W8L145 PCV ELD3	-	No	RC531B	Yes
910505103120	RC534B 40S/940 PSD W8L120 VPC IP	-	No	RC534B	Yes
910505103123	RC534B 50S/940 PSD W8L141 PCV	-	No	RC534B	Yes
910505103125	RC535B 50S/940 PSD W8L141 PCV	-	No	RC535B	Yes
910505103130	RC535B 43S/940 PSD W8L141 PCV	-	No	RC535B	Yes
910505103101	RC530B 43S/940 PSD W8L150 VPC IP	-	No	RC530B	Yes
910505103105	RC530B 34S/930 PSD W8L120 VPC IP	-	No	RC530B	Yes
910505103113	RC530B 50S/940 PSD W8L150 VPC IP	-	No	RC530B	Yes
910505103149	RC530B 40S/940 PSD W8L120 VPC IP	-	No	RC530B	Yes
910505103150	RC530B 34S/940 PSD W8L120 VPC IP	-	No	RC530B	Yes
910505103293	RC530B 34S/940 PSD W8L120 VPC IP SC	-	No	RC530B	Yes
910505103128	RC534B 43S/940 PSD W8L141 PCV	-	No	RC534B	Yes
910505103106	RC532B 19S/940 PSD W8L141 PCV	-	No	RC532B	Yes
910505103109	RC533B 15S/940 PSD W8L113 PCV	-	No	RC533B	Yes
910505103119	RC532B 25S/940 PSD W8L113 PCV	-	No	RC532B	Yes
910505103122	RC532B 31S/940 PSD W8L141 PCV	-	No	RC532B	Yes
910505103124	RC532B 43S/940 PSD W8L141 PCV	-	No	RC532B	Yes
910505103126	RC533B 31S/940 PSD W8L141 PCV	-	No	RC533B	Yes
910505103131	RC533B 19S/940 PSD W8L141 PCV	-	No	RC533B	Yes
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	Interact Ready light source with multi-sensor (upgradable)	No	RC530B	-
910505103155	RC532B 43S/940 SIA W8L145 PCV U4 W3	Upgradable sensor slot with SNS210 sensor	No	RC532B	Yes
910505103160	RC530B 43S/940 SIA W8L145 PCV U4	Upgradable sensor slot with SNS210 sensor	No	RC530B	Yes

Order Code	Full Product Name	Embedded control	Light source replaceable	Product family code	Service tag
910505103285	RC530B 43S/TW9 SIA W8L145 PCV U4	Upgradable sensor slot with SNS210 sensor	No	RC530B	Yes
910505103291	RC530B 43S/TW9 SIA W8L145 PCV U4 SC	Upgradable sensor slot with SNS210 sensor	No	RC530B	Yes
910505105669	RC530B 50S/TW9 SIA W8L145 PCV U4	Upgradable sensor slot with SNS210 sensor	-	RC530B	Yes
910505105670	RC531B 31S/TW9 SIA W8L145 PCV U4	Upgradable sensor slot with SNS210 sensor	-	RC531B	Yes
910505103102	RC532B 25S/940 PSD W8L113 VPC	-	No	RC532B	Yes
910505103103	RC531B 19S/930 PSD W8L150 VPC IP	-	No	RC531B	Yes
910505103111	RC531B 15S/940 PSD W8L120 VPC IP	-	No	RC531B	Yes
910505103112	RC531B 15S/930 PSD W8L120 VPC IP	-	No	RC531B	Yes
910505103156	RC530B 34S/940 SIA W8L120 VPC U4 SC	Upgradable sensor slot with SNS210 sensor	No	RC530B	Yes
910505103157	RC530B 34S/930 SIA W8L120 VPC U4 W3	Upgradable sensor slot with SNS210 sensor	No	RC530B	Yes
910505103158	RC530B 34S/930 SIA W8L120 VPC U4 W3 SC	Upgradable sensor slot with SNS210 sensor	No	RC530B	Yes
910505103159	RC530B 25S/930 SIA W8L120 VPC U4 W3	Upgradable sensor slot with SNS210 sensor	No	RC530B	Yes
910505103288	RC530B 34S/TW9 SIA W8L120 VPC U4	Upgradable sensor slot with SNS210 sensor	No	RC530B	Yes
910505103289	RC530B 43S/TW9 SIA W8L145 VPC U4 SC	Upgradable sensor slot with SNS210 sensor	No	RC530B	Yes
910505103290	RC531B 25S/TW9 SIA W8L120 VPC U4	Upgradable sensor slot with SNS210 sensor	No	RC534B	Yes

Light Technical (1/2)

TrueLine, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103104	RC530B 15S/940 PSD W8L115 PCV	- degree(s)	4000 K	127 lm/W	1,500 lm
910505103107	RC530B 31S/940 PSD W8L141 PCV	- degree(s)	4000 K	148 lm/W	3,100 lm
910505103110	RC530B 43S/940 PSD W8L141 PCV	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103114	RC530B 19S/940 PSD W8L141 PCV	- degree(s)	4000 K	139 lm/W	1,900 lm
910505103115	RC530B 34S/940 PSD W8L115 PCV	- degree(s)	4000 K	145 lm/W	3,400 lm
910505103116	RC531B 15S/930 PSD W8L115 PCV	- degree(s)	3000 K	99 lm/W	1,500 lm
910505103117	RC531B 15S/940 PSD W8L115 PCV	- degree(s)	4000 K	106 lm/W	1,500 lm
910505103121	RC531B 31S/940 PSD W8L141 PCV	- degree(s)	4000 K	110 lm/W	3,100 lm
910505103127	RC530B 50S/940 PSD W8L141 PCV	- degree(s)	4000 K	142 lm/W	5,000 lm
910505103129	RC531B 19S/940 PSD W8L141 PCV	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103147	RC530B 40S/940 POE W8L120 VPC U0	- degree(s)	4000 K	143 lm/W	4,000 lm
910505103284	RC530B 34S/TW9 DIA W8L115 PCV	120 degree(s)	Tunable white 2700-6500 K	124 lm/W	3,400 lm
910505103286	RC530B 40S/TW9 DIA W8L115 PCV	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,000 lm
910505103287	RC530B 50S/TW9 DIA W8L145 PCV	120 degree(s)	Tunable white 2700-6500 K	120 lm/W	5,000 lm
910505103292	RC530B 34S/940 PSD W8L115 PCV SC	120 degree(s)	4000 K	145 lm/W	3,400 lm
910505103118	RC532B LED15S/940	- degree(s)	4000 K	127 lm/W	1,500 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	PSD W8L113 PCV PI5				
910505103138	RC531B 31S/940 W8L150 VPC ELP3	- degree(s)	4000 K	110 lm/W	3,100 lm
910505103140	RC531B 19S/940 W8L150 VPC ELP3	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103141	RC530B 50S/940 W8L150 VPC ELP3	- degree(s)	4000 K	142 lm/W	5,000 lm
910505103144	RC530B 43S/940 W8L150 VPC ELP3	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103154	RC530B 43S/940 PSD W8L150 VPC ELD3	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103135	RC530B 43S/940 W8L145 PCV ELP3	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103136	RC530B 50S/940 W8L145 PCV ELP3	- degree(s)	4000 K	142 lm/W	5,000 lm
910505103139	RC531B 19S/940 W8L145 PCV ELP3	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103145	RC531B 31S/940 W8L145 PCV ELP3	- degree(s)	4000 K	110 lm/W	3,100 lm
910505103153	RC531B 19S/940 PSD W8L145 PCV ELD3	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103120	RC534B 40S/940 PSD W8L120 VPC IP	- degree(s)	4000 K	130 lm/W	4,000 lm
910505103123	RC534B 50S/940 PSD W8L141 PCV	- degree(s)	4000 K	132 lm/W	5,000 lm

TrueLine, recessed

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103125	RC535B 50S/940 PSD W8L141 PCV	- degree(s)	4000 K	132 lm/W	5,000 lm
910505103130	RC535B 43S/940 PSD W8L141 PCV	- degree(s)	4000 K	138 lm/W	4,300 lm
910505103101	RC530B 43S/940 PSD W8L150 VPC IP	- degree(s)	4000 K	144 lm/W	4,300 lm
910505103105	RC530B 34S/930 PSD W8L120 VPC IP	- degree(s)	3000 K	133 lm/W	3,400 lm
910505103113	RC530B 50S/940 PSD W8L150 VPC IP	- degree(s)	4000 K	142 lm/W	5,000 lm
910505103149	RC530B 40S/940 PSD W8L120 VPC IP	- degree(s)	4000 K	140 lm/W	4,000 lm
910505103150	RC530B 34S/940 PSD W8L120 VPC IP	- degree(s)	4000 K	145 lm/W	3,400 lm
910505103293	RC530B 34S/940 PSD W8L120 VPC IP SC	120 degree(s)	4000 K	145 lm/W	3,400 lm
910505103128	RC534B 43S/940 PSD W8L141 PCV	- degree(s)	4000 K	138 lm/W	4,300 lm
910505103106	RC532B 19S/940 PSD W8L141 PCV	- degree(s)	4000 K	139 lm/W	1,900 lm
910505103109	RC533B 15S/940 PSD W8L113 PCV	- degree(s)	4000 K	103 lm/W	1,500 lm
910505103119	RC532B 25S/940 PSD W8L113 PCV	- degree(s)	4000 K	139 lm/W	2,500 lm
910505103122	RC532B 31S/940 PSD W8L141 PCV	- degree(s)	4000 K	148 lm/W	3,100 lm
910505103124	RC532B 43S/940 PSD W8L141 PCV	- degree(s)	4000 K	144 lm/W	4,300 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103126	RC533B 31S/940 PSD W8L141 PCV	- degree(s)	4000 K	110 lm/W	3,100 lm
910505103131	RC533B 19S/940 PSD W8L141 PCV	- degree(s)	4000 K	110 lm/W	1,900 lm
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	- degree(s)	4000 K	143 lm/W	4,000 lm
910505103155	RC532B 43S/940 SIA W8L145 PCV U4 W3	- degree(s)	4000 K	143 lm/W	4,300 lm
910505103160	RC530B 43S/940 SIA W8L145 PCV U4	- degree(s)	4000 K	143 lm/W	4,300 lm
910505103285	RC530B 43S/TW9 SIA W8L145 PCV U4	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm
910505103291	RC530B 43S/TW9 SIA W8L145 PCV U4 SC	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm
910505105669	RC530B 50S/TW9 SIA W8L145 PCV U4	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	5,000 lm
910505105670	RC531B 31S/TW9 SIA W8L145 PCV U4	120 degree(s)	Tunable white 2700-6500 K	91 lm/W	3,100 lm
910505103102	RC532B 25S/940 PSD W8L113 VPC	- degree(s)	4000 K	139 lm/W	2,500 lm
910505103103	RC531B 19S/930 PSD W8L150 VPC IP	- degree(s)	3000 K	104 lm/W	1,900 lm
910505103111	RC531B 15S/940 PSD W8L120 VPC IP	- degree(s)	4000 K	106 lm/W	1,500 lm
910505103112	RC531B 15S/930 PSD W8L120 VPC IP	- degree(s)	3000 K	99 lm/W	1,500 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103156	RC530B 34S/940 SIA W8L120 VPC U4 SC	- degree(s)	4000 K	142 lm/W	3,400 lm
910505103157	RC530B 34S/930 SIA W8L120 VPC U4 W3	- degree(s)	3000 K	133 lm/W	3,400 lm
910505103158	RC530B 34S/930 SIA W8L120 VPC U4 W3 SC	- degree(s)	3000 K	133 lm/W	3,400 lm
910505103159	RC530B 25S/930 SIA	- degree(s)	3000 K	133 lm/W	2,500 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type
910505103104	RC530B 15S/940 PSD W8L115 PCV	Wide beam
910505103107	RC530B 31S/940 PSD W8L141 PCV	Wide beam
910505103110	RC530B 43S/940 PSD W8L141 PCV	Wide beam
910505103114	RC530B 19S/940 PSD W8L141 PCV	Wide beam
910505103115	RC530B 34S/940 PSD W8L115 PCV	Wide beam
910505103116	RC531B 15S/930 PSD W8L115 PCV	Wide beam
910505103117	RC531B 15S/940 PSD W8L115 PCV	Wide beam
910505103121	RC531B 31S/940 PSD W8L141 PCV	Wide beam
910505103127	RC530B 50S/940 PSD W8L141 PCV	Wide beam
910505103129	RC531B 19S/940 PSD W8L141 PCV	Wide beam
910505103147	RC530B 40S/940 POE W8L120 VPC U0	Wide beam
910505103284	RC530B 34S/TW9 DIA W8L115 PCV	Wide beam
910505103286	RC530B 40S/TW9 DIA W8L115 PCV	Wide beam
910505103287	RC530B 50S/TW9 DIA W8L145 PCV	Wide beam
910505103292	RC530B 34S/940 PSD W8L115 PCV SC	Wide beam
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	Wide beam
910505103138	RC531B 31S/940 W8L150 VPC ELP3	Wide beam
910505103140	RC531B 19S/940 W8L150 VPC ELP3	Wide beam
910505103141	RC530B 50S/940 W8L150 VPC ELP3	Wide beam
910505103144	RC530B 43S/940 W8L150 VPC ELP3	Wide beam
910505103154	RC530B 43S/940 PSD W8L150 VPC ELD3	Wide beam
910505103135	RC530B 43S/940 W8L145 PCV ELP3	Wide beam
910505103136	RC530B 50S/940 W8L145 PCV ELP3	Wide beam
910505103139	RC531B 19S/940 W8L145 PCV ELP3	Wide beam
910505103145	RC531B 31S/940 W8L145 PCV ELP3	Wide beam
910505103153	RC531B 19S/940 PSD W8L145 PCV ELD3	Wide beam
910505103120	RC534B 40S/940 PSD W8L120 VPC IP	Asymmetrical mirror
910505103123	RC534B 50S/940 PSD W8L141 PCV	Asymmetrical mirror
910505103125	RC535B 50S/940 PSD W8L141 PCV	Asymmetrical mirror
910505103130	RC535B 43S/940 PSD W8L141 PCV	Asymmetrical mirror
910505103101	RC530B 43S/940 PSD W8L150 VPC IP	Wide beam

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	W8L120 VPC U4 W3				
910505103288	RC530B 34S/TW9 SIA W8L120 VPC U4	120 degree(s)	Tunable white 2700-6500 K	124 lm/W	3,400 lm
910505103289	RC530B 43S/TW9 SIA W8L145 VPC U4 SC	120 degree(s)	Tunable white 2700-6500 K	121 lm/W	4,300 lm
910505103290	RC531B 25S/TW9 SIA W8L120 VPC U4	120 degree(s)	Tunable white 2700-6500 K	93 lm/W	2,500 lm

Order Code	Full Product Name	Optic type
910505103105	RC530B 34S/930 PSD W8L120 VPC IP	Wide beam
910505103113	RC530B 50S/940 PSD W8L150 VPC IP	Wide beam
910505103149	RC530B 40S/940 PSD W8L120 VPC IP	Wide beam
910505103150	RC530B 34S/940 PSD W8L120 VPC IP	Wide beam
910505103293	RC530B 34S/940 PSD W8L120 VPC IP SC	Wide beam
910505103128	RC534B 43S/940 PSD W8L141 PCV	Asymmetrical mirror
910505103106	RC532B 19S/940 PSD W8L141 PCV	Wide beam
910505103109	RC533B 15S/940 PSD W8L113 PCV	Wide beam
910505103119	RC532B 25S/940 PSD W8L113 PCV	Wide beam
910505103122	RC532B 31S/940 PSD W8L141 PCV	Wide beam
910505103124	RC532B 43S/940 PSD W8L141 PCV	Wide beam
910505103126	RC533B 31S/940 PSD W8L141 PCV	Wide beam
910505103131	RC533B 19S/940 PSD W8L141 PCV	Wide beam
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	Wide beam
910505103155	RC532B 43S/940 SIA W8L145 PCV U4 W3	Wide beam
910505103160	RC530B 43S/940 SIA W8L145 PCV U4	Wide beam
910505103285	RC530B 43S/TW9 SIA W8L145 PCV U4	Wide beam
910505103291	RC530B 43S/TW9 SIA W8L145 PCV U4 SC	Wide beam
910505105669	RC530B 50S/TW9 SIA W8L145 PCV U4	Wide beam office compliant
910505105670	RC531B 31S/TW9 SIA W8L145 PCV U4	Wide beam
910505103102	RC532B 25S/940 PSD W8L113 VPC	Wide beam
910505103103	RC531B 19S/930 PSD W8L150 VPC IP	Wide beam
910505103111	RC531B 15S/940 PSD W8L120 VPC IP	Wide beam
910505103112	RC531B 15S/930 PSD W8L120 VPC IP	Wide beam
910505103156	RC530B 34S/940 SIA W8L120 VPC U4 SC	Wide beam
910505103157	RC530B 34S/930 SIA W8L120 VPC U4 W3	Wide beam
910505103158	RC530B 34S/930 SIA W8L120 VPC U4 W3 SC	Wide beam
910505103159	RC530B 25S/930 SIA W8L120 VPC U4 W3	Wide beam
910505103288	RC530B 34S/TW9 SIA W8L120 VPC U4	Wide beam
910505103289	RC530B 43S/TW9 SIA W8L145 VPC U4 SC	Wide beam

Order Code	Full Product Name	Optic type
910505103290	RC531B 25S/TW9 SIA W8L120 VPC U4	Wide beam

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103104	RC530B 15S/940 PSD W8L115 PCV	220 to 240 V	12.2 W
910505103107	RC530B 31S/940 PSD W8L141 PCV	220 to 240 V	21 W
910505103110	RC530B 43S/940 PSD W8L141 PCV	220 to 240 V	30.5 W
910505103114	RC530B 19S/940 PSD W8L141 PCV	220 to 240 V	14 W
910505103115	RC530B 34S/940 PSD W8L115 PCV	220 to 240 V	24.5 W
910505103116	RC531B 15S/930 PSD W8L115 PCV	220 to 240 V	14.6 W
910505103117	RC531B 15S/940 PSD W8L115 PCV	220 to 240 V	14.6 W
910505103121	RC531B 31S/940 PSD W8L141 PCV	220 to 240 V	29 W
910505103127	RC530B 50S/940 PSD W8L141 PCV	220 to 240 V	36 W
910505103129	RC531B 19S/940 PSD W8L141 PCV	220 to 240 V	17.8 W
910505103147	RC530B 40S/940 POE W8L120 VPC U0	51 to 54 V	28 W
910505103284	RC530B 34S/TW9 DIA W8L115 PCV	220 to 240 V	27.5 W
910505103286	RC530B 40S/TW9 DIA W8L115 PCV	220 to 240 V	33 W
910505103287	RC530B 50S/TW9 DIA W8L145 PCV	220 to 240 V	41.5 W
910505103292	RC530B 34S/940 PSD W8L115 PCV SC	220 to 240 V	24.5 W
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	220 to 240 V	12.2 W
910505103138	RC531B 31S/940 W8L150 VPC ELP3	220 to 240 V	29 W
910505103140	RC531B 19S/940 W8L150 VPC ELP3	220 to 240 V	17.8 W
910505103141	RC530B 50S/940 W8L150 VPC ELP3	220 to 240 V	36 W
910505103144	RC530B 43S/940 W8L150 VPC ELP3	220 to 240 V	30.5 W
910505103154	RC530B 43S/940 PSD W8L150 VPC ELD3	220 to 240 V	30.5 W
910505103135	RC530B 43S/940 W8L145 PCV ELP3	220 to 240 V	30.5 W
910505103136	RC530B 50S/940 W8L145 PCV ELP3	220 to 240 V	36 W
910505103139	RC531B 19S/940 W8L145 PCV ELP3	220 to 240 V	17.8 W
910505103145	RC531B 31S/940 W8L145 PCV ELP3	220 to 240 V	29 W
910505103153	RC531B 19S/940 PSD W8L145 PCV ELD3	220 to 240 V	17.8 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103120	RC534B 40S/940 PSD W8L120 VPC IP	220 to 240 V	31.5 W
910505103123	RC534B 50S/940 PSD W8L141 PCV	220 to 240 V	38 W
910505103125	RC535B 50S/940 PSD W8L141 PCV	220 to 240 V	38 W
910505103130	RC535B 43S/940 PSD W8L141 PCV	220 to 240 V	32 W
910505103101	RC530B 43S/940 PSD W8L150 VPC IP	220 to 240 V	30.5 W
910505103105	RC530B 34S/930 PSD W8L120 VPC IP	220 to 240 V	24.5 W
910505103113	RC530B 50S/940 PSD W8L150 VPC IP	220 to 240 V	36 W
910505103149	RC530B 40S/940 PSD W8L120 VPC IP	220 to 240 V	29 W
910505103150	RC530B 34S/940 PSD W8L120 VPC IP	220 to 240 V	24.5 W
910505103293	RC530B 34S/940 PSD W8L120 VPC IP SC	220 to 240 V	24.5 W
910505103128	RC534B 43S/940 PSD W8L141 PCV	220 to 240 V	32 W
910505103106	RC532B 19S/940 PSD W8L141 PCV	220 to 240 V	14 W
910505103109	RC533B 15S/940 PSD W8L113 PCV	220 to 240 V	14.6 W
910505103119	RC532B 25S/940 PSD W8L113 PCV	220 to 240 V	18 W
910505103122	RC532B 31S/940 PSD W8L141 PCV	220 to 240 V	21 W
910505103124	RC532B 43S/940 PSD W8L141 PCV	220 to 240 V	30.5 W
910505103126	RC533B 31S/940 PSD W8L141 PCV	220 to 240 V	29 W
910505103131	RC533B 19S/940 PSD W8L141 PCV	220 to 240 V	17.8 W
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	51 to 54 V	28 W
910505103155	RC532B 43S/940 SIA W8L145 PCV U4 W3	220 to 240 V	30 W
910505103160	RC530B 43S/940 SIA W8L145 PCV U4	220 to 240 V	30 W
910505103285	RC530B 43S/TW9 SIA W8L145 PCV U4	220 to 240 V	35.5 W
910505103291	RC530B 43S/TW9 SIA W8L145 PCV U4 SC	220 to 240 V	35.5 W
910505105669	RC530B 50S/TW9 SIA W8L145 PCV U4	220 to 240 V	41.5 W
910505105670	RC531B 31S/TW9 SIA W8L145 PCV U4	220 to 240 V	34 W
910505103102	RC532B 25S/940 PSD W8L113 VPC	220 to 240 V	18 W
910505103103	RC531B 19S/930 PSD W8L150 VPC IP	220 to 240 V	17.8 W

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103111	RC531B 15S/940 PSD W8L120 VPC IP	220 to 240 V	14.6 W
910505103112	RC531B 15S/930 PSD W8L120 VPC IP	220 to 240 V	14.6 W
910505103156	RC530B 34S/940 SIA W8L120 VPC U4 SC	220 to 240 V	24 W
910505103157	RC530B 34S/930 SIA W8L120 VPC U4 W3	220 to 240 V	25.5 W
910505103158	RC530B 34S/930 SIA W8L120 VPC U4 W3 SC	220 to 240 V	25.5 W

Emergency Operation

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505103104	RC530B 15S/940 PSD W8L115 PCV	-	-	-	-
910505103107	RC530B 31S/940 PSD W8L141 PCV	-	-	-	-
910505103110	RC530B 43S/940 PSD W8L141 PCV	-	-	-	-
910505103114	RC530B 19S/940 PSD W8L141 PCV	-	-	-	-
910505103115	RC530B 34S/940 PSD W8L115 PCV	-	-	-	-
910505103116	RC531B 15S/930 PSD W8L115 PCV	-	-	-	-
910505103117	RC531B 15S/940 PSD W8L115 PCV	-	-	-	-
910505103121	RC531B 31S/940 PSD W8L141 PCV	-	-	-	-
910505103127	RC530B 50S/940 PSD W8L141 PCV	-	-	-	-
910505103129	RC531B 19S/940 PSD W8L141 PCV	-	-	-	-
910505103147	RC530B 40S/940 POE	-	-	-	-

Order Code	Full Product Name	Input Voltage	Power Consumption
910505103159	RC530B 25S/930 SIA W8L120 VPC U4 W3	220 to 240 V	18.8 W
910505103288	RC530B 34S/TW9 SIA W8L120 VPC U4	220 to 240 V	27.5 W
910505103289	RC530B 43S/TW9 SIA W8L145 VPC U4 SC	220 to 240 V	35.5 W
910505103290	RC531B 25S/TW9 SIA W8L120 VPC U4	220 to 240 V	27 W

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
	W8L120 VPC U0				
910505103284	RC530B 34S/TW9 DIA W8L115 PCV	-	-	-	-
910505103286	RC530B 40S/TW9 DIA W8L115 PCV	-	-	-	-
910505103287	RC530B 50S/TW9 DIA W8L145 PCV	-	-	-	-
910505103292	RC530B 34S/940 PSD W8L115 PCV SC	-	-	-	-
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	-	-	-	-
910505103138	RC531B 31S/940 W8L150 VPC ELP3	No	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103140	RC531B 19S/940 W8L150 VPC ELP3	-	Emergency lighting 3 hours duration Pro version	Lithium	3 hour(s)
910505103141	RC530B 50S/940 W8L150 VPC ELP3	-	Emergency lighting 3 hours	Lithium	3 hour(s)

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
			duration Pro version		
910505103144	RC530B 43S/940 W8L150 VPC ELP3	-	Emergency lighting 3 hours	Lithium	3 hour(s)
910505103154	RC530B 43S/940 PSD W8L150 VPC ELD3	-	Emergency lighting 3 hours	Lithium	3 hour(s)
			duration with DALI interface		
910505103135	RC530B 43S/940 W8L145 PCV ELP3	No	Emergency lighting 3 hours	Lithium	3 hour(s)
			duration Pro version		
910505103136	RC530B 50S/940 W8L145 PCV ELP3	No	Emergency lighting 3 hours	Lithium	3 hour(s)
			duration Pro version		
910505103139	RC531B 19S/940 W8L145 PCV ELP3	-	Emergency lighting 3 hours	Lithium	3 hour(s)
			duration Pro version		
910505103145	RC531B 31S/940 W8L145 PCV ELP3	-	Emergency lighting 3 hours	Lithium	3 hour(s)
			duration Pro version		
910505103153	RC531B 19S/940 PSD W8L145 PCV ELD3	-	Emergency lighting 3 hours	Lithium	3 hour(s)
			duration with DALI interface		
910505103120	RC534B 40S/940 PSD W8L120 VPC IP	-	-	-	-
910505103123	RC534B 50S/940 PSD W8L141 PCV	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505103125	RC535B 50S/940 PSD W8L141 PCV	-	-	-	-
910505103130	RC535B 43S/940 PSD W8L141 PCV	-	-	-	-
910505103101	RC530B 43S/940 PSD W8L150 VPC IP	-	-	-	-
910505103105	RC530B 34S/930 PSD W8L120 VPC IP	-	-	-	-
910505103113	RC530B 50S/940 PSD W8L150 VPC IP	-	-	-	-
910505103149	RC530B 40S/940 PSD W8L120 VPC IP	-	-	-	-
910505103150	RC530B 34S/940 PSD W8L120 VPC IP	-	-	-	-
910505103293	RC530B 34S/940 PSD W8L120 VPC IP SC	-	-	-	-
910505103128	RC534B 43S/940 PSD W8L141 PCV	-	-	-	-
910505103106	RC532B 19S/940 PSD W8L141 PCV	-	-	-	-
910505103109	RC533B 15S/940 PSD W8L113 PCV	-	-	-	-
910505103119	RC532B 25S/940 PSD W8L113 PCV	-	-	-	-
910505103122	RC532B 31S/940 PSD W8L141 PCV	-	-	-	-
910505103124	RC532B 43S/940 PSD W8L141 PCV	-	-	-	-
910505103126	RC533B 31S/940 PSD W8L141 PCV	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505103131	RC533B 19S/940 PSD W8L141 PCV	-	-	-	-
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	-	-	-	-
910505103155	RC532B 43S/940 SIA W8L145 PCV U4 W3	-	-	-	-
910505103160	RC530B 43S/940 SIA W8L145 PCV U4	-	-	-	-
910505103285	RC530B 43S/TW9 SIA W8L145 PCV U4	-	-	-	-
910505103291	RC530B 43S/TW9 SIA W8L145 PCV U4 SC	-	-	-	-
910505105669	RC530B 50S/TW9 SIA W8L145 PCV U4	-	-	-	-
910505105670	RC531B 31S/TW9 SIA W8L145 PCV U4	-	-	-	-
910505103102	RC532B 25S/940 PSD W8L113 VPC	-	-	-	-
910505103103	RC531B 19S/930 PSD W8L150 VPC IP	-	-	-	-

Order Code	Full Product Name	Central Emergency	Emergency lighting	Type of emergency lighting battery	Rated duration of the emergency lighting (when fully charged)
910505103111	RC531B 15S/940 PSD W8L120 VPC IP	-	-	-	-
910505103112	RC531B 15S/930 PSD W8L120 VPC IP	-	-	-	-
910505103156	RC530B 34S/940 SIA W8L120 VPC U4 SC	-	-	-	-
910505103157	RC530B 34S/930 SIA W8L120 VPC U4 W3	-	-	-	-
910505103158	RC530B 34S/930 SIA W8L120 VPC U4 W3 SC	-	-	-	-
910505103159	RC530B 25S/930 SIA W8L120 VPC U4 W3	-	-	-	-
910505103288	RC530B 34S/TW9 SIA W8L120 VPC U4	-	-	-	-
910505103289	RC530B 43S/TW9 SIA W8L145 VPC U4 SC	-	-	-	-
910505103290	RC531B 25S/TW9 SIA W8L120 VPC U4	-	-	-	-

Approval and Application

Order Code	Full Product Name	Protection class IEC	Mech. impact protection code	Ingress protection code
910505103104	RC530B 15S/940 PSD W8L115 PCV	Safety class I	IK03	IP20/40

Order Code	Full Product Name	Protection class IEC	Mech. impact protection code	Ingress protection code
910505103107	RC530B 31S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40

Order Code	Full Product Name	Protection class IEC	Mech. impact protection code	Ingress protection code
910505103110	RC530B 43S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103114	RC530B 19S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103115	RC530B 34S/940 PSD W8L115 PCV	Safety class I	IK03	IP20/40
910505103116	RC531B 15S/930 PSD W8L115 PCV	Safety class I	IK03	IP20/54
910505103117	RC531B 15S/940 PSD W8L115 PCV	Safety class I	IK03	IP20/54
910505103121	RC531B 31S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103127	RC530B 50S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103129	RC531B 19S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/54
910505103147	RC530B 40S/940 POE W8L120 VPC U0	Safety class III	IK03	IP20
910505103284	RC530B 34S/TW9 DIA W8L115 PCV	Safety class I	IK03	IP20/40
910505103286	RC530B 40S/TW9 DIA W8L115 PCV	Safety class I	IK03	IP20/40
910505103287	RC530B 50S/TW9 DIA W8L145 PCV	Safety class I	IK03	IP20/40
910505103292	RC530B 34S/940 PSD W8L115 PCV SC	Safety class I	IK03	IP20/40
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	Safety class I	IK02	IP20/40
910505103138	RC531B 31S/940 W8L150 VPC ELP3	Safety class I	IK03	IP20
910505103140	RC531B 19S/940 W8L150 VPC ELP3	Safety class I	IK03	IP20/54
910505103141	RC530B 50S/940 W8L150 VPC ELP3	Safety class I	IK03	IP20
910505103144	RC530B 43S/940 W8L150 VPC ELP3	Safety class I	IK03	IP20
910505103154	RC530B 43S/940 PSD W8L150 VPC ELD3	Safety class I	IK03	IP20/54
910505103135	RC530B 43S/940 W8L145 PCV ELP3	Safety class I	IK03	IP20/54
910505103136	RC530B 50S/940 W8L145 PCV ELP3	Safety class I	IK03	IP20
910505103139	RC531B 19S/940 W8L145 PCV ELP3	Safety class I	IK03	IP20
910505103145	RC531B 31S/940 W8L145 PCV ELP3	Safety class I	IK03	IP20/54
910505103153	RC531B 19S/940 PSD W8L145 PCV ELD3	Safety class I	IK03	IP20

Order Code	Full Product Name	Protection class IEC	Mech. impact protection code	Ingress protection code
910505103120	RC534B 40S/940 PSD W8L120 VPC IP	Safety class I	IK03	IP20/40
910505103123	RC534B 50S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103125	RC535B 50S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103130	RC535B 43S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103101	RC530B 43S/940 PSD W8L150 VPC IP	Safety class I	IK03	IP20/40
910505103105	RC530B 34S/930 PSD W8L120 VPC IP	Safety class I	IK03	IP20/40
910505103113	RC530B 50S/940 PSD W8L150 VPC IP	Safety class I	IK03	IP20/40
910505103149	RC530B 40S/940 PSD W8L120 VPC IP	Safety class I	IK03	IP20/40
910505103150	RC530B 34S/940 PSD W8L120 VPC IP	Safety class I	IK03	IP20/40
910505103293	RC530B 34S/940 PSD W8L120 VPC IP SC	Safety class I	IK03	IP20/40
910505103128	RC534B 43S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103106	RC532B 19S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103109	RC533B 15S/940 PSD W8L113 PCV	Safety class I	IK03	IP20/40
910505103119	RC532B 25S/940 PSD W8L113 PCV	Safety class I	IK03	IP20/40
910505103122	RC532B 31S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103124	RC532B 43S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103126	RC533B 31S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103131	RC533B 19S/940 PSD W8L141 PCV	Safety class I	IK03	IP20/40
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	Safety class III	IK02	IP20/54
910505103155	RC532B 43S/940 SIA W8L145 PCV U4 W3	Safety class I	IK03	IP20
910505103160	RC530B 43S/940 SIA W8L145 PCV U4	Safety class I	IK03	IP20/54
910505103285	RC530B 43S/TW9 SIA W8L145 PCV U4	Safety class I	IK03	IP20
910505103291	RC530B 43S/TW9 SIA W8L145 PCV U4 SC	Safety class I	IK03	IP20/54
910505105669	RC530B 50S/TW9 SIA W8L145 PCV U4	Safety class I	IK03	IP20

Order Code	Full Product Name	Protection class IEC	Mech. impact protection	Ingress protection
			code	code
910505105670	RC531B 31S/TW9 SIA W8L145 PCV U4	Safety class I	IK03	IP20
910505103102	RC532B 25S/940 PSD W8L113 VPC	Safety class I	IK03	IP20/40
910505103103	RC531B 19S/930 PSD W8L150 VPC IP	Safety class I	IK03	IP20
910505103111	RC531B 15S/940 PSD W8L120 VPC IP	Safety class I	IK03	IP20/54
910505103112	RC531B 15S/930 PSD W8L120 VPC IP	Safety class I	IK03	IP20/54
910505103156	RC530B 34S/940 SIA W8L120 VPC U4 SC	Safety class I	IK03	IP20/54

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505103104	RC530B 15S/940 PSD W8L115 PCV	(0.38, 0.38) SDCM <3
910505103107	RC530B 31S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103110	RC530B 43S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103114	RC530B 19S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103115	RC530B 34S/940 PSD W8L115 PCV	(0.38, 0.38) SDCM <3
910505103116	RC531B 15S/930 PSD W8L115 PCV	(0.38, 0.38) SDCM <3
910505103117	RC531B 15S/940 PSD W8L115 PCV	(0.38, 0.38) SDCM <3
910505103121	RC531B 31S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103127	RC530B 50S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103129	RC531B 19S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103147	RC530B 40S/940 POE W8L120 VPC U0	(0.38, 0.38) SDCM <3
910505103284	RC530B 34S/TW9 DIA W8L115 PCV	(0.38, 0.38) SDCM <3
910505103286	RC530B 40S/TW9 DIA W8L115 PCV	(0.38, 0.38) SDCM <3
910505103287	RC530B 50S/TW9 DIA W8L145 PCV	(0.38, 0.38) SDCM <3
910505103292	RC530B 34S/940 PSD W8L115 PCV SC	(0.38, 0.38) SDCM <3
910505103118	RC532B LED15S/940 PSD W8L113 PCV PI5	(0.38, 0.38) SDCM <3
910505103138	RC531B 31S/940 W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103140	RC531B 19S/940 W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103141	RC530B 50S/940 W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103144	RC530B 43S/940 W8L150 VPC ELP3	(0.38, 0.38) SDCM <3
910505103154	RC530B 43S/940 PSD W8L150 VPC ELD3	(0.38, 0.38) SDCM <3
910505103135	RC530B 43S/940 W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103136	RC530B 50S/940 W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103139	RC531B 19S/940 W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103145	RC531B 31S/940 W8L145 PCV ELP3	(0.38, 0.38) SDCM <3
910505103153	RC531B 19S/940 PSD W8L145 PCV ELD3	(0.38, 0.38) SDCM <3
910505103120	RC534B 40S/940 PSD W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103123	RC534B 50S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103125	RC535B 50S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103130	RC535B 43S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103101	RC530B 43S/940 PSD W8L150 VPC IP	(0.38, 0.38) SDCM <3

Order Code	Full Product Name	Protection class IEC	Mech. impact protection	Ingress protection
			code	code
910505103157	RC530B 34S/930 SIA W8L120 VPC U4 W3	Safety class I	IK03	IP20
910505103158	RC530B 34S/930 SIA W8L120 VPC U4 W3 SC	Safety class I	IK03	IP20/54
910505103159	RC530B 25S/930 SIA W8L120 VPC U4 W3	Safety class I	IK03	IP20/54
910505103288	RC530B 34S/TW9 SIA W8L120 VPC U4	Safety class I	IK03	IP20
910505103289	RC530B 43S/TW9 SIA W8L145 VPC U4 SC	Safety class I	IK03	IP20
910505103290	RC531B 25S/TW9 SIA W8L120 VPC U4	Safety class I	IK03	IP20/54


Order Code	Full Product Name	Initial chromaticity
910505103105	RC530B 34S/930 PSD W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103113	RC530B 50S/940 PSD W8L150 VPC IP	(0.38, 0.38) SDCM <3
910505103149	RC530B 40S/940 PSD W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103150	RC530B 34S/940 PSD W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103293	RC530B 34S/940 PSD W8L120 VPC IP SC	(0.38, 0.38) SDCM <3
910505103128	RC534B 43S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103106	RC532B 19S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103109	RC533B 15S/940 PSD W8L113 PCV	(0.38, 0.38) SDCM <3
910505103119	RC532B 25S/940 PSD W8L113 PCV	(0.38, 0.38) SDCM <3
910505103122	RC532B 31S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103124	RC532B 43S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103126	RC533B 31S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103131	RC533B 19S/940 PSD W8L141 PCV	(0.38, 0.38) SDCM <3
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	(0.38, 0.38) SDCM <3
910505103155	RC532B 43S/940 SIA W8L145 PCV U4 W3	(0.38, 0.38) SDCM <3
910505103160	RC530B 43S/940 SIA W8L145 PCV U4	(0.38, 0.38) SDCM <3
910505103285	RC530B 43S/TW9 SIA W8L145 PCV U4	(0.38, 0.38) SDCM <3
910505103291	RC530B 43S/TW9 SIA W8L145 PCV U4 SC	(0.38, 0.38) SDCM <3
910505105669	RC530B 50S/TW9 SIA W8L145 PCV U4	Tunable, SDCM ≤3
910505105670	RC531B 31S/TW9 SIA W8L145 PCV U4	Tunable, SDCM ≤3
910505103102	RC532B 25S/940 PSD W8L113 VPC	(0.38, 0.38) SDCM <3
910505103103	RC531B 19S/930 PSD W8L150 VPC IP	(0.38, 0.38) SDCM <3
910505103111	RC531B 15S/940 PSD W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103112	RC531B 15S/930 PSD W8L120 VPC IP	(0.38, 0.38) SDCM <3
910505103156	RC530B 34S/940 SIA W8L120 VPC U4 SC	(0.38, 0.38) SDCM <3
910505103157	RC530B 34S/930 SIA W8L120 VPC U4 W3	(0.38, 0.38) SDCM <3
910505103158	RC530B 34S/930 SIA W8L120 VPC U4 W3 SC	(0.38, 0.38) SDCM <3
910505103159	RC530B 25S/930 SIA W8L120 VPC U4 W3	(0.38, 0.38) SDCM <3
910505103288	RC530B 34S/TW9 SIA W8L120 VPC U4	(0.38, 0.38) SDCM <3
910505103289	RC530B 43S/TW9 SIA W8L145 VPC U4 SC	(0.38, 0.38) SDCM <3
910505103290	RC531B 25S/TW9 SIA W8L120 VPC U4	(0.38, 0.38) SDCM <3

Application Conditions


Order Code	Full Product Name	Suitable for random switching
910505103104	RC530B 15S/940 PSD W8L115 PCV	No
910505103107	RC530B 31S/940 PSD W8L141 PCV	No
910505103110	RC530B 43S/940 PSD W8L141 PCV	No
910505103114	RC530B 19S/940 PSD W8L141 PCV	No
910505103115	RC530B 34S/940 PSD W8L115 PCV	No
910505103116	RC531B 15S/930 PSD W8L115 PCV	No
910505103117	RC531B 15S/940 PSD W8L115 PCV	No
910505103121	RC531B 31S/940 PSD W8L141 PCV	No
910505103127	RC530B 50S/940 PSD W8L141 PCV	No
910505103129	RC531B 19S/940 PSD W8L141 PCV	No
910505103147	RC530B 40S/940 POE W8L120 VPC U0	No
910505103284	RC530B 34S/TW9 DIA W8L115 PCV	No
910505103286	RC530B 40S/TW9 DIA W8L115 PCV	No
910505103287	RC530B 50S/TW9 DIA W8L145 PCV	No
910505103292	RC530B 34S/940 PSD W8L115 PCV SC	No
910505103118	RC532B LED15S/940 PSD W8L113 PCV P15	No
910505103138	RC531B 31S/940 W8L150 VPC ELP3	No
910505103140	RC531B 19S/940 W8L150 VPC ELP3	No
910505103141	RC530B 50S/940 W8L150 VPC ELP3	No
910505103144	RC530B 43S/940 W8L150 VPC ELP3	No
910505103154	RC530B 43S/940 PSD W8L150 VPC ELD3	No
910505103135	RC530B 43S/940 W8L145 PCV ELP3	No
910505103136	RC530B 50S/940 W8L145 PCV ELP3	No
910505103139	RC531B 19S/940 W8L145 PCV ELP3	No
910505103145	RC531B 31S/940 W8L145 PCV ELP3	No
910505103153	RC531B 19S/940 PSD W8L145 PCV ELD3	No
910505103120	RC534B 40S/940 PSD W8L120 VPC IP	No
910505103123	RC534B 50S/940 PSD W8L141 PCV	No
910505103125	RC535B 50S/940 PSD W8L141 PCV	No
910505103130	RC535B 43S/940 PSD W8L141 PCV	No
910505103101	RC530B 43S/940 PSD W8L150 VPC IP	No
910505103105	RC530B 34S/930 PSD W8L120 VPC IP	No
910505103113	RC530B 50S/940 PSD W8L150 VPC IP	No

Order Code	Full Product Name	Suitable for random switching
910505103149	RC530B 40S/940 PSD W8L120 VPC IP	No
910505103150	RC530B 34S/940 PSD W8L120 VPC IP	No
910505103293	RC530B 34S/940 PSD W8L120 VPC IP SC	No
910505103128	RC534B 43S/940 PSD W8L141 PCV	No
910505103106	RC532B 19S/940 PSD W8L141 PCV	No
910505103109	RC533B 15S/940 PSD W8L113 PCV	No
910505103119	RC532B 25S/940 PSD W8L113 PCV	No
910505103122	RC532B 31S/940 PSD W8L141 PCV	No
910505103124	RC532B 43S/940 PSD W8L141 PCV	No
910505103126	RC533B 31S/940 PSD W8L141 PCV	No
910505103131	RC533B 19S/940 PSD W8L141 PCV	No
910505103148	RC530B LED40S/940 POE W8L120 VPC U3	No
910505103155	RC532B 43S/940 SIA W8L145 PCV U4 W3	No
910505103160	RC530B 43S/940 SIA W8L145 PCV U4	No
910505103285	RC530B 43S/TW9 SIA W8L145 PCV U4	No
910505103291	RC530B 43S/TW9 SIA W8L145 PCV U4 SC	No
910505105669	RC530B 50S/TW9 SIA W8L145 PCV U4	Yes (relates to presence/ movement detection and daylight harvesting)
910505105670	RC531B 31S/TW9 SIA W8L145 PCV U4	Yes (relates to presence/ movement detection and daylight harvesting)
910505103102	RC532B 25S/940 PSD W8L113 VPC	No
910505103103	RC531B 19S/930 PSD W8L150 VPC IP	No
910505103111	RC531B 15S/940 PSD W8L120 VPC IP	No
910505103112	RC531B 15S/930 PSD W8L120 VPC IP	No
910505103156	RC530B 34S/940 SIA W8L120 VPC U4 SC	No
910505103157	RC530B 34S/930 SIA W8L120 VPC U4 W3	No
910505103158	RC530B 34S/930 SIA W8L120 VPC U4 W3 SC	No
910505103159	RC530B 25S/930 SIA W8L120 VPC U4 W3	No
910505103288	RC530B 34S/TW9 SIA W8L120 VPC U4	No
910505103289	RC530B 43S/TW9 SIA W8L145 VPC U4 SC	No
910505103290	RC531B 25S/TW9 SIA W8L120 VPC U4	No


Polar Wide Diagrams



Polar Normal (separate) - RC530BI - 910505103103




Polar Normal (separate) - RC530BI - 910505103127




Polar Normal (separate) - RC530BI - 910505103119


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103145




Polar Normal (separate) - RC530BI - 910505103150




Polar Normal (separate) - RC530BI - 910505103139




Polar Normal (separate) - RC530BI - 910505103122




Polar Normal (separate) - RC530BI - 910505103289




Polar Normal (separate) - RC530BI - 910505103106



Polar Normal (separate) - RC530BI - 910505103102




Polar Normal (separate) - RC530BI - 910505103115




**Polar Normal (separate) - RC530BI -
910505103153**


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103136




Polar Normal (separate) - RC530BI - 910505103128




Polar Normal (separate) - RC530BI - 910505103160




Polar Normal (separate) - RC530BI - 910505103120




Polar Normal (separate) - RC530BI - 910505103157




Polar Normal (separate) - RC530BI - 910505103285



Polar Normal (separate) - RC530BI - 910505103138




Polar Normal (separate) - RC530BI - 910505103159




Polar Normal (separate) - RC530BI - 910505103156


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103123




Polar Normal (separate) - RC530BI - 910505103293




Polar Normal (separate) - RC530BI - 910505103291




Polar Normal (separate) - RC530BI - 910505103117




Polar Normal (separate) - RC530BI - 910505103290




Polar Normal (separate) - RC530BI - 910505103129



Polar Normal (separate) - RC530BI - 910505103147




Polar Normal (separate) - RC530BI - 910505103148




Polar Normal (separate) - RC530BI - 910505103287


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103149




Polar Normal (separate) - RC530BI - 910505103112




Polar Normal (separate) - RC530BI - 910505103110




Polar Normal (separate) - RC530BI - 910505103116




Polar Normal (separate) - RC530BI - 910505103125




Polar Normal (separate) - RC530BI - 910505103101



Polar Normal (separate) - RC530BI - 910505103118




Polar Normal (separate) - RC530BI - 910505103288




Polar Normal (separate) - RC530BI - 910505103140


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103284




Polar Normal (separate) - RC530BI - 910505103155




Polar Normal (separate) - RC530BI - 910505103111




Polar Normal (separate) - RC530BI - 910505103124




Polar Normal (separate) - RC530BI - 910505103286




Polar Normal (separate) - RC530BI - 910505103104



Polar Normal (separate) - RC530BI - 910505103105




Polar Normal (separate) - RC530BI - 910505103292




Polar Normal (separate) - RC530BI - 910505103141


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103154




Polar Normal (separate) - RC530BI - 910505103144




Polar Normal (separate) - RC530BI - 910505103107




Polar Normal (separate) - RC530BI - 910505103109




Polar Normal (separate) - RC530BI - 910505103114




Polar Normal (separate) - RC530BI - 910505103113



Polar Normal (separate) - RC530BI - 910505103121




Polar Normal (separate) - RC530BI - 910505103126




Polar Normal (separate) - RC530BI - 910505103131


Polar Wide Diagrams




Polar Normal (separate) - RC530BI - 910505103130




Polar Normal (separate) - RC530BI - 910505103135



Polar Normal (separate) - RC530BI - 910505103158



Polar Normal (separate) - RC530BI - 910505105669



Polar Normal (separate) - RC530BI - 910505105670

