



RCS750 3-circuit square track system – flexible and multifunctional

3-circuit Square RCS750

The RCS750 3-circuit square track system is made up of a solid aluminum track available in lengths of 1, 2, 3 and 4 m with four electrical conductors. Any given configuration can be created easily: horizontal or vertical, mounted on or in the ceiling, on the wall or on free-standing panels. The system can also be used as a floating structure. All luminaires have a separate power supply and can be switched selectively. They can be moved easily to change the lighting and presentation. In this way, a multifunctional track system can be created for accent lighting as well as for suspending advertising and decorative material. A range of adaptors, power supply connections and mounting accessories is also available

Benefits

- Flexible 3-circuit track system for the professional user, allowing any required configuration to be created relatively easily.
- All luminaires have separate power switching so they can easily be moved, for example to create changing atmospheres in shop windows or interiors.
- Can be applied as a 'floating' structure using the suspension tubes and clamps provided.

Features

- Can be used with all Philips LED 3C track spots
- Available in lengths of 1, 2, 3 and 4 m
- Available in three finishes – white, black, aluminum
- Range of adaptors, power supply connections and mounting accessories available

3-circuit Square RCS750

Application

- Retail
- Indoor architectural lighting

Versions

ZRS750 CPF BK (XTS23-2)



ZRS750 CPS BK (XTS14-2)



ZRS750 TCPR WH (XTS36-3)



RBS750 recessed track, white



ZRS750 CPF WH (XTS23-3)



ZRS750 EPSR BK (XTS11-2+41-2)



ZRS750 EPSL BK (XTS12-2+41-2)



ZRS750 CPS WH (XTS14-3)



3-circuit Square RCS750

Versions

ZRS750 CCPI WH (XTS34-3)



ZRS750 EP BK (XTS41-2)



ZRS750 EP WH (XTS41-3)



ZRS750 ICP WH (XTS21-3)



ZRS750 ACP WH (XTS24-3)



ZRS750 3C BA WH (GA70-3)



ZRS750 EPSL WH (XTS12-3+41-3)



ZRS750 TCPR BK (XTS36-2)



3-circuit Square RCS750

Versions







ZRS700 SPCL ALU SUSP CLAMP L
(SKB18-1)



ZRS750 ICP BK (XTS21-2)











Dimensional drawing




3-circuit Square RCS750

Dimensional drawing



3-circuit Square RCS750

Dimensional drawing



Product details

Coupling piece with suspension set



Power supply connector end left



Fish plate connection



Flexible coupling/corner piece



End piece



3-circuit Square RCS750

Approval and Application	
CE mark	Yes
CE mark	Yes

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Protection class IEC	Input Voltage	Input Voltage
910930013618	ZRS750 CPF BK (XTS23-2)	-	-	250 V	250 V
910502559118	ZRS750 CPS BK (XTS14-2)	-	-	250 V	250 V
910500188015	ZRS750 TCPR WH (XTS36-3)	-	-	-	-
910930009118	RBS750 3C L2000 WH (XTSF4200-3)	Safety class I	Safety class I	-	-
910930009318	RBS750 3C L3000 WH (XTSF4300-3)	Safety class I	Safety class I	-	-
910500187515	ZRS750 CPF WH (XTS23-3)	-	-	-	-
910502558518	ZRS750 EPSR BK (XTS11-2+41-2)	-	-	250 V	250 V
910500188815	RCS750 3C L1000 WH (XTS4100-3)	Safety class I	Safety class I	-	-
910500188915	RCS750 3C L2000 WH (XTS4200-3)	Safety class I	Safety class I	-	-
910500189015	RCS750 3C L3000 WH (XTS4300-3)	Safety class I	Safety class I	-	-
910500189115	RCS750 3C L4000 WH (XTS4400-3)	Safety class I	Safety class I	-	-
910502558418	ZRS750 EPSL BK (XTS12-2+41-2)	-	-	250 V	250 V
910500187615	ZRS750 CPS WH (XTS14-3)	-	-	250 V	250 V
910500187815	ZRS750 CCPI WH (XTS34-3)	-	-	-	-

Order Code	Full Product Name	Protection class IEC	Protection class IEC	Input Voltage	Input Voltage
910502558618	ZRS750 EP BK (XTS41-2)	-	-	-	-
910500187715	ZRS750 EP WH (XTS41-3)	-	-	-	-
910500187415	ZRS750 ICP WH (XTS21-3)	-	-	-	-
910500188315	ZRS750 ACP WH (XTS24-3)	-	-	-	-
910930000818	ZRS750 3C BA WH (GA70-3)	-	-	250 V	250 V
910500187315	ZRS750 EPSL WH (XTS12-3+41-3)	-	-	250 V	250 V
910502559018	ZRS750 TCPR BK (XTS36-2)	-	-	-	-
914770011915	ZRS700 SPCL ALU SUSP CLAMP L (SKB18-1)	-	-	-	-
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Safety class I	Safety class I	-	-
910930013318	RCS750 3C L2000 BK (XTS4200-2)	Safety class I	Safety class I	-	-
910930013418	RCS750 3C L3000 BK (XTS4300-2)	Safety class I	Safety class I	-	-
910930013518	RCS750 3C L4000 BK (XTS4400-2)	Safety class I	Safety class I	-	-
910502558718	ZRS750 ICP BK (XTS21-2)	-	-	250 V	250 V

Mechanical and Housing

Order Code	Full Product Name	Accessory color	Ingress protection code	Ingress protection code
910930013618	ZRS750 CPF BK (XTS23-2)	Black	-	-
910502559118	ZRS750 CPS BK (XTS14-2)	Black	-	-
910500188015	ZRS750 TCPR WH (XTS36-3)	White	-	-
910930009118	RBS750 3C L2000 WH (XTSF4200-3)	White	IP30	IP30
910930009318	RBS750 3C L3000 WH (XTSF4300-3)	White	IP30	IP30
910500187515	ZRS750 CPF WH (XTS23-3)	White	-	-

Order Code	Full Product Name	Accessory color	Ingress protection code	Ingress protection code
910502558518	ZRS750 EPSR BK (XTS11-2+41-2)	Black	-	-
910500188815	RCS750 3C L1000 WH (XTS4100-3)	White	IP30	IP30
910500188915	RCS750 3C L2000 WH (XTS4200-3)	White	IP30	IP30
910500189015	RCS750 3C L3000 WH (XTS4300-3)	White	IP30	IP30
910500189115	RCS750 3C L4000 WH (XTS4400-3)	White	IP30	IP30

3-circuit Square RCS750

Order Code	Full Product Name	Accessory color	Ingress protection code	Ingress protection code
910502558418	ZRS750 EPSL BK (XTS12-2+41-2)	Black	-	-
910500187615	ZRS750 CPS WH (XTS14-3)	White	-	-
910500187815	ZRS750 CCPI WH (XTS34-3)	White	-	-
910502558618	ZRS750 EP BK (XTS41-2)	Black	-	-
910500187715	ZRS750 EP WH (XTS41-3)	White	-	-
910500187415	ZRS750 ICP WH (XTS21-3)	White	-	-
910500188315	ZRS750 ACP WH (XTS24-3)	White	-	-
910930000818	ZRS750 3C BA WH (GA70-3)	White	-	-
910500187315	ZRS750 EPSL WH (XTS12-3+41-3)	White	-	-

Approval and Application

Order Code	Full Product Name	Glow-wire test	Glow-wire test
910930013618	ZRS750 CPF BK (XTS23-2)	-	-
910502559118	ZRS750 CPS BK (XTS14-2)	-	-
910500188015	ZRS750 TCPR WH (XTS36-3)	-	-
910930009118	RBS750 3C L2000 WH (XTSF4200-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910930009318	RBS750 3C L3000 WH (XTSF4300-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910500187515	ZRS750 CPF WH (XTS23-3)	-	-
910502558518	ZRS750 EPSR BK (XTS11-2+41-2)	-	-
910500188815	RCS750 3C L1000 WH (XTS4100-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910500188915	RCS750 3C L2000 WH (XTS4200-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910500189015	RCS750 3C L3000 WH (XTS4300-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910500189115	RCS750 3C L4000 WH (XTS4400-3)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910502558418	ZRS750 EPSL BK (XTS12-2+41-2)	-	-
910500187615	ZRS750 CPS WH (XTS14-3)	-	-
910500187815	ZRS750 CCPI WH (XTS34-3)	-	-

Order Code	Full Product Name	Accessory color	Ingress protection code	Ingress protection code
910502559018	ZRS750 TCPR BK (XTS36-2)	Black	-	-
914770011915	ZRS700 SPCL ALU SUSP CLAMP L (SKB18-1)	Aluminum	-	-
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Black	IP30	IP30
910930013318	RCS750 3C L2000 BK (XTS4200-2)	Black	IP30	IP30
910930013418	RCS750 3C L3000 BK (XTS4300-2)	Black	IP30	IP30
910930013518	RCS750 3C L4000 BK (XTS4400-2)	Black	IP30	IP30
910502558718	ZRS750 ICP BK (XTS21-2)	Black	-	-

Order Code	Full Product Name	Glow-wire test	Glow-wire test
910502558618	ZRS750 EP BK (XTS41-2)	-	-
910500187715	ZRS750 EP WH (XTS41-3)	-	-
910500187415	ZRS750 ICP WH (XTS21-3)	-	-
910500188315	ZRS750 ACP WH (XTS24-3)	-	-
910930000818	ZRS750 3C BA WH (GA70-3)	-	-
910500187315	ZRS750 EPSL WH (XTS12-3+41-3)	-	-
910502559018	ZRS750 TCPR BK (XTS36-2)	-	-
914770011915	ZRS700 SPCL ALU SUSP CLAMP L (SKB18-1)	-	-
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910930013318	RCS750 3C L2000 BK (XTS4200-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910930013418	RCS750 3C L3000 BK (XTS4300-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910930013518	RCS750 3C L4000 BK (XTS4400-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s
910502558718	ZRS750 ICP BK (XTS21-2)	-	-

3-circuit Square RCS750

