



# RCS750 3-circuit square track system – flexible and multifunctional

## 3-circuit Square RCS750

The RCS750 3-circuit square track system is made up of a solid aluminium track available in lengths of 1, 2, 3 and 4 m with four electrical conductors. Any given configuration can be created easily: horizontal or vertical, mounted on or in the ceiling, on the wall or on free-standing panels. The system can also be used as a floating structure. All luminaires have a separate power supply and can be switched selectively. They can be moved easily to change the lighting and presentation. In this way, a multifunctional track system can be created for accent lighting as well as for suspending advertising and decorative material. A range of adaptors, power supply connections and mounting accessories is also available.

### Benefits

- Flexible 3-circuit track system for the professional user, allowing any required configuration to be created relatively easily
- Flexible 3-circuit track system for the professional user, allowing any required configuration to be created relatively easily
- All luminaires have separate power switching so they can easily be moved, for example to create changing atmospheres in shop windows or interiors
- All luminaires have separate power switching so they can easily be moved, for example to create changing atmospheres in shop windows or interiors
- Can be applied as a 'floating' structure using the suspension tubes and clamps provided
- Can be applied as a 'floating' structure using the suspension tubes and clamps provided

# 3-circuit Square RCS750

## Features

- -
- -

## Application

- Retail
- Retail
- Indoor architectural lighting
- Indoor architectural lighting

## Versions



ZRS750 CPS BK (XTS14-2)



ZRS750 EPSR BK (XTS11-2+41-2)



ZRS750 EP BK (XTS41-2)





ZRS750 EP WH (XTS41-3)





RCS750 track, black

## Dimensional drawing



3-circuit Square RCS750

Dimensional drawing



Product details

Coupling piece with suspension set



Power supply connector end left



End piece



Approval and Application

CE mark	Yes
CE mark	Yes

Operating and Electrical

Order Code	Full Product Name	Protection class IEC	Protection class IEC	Input Voltage	Input Voltage
910502559118	ZRS750 CPS BK (XTS14-2)	-	-	250 V	250 V
910502558518	ZRS750 EPSR BK (XTS11-2+41-2)	-	-	250 V	250 V
910502558618	ZRS750 EP BK (XTS41-2)	-	-	-	-

Order Code	Full Product Name	Protection class IEC	Protection class IEC	Input Voltage	Input Voltage
910500187715	ZRS750 EP WH (XTS41-3)	-	-	-	-
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Safety class I	Safety class I	-	-

## 3-circuit Square RCS750

### Mechanical and Housing

Order Code	Full Product Name	Accessory color	Ingress protection code	Ingress protection code
910502559118	ZRS750 CPS BK (XTS14-2)	Black	-	-
910502558518	ZRS750 EPSR BK (XTS11-2+41-2)	Black	-	-

Order Code	Full Product Name	Accessory color	Ingress protection code	Ingress protection code
910502558618	ZRS750 EP BK (XTS41-2)	Black	-	-
910500187715	ZRS750 EP WH (XTS41-3)	White	-	-
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Black	IP30	IP30

### Approval and Application

Order Code	Full Product Name	Glow-wire test	Glow-wire test
910502559118	ZRS750 CPS BK (XTS14-2)	-	-
910502558518	ZRS750 EPSR BK (XTS11-2+41-2)	-	-
910502558618	ZRS750 EP BK (XTS41-2)	-	-

Order Code	Full Product Name	Glow-wire test	Glow-wire test
910500187715	ZRS750 EP WH (XTS41-3)	-	-
910930013218	RCS750 3C L1000 BK (XTS4100-2)	Temperature 850 °C, duration 5 s	Temperature 850 °C, duration 5 s

