



A sustainable spot in a small and subtle design

GreenSpace Evo Mini Adjustable

GreenSpace Evo Mini Adjustable is a miniaturized accent spot with a subtle and neutral design which can be aimed up to 30 degrees. This makes the product an ideal choice for fashion, hospitality and residential applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo Mini Adjustable a sustainable choice for accent lighting. The PerfectAccent deep reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. Renovation projects are easy with Perfect Fit due to the multiple cutout dimensions that are available. Further customization of colors, textures and Perfect Fit cutouts is possible via Philips MyCreation

Benefits

- Blends into stores with a clean and neutral design
- Easy to aim the light up to 30 degrees
- Retrofitting older installations is easy with Perfect Fit's multiple available cutout options
- More sparkle and enhanced shopper eye comfort with PerfectAccent deep reflectors
- Extend the useful life of the product with easy serviceability and upgradeability
- The recycled materials and high energy efficiency help further reduce the carbon footprint of the product

GreenSpace Evo Mini Adjustable

Features

- Easy access to the optics, LED and front glass
- Serviceable and upgradeable with standard tools
- Available in multiple Perfect Fit cutout dimensions (80mm-100mm)
- Reduced carbon footprint due to high efficacy
- Equipped with state-of-the-art PerfectAccent deep reflectors
- Connectivity options: Interact compatible DALI (DIA) and Wireless (WIA)
- Optional front glass (recommended for dusty environments)

Application

- Fashion
- Hospitality
- Residential

Warnings and Safety


- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth
- During maintenance, the product must be switched off and cooled down
- The product must be installed out of arm's reach. Manipulating the product when hot is only possible with an insulated glove

Versions



RS321B GreenSpace Evo Mini
adjustable black

Dimensional drawing



GreenSpace Evo Mini Adjustable

Product details



RS321B GreenSpace Evo Mini
adjustable black



RS321B GreenSpace Evo Mini
adjustable white



RS321B GreenSpace Evo Mini
adjustable grey

General Information

Driver included	Yes
Number of gear units	1 unit
Service tag	Yes

Operating and Electrical

Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	Not applicable

Mechanical and Housing

Mech. impact protection code	IK02
------------------------------	------

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Product Data

Product family code	RS321B
---------------------	--------

Light Technical (1/2)

Order Code	Full Product Name	Correlated Color	Color	Luminous Efficacy	Luminous Flux
		Temperature	rendering		
(Nom)			index (CRI)	(rated) (Nom)	
59065600	RS321B 17S/PW940 DIA-E HWP FG GR	4000 K	>90	128 lm/W	1,700 lm
59078600	RS321B 12S/PW940 PSU-E HNB FG GR	4000 K	>90	119 lm/W	1,200 lm
58995700	RS321B 17S/840 PSU-E HMB BK	4000 K	>80	133 lm/W	1,700 lm
58997100	RS321B 20S/830 PSU-E HWP BK	3000 K	>80	122 lm/W	2,000 lm
59064900	RS321B 7S/PC930 PSU-E HMB FG BK	3000 K	>90	105 lm/W	700 lm
59074800	RS321B 7S/PW930 PSU-E HWP BK	3000 K	>90	120 lm/W	700 lm
59075500	RS321B 7S/PW940 PSU-E HWP BK	4000 K	>90	127 lm/W	700 lm
59079300	RS321B 12S/PC930 WIA-E HMB BK	3000 K	>90	117 lm/W	1,200 lm
58996400	RS321B 17S/PC930 WIA-E HMB WH	3000 K	>90	111 lm/W	1,700 lm
58998800	RS321B 20S/PW940 DIA-E HMB WH	4000 K	>90	128 lm/W	2,000 lm
59066300	RS321B 20S/PW930 WIA-E HMB WH	3000 K	>90	122 lm/W	2,000 lm
59072400	RS321B 7S/830 PSU-E HWP WH	3000 K	>80	118 lm/W	700 lm
59073100	RS321B 7S/840 PSU-E HVWB WH	4000 K	>80	123 lm/W	700 lm
59076200	RS321B 12S/830 PSU-E HWP WH	3000 K	>80	127 lm/W	1,200 lm

GreenSpace Evo Mini Adjustable

Order Code	Full Product Name	Correlated Color	Color	Luminous Efficacy (rated) (Nom)	Luminous Flux
		Temperature (Nom)	rendering index (CRI)		
59077900	RS321B 12S/PW930 PSU-E HMB FG WH	3000 K	>90	121 lm/W	1,200 lm

Light Technical (2/2)

Order Code	Full Product Name	Optic type	Order Code	Full Product Name	Optic type
59065600	RS321B 17S/PW940 DIA-E HWB FG GR	High-reflective metal reflector Medium beam 20 to 40 degrees	58996400	RS321B 17S/PC930 WIA-E HMB WH	High-reflective metal reflector Medium beam 20 to 40 degrees
59078600	RS321B 12S/PW940 PSU-E HNB FG GR	High-reflective metal reflector Narrow beam 10 to 20 degrees	58998800	RS321B 20S/PW940 DIA-E HMB WH	High-reflective metal reflector Medium beam 20 to 40 degrees
58995700	RS321B 17S/840 PSU-E HMB BK	High-reflective metal reflector Medium beam 20 to 40 degrees	59066300	RS321B 20S/PW930 WIA-E HMB WH	High-reflective metal reflector Medium beam 20 to 40 degrees
58997100	RS321B 20S/830 PSU-E HWB BK	High-reflective metal reflector Medium beam 20 to 40 degrees	59072400	RS321B 7S/830 PSU-E HWB WH	High-reflective metal reflector Medium beam 20 to 40 degrees
59064900	RS321B 7S/PC930 PSU-E HMB FG BK	High-reflective metal reflector Medium beam 20 to 40 degrees	59073100	RS321B 7S/840 PSU-E HVWB WH	High-reflective metal reflector Wide beam 40 to 80 degrees
59074800	RS321B 7S/PW930 PSU-E HWB BK	High-reflective metal reflector Medium beam 20 to 40 degrees	59076200	RS321B 12S/830 PSU-E HWB WH	High-reflective metal reflector Medium beam 20 to 40 degrees
59075500	RS321B 7S/PW940 PSU-E HWB BK	High-reflective metal reflector Medium beam 20 to 40 degrees	59077900	RS321B 12S/PW930 PSU-E HMB FG WH	High-reflective metal reflector Medium beam 20 to 40 degrees
59079300	RS321B 12S/PC930 WIA-E HMB BK	High-reflective metal reflector Medium beam 20 to 40 degrees			

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
59065600	RS321B 17S/PW940 DIA-E HWB FG GR	13.8 W	58996400	RS321B 17S/PC930 WIA-E HMB WH	17.7 W
59078600	RS321B 12S/PW940 PSU-E HNB FG GR	10.4 W	58998800	RS321B 20S/PW940 DIA-E HMB WH	17.9 W
58995700	RS321B 17S/840 PSU-E HMB BK	13.9 W	59066300	RS321B 20S/PW930 WIA-E HMB WH	17.7 W
58997100	RS321B 20S/830 PSU-E HWB BK	17.9 W	59072400	RS321B 7S/830 PSU-E HWB WH	6.6 W
59064900	RS321B 7S/PC930 PSU-E HMB FG BK	6.6 W	59073100	RS321B 7S/840 PSU-E HVWB WH	6.6 W
59074800	RS321B 7S/PW930 PSU-E HWB BK	6.6 W	59076200	RS321B 12S/830 PSU-E HWB WH	10.3 W
59075500	RS321B 7S/PW940 PSU-E HWB BK	6.6 W	59077900	RS321B 12S/PW930 PSU-E HMB FG WH	10.2 W
59079300	RS321B 12S/PC930 WIA-E HMB BK	10 W			

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
59065600	RS321B 17S/PW940 DIA-E HWB FG GR	Yes	58996400	RS321B 17S/PC930 WIA-E HMB WH	Yes
59078600	RS321B 12S/PW940 PSU-E HNB FG GR	No	58998800	RS321B 20S/PW940 DIA-E HMB WH	Yes
58995700	RS321B 17S/840 PSU-E HMB BK	No	59066300	RS321B 20S/PW930 WIA-E HMB WH	Yes
58997100	RS321B 20S/830 PSU-E HWB BK	No	59072400	RS321B 7S/830 PSU-E HWB WH	No
59064900	RS321B 7S/PC930 PSU-E HMB FG BK	No	59073100	RS321B 7S/840 PSU-E HVWB WH	No
59074800	RS321B 7S/PW930 PSU-E HWB BK	No	59076200	RS321B 12S/830 PSU-E HWB WH	No
59075500	RS321B 7S/PW940 PSU-E HWB BK	No	59077900	RS321B 12S/PW930 PSU-E HMB FG WH	No
59079300	RS321B 12S/PC930 WIA-E HMB BK	Yes			

Mechanical and Housing

GreenSpace Evo Mini Adjustable

Order Code	Full Product Name	Ingress	
		Housing Color	protection code
59065600	RS321B 17S/PW940 DIA-E HWB FG GR	Gray	IP20/54
59078600	RS321B 12S/PW940 PSU-E HNB FG GR	Gray	IP20/54
58995700	RS321B 17S/840 PSU-E HMB BK	Black	IP20
58997100	RS321B 20S/830 PSU-E HWB BK	Black	IP20
59064900	RS321B 7S/PC930 PSU-E HMB FG BK	Black	IP20/54
59074800	RS321B 7S/PW930 PSU-E HWB BK	Black	IP20
59075500	RS321B 7S/PW940 PSU-E HWB BK	Black	IP20
59079300	RS321B 12S/PC930 WIA-E HMB BK	Black	IP20

Order Code	Full Product Name	Ingress	
		Housing Color	protection code
58996400	RS321B 17S/PC930 WIA-E HMB WH	White	IP20
58998800	RS321B 20S/PW940 DIA-E HMB WH	White	IP20
59066300	RS321B 20S/PW930 WIA-E HMB WH	White	IP20
59072400	RS321B 7S/830 PSU-E HWB WH	White	IP20
59073100	RS321B 7S/840 PSU-E HVWB WH	White	IP20
59076200	RS321B 12S/830 PSU-E HWB WH	White	IP20
59077900	RS321B 12S/PW930 PSU-E HMB FG WH	White	IP20/54

Approval and Application

Order Code	Full Product Name	Stroboscopic effect visibility
		measure (SVM)
59065600	RS321B 17S/PW940 DIA-E HWB FG GR	0.4
59078600	RS321B 12S/PW940 PSU-E HNB FG GR	0.4
58995700	RS321B 17S/840 PSU-E HMB BK	0.4
58997100	RS321B 20S/830 PSU-E HWB BK	0.4
59064900	RS321B 7S/PC930 PSU-E HMB FG BK	0.4
59074800	RS321B 7S/PW930 PSU-E HWB BK	0.4
59075500	RS321B 7S/PW940 PSU-E HWB BK	0.4
59079300	RS321B 12S/PC930 WIA-E HMB BK	0.5


Order Code	Full Product Name	Stroboscopic effect visibility
		measure (SVM)
58996400	RS321B 17S/PC930 WIA-E HMB WH	0.5
58998800	RS321B 20S/PW940 DIA-E HMB WH	0.4
59066300	RS321B 20S/PW930 WIA-E HMB WH	0.5
59072400	RS321B 7S/830 PSU-E HWB WH	0.4
59073100	RS321B 7S/840 PSU-E HVWB WH	0.4
59076200	RS321B 12S/830 PSU-E HWB WH	0.4
59077900	RS321B 12S/PW930 PSU-E HMB FG WH	0.4

Initial Performance (IEC Compliant)


Order Code	Full Product Name	Initial chromaticity
59065600	RS321B 17S/PW940 DIA-E HWB FG GR	(0.374, 0.364) SDCM <2
59078600	RS321B 12S/PW940 PSU-E HNB FG GR	(0.374, 0.364) SDCM <2
58995700	RS321B 17S/840 PSU-E HMB BK	(0.382, 0.380) SDCM <3
58997100	RS321B 20S/830 PSU-E HWB BK	(0.434, 0.403) SDCM <3
59064900	RS321B 7S/PC930 PSU-E HMB FG BK	(0.422, 0.386) SDCM <2
59074800	RS321B 7S/PW930 PSU-E HWB BK	(0.422, 0.386) SDCM <2
59075500	RS321B 7S/PW940 PSU-E HWB BK	(0.374, 0.364) SDCM <2
59079300	RS321B 12S/PC930 WIA-E HMB BK	(0.422, 0.386) SDCM <2

Order Code	Full Product Name	Initial chromaticity
58996400	RS321B 17S/PC930 WIA-E HMB WH	(0.422, 0.386) SDCM <2
58998800	RS321B 20S/PW940 DIA-E HMB WH	(0.374, 0.364) SDCM <2
59066300	RS321B 20S/PW930 WIA-E HMB WH	(0.422, 0.386) SDCM <2
59072400	RS321B 7S/830 PSU-E HWB WH	(0.434, 0.403) SDCM <3
59073100	RS321B 7S/840 PSU-E HVWB WH	(0.382, 0.380) SDCM <3
59076200	RS321B 12S/830 PSU-E HWB WH	(0.434, 0.403) SDCM <3
59077900	RS321B 12S/PW930 PSU-E HMB FG WH	(0.422, 0.386) SDCM <2


Polar Wide Diagrams



Polar Normal (separate) - RS320BI - 910505104585




Polar Normal (separate) - RS320BI - 910505104589




Polar Normal (separate) - RS320BI - 910505104590

GreenSpace Evo Mini Adjustable


Polar Wide Diagrams




Polar Normal (separate) - RS320BI - 910505104591




Polar Normal (separate) - RS320BI - 910505104588




Polar Normal (separate) - RS320BI - 910505104586




Polar Normal (separate) - RS320BI - 910505104587




Polar Normal (separate) - RS320BI - 910505104584




Polar Normal (separate) - RS320BI - 910505104501



Polar Normal (separate) - RS320BI - 910505102999




Polar Normal (separate) - RS320BI - 910505104502




Polar Normal (separate) - RS320BI - 910505102998

GreenSpace Evo Mini Adjustable


Polar Wide Diagrams



Polar Normal (separate) - RS320BI -
910505104569



Polar Normal (separate) - RS320BI -
910505104570



Polar Normal (separate) - RS320BI -
910505104568

