



# Philips GreenSpace Accent Elbow Gen2: A serviceable, upgradeable and extractable accent downlight for retail

## GreenSpace Accent Elbow Gen2

With GreenSpace Accent Elbow Gen2, retailers and building operators can enjoy the superior quality of light and market-leading energy efficiency of PerfectAccent optics in an affordable and sustainable accent downlighter. Maintenance and upgrades of the driver, LED and optics is easy and requires only standard tools. Because of this, GreenSpace Accent Elbow Gen2 can support a circular lighting installation. The luminaire's extractable and rotatable spotlight ensures that light can be aimed where required. In addition to dimming options, multiple system integration options are available, including wired and wireless. Fresh food LED lighting recipes are available for prolonged shelf life, better visual representation of food, reduction of food waste and increased sales. Check out our Fashion and Food catalogue pages to find out more about our PremiumWhite, PremiumColor, Fresh Meat, Rosé, Frost and Champagne recipes.

### Benefits

- More sparkle and enhanced eye comfort for shoppers with PerfectAccent optics
- Extend the useful life of the product with easy maintenance and upgrades
- The neutral clean product design helps blend in with the ceiling
- Flexible in store due to wide freedom of aiming

# GreenSpace Accent Elbow Gen2

## Features

- Serviceable and upgradeable with standard tools
- Equipped with state-of-the-art PerfectAccent reflector optics
- Reduced carbon footprint due to high efficacy
- Available with fresh food LED lighting recipes and LED flavours
- Wired (DALI) and wireless connectivity options
- Optional front glass (recommended for dusty environments)

## Application

- Supermarkets and hypermarkets
- Large retail
- Shopping malls

## Warnings and Safety


- All photometrical data are calculated without optional front glass. Flux should be reduced by 3.5% when using front glass.
- Cleaning of the optic should be done only with compressed air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, we strongly advise the use of the optional front glass, as it can be cleaned with a dry microfiber cloth.
- During maintenance, the product must be switched off and cooled down.
- The product must be installed out of arm's reach. Manipulating the product when hot is possible only with an insulated glove.

## Versions



RS352B GreenSpace Accent Elbow White

## Dimensional drawing



# GreenSpace Accent Elbow Gen2

## Product details

GreenSpace Accent Elbow is fully serviceable and upgradeable

RS352B GreenSpace Accent Elbow White



General Information	
Driver included	Yes
Number of gear units	2 units
Service Tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Colour Temperature (Nom)	3000 K
Optic type	Wide beam
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Mechanical and Housing	
Explosion hazard class	-
Housing Colour	White
Mech. impact protection code	IK02
Ingress protection code	IP20
Emergency Operation	
Central Emergency	No
Approval and Application	
Ambient temperature range	+10 to +35 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM)	0.9
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%
Product Data	
Product family code	RS352B

## Light Technical

Order Code	Full Product Name	Colour rendering	Luminous efficacy	Luminous Flux
		index (CRI)	(rated) (nom.)	
910505102761	RS352B 27S/830 PSU-E WB WH	>80	133 lm/W	3,000 lm
910505102765	RS352B 27S/PC930 WIA-E WB	>90	113 lm/W	2,700 lm
	ACC WH			

# GreenSpace Accent Elbow Gen2

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505102761	RS352B 27S/830 PSU-E WB WH	22.5 W

Order Code	Full Product Name	Power Consumption
910505102765	RS352B 27S/PC930 WIA-E WB ACC WH	24 W

## Controls and Dimming



Order Code	Full Product Name	Dimmable	Maximum dim level
910505102761	RS352B 27S/830 PSU-E WB WH	No	Not applicable
910505102765	RS352B 27S/PC930 WIA-E WB ACC WH	Yes	10%

## Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
910505102761	RS352B 27S/830 PSU-E WB WH	(0.434, 0.403) SDCM <2

Order Code	Full Product Name	Initial chromaticity
910505102765	RS352B 27S/PC930 WIA-E WB ACC WH	(0.422, 0.386) SDCM <2

## Polar Wide Diagrams



Polar Normal (separate) - RS352BI -  
910505102761

Polar Normal (separate) - RS352BI -  
910505102765

