



It delivers super flexibility, complete product range and seamlessly system integration to Hospitality customers..

Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Benefits

- Complete portfolio covering from 400lm to 3000lm, 3CCT and 3 beam angles.
- Super flexibility with modular design, and different trims to suit different application.
- Smart connectivity to seamlessly integration with Interact Hospitality.
- Deep recess for visual comfort
- Easy installation and maintenance

Features

- 6w ~42w (400lm~3200lm)
- CRI 90, SDCM <3
- Beam Angle: NB, MB, WB
- CCT: 2700K, 3000K, 4000K
- High reliability, 50Khrs (L80B50@25°C)

Application

- Guest room
- Bath room
- Corridor
- Lobby

Specifications

Mounting type	Recessed
Operating Temperature range	-20 to +45 °C
Light Source	COB
Mains Voltage	220-240V AC/ 50-60Hz
Optical Accessories	available through ETO
Dimming	PSU: non-dimmable PSD: dimmable via Dali protocol PSR: trailing dimmable PSR 1-10V: 1-10v dimmable DMX: dimmable via DMX protocol
Control system input	DALI / 1-10V / DMX / trailing edge
Material	Heat sink: die-cast aluminum
Main color of the luminaire	Housing: dark Grey Reflector: color available through ETO
Lumen maintenance at median useful life 50.000h	L80
Luminous flux	468-3990lm
Power consumption	6W-42W

Correlated color temperature - CCT	2700K, 3000K, 4000K
Color Rendering index - CRI	90
Beam angle	NB (Narrow Beam): 15-18° MB (Medium Beam): 20-24° WB (Wide Beam): 30-40° VWB (Very Wide Beam): 50°
Protection Class IEC61140	Class II & Class III for MR16 version
Mechanical impact protection	IK04
Ingress protection	IP20 / IP54(Front side) for selected SKU only
Light source replaceable	No
Driver replaceable	yes
Overall diameter	D55-D150
Installation	recessed Fixation by means of spring fasteners

Versions



RS378B P24 M70



RS378B P33 M87

Dimensional drawing



Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	DALI
Mechanical and Housing	
Optical cover type	PMMA
Housing Color	Grey
Mech. impact protection code	IK04
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	-20 to +45 °C
CE mark	Yes
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

Light Technical		Correlated Color	Luminous Efficacy	
Order Code	Full Product Name	Temperature (Nom)	(rated) (Nom)	Luminous Flux
911401536271	RS378B P11 930 PSD-E MB M55	3000 K	87 lm/W	957 lm
911401536371	RS378B P11 930 PSD-E WB M55	3000 K	87 lm/W	957 lm
911401536471	RS378B P11 940 PSD-E NB M55	4000 K	78 lm/W	858 lm
911401536571	RS378B P11 940 PSD-E MB M55	4000 K	92 lm/W	1,012 lm
911401536671	RS378B P11 940 PSD-E WB M55	4000 K	92 lm/W	1,012 lm
911401538071	RS378B P24 930 PSD-E MB M70	3000 K	98 lm/W	2,350 lm
911401538171	RS378B P24 930 PSD-E WB M70	3000 K	98 lm/W	2,350 lm
911401538271	RS378B P24 940 PSD-E NB M70	4000 K	100 lm/W	2,400 lm
911401538371	RS378B P24 940 PSD-E MB M70	4000 K	100 lm/W	2,400 lm
911401538471	RS378B P24 940 PSD-E WB M70	4000 K	100 lm/W	2,400 lm
911401538871	RS378B P33 930 PSD-E NB M87	3000 K	71 lm/W	2,350 lm
911401539171	RS378B P33 940 PSD-E NB M87	4000 K	73 lm/W	2,400 lm
911401537171	RS378B P15 930 PSD-E MB M55	3000 K	90 lm/W	1,350 lm
911401537271	RS378B P15 930 PSD-E WB M55	3000 K	90 lm/W	1,350 lm
911401537371	RS378B P15 940 PSD-E NB M55	4000 K	78 lm/W	1,170 lm
911401537471	RS378B P15 940 PSD-E MB M55	4000 K	94 lm/W	1,410 lm
911401537571	RS378B P15 940 PSD-E WB M55	4000 K	94 lm/W	1,410 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401536271	RS378B P11 930 PSD-E MB M55	11 W
911401536371	RS378B P11 930 PSD-E WB M55	11 W
911401536471	RS378B P11 940 PSD-E NB M55	11 W
911401536571	RS378B P11 940 PSD-E MB M55	11 W
911401536671	RS378B P11 940 PSD-E WB M55	11 W
911401538071	RS378B P24 930 PSD-E MB M70	24 W
911401538171	RS378B P24 930 PSD-E WB M70	24 W
911401538271	RS378B P24 940 PSD-E NB M70	24 W
911401538371	RS378B P24 940 PSD-E MB M70	24 W

Order Code	Full Product Name	Power Consumption
911401538471	RS378B P24 940 PSD-E WB M70	24 W
911401538871	RS378B P33 930 PSD-E NB M87	33 W
911401539171	RS378B P33 940 PSD-E NB M87	33 W
911401537171	RS378B P15 930 PSD-E MB M55	15 W
911401537271	RS378B P15 930 PSD-E WB M55	15 W
911401537371	RS378B P15 940 PSD-E NB M55	15 W
911401537471	RS378B P15 940 PSD-E MB M55	15 W
911401537571	RS378B P15 940 PSD-E WB M55	15 W

