



A small and sustainable surface mounted cylinder in a sleek, subtle design

GreenSpace Evo Mini Cylinder

GreenSpace Evo Mini Cylinder is a sustainable lighting fixture that comes with a sleek and subtle design. This makes the Cylinder an ideal choice for hospitality and fashion retail applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminium. Because of its circular design, the luminaire is upgradable, reusable, fully serviceable and recyclable. Combined with the high energy efficiency, this makes the GreenSpace Evo Mini Cylinder a sustainable choice. The new PerfectAccent deep reflectors ensure a light effect with increased sparkle and improved shopper eye comfort. Further customization of colors and textures is possible via Philips MyCreation

Benefits

- The sleek and subtle design fits perfectly in any installation
- More sparkle and enhanced shopper eye comfort with PerfectAccent deep reflectors
- Extend the useful life of the product with easy serviceability and upgradeability
- The recycled materials and high energy efficiency help further reduce the carbon footprint of the product

GreenSpace Evo Mini Cylinder

Features

- Toolless access to the optics, LED and front glass
- Serviceable and upgradeable with standard tools
- Reduced carbon footprint due to high efficacy
- Equipped with state-of-the-art PerfectAccent deep reflectors
- Connectivity options: Interact compatible DALI (DIA) and Wireless (WIA)
- Optional front glass (recommended for dusty environments)

Application

- Fashion
- Hospitality
- Residential

Warnings and Safety

- Cleaning of the optic should only be done with pressurized air. Touching the LED or reflector is forbidden. For food preparation areas and areas with high levels of dust, the use of the optional front glass is strongly advised, as it can be cleaned with a (dry) microfiber cloth

Versions



SA332C GreenSpace Evo Mini
Cylinder DIA-WIA - White




SA332C GreenSpace Evo Mini
Cylinder DIA-WIA - Grey



SA332C GreenSpace Evo Mini
Cylinder PSU - White

GreenSpace Evo Mini Cylinder

Dimensional drawing



| General Information | |
|-------------------------------------|-----------------------------------|
| Driver included | Yes |
| Number of gear units | 1 unit |
| Light Technical | |
| Correlated Color Temperature (Nom) | 3000 K |
| Color rendering index (CRI) | >90 |
| Operating and Electrical | |
| Protection class IEC | Safety class II |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Suitable for random switching | Not applicable |
| Mechanical and Housing | |
| Mech. impact protection code | IK02 |
| Ingress protection code | IP20 |
| Approval and Application | |
| Ambient temperature range | +10 to +35 °C |
| CE mark | Yes |
| ENEC mark | - |
| Flammability mark | - |
| Glow-wire test | Temperature 650 °C, duration 30 s |
| Initial Performance (IEC Compliant) | |
| Initial chromaticity | (0.422, 0.386) SDCM <2 |
| Luminous flux tolerance | +/-10% |
| Product Data | |
| Product family code | SA332C |

Light Technical

| Order Code | Full Product Name | Luminous Efficacy | | |
|--------------|--------------------------------|-------------------|---------------|-------------|
| | | (rated) (Nom) | Luminous Flux | Optic type |
| 910505104953 | SA332C 10S/PC930 PSU HMB BK482 | 125 lm/W | 1,021 lm | Medium beam |
| 910505104954 | SA332C 12S/PW930 PSU HWB BK482 | 126 lm/W | 1,355 lm | Wide beam |
| 910505104956 | SA332C 10S/PC930 DIA HMB WH481 | 121 lm/W | 1,021 lm | Medium beam |
| 910505104957 | SA332C 12S/PW930 DIA HWB WH481 | 122 lm/W | 1,355 lm | Wide beam |
| 910505104959 | SA332C 10S/PC930 WIA HMB WH481 | 119 lm/W | 1,021 lm | Medium beam |
| 910505104958 | SA332C 8S/PW930 WIA HNB BK482 | 111 lm/W | 790 lm | Narrow beam |
| 910505104960 | SA332C 12S/PW930 WIA HWB BK482 | 122 lm/W | 1,355 lm | Wide beam |
| 910505104955 | SA332C 8S/PW930 DIA HNB GR482 | 114 lm/W | 790 lm | Narrow beam |
| 910505104952 | SA332C 8S/PW930 PSU HNB WH481 | 122 lm/W | 790 lm | Narrow beam |

Operating and Electrical

| Order Code | Full Product Name | Power Consumption | Order Code | Full Product Name | Power Consumption |
|--------------|--------------------------------|-------------------|--------------|--------------------------------|-------------------|
| 910505104953 | SA332C 10S/PC930 PSU HMB BK482 | 8.1 W | 910505104954 | SA332C 12S/PW930 PSU HWB BK482 | 10 W |

GreenSpace Evo Mini Cylinder

| Order Code | Full Product Name | Power Consumption |
|--------------|--------------------------------|-------------------|
| 910505104956 | SA332C 10S/PC930 DIA HMB WH481 | 8.5 W |
| 910505104957 | SA332C 12S/PW930 DIA HWB WH481 | 10.3 W |
| 910505104959 | SA332C 10S/PC930 WIA HMB WH481 | 8.6 W |
| 910505104958 | SA332C 8S/PW930 WIA HNB BK482 | 7.1 W |

| Order Code | Full Product Name | Power Consumption |
|--------------|--------------------------------|-------------------|
| 910505104960 | SA332C 12S/PW930 WIA HWB BK482 | 10.3 W |
| 910505104955 | SA332C 8S/PW930 DIA HNB GR482 | 6.9 W |
| 910505104952 | SA332C 8S/PW930 PSU HNB WH481 | 6.5 W |

Controls and Dimming

| Order Code | Full Product Name | Dimmable |
|--------------|--------------------------------|----------|
| 910505104953 | SA332C 10S/PC930 PSU HMB BK482 | No |
| 910505104954 | SA332C 12S/PW930 PSU HWB BK482 | No |
| 910505104956 | SA332C 10S/PC930 DIA HMB WH481 | Yes |
| 910505104957 | SA332C 12S/PW930 DIA HWB WH481 | Yes |
| 910505104959 | SA332C 10S/PC930 WIA HMB WH481 | Yes |


| Order Code | Full Product Name | Dimmable |
|--------------|--------------------------------|----------|
| 910505104958 | SA332C 8S/PW930 WIA HNB BK482 | Yes |
| 910505104960 | SA332C 12S/PW930 WIA HWB BK482 | Yes |
| 910505104955 | SA332C 8S/PW930 DIA HNB GR482 | Yes |
| 910505104952 | SA332C 8S/PW930 PSU HNB WH481 | No |

Mechanical and Housing


| Order Code | Full Product Name | Housing Color |
|--------------|--------------------------------|---------------|
| 910505104953 | SA332C 10S/PC930 PSU HMB BK482 | Black |
| 910505104954 | SA332C 12S/PW930 PSU HWB BK482 | Black |
| 910505104956 | SA332C 10S/PC930 DIA HMB WH481 | White |
| 910505104957 | SA332C 12S/PW930 DIA HWB WH481 | White |
| 910505104959 | SA332C 10S/PC930 WIA HMB WH481 | White |

| Order Code | Full Product Name | Housing Color |
|--------------|--------------------------------|---------------|
| 910505104958 | SA332C 8S/PW930 WIA HNB BK482 | Black |
| 910505104960 | SA332C 12S/PW930 WIA HWB BK482 | Black |
| 910505104955 | SA332C 8S/PW930 DIA HNB GR482 | Gray |
| 910505104952 | SA332C 8S/PW930 PSU HNB WH481 | White |


Polar Wide Diagrams




Polar Normal (separate) - SA332CI - 910505104956




Polar Normal (separate) - SA332CI - 910505104952




Polar Normal (separate) - SA332CI - 910505104959



Polar Normal (separate) - SA332CI - 910505104958




Polar Normal (separate) - SA332CI - 910505104954




Polar Normal (separate) - SA332CI - 910505104955

GreenSpace Evo Mini Cylinder


Polar Wide Diagrams



Polar Normal (separate) - SA332CI - 910505104957



Polar Normal (separate) - SA332CI - 910505104953



Polar Normal (separate) - SA332CI - 910505104960

