



Philips TrueLine Surface: True line of light

TrueLine, surface mounted

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in suspended and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

TrueLine, surface mounted

Features

- Highly-uniform lighting with excellent glare control ($UGR < 19$, $L65 < 3000 \text{cd/m}^2$)
- Best-in-class efficacy up to 140 lm/W
- 3000K, 4000K, and Tunable White versions, all CRI > 90
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options, including all accessories

Application

- Offices
- Education
- Retail

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions

TrueLine surface mounted-
SM530C L1130 ALU



TrueLine-SM534C



TrueLine surface mounted-
SM530C L1130 WH



TrueLine-SM530 L570 WH



SP530P with U4 BK sensor



TrueLine, surface mounted

Versions



TrueLine Surface Mounted black housing



TrueLine-SM530 L570 Alu



TrueLine-SM530 U3 SNS210 L2850 Alu




TrueLine-SM530 L570 BK




TrueLine-SM530 L2810 WH

Dimensional drawing



Dimensional drawing



TrueLine, surface mounted

Product details



TrueLine-SP534_SM534P-DPP.tif



TrueLine-RC534B_SM534C_SP534P-DPP.tif




TrueLine_SM-line-U3



TrueLine Surface Mounted black housing



TrueLine_SM_SP-line-coupling-piece-side-view



TrueLine_SM_SP-line-connection-top-view-2



TrueLine_Surface-Mounted-line-side-view



SP530P U4 BK DPP

TrueLine, surface mounted

Product details



TrueLine_SM_SP-line-connectio-
side-view-2

TrueLine, surface mounted

General Information

Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>90

Operating and Electrical

Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No

Controls and Dimming

Dimmable	Yes
Maximum dim level	1%

Mechanical and Housing

Mech. impact protection code	IK03
Ingress protection code	IP20

Approval and Application

Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
97213100	SM530C 40S/940 PSD L1130 ALU	4000 K	138 lm/W	4,000 lm	Wide beam
97212400	SM530C 34S/940 PSD L1130 ALU	4000 K	143 lm/W	3,400 lm	Wide beam
97204900	SM530C 19S/940 PSD L1410 ALU	4000 K	139 lm/W	1,900 lm	Wide beam
97222300	SM531C 19S/940 PSD L1410 ALU	4000 K	110 lm/W	1,900 lm	Wide beam
97220900	SM531C 19S/930 PSD L1410 ALU	3000 K	104 lm/W	1,900 lm	Wide beam
97215500	SM530C 43S/940 PSD L1410 ALU	4000 K	144 lm/W	4,300 lm	Wide beam
97210000	SM530C 34S/930 PSD L1130 ALU	3000 K	133 lm/W	3,400 lm	Wide beam
97206300	SM531C 31S/940 PSD L1410 ALU	4000 K	148 lm/W	3,100 lm	Wide beam
97218600	SM530C 50S/940 PSD L1410 ALU	4000 K	142 lm/W	5,000 lm	Wide beam
97311400	SM530C 40S/TW9 DIA L1130 ALU	Tunable white 2700-6500 K	121 lm/W	4,000 lm	Wide beam
97224700	SM534C 40S/940 PSD L1130 ALU	4000 K	130 lm/W	4,000 lm	Asymmetrical mirror
97225400	SM534C 50S/940 PSD L1410 ALU	4000 K	132 lm/W	5,000 lm	Asymmetrical mirror
97205600	SM530C 19S/940 PSD L1410 WH	4000 K	139 lm/W	1,900 lm	Wide beam
97216200	SM530C 43S/940 PSD L1410 WH	4000 K	144 lm/W	4,300 lm	Wide beam
97219300	SM530C 50S/940 PSD L1410 WH	4000 K	142 lm/W	5,000 lm	Wide beam
97208700	SM530C 31S/940 PSD L1410 WH	4000 K	148 lm/W	3,100 lm	Wide beam
97221600	SM531C 19S/930 PSD L1410 WH	3000 K	104 lm/W	1,900 lm	Wide beam
97223000	SM531C 19S/940 PSD L1410 WH	4000 K	110 lm/W	1,900 lm	Wide beam
97313800	SM531C 31S/TW9 DIA L1410 WH	Tunable white 2700-6500 K	91 lm/W	3,100 lm	Wide beam
97278000	SM531C 12S/940 PSD LE2 L570 WH	4000 K	102 lm/W	1,250 lm	Wide beam
97286500	SM530C 30S/940 PSD L2250 ALU	4000 K	136 lm/W	3,000 lm	Wide beam
97289600	SM530C 50S/930 PSD L2250 ALU	3000 K	141 lm/W	5,000 lm	Wide beam
97290200	SM530C 30S/940 PSD LF1 L2250 ALU	4000 K	136 lm/W	3,000 lm	Wide beam
97291900	SM530C 68S/940 PSD L2250 ALU	4000 K	146 lm/W	6,800 lm	Wide beam

TrueLine, surface mounted

Order Code	Full Product Name	Correlated Color	Luminous	Luminous Flux	Optic type
		Temperature (Nom)	Efficacy (rated) (Nom)		
97300800	SM530C 62S/930 PSD L2810 ALU	3000 K	140 lm/W	6,200 lm	Wide beam
97303900	SM530C 38S/940 PSD LF1 L2810 ALU	4000 K	141 lm/W	3,800 lm	Wide beam
97288900	SM530C 50S/940 SIA U4 L2290 BK	4000 K	141 lm/W	5,000 lm	Wide beam
97207000	SM530C 31S/940 PSD L1410 BK	4000 K	148 lm/W	3,100 lm	Wide beam
97312100	SM530C 34S/TW9 DIA L1130 BK	Tunable white 2700-6500 K	124 lm/W	3,400 lm	Wide beam
97277300	SM530C 12S/940 PSD LE2 L570 ALU	4000 K	143 lm/W	1,250 lm	Wide beam
97287200	SM531C 30S/940 PSD L2250 BK	4000 K	115 lm/W	3,000 lm	Wide beam
97301500	SM530C 62S/940 PSD L2810 BK	4000 K	150 lm/W	6,200 lm	Wide beam
97304600	SM530C 86S/940 SIA U4LF1 L2850 ALU	4000 K	141 lm/W	8,600 lm	Wide beam
97279700	SM530C 17S/940 PSD LE2 L570 BK	4000 K	143 lm/W	1,700 lm	Wide beam
97214800	SM530C 40S/940 SIA U4 L1170 ALU	4000 K	143 lm/W	4,000 lm	Wide beam
97211700	SM530C 34S/930 SIA U4 L1170 ALU	3000 K	138 lm/W	3,400 lm	Wide beam
97217900	SM530C 43S/940 SIA U4 L1450 ALU	4000 K	141 lm/W	4,300 lm	Wide beam
97209400	SM530C 31S/940 SIA U4 L1450 ALU	4000 K	144 lm/W	3,100 lm	Wide beam
97314500	SM530C 43S/TW9 SIA U4 L1450 ALU	Tunable white 2700-6500 K	121 lm/W	4,300 lm	Wide beam
97302200	SM531C 62S/940 PSD L2810 WH	4000 K	111 lm/W	6,200 lm	Wide beam

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
97213100	SM530C 40S/940 PSD L1130 ALU	28.5 W	97219300	SM530C 50S/940 PSD L1410 WH	36 W
97212400	SM530C 34S/940 PSD L1130 ALU	24.5 W	97208700	SM530C 31S/940 PSD L1410 WH	22 W
97204900	SM530C 19S/940 PSD L1410 ALU	14 W	97221600	SM531C 19S/930 PSD L1410 WH	18.6 W
97222300	SM531C 19S/940 PSD L1410 ALU	17.8 W	97223000	SM531C 19S/940 PSD L1410 WH	17.8 W
97220900	SM531C 19S/930 PSD L1410 ALU	18.6 W	97313800	SM531C 31S/TW9 DIA L1410 WH	34 W
97215500	SM530C 43S/940 PSD L1410 ALU	30.5 W	97278000	SM531C 12S/940 PSD LE2 L570 WH	11.8 W
97210000	SM530C 34S/930 PSD L1130 ALU	26 W	97286500	SM530C 30S/940 PSD L2250 ALU	22 W
97206300	SM531C 31S/940 PSD L1410 ALU	22 W	97289600	SM530C 50S/930 PSD L2250 ALU	37.5 W
97218600	SM530C 50S/940 PSD L1410 ALU	36 W	97290200	SM530C 30S/940 PSD LF1 L2250 ALU	22 W
97311400	SM530C 40S/TW9 DIA L1130 ALU	33 W	97291900	SM530C 68S/940 PSD L2250 ALU	48.5 W
97224700	SM534C 40S/940 PSD L1130 ALU	28.5 W	97300800	SM530C 62S/930 PSD L2810 ALU	46 W
97225400	SM534C 50S/940 PSD L1410 ALU	38.5 W	97303900	SM530C 38S/940 PSD LF1 L2810 ALU	27 W
97205600	SM530C 19S/940 PSD L1410 WH	14 W	97288900	SM530C 50S/940 SIA U4 L2290 BK	35.5 W
97216200	SM530C 43S/940 PSD L1410 WH	30.5 W	97207000	SM530C 31S/940 PSD L1410 BK	22 W

TrueLine, surface mounted

Order Code	Full Product Name	Power Consumption
97312100	SM530C 34S/TW9 DIA L1130 BK	27.5 W
97277300	SM530C 12S/940 PSD LE2 L570 ALU	9.1 W
97287200	SM531C 30S/940 PSD L2250 BK	26.5 W
97301500	SM530C 62S/940 PSD L2810 BK	44 W
97304600	SM530C 86S/940 SIA U4LF1 L2850 ALU	61 W
97279700	SM530C 17S/940 PSD LE2 L570 BK	12.2 W

Order Code	Full Product Name	Power Consumption
97214800	SM530C 40S/940 SIA U4 L1170 ALU	28.5 W
97211700	SM530C 34S/930 SIA U4 L1170 ALU	25.5 W
97217900	SM530C 43S/940 SIA U4 L1450 ALU	30.5 W
97209400	SM530C 31S/940 SIA U4 L1450 ALU	21.5 W
97314500	SM530C 43S/TW9 SIA U4 L1450 ALU	35.5 W
97302200	SM531C 62S/940 PSD L2810 WH	56 W

Controls and Dimming

Order Code	Full Product Name	Embedded control
97213100	SM530C 40S/940 PSD L1130 ALU	-
97212400	SM530C 34S/940 PSD L1130 ALU	-
97204900	SM530C 19S/940 PSD L1410 ALU	-
97222300	SM531C 19S/940 PSD L1410 ALU	-
97220900	SM531C 19S/930 PSD L1410 ALU	-
97215500	SM530C 43S/940 PSD L1410 ALU	-
97210000	SM530C 34S/930 PSD L1130 ALU	-
97206300	SM531C 31S/940 PSD L1410 ALU	-
97218600	SM530C 50S/940 PSD L1410 ALU	-
97311400	SM530C 40S/TW9 DIA L1130 ALU	-
97224700	SM534C 40S/940 PSD L1130 ALU	-
97225400	SM534C 50S/940 PSD L1410 ALU	-
97205600	SM530C 19S/940 PSD L1410 WH	-
97216200	SM530C 43S/940 PSD L1410 WH	-
97219300	SM530C 50S/940 PSD L1410 WH	-
97208700	SM530C 31S/940 PSD L1410 WH	-
97221600	SM531C 19S/930 PSD L1410 WH	-
97223000	SM531C 19S/940 PSD L1410 WH	-
97313800	SM531C 31S/TW9 DIA L1410 WH	-
97278000	SM531C 12S/940 PSD LE2 L570 WH	-
97286500	SM530C 30S/940 PSD L2250 ALU	-
97289600	SM530C 50S/930 PSD L2250 ALU	-
97290200	SM530C 30S/940 PSD LF1 L2250 ALU	-
97291900	SM530C 68S/940 PSD L2250 ALU	-

Order Code	Full Product Name	Embedded control
97300800	SM530C 62S/930 PSD L2810 ALU	-
97303900	SM530C 38S/940 PSD LF1 L2810 ALU	-
97288900	SM530C 50S/940 SIA U4 L2290 BK	Upgradable sensor slot with SNS210 sensor
97207000	SM530C 31S/940 PSD L1410 BK	-
97312100	SM530C 34S/TW9 DIA L1130 BK	-
97277300	SM530C 12S/940 PSD LE2 L570 ALU	-
97287200	SM531C 30S/940 PSD L2250 BK	-
97301500	SM530C 62S/940 PSD L2810 BK	-
97304600	SM530C 86S/940 SIA U4LF1 L2850 ALU	Upgradable sensor slot with SNS210 sensor
97279700	SM530C 17S/940 PSD LE2 L570 BK	-
97214800	SM530C 40S/940 SIA U4 L1170 ALU	Upgradable sensor slot with SNS210 sensor
97211700	SM530C 34S/930 SIA U4 L1170 ALU	Upgradable sensor slot with SNS210 sensor
97217900	SM530C 43S/940 SIA U4 L1450 ALU	Upgradable sensor slot with SNS210 sensor
97209400	SM530C 31S/940 SIA U4 L1450 ALU	Upgradable sensor slot with SNS210 sensor
97314500	SM530C 43S/TW9 SIA U4 L1450 ALU	Upgradable sensor slot with SNS210 sensor
97302200	SM531C 62S/940 PSD L2810 WH	-

Mechanical and Housing

Order Code	Full Product Name	Housing Color
97213100	SM530C 40S/940 PSD L1130 ALU	Aluminum
97212400	SM530C 34S/940 PSD L1130 ALU	Aluminum
97204900	SM530C 19S/940 PSD L1410 ALU	Aluminum
97222300	SM531C 19S/940 PSD L1410 ALU	Aluminum
97220900	SM531C 19S/930 PSD L1410 ALU	Aluminum
97215500	SM530C 43S/940 PSD L1410 ALU	Aluminum
97210000	SM530C 34S/930 PSD L1130 ALU	Aluminum
97206300	SM531C 31S/940 PSD L1410 ALU	Aluminum
97218600	SM530C 50S/940 PSD L1410 ALU	Aluminum
97311400	SM530C 40S/TW9 DIA L1130 ALU	Aluminum
97224700	SM534C 40S/940 PSD L1130 ALU	Aluminum
97225400	SM534C 50S/940 PSD L1410 ALU	Aluminum
97205600	SM530C 19S/940 PSD L1410 WH	White

Order Code	Full Product Name	Housing Color
97216200	SM530C 43S/940 PSD L1410 WH	White
97219300	SM530C 50S/940 PSD L1410 WH	White
97208700	SM530C 31S/940 PSD L1410 WH	White
97221600	SM531C 19S/930 PSD L1410 WH	White
97223000	SM531C 19S/940 PSD L1410 WH	White
97313800	SM531C 31S/TW9 DIA L1410 WH	White
97278000	SM531C 12S/940 PSD LE2 L570 WH	White
97286500	SM530C 30S/940 PSD L2250 ALU	Aluminum
97289600	SM530C 50S/930 PSD L2250 ALU	Aluminum
97290200	SM530C 30S/940 PSD LF1 L2250 ALU	Aluminum
97291900	SM530C 68S/940 PSD L2250 ALU	Aluminum
97300800	SM530C 62S/930 PSD L2810 ALU	Aluminum
97303900	SM530C 38S/940 PSD LF1 L2810 ALU	Aluminum

TrueLine, surface mounted

Order Code	Full Product Name	Housing Color
97288900	SM530C 50S/940 SIA U4 L2290 BK	Black
97207000	SM530C 31S/940 PSD L1410 BK	Black
97312100	SM530C 34S/TW9 DIA L1130 BK	Black
97277300	SM530C 12S/940 PSD LE2 L570 ALU	Aluminum
97287200	SM531C 30S/940 PSD L2250 BK	Black
97301500	SM530C 62S/940 PSD L2810 BK	Black
97304600	SM530C 86S/940 SIA U4LF1 L2850 ALU	Aluminum


Order Code	Full Product Name	Housing Color
97279700	SM530C 17S/940 PSD LE2 L570 BK	Black
97214800	SM530C 40S/940 SIA U4 L1170 ALU	Aluminum
97211700	SM530C 34S/930 SIA U4 L1170 ALU	Aluminum
97217900	SM530C 43S/940 SIA U4 L1450 ALU	Aluminum
97209400	SM530C 31S/940 SIA U4 L1450 ALU	Aluminum
97314500	SM530C 43S/TW9 SIA U4 L1450 ALU	Aluminum
97302200	SM531C 62S/940 PSD L2810 WH	White

Product Data


Order Code	Full Product Name	Product family code
97213100	SM530C 40S/940 PSD L1130 ALU	SM530C
97212400	SM530C 34S/940 PSD L1130 ALU	SM530C
97204900	SM530C 19S/940 PSD L1410 ALU	SM530C
97222300	SM531C 19S/940 PSD L1410 ALU	SM531C
97220900	SM531C 19S/930 PSD L1410 ALU	SM531C
97215500	SM530C 43S/940 PSD L1410 ALU	SM530C
97210000	SM530C 34S/930 PSD L1130 ALU	SM530C
97206300	SM531C 31S/940 PSD L1410 ALU	SM531C
97218600	SM530C 50S/940 PSD L1410 ALU	SM530C
97311400	SM530C 40S/TW9 DIA L1130 ALU	SM530C
97224700	SM534C 40S/940 PSD L1130 ALU	SM534C
97225400	SM534C 50S/940 PSD L1410 ALU	SM534C
97205600	SM530C 19S/940 PSD L1410 WH	SM530C
97216200	SM530C 43S/940 PSD L1410 WH	SM530C
97219300	SM530C 50S/940 PSD L1410 WH	SM530C
97208700	SM530C 31S/940 PSD L1410 WH	SM530C
97221600	SM531C 19S/930 PSD L1410 WH	SM531C
97223000	SM531C 19S/940 PSD L1410 WH	SM531C
97313800	SM531C 31S/TW9 DIA L1410 WH	SM531C
97278000	SM531C 12S/940 PSD LE2 L570 WH	SM531C

Order Code	Full Product Name	Product family code
97286500	SM530C 30S/940 PSD L2250 ALU	SM530C
97289600	SM530C 50S/930 PSD L2250 ALU	SM530C
97290200	SM530C 30S/940 PSD LF1 L2250 ALU	SM530C
97291900	SM530C 68S/940 PSD L2250 ALU	SM530C
97300800	SM530C 62S/930 PSD L2810 ALU	SM530C
97303900	SM530C 38S/940 PSD LF1 L2810 ALU	SM530C
97288900	SM530C 50S/940 SIA U4 L2290 BK	SM530C
97207000	SM530C 31S/940 PSD L1410 BK	SM530C
97312100	SM530C 34S/TW9 DIA L1130 BK	SM530C
97277300	SM530C 12S/940 PSD LE2 L570 ALU	SM530C
97287200	SM531C 30S/940 PSD L2250 BK	SM531C
97301500	SM530C 62S/940 PSD L2810 BK	SM530C
97304600	SM530C 86S/940 SIA U4LF1 L2850 ALU	SM530C
97279700	SM530C 17S/940 PSD LE2 L570 BK	SM530C
97214800	SM530C 40S/940 SIA U4 L1170 ALU	SM530C
97211700	SM530C 34S/930 SIA U4 L1170 ALU	SM530C
97217900	SM530C 43S/940 SIA U4 L1450 ALU	SM530C
97209400	SM530C 31S/940 SIA U4 L1450 ALU	SM530C
97314500	SM530C 43S/TW9 SIA U4 L1450 ALU	SM530C
97302200	SM531C 62S/940 PSD L2810 WH	SM531C


Polar Wide Diagrams



Polar Normal (separate) - SM530CI -
910505103239




Polar Normal (separate) - SM530CI -
910505103223




Polar Normal (separate) - SM530CI -
910505103224


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103237




Polar Normal (separate) - SM530CI - 910505103228




Polar Normal (separate) - SM530CI - 910505103278




Polar Normal (separate) - SM530CI - 910505103251




Polar Normal (separate) - SM530CI - 910505103229




Polar Normal (separate) - SM530CI - 910505103267



Polar Normal (separate) - SM530CI - 910505103264




Polar Normal (separate) - SM530CI - 910505103255




Polar Normal (separate) - SM530CI - 910505103226


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103217




Polar Normal (separate) - SM530CI - 910505103230




Polar Normal (separate) - SM530CI - 910505103232




Polar Normal (separate) - SM530CI - 910505103222




Polar Normal (separate) - SM530CI - 910505103238




Polar Normal (separate) - SM530CI - 910505103221



Polar Normal (separate) - SM530CI - 910505103250




Polar Normal (separate) - SM530CI - 910505103227




Polar Normal (separate) - SM530CI - 910505103218


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103225




Polar Normal (separate) - SM530CI - 910505103275




Polar Normal (separate) - SM530CI - 910505103254




Polar Normal (separate) - SM530CI - 910505103243




Polar Normal (separate) - SM530CI - 910505103252




Polar Normal (separate) - SM530CI - 910505103277



Polar Normal (separate) - SM530CI - 910505103276




Polar Normal (separate) - SM530CI - 910505103240




Polar Normal (separate) - SM530CI - 910505103266


Polar Wide Diagrams




Polar Normal (separate) - SM530CI - 910505103268




Polar Normal (separate) - SM530CI - 910505103242




Polar Normal (separate) - SM530CI - 910505103231




Polar Normal (separate) - SM530CI - 910505103253




Polar Normal (separate) - SM530CI - 910505103233




Polar Normal (separate) - SM530CI - 910505103265



Polar Normal (separate) - SM530CI - 910505103219




Polar Normal (separate) - SM530CI - 910505103241



Polar Normal (separate) - SM530CI - 910505103220

TrueLine, surface mounted

Polar Wide Diagrams



Polar Normal (separate) - SM530CI -
910505103236

