



Philips TrueLine suspended: True line of light

TrueLine, suspended

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in surface and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

TrueLine, suspended

Features

- Highly-uniform lighting with excellent glare control ($UGR < 19$, $L65 < 3000 \text{cd/m}^2$)
- Best-in-class efficacy up to 140 lm/W
- 3000K, 4000K, and Tunable White versions, all CRI > 90
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options, including all accessories

Application

- Offices
- Education
- Retail

Warnings and Safety


- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions



TrueLine suspended-SP530P
SP532P L1130 ALU

Dimensional drawing



TrueLine, suspended

Product details



TrueLine_Suspended-line-side-view



TrueLine_Suspended-line-top-view



TrueLine Suspended black housing



TrueLine_Suspended-top-view



TrueLine_Suspended-U0



TrueLine Suspended-SP530P-LF-power-cable-03



TrueLine Suspended black housing

TrueLine, suspended

Product details



TrueLine_SM_SP-line-connectio-
side-view-2

TrueLine, suspended

General Information	
Driver included	Yes
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes
Light Technical	
Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	>90
Optic type	Wide beam
Operating and Electrical	
Protection class IEC	Safety class I
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Suitable for random switching	No
Controls and Dimming	
Dimmable	Yes
Maximum dim level	1%
Mechanical and Housing	
Mech. impact protection code	IK03
Ingress protection code	IP20
Approval and Application	
Ambient temperature range	+10 to +40 °C
CE mark	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
910505103169	SP532P 36S/940 PSD SM2 L1130 ALU	136 lm/W	3,600 lm
910505103198	SP531P 15S/940 PSD SM2 L1130 BK	104 lm/W	1,500 lm
910505103199	SP530P 34S/940 PSD SM2 L1130 BK	139 lm/W	3,400 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
910505103169	SP532P 36S/940 PSD SM2 L1130 ALU	26.5 W
910505103198	SP531P 15S/940 PSD SM2 L1130 BK	14.4 W

Order Code	Full Product Name	Power Consumption
910505103199	SP530P 34S/940 PSD SM2 L1130 BK	24.5 W

Mechanical and Housing

TrueLine, suspended

Order Code	Full Product Name	Housing Color
910505103169	SP532P 36S/940 PSD SM2 L1130 ALU	Aluminum
910505103198	SP531P 15S/940 PSD SM2 L1130 BK	Black


Order Code	Full Product Name	Housing Color
910505103199	SP530P 34S/940 PSD SM2 L1130 BK	Black

Product Data


Order Code	Full Product Name	Product family code
910505103169	SP532P 36S/940 PSD SM2 L1130 ALU	SP532P
910505103198	SP531P 15S/940 PSD SM2 L1130 BK	SP531P

Order Code	Full Product Name	Product family code
910505103199	SP530P 34S/940 PSD SM2 L1130 BK	SP530P


Polar Wide Diagrams



Polar Normal (separate) - SM530CI - 910505103199



Polar Normal (separate) - SM530CI - 910505103169



Polar Normal (separate) - SM530CI - 910505103198

