



Flexible and Elegant

SlimBalance G3

SlimBalance G3 SP570P is a flexible linear office offer which fits a variety of spaces like office, education. It offers flexible width of 35/60/90/120mm and length of 600/1200/1500mm to fit multiple applications. Geometric shapes help further create differentiated space. By means of its special designed structure, it offers quick and easy installation and maintenance. UGR19 is available for certain types through customized solution to provide a better visual comfort office environment.

Benefits

- High lm/w provides better energy saving
- Flexible width offers the feasibility to fit multiple ceiling spaces
- Dali and Interact interfaces available for easy system control
- Low UGR offer for visual comfort
- Multiple mounting installations and geometric shapes to cater for various applications
- Easy installation mechanism and modular design help save installation and maintenance time

Features

- System efficiency: max 130lm/W
- Product width with 35/60/90/120mm options
- CRI 80 and 90 available
- Lifetime: 50k hours (L70@ta=25deg)
- UGR19 available for certain types through customized solution
- Easy 'Slide and Click' mechanism for quick continuous installation

Application

- Open plan office
- Public indoor area
- Meeting/Training room
- Library

Specifications

SlimBalance G3

| | |
|----------------------|--|
| Ceiling type | Open ceiling office for suspension installation |
| | Plaster board ceiling for recessed installation and surface mounted installation |
| Mains Voltage | 220-240V / 50 - 60Hz |
| Dimming | PSU: non-dimmable |
| | PSD: Dimmable via Dali-broadcasting |
| | WIA: Wireless control, compatible with Interact |
| | SIA: Wireless control, compatible with SNS210 sensor |
| Control system input | Dali |
| Integrated sensors | SNS210 available for SIA version |
| Material | Extrusion aluminium |
| Luminaire efficacy | 130lm/w |


| | |
|----------------------------------|--|
| Correlated color | 840 |
| temperature - CCT | 940 |
| Color Rendering index - 840, 940 | |
| CRI | |
| Optic | UGR19 is available through lens design |
| Ingress protection | IP20 |
| Driver replaceable | Yes |
| UGR | 19 is available through lens design |
| Installation | Suspension |
| | Recessed |
| | Surface mounted |

Versions



SlimBalance G3

Dimensional drawing



SlimBalance G3

