



Elegant outlook design projector for the retail segment

Truefashion Projector GCGM

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

Benefits

- Slim and compact outlook design with inside track driver.
- Excellent light quality of punch effect.
- Dedicated light recipe for fashion and food.
- System connectivity with Dali-VLC.

Features

- Lumen packages (1000/2000/3000/4000lm).
- 3 beams options (NB/MB/WB).
- Dali-VLC Control.
- Track version available in 1C, 3C.
- CB, EMC, CCC, ACC.
- Lifetime 50K Hours.

Application

- Retail fashion store
- Shopping mall
- Food & large retail

Warnings and Safety

- 3 years

Truefashion Projector GCGM

Specifications

Type	ST700T: Tracklight
	RS700B: recessed round
	GD700B: recessed square
Mounting type	Track installation
	Recessed
Operating Temperature range	-15 to +35°C
Light Source	COB
Mains Voltage	220-240V AC/ 50-60Hz
Dimming	PSD: Dimmable via Dali protocol
Control system input	DALI
Material	Housing: die-cast aluminum
Main color of the luminaire	White RAL9003 / Black RAL9011
Lumen maintenance at median useful life	L70 50.000h

Luminous flux	1000lm - 4000lm
Power consumption	8.2W - 40.3W
Correlated color temperature - CCT	3000K,4000K,Premium White, Premium Color
Color Rendering index -	80/90
CRI	
Beam angle	VNB(Very Narrow Beam): 11°
	NB (Narrow Beam): 13-19°
	MB (Medium Beam): 23-24°
	WB (Wide Beam): 30-34°
Protection Class	Class II
IEC61140	
Ingress protection	IP20
Installation	Track
	Recessed

Versions



Truefashion projector GCGM





GD700B 1 head BK






GD700B 2 heads WH

Dimensional drawing



Truefashion Projector GCGM

Dimensional drawing



General Information	
Service tag	Yes
Light Technical	
Color rendering index (CRI)	>90
Operating and Electrical	
Protection class IEC	Safety class II
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Mech. impact protection code	-
Ingress protection code	IP20
Approval and Application	
CE mark	Yes
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Light Technical

Order Code	Full Product Name	Correlated Color	Luminous Efficacy	Luminous Flux
		Temperature (Nom)	(rated) (Nom)	
911401518571	GD700B LED20 930PW PSU MB WH	3000 K	79 lm/W	1,685 lm
911401530571	GD700B LED20 940PW PSU MB WH HB	4000 K	56 lm/W	1,184 lm
911401575561	ST700T LED30 930PW PSU MB 3C BK	3000 K	85 lm/W	3,168.44 lm
911401576061	ST700T LED30 930PW PSD VLC WB BK	3000 K	85 lm/W	3,001.68 lm
911401576261	ST700T LED30 930PW PSD VLC WB WH	3000 K	85 lm/W	3,001.68 lm
911401518671	GD700B LED20 930PW PSU MB BK	3000 K	79 lm/W	1,685 lm
911401520771	RS700B LED30 930PW PSU MB WH	3000 K	92 lm/W	2,844 lm
911401520871	RS700B LED30 930PW PSU WB WH	3000 K	91 lm/W	2,809 lm
911401521471	RS700B LED30 930PC PSU MB WH	3000 K	87 lm/W	2,669 lm
911401518971	GD700B 2XLED20 930PW PSU MB WH	3000 K	79 lm/W	3,369 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401518571	GD700B LED20 930PW PSU MB WH	21 W
911401530571	GD700B LED20 940PW PSU MB WH HB	21 W
911401575561	ST700T LED30 930PW PSU MB 3C BK	37.1 W
911401576061	ST700T LED30 930PW PSD VLC WB BK	35 W
911401576261	ST700T LED30 930PW PSD VLC WB WH	35 W

Order Code	Full Product Name	Power Consumption
911401518671	GD700B LED20 930PW PSU MB BK	21 W
911401520771	RS700B LED30 930PW PSU MB WH	31 W
911401520871	RS700B LED30 930PW PSU WB WH	31 W
911401521471	RS700B LED30 930PC PSU MB WH	31 W
911401518971	GD700B 2XLED20 930PW PSU MB WH	42 W

Mechanical and Housing

Order Code	Full Product Name	Optical cover type	Housing Color
911401518571	GD700B LED20 930PW PSU MB WH	Lens	White RAL 9003
911401530571	GD700B LED20 940PW PSU MB WH HB	Lens	White RAL 9003
911401575561	ST700T LED30 930PW PSU MB 3C BK	Fashion proof optic beam angle 24°	White and black
911401576061	ST700T LED30 930PW PSD VLC WB BK	Fashion proof optic beam angle 36°	White and black
911401576261	ST700T LED30 930PW PSD VLC WB WH	Fashion proof optic beam angle 36°	White and black

Order Code	Full Product Name	Optical cover type	Housing Color
911401518671	GD700B LED20 930PW PSU MB BK	Lens	Black
911401520771	RS700B LED30 930PW PSU MB WH	Lens	White RAL 9003
911401520871	RS700B LED30 930PW PSU WB WH	Lens	White RAL 9003
911401521471	RS700B LED30 930PC PSU MB WH	Lens	White RAL 9003
911401518971	GD700B 2XLED20 930PW PSU MB WH	Lens	White RAL 9003

Approval and Application

Order Code	Full Product Name	Ambient temperature range
911401518571	GD700B LED20 930PW PSU MB WH	-15 to +35 °C
911401530571	GD700B LED20 940PW PSU MB WH HB	-15 to +35 °C
911401575561	ST700T LED30 930PW PSU MB 3C BK	-20 to +35 °C
911401576061	ST700T LED30 930PW PSD VLC WB BK	-20 to +35 °C
911401576261	ST700T LED30 930PW PSD VLC WB WH	-20 to +35 °C

Order Code	Full Product Name	Ambient temperature range
911401518671	GD700B LED20 930PW PSU MB BK	-15 to +35 °C
911401520771	RS700B LED30 930PW PSU MB WH	-15 to +35 °C
911401520871	RS700B LED30 930PW PSU WB WH	-15 to +35 °C
911401521471	RS700B LED30 930PC PSU MB WH	-15 to +35 °C
911401518971	GD700B 2XLED20 930PW PSU MB WH	-15 to +35 °C

