



Accent Track D65

TCAT65



Signify myCreation Accent Track D65 – To spotlight what truly matters

Accent Track D65 is a sustainable lighting projector that comes with a sleek and subtle design, featuring a diameter size of 65mm. This versatile lighting solution is highly energy efficient and offers various color and texture options, making it an ideal choice for fashion retail, hospitality or residential applications. The 3D printed housing is crafted from at least 65% recycled or bio-circular materials, while the heatsink is made from 85% recycled aluminum. Because of its circular design, the luminaire is upgradable, reusable, serviceable, and recyclable, making it a true game-changer in the world of lighting design

Benefits

- Circular design
- Fulfills all accent lighting needs
- Consistent and best in class lighting technology
- Sustainably 3D printed

Applications

- Fashion Retail
- Retail
- Hospitality
- Offices

Features

- Rich pallet of housing colors and Textures – Standard & On demand
- Various light recipes to choose from – 3000K, 4000K, Premium White
- Wide range of beam angles to choose from
- Option for Collimator Optics for precise beam control


- Efficacy upto 143 lm/w
- Option for CRI80 or CRI90
- Lumens : 1200 – 2700 Lumens
- Different Driver options – Non Dimming / DIA (Dali interact Dimming / WIA (Wireless interact dimming)
- Lifetime: 100,000hrs* to L80 @ 25°C Ta

Versions



D65-SPOT-R-T102-
SHADE-BK402-RING-
BS410-A

Dimensional drawing



TCAT65 17S/PW940 PSU HNB FG T302 GN402SN

General Information

Number of gear units	1 unit
Driver included	Yes

Light Technical

Luminous Flux	1,681 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	121 lm/W
Color rendering index (CRI)	>90
Optic type	High-reflective metal reflector Wide beam 40 to 80 degrees

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Power Consumption	13.9 W
Suitable for random switching	Not applicable
Protection class IEC	Safety class II

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Color	Satin Sage
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
Ambient temperature range	+10 to +35 °C


Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.374, 0.364) SDCM <2

Product Data

Product family code	TCAT65 [TCAT65]
---------------------	-----------------

Polar normal diagrams



TCAT65I - 910505104888