



Philips DRUM – Illuminate your open ceiling with a versatile and efficient downlight

DRUM

Bring a new level of sophistication and elegance to your open ceiling. Philips Drum downlights are designed with 3D printing technology and available in multiple installation options, surface-mounted, track-mounted and pendant. Philips Drum has an easy-to-use configurator where end-users can mix and match the options they need. Digitally manufactured light-weight housing provides a distinctive aesthetic to a wide range of applications, making them a perfect fit for any indoor space. High efficiency, perfect color rendering and various light output options, Philips Drum downlights deliver a truly exceptional lighting experience.

Benefits

- Low return of investment years due to high efficiency and long lifetime
- Wide range of mounting options with low weight
- Various light output choices to suit different application needs
- Office-compliant, with stable colour performance and wide light distribution

DRUM

Features

- One size diameter with surface, track mounted and pendant options
- 3D printed parts with at least 55% recycled or mass balanced bio-circular material
- High system efficacy: up to 144 lm/w
- UGR19 version with anti-glare ring
- Available between 1100-3000 lumen to cover various applications
- Various housing colors as a standard part of the configurator
- DALI dimming and wireless driver options available
- IP54 version with a front cover

Application

- Offices
- Retail
- Hospitality
- Healthcare

Versions



Drum Surface-mounted Downlight

Dimensional drawing



