



Efficient fluorescent lighting with improved color rendering

TL-D LIFEMAX Super 80 JIS

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires. The lamp is complying with Japanese Industrial Standard.

Benefits

- Good color rendering
- Good color rendering
- Relatively high efficacy, both initially and during lamp lifetime, with high lumen maintenance
- Relatively high efficacy, both initially and during lamp lifetime, with high lumen maintenance
- Create atmospheres from warm white to cool daylight
- Create atmospheres from warm white to cool daylight

Features

- Highly efficient 3-band fluorescent coating
- Highly efficient 3-band fluorescent coating
- High initial light output compared with standard colors
- High initial light output compared with standard colors
- Low mercury dose
- Low mercury dose
- Can be used with conventional or electronic gear
- Can be used with conventional or electronic gear
- Higher efficacy is achieved with electronic gear
- Higher efficacy is achieved with electronic gear

TL-D LIFEMAX Super 80 JIS

Application


- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps for 'human' applications such as schools, offices, shops, factory halls etc
- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps for 'human' applications such as schools, offices, shops, factory halls etc

Versions



LPPR TL-D8JIS G13 GC T8

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/865 JIS 1SL/25	28 mm	581.3 mm	588.4 mm	585.8 mm	595.5 mm

