



Product Description

TL-D Standard Colours

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Benefits

- Create atmospheres from warm white to cool daylight
- Create atmospheres from warm white to cool daylight

Features

- Standard colors with moderate color rendering
- Standard colours with moderate colour rendering
- Available in various color designations
- Available in various colour designations

Application


- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where color rendering is not an important factor
- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps, used in applications where colour rendering is not an important factor

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

TL-D Standard Colours

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 15W/54-765 1SL/50	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
TL-D 18W/33-640 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 18W/54-765 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 36W/54-765 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
TL-D 58W/54-765 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

General Information

Cap-Base G13

Controls and Dimming

Dimmable Yes

Mechanical and Housing

Bulb Shape T8

Light Technical

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
928024805436	TL-D 15W/54-765 1SL/50	Cool Daylight	6200 K	72	725 lm
928048003312	TL-D 18W/33-640 1SL/25	Cool White (CW)	4100 K	63	1,200 lm
928048005422	TL-D 18W/54-765 1SL/25	Cool Daylight	6200 K	72	1,050 lm

Order Code	Full Product Name	Color Designation	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Flux
928048505422	TL-D 36W/54-765 1SL/25	Cool Daylight	6200 K	75	2,500 lm
928049005422	TL-D 58W/54-765 1SL/25	Cool Daylight	6200 K	72	4,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power Consumption
928024805436	TL-D 15W/54-765 1SL/50	0.310 A	51 V	15.0 W
928048003312	TL-D 18W/33-640 1SL/25	0.360 A	59 V	18.0 W
928048005422	TL-D 18W/54-765 1SL/25	0.360 A	59 V	18.0 W

Order Code	Full Product Name	Lamp Current (Nom)	Voltage (Nom)	Power Consumption
928048505422	TL-D 36W/54-765 1SL/25	0.440 A	103 V	36.0 W
928049005422	TL-D 58W/54-765 1SL/25	0.670 A	111 V	58.5 W

Approval and Application

TL-D Standard Colours

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
928024805436	TL-D 15W/54-765 1SL/50	20 kWh	8.0 mg
928048003312	TL-D 18W/33-640 1SL/25	22 kWh	5.0 mg
928048005422	TL-D 18W/54-765 1SL/25	22 kWh	5.0 mg

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Mercury (Hg) Content (Nom)
928048505422	TL-D 36W/54-765 1SL/25	43 kWh	5.0 mg
928049005422	TL-D 58W/54-765 1SL/25	68 kWh	5.0 mg

