



Architectural MSD – single ended night colors

Architectural MSD

The high luminous efficacy and optimal lamp filling of the single ended Architectural MSD lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Benefits

- High lumen output
- Low cost of ownership
- Excellent colors

Features

- High luminous efficacy
- Long life
- Optimal lamp filling


Application

- Display lighting
- Architectural lighting
- Studio and disco lighting
- Fibre-optic lighting

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions





XPPR XDMSD 0013



XPPR XDMSD 0006

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD	42.5	14.0	84 mm	86 mm	85	183 mm	54 mm	53	52 mm
1200.1CT/3	mm	mm			mm			mm	

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD 575	30 mm	8.0	69 mm	71 mm	70	145 mm	43 mm	42	41 mm
HR 1CT/8		mm			mm			mm	

General Information	
Cap-Base	G22
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	6000 K
Color Code	-
Controls and Dimming	
Dimmable	No

Light Technical

Architectural MSD

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Flux
928172005114	MSD 1200.1CT/3	73	92,000 lm

Order Code	Full Product Name	Color rendering index (CRI)	Luminous Flux
928098905114	MSD 575 HR 1CT/8	75	47,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928172005114	MSD 1200.1CT/3	13.8 A	1,200 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928098905114	MSD 575 HR 1CT/8	6.95 A	575 W

