



Product Description

MSR Hot Restrike

High-efficiency hot restrike metal halide lamps designed for optimum light collection

Benefits

- High luminous efficacy
- Compact arc (5 - 20 mm)
- Excellent colour rendering
- Dimmable with a stable colour temperature

Features

- Run-up time 2 minutes
- Frosted top of outer bulb to avoid excessively bright centre beam in open face luminaires
- Universal burning position

Application

- Indoor and outdoor filming
- Studios and theatres
- Professional photography
- Solar simulation

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

MSR Hot Restrike

Versions





XPPR_XDMSR_0005-Product photo



XPPR_XDMSR_0023-Product photo

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 1200	40 mm	10.0	106	108 mm	107	200	67 mm	65	63 mm
HR 1CT/2		mm	mm		mm	mm		mm	

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575	30 mm	7.0	69 mm	71 mm	70	145 mm	43 mm	42	41 mm
HR 1CT/4		mm			mm			mm	

General Information	
Operating Position	UNIVERSAL
Light Technical	
Correlated Color Temperature (Nom)	6000 K
Color Code	-
Controls and Dimming	
Dimmable	Yes

General Information

MSR Hot Restrike

Order Code	Full Product Name	Cap-Base
928097705115	MSR 575 HR 1CT/4	G22

Order Code	Full Product Name	Cap-Base
928105005114	MSR 1200 HR 1CT/2	G38

Light Technical

Order Code	Full Product Name	Color rendering	Luminous Flux	
		index (CRI)	(Min)	Luminous Flux
928097705115	MSR 575 HR 1CT/4	90	43,200 lm	48,000 lm

Order Code	Full Product Name	Color rendering	Luminous Flux	
		index (CRI)	(Min)	Luminous Flux
928105005114	MSR 1200 HR 1CT/2	95	-	103,000 lm

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928097705115	MSR 575 HR 1CT/4	6.75 A	575 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928105005114	MSR 1200 HR 1CT/2	13.5 A	1,200 W

