



# UVB Narrowband PL-L/PL-S – most effective phototherapy lamp plus design freedom

## UV-B Narrowband PL-L/PL-S

More than 400 independent clinical studies have proven that the UVB Narrowband PL-L/PL-S lamps are safer and more effective than any other lamps in their class. The PL-L/PL-S versions provide additional design freedom for system manufacturers since these are space-saving compact, single-ended lamps. Further flexibility is assured since they use the same lamp caps as general lighting lamps, they also use the same universal ballasts. Their best-in-class treatment effectiveness is a result of their very narrow waveband emission: between 305 and 315 nm with a peak at 311 nm. This is the most efficacious waveband for the treatment of psoriasis, and is therefore much more focused. As a result, exposure times are much shorter and this in turn leads to a reduction of side effects such as reddening of the skin and itching. All of this makes them ideal for phototherapy treatment of diseases such as psoriasis and vitiligo. What's more, because the overall dosage of this narrowband radiation can be closely controlled, these lamps are suitable for home therapy.

### Benefits

- Minimum side effects like redness, itching and burns
- Shorter period of exposure and less erythematous radiation than conventional UVB lamps
- Optimal therapeutic effect with minimum side effects
- Proven to be most effective on the skin

# UV-B Narrowband PL-L/PL-S

## Features

- Emission peak at 311 nm
- Narrowband
- Special developed phosphor and glass
- World wide tested in more than 400 clinical tests

## Application

- Psoriasis, Vitiligo

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## Versions




LPPR PLS4PLM 9W



XPPR\_XUVBPLL\_2G11\_4P-Product photo


## Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-S 8W/01/4P 1CT/6X10BOX	13 mm	28 mm	128 mm	145 mm	151.1 mm

UV-B Narrowband PL-L/PL-S

Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-L 36W/01/4P 1CT/25	18 mm	39 mm	384.2 mm	410 mm	416.6 mm

Light Technical	
Color Code	01

General Information

Order Code	Full Product Name	Cap-Base
927912900121	PL-S 8W/01/4P 1CT/6X10BOX	2G7

Order Code	Full Product Name	Cap-Base
927903400121	PL-L 36W/01/4P 1CT/25	2G11

Light Technical

Order Code	Full Product Name	Color Designation
927912900121	PL-S 8W/01/4P 1CT/6X10BOX	Ultra Violet B

Order Code	Full Product Name	Color Designation
927903400121	PL-L 36W/01/4P 1CT/25	-

Operating and Electrical

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
927912900121	PL-S 8W/01/4P 1CT/6X10BOX	0.165 A	8.0 W

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
927903400121	PL-L 36W/01/4P 1CT/25	0.435 A	36 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
927912900121	PL-S 8W/01/4P 1CT/6X10BOX	No

Order Code	Full Product Name	Dimmable
927903400121	PL-L 36W/01/4P 1CT/25	-

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
927912900121	PL-S 8W/01/4P 1CT/6X10BOX	2XT12

Order Code	Full Product Name	Bulb Shape
927903400121	PL-L 36W/01/4P 1CT/25	2xT16

Approval and Application

Order Code	Full Product Name	Mercury (Hg)	Mercury (Hg)
		Content (Max)	Content (Nom)
927912900121	PL-S 8W/01/4P 1CT/6X10BOX	3.2 mg	3.0 mg

Order Code	Full Product Name	Mercury (Hg)	Mercury (Hg)
		Content (Max)	Content (Nom)
927903400121	PL-L 36W/01/4P 1CT/25	-	4.4 mg

## UV-B Narrowband PL-L/PL-S

