



Product Description

UV-B Narrowband TL

Tubular or compact single-ended low-pressure mercury vapour fluorescent lamps

Benefits

- Minimum side effects like redness, itching and burns
- Minimum side effects like redness, itching and burns
- Shorter period of exposure and less erythema radiation than conventional UVB lamps
- Shorter period of exposure and less erythema radiation than conventional UVB lamps
- Optimal therapeutic effect with minimum side effects
- Optimal therapeutic effect with minimum side effects
- Proven to be most effective on the skin
- Proven to be most effective on the skin

Features

- Emission peak at 311 nm
- Emit radiation for therapeutic and other applications
- Narrowband
- Special developed phosphor and glass
- World wide tested in more than 400 clinical tests

Application

- Psoriasis, Vitiligo
- Phototherapy in dermatology (psoriasis, SUP)
- These lamps produce UV-B radiation which is harmful to human skin and eyes. They are therefore only available for medical and industrial applications

UV-B Narrowband TL

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



XPPR_XUMTL_0002-Product photo

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 100W/01 SLV/10	40.5 mm	1,763.8 mm	1,770.9 mm	1,768.5 mm	1,782.2 mm

