



# Product Description

## Flexo Print

Tubular low-pressure mercury vapour discharge lamps

### Benefits

- Best match with photo sensitizers
- Best match with photo sensitizers
- Highest output on irradiated area
- Highest output on irradiated area

### Features

- Emit radiation in the range 380-480 nm with a maximum at 370 nm
- Internally coated with a white fluorescent powder to convert the short-wave UV radiation into useful actinic radiation
- Internal reflector
- Emit radiation in the range 380 - 480 nm with a maximum at 420 nm
- Spectral energy distribution in accordance with the spectral sensitivity of a number of diazo copying papers
- For maximum beauty of marine aquaria, TL /03 "Aqua Coral" lamps can be used in combination with full-spectrum "Natural Daylight" fluorescent lamps

### Application

- Flexoprint reprographic equipment, Diazo copying machines
- Diazo copying machines
- Marine aquaria
- Phototherapy (neonatal jaundice treatment)

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# Flexo Print

## Versions



XPPR\_XUVATL\_G13\_--Product photo

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 100W/10-R UV-A	40.5 mm	1,763.8 mm	1,770.9 mm	1,768.5 mm	1,778 mm
TL 80W/10-R SLV/25	40.5 mm	1,500 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm



# Flexo Print

## General Information

Cap-Base G13

## Light Technical

Color Designation Ultra Violet A

Color Code 10-R

## Mechanical and Housing

Bulb Shape T38

## Approval and Application

Mercury (Hg) Content (Nom) 13.0 mg

## Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928005901029	TL 80W/10-R SLV/25	0.83 A	80 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
928006901029	TL 100W/10-R UV-A	0.97 A	100 W

