

Product Description

TUV PL-L

TUV PL-L lamps are compact UVC (germicidal) lamps used in residential water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

Benefits

- Security of effective disinfection over the complete lifetime of the lamp
- High system efficacy because it is not required to over-design the purification system to maintain effectiveness of disinfection

Features

- Short-wave UV radiation with a peak at 253.7 nm (UVC) for disinfection purposes
- Protective inside coating ensures constant UV output over the complete lifetime of the lamp
- Special lamp glass filters out the 185 nm ozone-forming radiation
- High Output versions contain wind-chill correction for improved performance in moving air and reducing amount of required lamps
- High Output versions for optimum UVC output per lamp length, allowing for reduction of system size
- Warning sign on lamp indicates that the lamp radiates UVC

Application

- Deactivation of bacteria, viruses and other micro-organisms
- Residential drinking water units
- Fish pond and process water units
- In-duct air treatment units
- Stand alone air purifiers
- Air disinfection systems in for example hospitals, universities and laboratories


Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Versions



Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-L 24W/4P 1CT/25	18 mm	39 mm	290 mm	315 mm	320 mm
TUV PL-L 35W/4P HO 1CT/25	18 mm	39 mm	195 mm	220 mm	225 mm
TUV PL-L 36W/4P 1CT/25	18 mm	38 mm	385 mm	410 mm	415 mm



TUV PL-L

General Information	
Cap-Base	2G11
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg

Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927903204007	TUV PL-L 24W/4P 1CT/25	0.345 A	24 W
927903404007	TUV PL-L 36W/4P 1CT/25	0.435 A	36 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927904204007	TUV PL-L 35W/4P HO 1CT/25	0.85 A	35 W

