



# Actinic BL PL-S/PL-L – compact for design freedom

## Actinic BL PL-S/PL-L

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

### Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- Design freedom

### Features

- Emits long-wave UV-A radiation in the 350–400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280–315nm)
- 100% lead-free
- Low mercury content
- Compact lamp format

### Application

- Insect traps, Electronic Fly Killers (EFKs)

# Actinic BL PL-S/PL-L

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



## Versions



XPPR\_XURPLL\_0001-Product photo

XPPR XUAPLS 0001

## Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
Actinic BL PL-S 9W/10/2P 1CT/ 6X10BOX	13 mm	28 mm	128.8 mm	144.5 mm	167 mm
PL-S 11W/10/2P 1CT/6X10BOX	13 mm	28 mm	198 mm	213.3 mm	236.3 mm

Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
PL-L 24W/10/4P 1CT/25	18 mm	39 mm	289.2 mm	315 mm	321.6 mm

Light Technical	
Color Designation	Ultra Violet A
Color Code	210

## General Information

# Actinic BL PL-S/PL-L

Order Code	Full Product Name	Cap-Base
927903221007	PL-L 24W/10/4P 1CT/25	2G11
927901721008	Actinic BL PL-S 9W/10/2P 1CT/6X10BOX	G23

Order Code	Full Product Name	Cap-Base
927902321007	PL-S 11W/10/2P 1CT/6X10BOX	G23

## Operating and Electrical

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927903221007	PL-L 24W/10/4P 1CT/25	0.345 A	24 W
927901721008	Actinic BL PL-S 9W/10/2P 1CT/ 6X10BOX	0.17 A	8.6 W

Order Code	Full Product Name	Lamp Current (Nom)	Power Consumption
927902321007	PL-S 11W/10/2P 1CT/6X10BOX	0.16 A	11.6 W

## Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
927903221007	PL-L 24W/10/4P 1CT/25	2xT16
927901721008	Actinic BL PL-S 9W/10/2P 1CT/6X10BOX	2XT12

Order Code	Full Product Name	Bulb Shape
927902321007	PL-S 11W/10/2P 1CT/6X10BOX	2XT12

## Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Max)	Mercury (Hg) Content (Nom)
927903221007	PL-L 24W/10/4P 1CT/25	4.4 mg	4.2 mg
927901721008	Actinic BL PL-S 9W/10/2P 1CT/ 6X10BOX	-	-

Order Code	Full Product Name	Mercury (Hg) Content (Max)	Mercury (Hg) Content (Nom)
927902321007	PL-S 11W/10/2P 1CT/6X10BOX	-	-

