



Actinic BL PL-S/PL-L – compact for design freedom

Actinic BL PL-S/PL-L

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Advantages

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- Design freedom

Fonctions

- Emits long-wave UV-A radiation in the 350-400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280-315nm)
- 100% lead-free
- Low mercury content
- Compact lamp format

Application

- Insect traps, Electronic Fly Killers (EFKs)

Actinic BL PL-S/PL-L


Mises en garde et sécurité

- Un bris de lampe est très peu susceptible d'influer sur votre santé. Si une lampe se brise, aérez la pièce pendant 30 minutes et retirez les morceaux, de préférence avec des gants. Placez-les dans un sac en plastique scellé et portez-le à votre site de gestion des déchets en vue de son recyclage. Évitez d'utiliser un aspirateur.

Versions



Schéma dimensionnel



Informations générales

Order Code	Full Product Name	Culot
26018540	PL-L 18W/10/4P 1CT/25	2G11
26481740	PL-L 36W/10/4P 1CT/25	2G11

Order Code	Full Product Name	Culot
95201180	PL-S 11W/10/2P 1CT/6X10BOX	G23

Actinic BL PL-S/PL-L

Données techniques de l'éclairage

Order Code	Full Product Name	Désignation de la couleur	Code couleur
26018540	PL-L 18W/10/4P 1CT/25	Ultraviolet A	10
26481740	PL-L 36W/10/4P 1CT/25	-	210

Order Code	Full Product Name	Désignation de la couleur	Code couleur
95201180	PL-S 11W/10/2P 1CT/6X10BOX	Ultraviolet A	210

Fonctionnement et électricité

Order Code	Full Product Name	Courant lampe (nom.)	Consommation électrique
26018540	PL-L 18W/10/4P 1CT/25	0,375 A	18 W
26481740	PL-L 36W/10/4P 1CT/25	0,435 A	36 W

Order Code	Full Product Name	Courant lampe (nom.)	Consommation électrique
95201180	PL-S 11W/10/2P 1CT/6X10BOX	0,16 A	11,6 W

Mécanique et boîtier

Order Code	Full Product Name	Forme de la lampe
26018540	PL-L 18W/10/4P 1CT/25	2xT16
26481740	PL-L 36W/10/4P 1CT/25	2xT16

Order Code	Full Product Name	Forme de la lampe
95201180	PL-S 11W/10/2P 1CT/6X10BOX	2XT12

Approbation et application

Order Code	Full Product Name	Taux de mercure (Hg) (max.)	Taux de mercure (Hg) (nom.)
26018540	PL-L 18W/10/4P 1CT/25	-	-
26481740	PL-L 36W/10/4P 1CT/25	2,1 mg	2,0 mg

Order Code	Full Product Name	Taux de mercure (Hg) (max.)	Taux de mercure (Hg) (nom.)
95201180	PL-S 11W/10/2P 1CT/6X10BOX	-	-

