



Actinic BL TL-D(K) Secura – additional safety and HACCP approval

Actinic BL TL-D(K) Secura

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Benefits

- Perfectly matches the eye sensitivity of houseflies and in this way attracts more insects
- Safe for use
- Good environmental choice
- No risk of glass particles

Features

- Emits long-wave UV-A radiation in the 350–400nm range
- UV-B/UV-A ratio less than 0.1 % (UV-B 280–315nm)
- 100% lead-free
- Low mercury content
- Shatterproof sleeve

Actinic BL TL-D(K) Secura


Application

- Insect traps, Electronic Fly Killers (EFKs)

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.



Versions



XPPR XUBTL 10 G5

XPPR_XUBTLD_0002-Product photo

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Insect TL 8W /10 SECURA	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 15W/10 Secura 1SL/25	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm
Actinic BL TL-D 18W/10 Secura 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

Light Technical	
Color Code	10

Actinic BL TL-D(K) Secura

General Information

Order Code	Full Product Name	Cap-Base
928011001029	Insect TL 8W /10 SECURA	G5
928024701029	Actinic BL TL-D 15W/10 Secura 1SL/25	G13

Order Code	Full Product Name	Cap-Base
928048201003	Actinic BL TL-D 18W/10 Secura 1SL/25	G13

Light Technical

Order Code	Full Product Name	Color Designation
928011001029	Insect TL 8W /10 SECURA	-
928024701029	Actinic BL TL-D 15W/10 Secura 1SL/25	Actinic

Order Code	Full Product Name	Color Designation
928048201003	Actinic BL TL-D 18W/10 Secura 1SL/25	Actinic

Operating and Electrical

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
928011001029	Insect TL 8W /10 SECURA	0.145 A	7.1 W
928024701029	Actinic BL TL-D 15W/10 Secura 1SL/25	0.335 A	15 W

Order Code	Full Product Name	Lamp Current	
		(Nom)	Power Consumption
928048201003	Actinic BL TL-D 18W/10 Secura 1SL/25	0.36 A	18 W

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
928011001029	Insect TL 8W /10 SECURA	T16
928024701029	Actinic BL TL-D 15W/10 Secura 1SL/25	T26

Order Code	Full Product Name	Bulb Shape
928048201003	Actinic BL TL-D 18W/10 Secura 1SL/25	T26

Approval and Application

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
928011001029	Insect TL 8W /10 SECURA	4.4 mg
928024701029	Actinic BL TL-D 15W/10 Secura 1SL/25	5

Order Code	Full Product Name	Mercury (Hg) Content (Nom)
928048201003	Actinic BL TL-D 18W/10 Secura 1SL/25	5.0 mg

